

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1215319

Luminaire Tested: 22-ID2-60-DBR-L940-U

Issue Date: 12/4/2025

Test Information

Test Method: LM-79-2019
Report Number: P1215319
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2506-458-16)
Test Lab: INNOVATION CENTER
Issue Date: 12/4/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 22-ID2-60-DBR-L940-U
Description: 2X2 IN DEPTH TROFFER WITH 2INCH DOUBLE BARREL REGRESSED
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5784.1 lumens
Efficiency: N/A
Efficacy: 110.2 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.2 / 1.29
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')
CIE Type: Direct

Input Watts (W): 52.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1215319
CATALOG NUMBER: 22-ID2-60-DBR-L940-U

Luminous Intensity Polar Plot



TEST NUMBER: P1215319

CATALOG NUMBER: 22-ID2-60-DBR-L940-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	109	105	101	97	107	102	99	95	98	95	92		94	92	89		85
2	100	92	85	80	97	90	84	79	86	81	77		83	79	75		71
3	91	81	73	67	89	79	72	66	76	70	65		74	68	64		61
4	84	72	63	57	81	71	63	56	68	61	56		66	60	55		52
5	77	65	56	49	75	63	55	49	61	54	48		59	53	48		45
6	71	58	50	43	69	57	49	43	56	48	43		54	47	42		40
7	66	53	44	38	65	52	44	38	51	43	38		49	43	38		35
8	62	48	40	34	60	48	40	34	46	39	34		45	39	34		32
9	58	45	36	31	56	44	36	31	43	36	31		42	35	31		29
10	54	41	33	28	53	41	33	28	40	33	28		39	32	28		26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6191	6191	6191
5°	6189	6176	6183
10°	6151	6137	6151
15°	6086	6071	6083
20°	5972	5970	5982
25°	5836	5839	5862
30°	5666	5680	5731
35°	5480	5505	5588
40°	5257	5313	5426
45°	5022	5106	5251
50°	4770	4888	5065
55°	4451	4646	4858
60°	4133	4385	4627
65°	3804	4114	4383
70°	3414	3814	4068
75°	2953	3423	3706
80°	2411	2968	3245
85°	1618	2282	2547

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 5251 cd/sqm

TEST NUMBER: P1215319
 CATALOG NUMBER: 22-ID2-60-DBR-L940-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	217.1	3.8
10°-20°	614.4	10.6
20°-30°	906.3	15.7
30°-40°	1050.9	18.2
40°-50°	1038.4	18.0
50°-60°	887.0	15.3
60°-70°	637.9	11.0
70°-80°	346.5	6.0
80°-90°	85.6	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1737.9	30.0
0°-40°	2788.8	48.2
0°-60°	4714.1	81.5
0°-90°	5784.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5784.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2300	2300	2300	2300	2300	
5°	2291	2288	2286	2287	2289	217
15°	2184	2182	2179	2179	2184	615
25°	1966	1964	1966	1975	1974	904
35°	1668	1670	1676	1692	1701	1043
45°	1320	1324	1342	1369	1380	1018
55°	949	962	990	1020	1036	851
65°	597	611	646	673	688	591
75°	284	306	329	346	356	303
85°	52	62	74	80	82	68
90°	0	0	0	0	0	

TEST NUMBER: P1215319

CATALOG NUMBER: 22-ID2-60-DBR-L940-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2300.5	2300.5	2300.5	2300.5	2300.5
2.5°	2300.5	2297.7	2295.5	2297.0	2299.8
5°	2291.2	2288.3	2286.2	2286.9	2289.1
7.5°	2274.7	2271.9	2269.0	2271.1	2274.0
10°	2251.1	2249.6	2246.0	2248.2	2251.1
12.5°	2223.1	2218.1	2215.2	2218.1	2220.9
15°	2184.4	2181.5	2179.3	2179.3	2183.6
17.5°	2137.8	2136.3	2134.9	2137.0	2139.2
20°	2085.4	2084.7	2084.7	2086.1	2089.0
22.5°	2029.5	2027.3	2030.2	2033.0	2035.2
25°	1965.6	1964.2	1966.4	1975.0	1974.2
27.5°	1897.5	1898.2	1898.9	1909.7	1916.2
30°	1823.6	1825.8	1828.0	1843.0	1844.4
32.5°	1748.4	1749.8	1756.2	1771.3	1777.8
35°	1668.0	1669.5	1675.9	1692.4	1701.0
37.5°	1587.7	1587.0	1593.5	1616.4	1620.7
40°	1496.6	1498.8	1512.4	1537.5	1544.7
42.5°	1412.7	1413.5	1429.2	1453.6	1463.7
45°	1319.5	1324.5	1341.7	1369.0	1379.7
47.5°	1226.3	1232.0	1257.1	1283.7	1296.6
50°	1139.5	1143.1	1167.5	1196.2	1209.8
52.5°	1044.9	1054.2	1079.3	1109.4	1123.0
55°	948.8	961.7	990.3	1019.8	1035.5
57.5°	860.6	872.7	902.9	933.0	947.3
60°	768.0	783.1	814.7	845.5	859.8
62.5°	679.8	696.3	730.0	761.6	777.4
65°	597.4	611.0	646.1	673.4	688.4
67.5°	511.3	530.0	562.9	591.6	600.2
70°	433.9	449.6	484.8	506.3	517.0
72.5°	354.3	377.2	406.6	426.7	439.6
75°	284.0	305.5	329.2	346.4	356.4
77.5°	216.6	233.8	260.3	273.9	279.7
80°	155.6	169.2	191.5	205.1	209.4
82.5°	101.1	113.3	129.1	137.7	142.0
85°	52.4	61.7	73.9	80.3	82.5
87.5°	17.2	21.5	26.5	28.7	30.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1215319

CATALOG NUMBER: 22-ID2-60-DBR-L940-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.01	18.60	17.37	18.92	19.23	17.51	19.11	17.88	19.42	19.74
	3H	18.53	19.97	18.91	20.30	20.66	19.22	20.66	19.60	20.99	21.35
	4H	19.06	20.41	19.46	20.76	21.13	19.85	21.20	20.25	21.55	21.93
	6H	19.39	20.65	19.80	21.01	21.40	20.29	21.55	20.71	21.91	22.30
	8H	19.48	20.67	19.90	21.06	21.46	20.43	21.62	20.85	22.01	22.41
	12H	19.52	20.66	19.95	21.05	21.47	20.51	21.65	20.94	22.03	22.46
4H	2H	17.64	19.00	18.04	19.34	19.72	18.05	19.40	18.45	19.75	20.12
	3H	19.39	20.52	19.80	20.92	21.32	19.98	21.11	20.39	21.50	21.91
	4H	20.03	21.05	20.46	21.47	21.90	20.73	21.75	21.16	22.16	22.60
	6H	20.48	21.37	20.93	21.81	22.27	21.30	22.19	21.76	22.63	23.09
	8H	20.60	21.43	21.06	21.87	22.34	21.48	22.31	21.94	22.75	23.22
	12H	20.67	21.41	21.15	21.89	22.36	21.60	22.35	22.08	22.82	23.29
8H	4H	20.35	21.18	20.81	21.62	22.09	20.97	21.80	21.43	22.25	22.71
	6H	20.90	21.59	21.40	22.08	22.56	21.65	22.34	22.15	22.83	23.31
	8H	21.08	21.70	21.59	22.20	22.69	21.90	22.52	22.41	23.02	23.51
	12H	21.19	21.74	21.70	22.23	22.79	22.08	22.63	22.59	23.12	23.68
12H	4H	20.38	21.13	20.86	21.61	22.08	20.98	21.73	21.46	22.21	22.68
	6H	20.96	21.58	21.47	22.08	22.57	21.68	22.30	22.19	22.81	23.30
	8H	21.18	21.73	21.69	22.22	22.78	21.98	22.52	22.48	23.01	23.58

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-11

Test Date: 08/26/2025

Luminaire Tested: 22ID2-55-CFR1-L940-U

Data in this report applies to families of products including 22ID2-55-CFR1-L940-U


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-11
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L940-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 4000K 90CRI

Spectral Parameters

CCT (K): 3910
 CIE u' : 0.2263
 CIE v' : 0.5043
 Duv: 0.0008
 CIE x: 0.3851
 CIE y: 0.3813
 CIE z: 0.2336
 Peak Wavelength (nm): 451
 Dominant Wavelength (nm): 578
 Purity: 30.01895
 R_f: 90.8
 R_g: 98.8

CRI (Ra): 92.4
 R1: 92.5
 R2: 94.9
 R3: 95.8
 R4: 92.7
 R5: 91.7
 R6: 92.1
 R7: 94.3
 R8: 85.2
 R9: 62.0
 R10: 87.0
 R11: 92.8
 R12: 71.7
 R13: 93.2
 R14: 97.3
 R15: 89.6



Test Conditions


Stabilization Time: 31M
 Operation Time: 1H 31M
 Sphere Temperature (°C): 25.2.

REPORT NUMBER: SP1-2506-458-11

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-11

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	394	NR	620	868	NR	750	58	NR	880	1	NR
365	0	NR	495	449	NR	625	858	NR	755	49	NR	885	1	NR
370	0	NR	500	505	NR	630	839	NR	760	42	NR	890	1	NR
375	0	NR	505	553	NR	635	813	NR	765	36	NR	895	1	NR
380	0	NR	510	593	NR	640	783	NR	770	31	NR	900	1	NR
385	0	NR	515	628	NR	645	746	NR	775	26	NR	905	1	NR
390	1	NR	520	651	NR	650	702	NR	780	22	NR	910	0	NR
395	4	NR	525	670	NR	655	657	NR	785	19	NR	915	0	NR
400	5	NR	530	687	NR	660	607	NR	790	16	NR	920	0	NR
405	8	NR	535	705	NR	665	559	NR	795	14	NR	925	0	NR
410	12	NR	540	717	NR	670	507	NR	800	12	NR	930	0	NR
415	19	NR	545	731	NR	675	458	NR	805	10	NR	935	0	NR
420	34	NR	550	745	NR	680	413	NR	810	9	NR	940	0	NR
425	60	NR	555	757	NR	685	367	NR	815	7	NR	945	0	NR
430	107	NR	560	767	NR	690	328	NR	820	6	NR	950	0	NR
435	194	NR	565	777	NR	695	289	NR	825	5	NR	955	0	NR
440	349	NR	570	785	NR	700	253	NR	830	5	NR	960	0	NR
445	678	NR	575	794	NR	705	221	NR	835	4	NR	965	0	NR
450	997	NR	580	809	NR	710	192	NR	840	3	NR	970	0	NR
455	819	NR	585	820	NR	715	165	NR	845	3	NR	975	0	NR
460	581	NR	590	838	NR	720	144	NR	850	2	NR	980	0	NR
465	517	NR	595	851	NR	725	124	NR	855	2	NR	985	0	NR
470	406	NR	600	861	NR	730	107	NR	860	2	NR	990	0	NR
475	327	NR	605	873	NR	735	91	NR	865	2	NR	995	0	NR
480	330	NR	610	875	NR	740	78	NR	870	1	NR	1000	0	NR
485	356	NR	615	877	NR	745	67	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-11

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.75

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	394	NR	620	868	NR	750	58	NR	880	1	NR
365	0	NR	495	449	NR	625	858	NR	755	49	NR	885	1	NR
370	0	NR	500	505	NR	630	839	NR	760	42	NR	890	1	NR
375	0	NR	505	553	NR	635	813	NR	765	36	NR	895	1	NR
380	0	NR	510	593	NR	640	783	NR	770	31	NR	900	1	NR
385	0	NR	515	628	NR	645	746	NR	775	26	NR	905	1	NR
390	1	NR	520	651	NR	650	702	NR	780	22	NR	910	0	NR
395	4	NR	525	670	NR	655	657	NR	785	19	NR	915	0	NR
400	5	NR	530	687	NR	660	607	NR	790	16	NR	920	0	NR
405	8	NR	535	705	NR	665	559	NR	795	14	NR	925	0	NR
410	12	NR	540	717	NR	670	507	NR	800	12	NR	930	0	NR
415	19	NR	545	731	NR	675	458	NR	805	10	NR	935	0	NR
420	34	NR	550	745	NR	680	413	NR	810	9	NR	940	0	NR
425	60	NR	555	757	NR	685	367	NR	815	7	NR	945	0	NR
430	107	NR	560	767	NR	690	328	NR	820	6	NR	950	0	NR
435	194	NR	565	777	NR	695	289	NR	825	5	NR	955	0	NR
440	349	NR	570	785	NR	700	253	NR	830	5	NR	960	0	NR
445	678	NR	575	794	NR	705	221	NR	835	4	NR	965	0	NR
450	997	NR	580	809	NR	710	192	NR	840	3	NR	970	0	NR
455	819	NR	585	820	NR	715	165	NR	845	3	NR	975	0	NR
460	581	NR	590	838	NR	720	144	NR	850	2	NR	980	0	NR
465	517	NR	595	851	NR	725	124	NR	855	2	NR	985	0	NR
470	406	NR	600	861	NR	730	107	NR	860	2	NR	990	0	NR
475	327	NR	605	873	NR	735	91	NR	865	2	NR	995	0	NR
480	330	NR	610	875	NR	740	78	NR	870	1	NR	1000	0	NR
485	356	NR	615	877	NR	745	67	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-11

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.61


λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	394	NR	620	868	NR	750	58	NR	880	1	NR
365	0	NR	495	449	NR	625	858	NR	755	49	NR	885	1	NR
370	0	NR	500	505	NR	630	839	NR	760	42	NR	890	1	NR
375	0	NR	505	553	NR	635	813	NR	765	36	NR	895	1	NR
380	0	NR	510	593	NR	640	783	NR	770	31	NR	900	1	NR
385	0	NR	515	628	NR	645	746	NR	775	26	NR	905	1	NR
390	1	NR	520	651	NR	650	702	NR	780	22	NR	910	0	NR
395	4	NR	525	670	NR	655	657	NR	785	19	NR	915	0	NR
400	5	NR	530	687	NR	660	607	NR	790	16	NR	920	0	NR
405	8	NR	535	705	NR	665	559	NR	795	14	NR	925	0	NR
410	12	NR	540	717	NR	670	507	NR	800	12	NR	930	0	NR
415	19	NR	545	731	NR	675	458	NR	805	10	NR	935	0	NR
420	34	NR	550	745	NR	680	413	NR	810	9	NR	940	0	NR
425	60	NR	555	757	NR	685	367	NR	815	7	NR	945	0	NR
430	107	NR	560	767	NR	690	328	NR	820	6	NR	950	0	NR
435	194	NR	565	777	NR	695	289	NR	825	5	NR	955	0	NR
440	349	NR	570	785	NR	700	253	NR	830	5	NR	960	0	NR
445	678	NR	575	794	NR	705	221	NR	835	4	NR	965	0	NR
450	997	NR	580	809	NR	710	192	NR	840	3	NR	970	0	NR
455	819	NR	585	820	NR	715	165	NR	845	3	NR	975	0	NR
460	581	NR	590	838	NR	720	144	NR	850	2	NR	980	0	NR
465	517	NR	595	851	NR	725	124	NR	855	2	NR	985	0	NR
470	406	NR	600	861	NR	730	107	NR	860	2	NR	990	0	NR
475	327	NR	605	873	NR	735	91	NR	865	2	NR	995	0	NR
480	330	NR	610	875	NR	740	78	NR	870	1	NR	1000	0	NR
485	356	NR	615	877	NR	745	67	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-11





TM-30-18

Summary

$R_f = 90.8$
 $R_g = 98.8$
 $CIE R_a = 92.4$
 $R_9 = 62.0$







Color Vector Graphics





Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 93	CES51 = 96	CES76 = 85
CES02 = 62	CES27 = 90	CES52 = 98	CES77 = 88
CES03 = 31	CES28 = 96	CES53 = 96	CES78 = 82
CES04 = 69	CES29 = 96	CES54 = 92	CES79 = 96
CES05 = 49	CES30 = 90	CES55 = 90	CES80 = 93
CES06 = 50	CES31 = 97	CES56 = 93	CES81 = 89
CES07 = 42	CES32 = 91	CES57 = 91	CES82 = 97
CES08 = 41	CES33 = 98	CES58 = 92	CES83 = 98
CES09 = 29	CES34 = 93	CES59 = 96	CES84 = 93
CES10 = 74	CES35 = 96	CES60 = 91	CES85 = 83
CES11 = 57	CES36 = 79	CES61 = 91	CES86 = 88
CES12 = 63	CES37 = 95	CES62 = 84	CES87 = 91
CES13 = 43	CES38 = 85	CES63 = 91	CES88 = 96
CES14 = 74	CES39 = 99	CES64 = 87	CES89 = 87
CES15 = 71	CES40 = 98	CES65 = 87	CES90 = 96
CES16 = 47	CES41 = 96	CES66 = 84	CES91 = 71
CES17 = 49	CES42 = 95	CES67 = 83	CES92 = 79
CES18 = 56	CES43 = 95	CES68 = 86	CES93 = 87
CES19 = 71	CES44 = 99	CES69 = 87	CES94 = 81
CES20 = 66	CES45 = 98	CES70 = 84	CES95 = 82
CES21 = 85	CES46 = 97	CES71 = 77	CES96 = 91
CES22 = 78	CES47 = 97	CES72 = 93	CES97 = 96
CES23 = 91	CES48 = 90	CES73 = 78	CES98 = 94
CES24 = 90	CES49 = 96	CES74 = 91	CES99 = 91
CES25 = 71	CES50 = 97	CES75 = 80	



Color Rendition by Hue-Angle Bin


Measure Comparisons



(END OF REPORT)