

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1216175

Luminaire Tested: 24-ID2-50-CNV-L940-U


Issue Date: 12/5/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P1216175  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2508-510-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/5/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: 24-ID2-50-CNV-L940-U  
Description: 2X4 IN DEPTH TROFFER WITH 2INCH CURVE DROP  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4740.3 lumens  
Efficiency: N/A  
Efficacy: 109.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.2 / 1.31  
Luminous Opening: Rectangular w/ Sides (W: 2' x L: 4' x H: 0.16')  
CIE Type: Direct  
  
Input Watts (W): 43.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P1216175  
CATALOG NUMBER: 24-ID2-50-CNV-L940-U

### Luminous Intensity Polar Plot





TEST NUMBER: P1216175  
 CATALOG NUMBER: 24-ID2-50-CNV-L940-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	110	110	110	106	106	106	101	101	101	99
1	108	104	99	95	105	101	97	94	97	93	90	93	90	87	89	87	85	82
2	99	90	84	78	96	88	82	77	85	79	75	81	77	73	78	74	71	69
3	90	80	71	65	87	78	70	64	75	68	63	72	66	62	69	65	61	58
4	83	71	62	55	80	69	61	55	67	60	54	64	58	53	62	57	52	50
5	76	63	54	48	74	62	54	47	60	52	47	58	51	46	56	50	46	43
6	70	57	48	42	68	56	48	42	54	47	41	52	46	41	51	45	40	38
7	65	52	43	37	63	51	43	37	49	42	36	48	41	36	46	40	36	34
8	61	47	39	33	59	47	39	33	45	38	33	44	37	32	43	37	32	30
9	57	44	35	30	55	43	35	30	42	35	30	40	34	29	39	33	29	27
10	53	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2388	2388	2388
5°	2386	2366	2370
10°	2367	2335	2341
15°	2335	2296	2303
20°	2291	2247	2253
25°	2239	2187	2194
30°	2183	2121	2123
35°	2116	2042	2047
40°	2043	1959	1961
45°	1968	1874	1871
50°	1882	1777	1777
55°	1797	1681	1664
60°	1704	1569	1558
65°	1601	1448	1431
70°	1477	1304	1310
75°	1329	1155	1176
80°	1125	1000	1077
85°	902	881	1032

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1968 cd/sqm



TEST NUMBER: P1216175  
 CATALOG NUMBER: 24-ID2-50-CNV-L940-U

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	167.7	3.5
10°-20°	475.7	10.0
20°-30°	705.7	14.9
30°-40°	824.5	17.4
40°-50°	824.1	17.4
50°-60°	717.5	15.1
60°-70°	531.9	11.2
70°-80°	312.4	6.6
80°-90°	125.4	2.6
90°-100°	32.8	0.7
100°-110°	10.7	0.2
110°-120°	6.2	0.1
120°-130°	3.4	0.1
130°-140°	1.7	0.0
140°-150°	0.8	0.0
150°-160°	0.1	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1349.0	28.5
0°-40°	2173.5	45.9
0°-60°	3715.1	78.4
0°-90°	4684.8	98.8
90°-120°	49.6	1.0
90°-150°	55.4	1.2
90°-180°	55.0	1.2
0°-180°	4740.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1775	1775	1775	1775	1775	
5°	1773	1768	1765	1763	1767	168
15°	1694	1689	1686	1685	1689	478
25°	1536	1534	1531	1530	1533	708
35°	1325	1321	1317	1316	1316	828
45°	1076	1074	1068	1065	1062	830
55°	810	808	803	800	790	724
65°	546	541	538	530	526	540
75°	294	291	292	294	294	311
85°	85	96	112	125	128	89
90°	34	44	57	68	70	21
95°	29	25	25	29	31	23
105°	20	17	10	3	0	22
115°	13	11	6	1	0	13
125°	8	6	4	1	0	7
135°	4	4	2	1	0	4
145°	3	2	1	1	1	2
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P1216175  
 CATALOG NUMBER: 24-ID2-50-CNV-L940-U

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1775.0	1775.0	1775.0	1775.0	1775.0
2.5°	1780.8	1774.3	1771.7	1769.8	1773.0
5°	1773.0	1767.8	1764.6	1762.6	1767.2
7.5°	1761.3	1755.5	1752.2	1750.9	1754.8
10°	1744.4	1737.3	1734.7	1733.4	1737.3
12.5°	1721.7	1715.8	1713.2	1711.9	1715.8
15°	1694.4	1688.6	1686.0	1685.3	1688.6
17.5°	1662.6	1656.7	1653.5	1653.5	1657.4
20°	1623.6	1619.7	1617.7	1617.1	1619.0
22.5°	1584.6	1578.7	1578.1	1575.5	1580.0
25°	1536.5	1533.9	1531.3	1530.0	1533.2
27.5°	1491.6	1484.5	1481.2	1481.9	1483.8
30°	1437.7	1433.1	1431.8	1428.6	1429.9
32.5°	1381.8	1378.5	1377.2	1373.3	1373.3
35°	1324.6	1321.3	1316.8	1316.1	1316.1
37.5°	1265.4	1262.2	1258.3	1255.0	1256.3
40°	1202.4	1199.1	1194.6	1193.9	1191.3
42.5°	1140.6	1137.4	1132.2	1131.5	1129.0
45°	1075.7	1073.7	1068.5	1064.6	1062.0
47.5°	1010.7	1007.4	1001.6	997.7	995.7
50°	941.8	938.5	934.6	930.7	930.1
52.5°	875.5	874.8	869.0	865.7	862.5
55°	809.8	807.9	803.3	800.1	790.3
57.5°	741.6	740.3	737.7	730.5	724.7
60°	677.2	673.3	668.8	660.3	659.0
62.5°	609.0	609.0	601.8	595.3	592.7
65°	546.0	541.4	537.5	529.7	526.5
67.5°	480.3	479.7	472.5	468.0	462.1
70°	416.6	414.7	408.8	407.5	406.2
72.5°	352.9	352.3	351.0	349.7	346.4
75°	293.8	291.2	292.5	294.4	293.8
77.5°	234.0	237.2	238.5	244.4	245.0
80°	178.1	183.3	191.1	200.2	202.1
82.5°	127.4	134.5	149.5	161.2	163.8
85°	85.1	96.2	112.4	125.4	128.0
87.5°	52.6	65.0	82.5	94.9	96.8
90°	34.4	44.2	57.2	67.6	70.2
92.5°	31.8	31.2	38.3	46.1	48.7
95°	29.2	24.7	24.7	29.2	31.2
97.5°	27.3	22.7	15.6	16.2	16.9
100°	24.7	20.8	11.7	7.1	7.1
102.5°	22.7	18.8	10.4	2.6	0.6
105°	20.1	16.9	9.7	2.6	0.0
107.5°	18.2	15.6	8.4	1.9	0.0
110°	16.2	13.6	7.8	1.9	0.0



TEST NUMBER: P1216175  
 CATALOG NUMBER: 24-ID2-50-CNV-L940-U

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	14.9	12.3	7.1	1.3	0.0
115°	13.0	11.0	5.8	1.3	0.0
117.5°	11.7	9.7	5.2	0.6	0.0
120°	10.4	8.4	4.5	0.6	0.0
122.5°	9.1	7.8	3.9	0.6	0.0
125°	8.4	6.5	3.9	0.6	0.0
127.5°	7.1	5.8	3.2	0.0	0.0
130°	6.5	5.2	2.6	0.0	0.0
132.5°	5.8	4.5	1.9	0.6	0.0
135°	4.5	3.9	1.9	0.6	0.0
137.5°	3.9	3.2	1.3	0.6	0.6
140°	3.2	2.6	1.3	0.6	0.6
142.5°	3.2	2.6	1.3	0.6	0.6
145°	2.6	1.9	0.6	0.6	0.6
147.5°	1.9	1.3	0.6	0.6	0.6
150°	1.3	1.3	0.6	0.6	0.6
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1216175  
 CATALOG NUMBER: 24-ID2-50-CNV-L940-U

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.64	15.24	14.03	15.58	15.92	13.66	15.25	14.04	15.59	15.94
	3H	15.31	16.75	15.71	17.10	17.49	15.34	16.78	15.73	17.13	17.52
	4H	15.91	17.27	16.33	17.64	18.04	15.99	17.35	16.41	17.72	18.12
	6H	16.33	17.59	16.76	17.98	18.40	16.53	17.79	16.96	18.18	18.60
	8H	16.45	17.66	16.90	18.07	18.50	16.76	17.96	17.20	18.38	18.80
	12H	16.53	17.69	16.98	18.09	18.55	16.97	18.12	17.42	18.53	18.99
4H	2H	14.21	15.57	14.63	15.94	16.35	14.23	15.59	14.64	15.96	16.36
	3H	16.09	17.23	16.52	17.65	18.08	16.12	17.26	16.55	17.68	18.11
	4H	16.81	17.85	17.26	18.28	18.74	16.90	17.93	17.35	18.37	18.83
	6H	17.35	18.26	17.83	18.72	19.21	17.58	18.49	18.05	18.95	19.43
	8H	17.52	18.37	18.00	18.84	19.33	17.87	18.72	18.35	19.18	19.68
	12H	17.65	18.41	18.14	18.91	19.40	18.15	18.91	18.65	19.41	19.91
8H	4H	17.09	17.94	17.57	18.41	18.90	17.17	18.02	17.65	18.49	18.98
	6H	17.75	18.46	18.26	18.97	19.47	17.98	18.69	18.50	19.20	19.70
	8H	17.99	18.63	18.52	19.15	19.67	18.37	19.01	18.89	19.53	20.04
	12H	18.19	18.75	18.71	19.26	19.85	18.76	19.33	19.29	19.84	20.42
12H	4H	17.13	17.89	17.63	18.39	18.89	17.20	17.96	17.70	18.46	18.96
	6H	17.81	18.45	18.34	18.98	19.49	18.03	18.67	18.56	19.20	19.71
	8H	18.11	18.68	18.64	19.19	19.78	18.48	19.05	19.01	19.56	20.14



Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-11

Test Date: 08/26/2025

Luminaire Tested: 22ID2-55-CFR1-L940-U

Data in this report applies to families of products including 22ID2-55-CFR1-L940-U


**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2506-458-11  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 08/27/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Corelite  
 Catalog Number: **22ID2-55-CFR1-L940-U**  
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 4000K 90CRI

**Spectral Parameters**

CCT (K): 3910  
 CIE u': 0.2263  
 CIE v': 0.5043  
 Duv: 0.0008  
 CIE x: 0.3851  
 CIE y: 0.3813  
 CIE z: 0.2336  
 Peak Wavelength (nm): 451  
 Dominant Wavelength (nm): 578  
 Purity: 30.01895  
 Rf: 90.8  
 Rg: 98.8

CRI (Ra):	92.4		
R1:	92.5	R9:	62.0
R2:	94.9	R10:	87.0
R3:	95.8	R11:	92.8
R4:	92.7	R12:	71.7
R5:	91.7	R13:	93.2
R6:	92.1	R14:	97.3
R7:	94.3	R15:	89.6
R8:	85.2		



**Test Conditions**


Stabilization Time: 31M  
 Operation Time: 1H 31M  
 Sphere Temperature (°C): 25.2.

REPORT NUMBER: SP1-2506-458-11


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-11

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-11

**Photopic Flux vs. Wavelength**




**Photopic Lumens: NR**

$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)
360	0	NR	490	394	NR	620	868	NR	750	58	NR	880	1	NR
365	0	NR	495	449	NR	625	858	NR	755	49	NR	885	1	NR
370	0	NR	500	505	NR	630	839	NR	760	42	NR	890	1	NR
375	0	NR	505	553	NR	635	813	NR	765	36	NR	895	1	NR
380	0	NR	510	593	NR	640	783	NR	770	31	NR	900	1	NR
385	0	NR	515	628	NR	645	746	NR	775	26	NR	905	1	NR
390	1	NR	520	651	NR	650	702	NR	780	22	NR	910	0	NR
395	4	NR	525	670	NR	655	657	NR	785	19	NR	915	0	NR
400	5	NR	530	687	NR	660	607	NR	790	16	NR	920	0	NR
405	8	NR	535	705	NR	665	559	NR	795	14	NR	925	0	NR
410	12	NR	540	717	NR	670	507	NR	800	12	NR	930	0	NR
415	19	NR	545	731	NR	675	458	NR	805	10	NR	935	0	NR
420	34	NR	550	745	NR	680	413	NR	810	9	NR	940	0	NR
425	60	NR	555	757	NR	685	367	NR	815	7	NR	945	0	NR
430	107	NR	560	767	NR	690	328	NR	820	6	NR	950	0	NR
435	194	NR	565	777	NR	695	289	NR	825	5	NR	955	0	NR
440	349	NR	570	785	NR	700	253	NR	830	5	NR	960	0	NR
445	678	NR	575	794	NR	705	221	NR	835	4	NR	965	0	NR
450	997	NR	580	809	NR	710	192	NR	840	3	NR	970	0	NR
455	819	NR	585	820	NR	715	165	NR	845	3	NR	975	0	NR
460	581	NR	590	838	NR	720	144	NR	850	2	NR	980	0	NR
465	517	NR	595	851	NR	725	124	NR	855	2	NR	985	0	NR
470	406	NR	600	861	NR	730	107	NR	860	2	NR	990	0	NR
475	327	NR	605	873	NR	735	91	NR	865	2	NR	995	0	NR
480	330	NR	610	875	NR	740	78	NR	870	1	NR	1000	0	NR
485	356	NR	615	877	NR	745	67	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-11

**Scotopic Flux vs. Wavelength**




**Scotopic Lumens: NR**

**S/P: 1.75**

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	394	NR	620	868	NR	750	58	NR	880	1	NR
365	0	NR	495	449	NR	625	858	NR	755	49	NR	885	1	NR
370	0	NR	500	505	NR	630	839	NR	760	42	NR	890	1	NR
375	0	NR	505	553	NR	635	813	NR	765	36	NR	895	1	NR
380	0	NR	510	593	NR	640	783	NR	770	31	NR	900	1	NR
385	0	NR	515	628	NR	645	746	NR	775	26	NR	905	1	NR
390	1	NR	520	651	NR	650	702	NR	780	22	NR	910	0	NR
395	4	NR	525	670	NR	655	657	NR	785	19	NR	915	0	NR
400	5	NR	530	687	NR	660	607	NR	790	16	NR	920	0	NR
405	8	NR	535	705	NR	665	559	NR	795	14	NR	925	0	NR
410	12	NR	540	717	NR	670	507	NR	800	12	NR	930	0	NR
415	19	NR	545	731	NR	675	458	NR	805	10	NR	935	0	NR
420	34	NR	550	745	NR	680	413	NR	810	9	NR	940	0	NR
425	60	NR	555	757	NR	685	367	NR	815	7	NR	945	0	NR
430	107	NR	560	767	NR	690	328	NR	820	6	NR	950	0	NR
435	194	NR	565	777	NR	695	289	NR	825	5	NR	955	0	NR
440	349	NR	570	785	NR	700	253	NR	830	5	NR	960	0	NR
445	678	NR	575	794	NR	705	221	NR	835	4	NR	965	0	NR
450	997	NR	580	809	NR	710	192	NR	840	3	NR	970	0	NR
455	819	NR	585	820	NR	715	165	NR	845	3	NR	975	0	NR
460	581	NR	590	838	NR	720	144	NR	850	2	NR	980	0	NR
465	517	NR	595	851	NR	725	124	NR	855	2	NR	985	0	NR
470	406	NR	600	861	NR	730	107	NR	860	2	NR	990	0	NR
475	327	NR	605	873	NR	735	91	NR	865	2	NR	995	0	NR
480	330	NR	610	875	NR	740	78	NR	870	1	NR	1000	0	NR
485	356	NR	615	877	NR	745	67	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-11

**Melanopic Flux vs. Wavelength**




**Melanopic Lumens: NR**

**M/P: 3.61**





λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	394	NR	620	868	NR	750	58	NR	880	1	NR
365	0	NR	495	449	NR	625	858	NR	755	49	NR	885	1	NR
370	0	NR	500	505	NR	630	839	NR	760	42	NR	890	1	NR
375	0	NR	505	553	NR	635	813	NR	765	36	NR	895	1	NR
380	0	NR	510	593	NR	640	783	NR	770	31	NR	900	1	NR
385	0	NR	515	628	NR	645	746	NR	775	26	NR	905	1	NR
390	1	NR	520	651	NR	650	702	NR	780	22	NR	910	0	NR
395	4	NR	525	670	NR	655	657	NR	785	19	NR	915	0	NR
400	5	NR	530	687	NR	660	607	NR	790	16	NR	920	0	NR
405	8	NR	535	705	NR	665	559	NR	795	14	NR	925	0	NR
410	12	NR	540	717	NR	670	507	NR	800	12	NR	930	0	NR
415	19	NR	545	731	NR	675	458	NR	805	10	NR	935	0	NR
420	34	NR	550	745	NR	680	413	NR	810	9	NR	940	0	NR
425	60	NR	555	757	NR	685	367	NR	815	7	NR	945	0	NR
430	107	NR	560	767	NR	690	328	NR	820	6	NR	950	0	NR
435	194	NR	565	777	NR	695	289	NR	825	5	NR	955	0	NR
440	349	NR	570	785	NR	700	253	NR	830	5	NR	960	0	NR
445	678	NR	575	794	NR	705	221	NR	835	4	NR	965	0	NR
450	997	NR	580	809	NR	710	192	NR	840	3	NR	970	0	NR
455	819	NR	585	820	NR	715	165	NR	845	3	NR	975	0	NR
460	581	NR	590	838	NR	720	144	NR	850	2	NR	980	0	NR
465	517	NR	595	851	NR	725	124	NR	855	2	NR	985	0	NR
470	406	NR	600	861	NR	730	107	NR	860	2	NR	990	0	NR
475	327	NR	605	873	NR	735	91	NR	865	2	NR	995	0	NR
480	330	NR	610	875	NR	740	78	NR	870	1	NR	1000	0	NR
485	356	NR	615	877	NR	745	67	NR	875	1	NR			

**Summary**

$R_f = 90.8$   
 $R_g = 98.8$   
 CIE  $R_a = 92.4$   
 $R_9 = 62.0$




**Color Vector Graphics**








**Individual Sample Fidelity Index ( $R_{f,i}$ )**



CES01 = 86	CES26 = 93	CES51 = 96	CES76 = 85
CES02 = 62	CES27 = 90	CES52 = 98	CES77 = 88
CES03 = 31	CES28 = 96	CES53 = 96	CES78 = 82
CES04 = 69	CES29 = 96	CES54 = 92	CES79 = 96
CES05 = 49	CES30 = 90	CES55 = 90	CES80 = 93
CES06 = 50	CES31 = 97	CES56 = 93	CES81 = 89
CES07 = 42	CES32 = 91	CES57 = 91	CES82 = 97
CES08 = 41	CES33 = 98	CES58 = 92	CES83 = 98
CES09 = 29	CES34 = 93	CES59 = 96	CES84 = 93
CES10 = 74	CES35 = 96	CES60 = 91	CES85 = 83
CES11 = 57	CES36 = 79	CES61 = 91	CES86 = 88
CES12 = 63	CES37 = 95	CES62 = 84	CES87 = 91
CES13 = 43	CES38 = 85	CES63 = 91	CES88 = 96
CES14 = 74	CES39 = 99	CES64 = 87	CES89 = 87
CES15 = 71	CES40 = 98	CES65 = 87	CES90 = 96
CES16 = 47	CES41 = 96	CES66 = 84	CES91 = 71
CES17 = 49	CES42 = 95	CES67 = 83	CES92 = 79
CES18 = 56	CES43 = 95	CES68 = 86	CES93 = 87
CES19 = 71	CES44 = 99	CES69 = 87	CES94 = 81
CES20 = 66	CES45 = 98	CES70 = 84	CES95 = 82
CES21 = 85	CES46 = 97	CES71 = 77	CES96 = 91
CES22 = 78	CES47 = 97	CES72 = 93	CES97 = 96
CES23 = 91	CES48 = 90	CES73 = 78	CES98 = 94
CES24 = 90	CES49 = 96	CES74 = 91	CES99 = 91
CES25 = 71	CES50 = 97	CES75 = 80	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)