

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1215060

Luminaire Tested: 22-ID2-70-CNV-L850-U

Issue Date: 12/4/2025


Test Information

Test Method: LM-79-2019
Report Number: P1215060
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2506-458-15)
Test Lab: INNOVATION CENTER
Issue Date: 12/4/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 22-ID2-70-CNV-L850-U
Description: 2X2 IN DEPTH TROFFER WITH 2INCH CURVE DROP
Light Source: 5000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7558.4 lumens
Efficiency: N/A
Efficacy: 120.9 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.2 / 1.31
Luminous Opening: Rectangular w/ Sides (W: 2' x L: 2' x H: 0.16')
CIE Type: Direct

Input Watts (W): 62.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1215060
CATALOG NUMBER: 22-ID2-70-CNV-L850-U

Luminous Intensity Polar Plot



TEST NUMBER: P1215060

CATALOG NUMBER: 22-ID2-70-CNV-L850-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		98
1	108	103	99	95	105	101	97	93	96	93	90		92	89	87		82
2	98	90	83	77	96	88	82	76	84	79	74		81	76	72		68
3	90	79	71	65	87	77	70	64	74	68	62		71	66	61		58
4	82	70	62	55	80	69	61	54	66	59	53		64	57	52		49
5	76	63	54	47	74	62	53	47	59	52	46		57	51	46		43
6	70	57	48	42	68	56	47	41	54	46	41		52	45	40		38
7	65	52	43	37	63	51	42	37	49	42	36		47	41	36		33
8	61	47	39	33	59	46	38	33	45	38	32		43	37	32		30
9	57	43	35	30	55	43	35	30	41	34	29		40	34	29		27
10	53	40	32	27	52	39	32	27	38	31	27		37	31	26		24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7557	7557	7557
5°	7495	7463	7498
10°	7403	7345	7406
15°	7265	7192	7273
20°	7100	7005	7108
25°	6909	6792	6909
30°	6669	6552	6686
35°	6429	6294	6435
40°	6171	6015	6187
45°	5903	5717	5892
50°	5607	5415	5577
55°	5356	5092	5252
60°	5069	4740	4876
65°	4722	4384	4495
70°	4378	3960	4078
75°	3935	3502	3669
80°	3335	3051	3385
85°	2776	2701	3205

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5903 cd/sqm

TEST NUMBER: P1215060
 CATALOG NUMBER: 22-ID2-70-CNV-L850-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	265.1	3.5
10°-20°	750.5	9.9
20°-30°	1110.1	14.7
30°-40°	1293.5	17.1
40°-50°	1291.5	17.1
50°-60°	1127.5	14.9
60°-70°	845.1	11.2
70°-80°	509.1	6.7
80°-90°	219.8	2.9
90°-100°	72.6	1.0
100°-110°	33.4	0.4
110°-120°	20.7	0.3
120°-130°	11.3	0.1
130°-140°	5.5	0.1
140°-150°	2.0	0.0
150°-160°	0.6	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2125.6	28.1
0°-40°	3419.1	45.2
0°-60°	5838.2	77.2
0°-90°	7412.2	98.1
90°-120°	126.7	1.7
90°-150°	145.5	1.9
90°-180°	146.0	1.9
0°-180°	7558.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2808	2808	2808	2808	2808	
5°	2794	2792	2790	2794	2795	265
15°	2664	2663	2660	2664	2667	751
25°	2414	2409	2408	2415	2414	1110
35°	2067	2066	2068	2072	2069	1293
45°	1675	1674	1672	1677	1672	1291
55°	1272	1267	1261	1256	1247	1137
65°	869	862	856	840	827	862
75°	492	488	479	472	458	519
85°	172	182	201	205	199	171
90°	91	103	114	116	109	53
95°	78	69	62	54	47	62
105°	59	51	32	10	1	62
115°	41	35	22	5	0	41
125°	27	23	12	1	0	24
135°	15	12	6	1	1	12
145°	7	6	2	1	1	4
155°	2	1	1	1	1	1
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	

TEST NUMBER: P1215060

CATALOG NUMBER: 22-ID2-70-CNV-L850-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2808.3	2808.3	2808.3	2808.3	2808.3
2.5°	2806.4	2804.5	2802.6	2804.5	2807.3
5°	2794.0	2792.1	2790.2	2794.0	2795.0
7.5°	2775.0	2773.1	2770.3	2773.1	2776.0
10°	2747.4	2744.6	2741.7	2744.6	2748.4
12.5°	2711.3	2710.4	2706.6	2708.5	2711.3
15°	2663.8	2662.8	2660.0	2663.8	2666.6
17.5°	2613.4	2608.6	2607.7	2610.5	2613.4
20°	2551.6	2549.7	2546.8	2551.6	2554.5
22.5°	2485.1	2485.1	2482.2	2485.1	2487.9
25°	2413.8	2409.0	2408.1	2414.7	2413.8
27.5°	2332.0	2333.9	2331.0	2332.9	2340.6
30°	2245.5	2246.4	2246.4	2250.2	2251.2
32.5°	2159.0	2159.9	2160.9	2161.8	2162.8
35°	2066.8	2065.8	2067.7	2071.5	2068.7
37.5°	1974.5	1971.7	1972.6	1973.6	1981.2
40°	1874.7	1873.8	1874.7	1880.4	1879.5
42.5°	1773.0	1773.0	1777.8	1779.7	1776.8
45°	1675.1	1674.1	1672.2	1677.0	1672.2
47.5°	1573.4	1570.5	1569.6	1573.4	1568.6
50°	1466.9	1469.7	1467.8	1465.0	1459.3
52.5°	1371.8	1369.0	1365.2	1361.4	1352.8
55°	1272.0	1267.2	1260.6	1255.8	1247.3
57.5°	1170.3	1164.6	1157.9	1149.4	1145.6
60°	1072.4	1062.9	1053.3	1046.7	1031.5
62.5°	966.8	964.9	952.6	945.0	936.4
65°	868.9	862.3	855.6	840.4	827.1
67.5°	771.9	769.1	754.8	743.4	731.1
70°	678.8	669.3	659.8	648.4	632.2
72.5°	584.7	579.0	567.6	555.2	542.8
75°	491.5	487.7	479.1	472.5	458.2
77.5°	397.4	397.4	398.3	395.5	386.0
80°	312.8	318.5	323.2	325.1	317.5
82.5°	237.7	243.4	259.5	264.3	254.8
85°	172.1	181.6	200.6	205.3	198.7
87.5°	122.6	136.9	152.1	157.8	151.2
90°	91.3	102.7	114.1	116.0	109.3
92.5°	83.7	80.8	83.7	81.8	75.1
95°	78.0	69.4	61.8	54.2	46.6
97.5°	73.2	64.6	46.6	33.3	26.6
100°	68.4	59.9	39.0	19.0	10.5
102.5°	63.7	56.1	36.1	12.4	1.9
105°	58.9	51.3	32.3	10.5	1.0
107.5°	54.2	47.5	29.5	8.6	1.0
110°	49.4	43.7	26.6	7.6	1.0

TEST NUMBER: P1215060

CATALOG NUMBER: 22-ID2-70-CNV-L850-U

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	45.6	39.9	23.8	5.7	0.0
115°	40.9	35.2	21.9	4.8	0.0
117.5°	37.1	32.3	19.0	3.8	0.0
120°	33.3	28.5	17.1	2.9	0.0
122.5°	29.5	25.7	14.3	1.9	0.0
125°	26.6	22.8	12.4	1.0	0.0
127.5°	22.8	20.0	10.5	1.0	0.0
130°	20.0	17.1	9.5	1.0	1.0
132.5°	18.1	15.2	7.6	1.0	1.0
135°	15.2	12.4	5.7	1.0	1.0
137.5°	13.3	10.5	4.8	1.0	1.0
140°	10.5	8.6	3.8	1.0	1.0
142.5°	8.6	6.7	2.9	1.0	1.0
145°	6.7	5.7	1.9	1.0	1.0
147.5°	4.8	3.8	1.0	1.0	1.0
150°	3.8	2.9	1.0	1.0	1.0
152.5°	2.9	1.9	1.0	1.0	1.0
155°	1.9	1.0	1.0	1.0	1.0
157.5°	1.0	1.0	1.0	1.0	1.0
160°	1.0	1.0	1.0	1.0	1.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1215060

CATALOG NUMBER: 22-ID2-70-CNV-L850-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.49	19.07	17.89	19.43	19.79	17.39	18.97	17.78	19.32	19.69
	3H	19.22	20.66	19.63	21.02	21.43	19.03	20.46	19.44	20.83	21.24
	4H	19.88	21.23	20.31	21.62	22.04	19.65	21.00	20.08	21.39	21.81
	6H	20.37	21.62	20.81	22.02	22.46	20.16	21.41	20.60	21.81	22.25
	8H	20.53	21.73	20.99	22.16	22.60	20.36	21.55	20.81	21.98	22.43
	12H	20.66	21.80	21.12	22.23	22.70	20.53	21.68	20.99	22.10	22.57
4H	2H	18.05	19.40	18.48	19.79	20.21	17.97	19.32	18.40	19.71	20.13
	3H	20.00	21.13	20.44	21.57	22.01	19.83	20.96	20.27	21.40	21.85
	4H	20.78	21.81	21.24	22.26	22.74	20.58	21.61	21.04	22.06	22.54
	6H	21.39	22.30	21.88	22.77	23.27	21.23	22.13	21.71	22.61	23.11
	8H	21.61	22.46	22.10	22.94	23.45	21.49	22.33	21.98	22.81	23.32
	12H	21.79	22.55	22.30	23.06	23.58	21.72	22.49	22.23	23.00	23.51
8H	4H	21.05	21.90	21.55	22.38	22.89	20.88	21.72	21.37	22.20	22.71
	6H	21.79	22.50	22.32	23.02	23.54	21.66	22.37	22.18	22.89	23.41
	8H	22.09	22.73	22.63	23.27	23.80	22.01	22.65	22.55	23.19	23.72
	12H	22.36	22.92	22.89	23.45	24.05	22.36	22.92	22.89	23.45	24.05
12H	4H	21.09	21.85	21.60	22.36	22.87	20.91	21.67	21.42	22.18	22.70
	6H	21.85	22.49	22.39	23.03	23.56	21.72	22.36	22.26	22.90	23.43
	8H	22.21	22.78	22.75	23.30	23.91	22.14	22.71	22.68	23.23	23.83

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-7

Test Date: 08/26/2025

Luminaire Tested: 22ID2-55-CFR1-L850-U

Data in this report applies to families of products including 22ID2-55-CFR1-L850-U


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L850-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 5000K 80CRI

Spectral Parameters

CCT (K): 4966
 CIE u' : 0.2093
 CIE v' : 0.4890
 Duv: 0.0036
 CIE x: 0.3468
 CIE y: 0.3601
 CIE z: 0.2931
 Peak Wavelength (nm): 450
 Dominant Wavelength (nm): 570
 Purity: 12.1135
 R_f: 84
 R_g: 96.2

CRI (Ra): 83.1
 R1: 81.0
 R2: 87.8
 R3: 92.7
 R4: 82.4
 R5: 81.0
 R6: 82.6
 R7: 88.5
 R8: 68.6
 R9: 10.3
 R10: 70.9
 R11: 81.3
 R12: 55.9
 R13: 82.8
 R14: 96.1
 R15: 75.1



Test Conditions


Stabilization Time: 37M
 Operation Time: 1H 37M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2506-458-7


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-7

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-7

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	262	NR	620	472	NR	750	15	NR	880	0	NR
365	0	NR	495	307	NR	625	443	NR	755	13	NR	885	0	NR
370	0	NR	500	358	NR	630	412	NR	760	11	NR	890	0	NR
375	0	NR	505	403	NR	635	379	NR	765	9	NR	895	0	NR
380	0	NR	510	440	NR	640	346	NR	770	8	NR	900	0	NR
385	1	NR	515	471	NR	645	313	NR	775	7	NR	905	0	NR
390	3	NR	520	490	NR	650	282	NR	780	6	NR	910	0	NR
395	4	NR	525	504	NR	655	252	NR	785	5	NR	915	0	NR
400	6	NR	530	515	NR	660	223	NR	790	4	NR	920	0	NR
405	9	NR	535	524	NR	665	197	NR	795	4	NR	925	0	NR
410	12	NR	540	530	NR	670	171	NR	800	3	NR	930	0	NR
415	20	NR	545	539	NR	675	149	NR	805	3	NR	935	0	NR
420	36	NR	550	545	NR	680	130	NR	810	2	NR	940	0	NR
425	64	NR	555	554	NR	685	112	NR	815	2	NR	945	0	NR
430	117	NR	560	562	NR	690	97	NR	820	2	NR	950	0	NR
435	212	NR	565	567	NR	695	83	NR	825	2	NR	955	0	NR
440	378	NR	570	571	NR	700	71	NR	830	1	NR	960	0	NR
445	709	NR	575	574	NR	705	61	NR	835	1	NR	965	0	NR
450	1000	NR	580	579	NR	710	52	NR	840	1	NR	970	0	NR
455	789	NR	585	578	NR	715	44	NR	845	1	NR	975	0	NR
460	519	NR	590	578	NR	720	38	NR	850	1	NR	980	0	NR
465	429	NR	595	571	NR	725	32	NR	855	1	NR	985	0	NR
470	316	NR	600	560	NR	730	28	NR	860	1	NR	990	0	NR
475	236	NR	605	545	NR	735	24	NR	865	1	NR	995	0	NR
480	224	NR	610	524	NR	740	20	NR	870	0	NR	1000	0	NR
485	235	NR	615	501	NR	745	17	NR	875	0	NR			

REPORT NUMBER: SP1-2506-458-7

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.94

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	262	NR	620	472	NR	750	15	NR	880	0	NR
365	0	NR	495	307	NR	625	443	NR	755	13	NR	885	0	NR
370	0	NR	500	358	NR	630	412	NR	760	11	NR	890	0	NR
375	0	NR	505	403	NR	635	379	NR	765	9	NR	895	0	NR
380	0	NR	510	440	NR	640	346	NR	770	8	NR	900	0	NR
385	1	NR	515	471	NR	645	313	NR	775	7	NR	905	0	NR
390	3	NR	520	490	NR	650	282	NR	780	6	NR	910	0	NR
395	4	NR	525	504	NR	655	252	NR	785	5	NR	915	0	NR
400	6	NR	530	515	NR	660	223	NR	790	4	NR	920	0	NR
405	9	NR	535	524	NR	665	197	NR	795	4	NR	925	0	NR
410	12	NR	540	530	NR	670	171	NR	800	3	NR	930	0	NR
415	20	NR	545	539	NR	675	149	NR	805	3	NR	935	0	NR
420	36	NR	550	545	NR	680	130	NR	810	2	NR	940	0	NR
425	64	NR	555	554	NR	685	112	NR	815	2	NR	945	0	NR
430	117	NR	560	562	NR	690	97	NR	820	2	NR	950	0	NR
435	212	NR	565	567	NR	695	83	NR	825	2	NR	955	0	NR
440	378	NR	570	571	NR	700	71	NR	830	1	NR	960	0	NR
445	709	NR	575	574	NR	705	61	NR	835	1	NR	965	0	NR
450	1000	NR	580	579	NR	710	52	NR	840	1	NR	970	0	NR
455	789	NR	585	578	NR	715	44	NR	845	1	NR	975	0	NR
460	519	NR	590	578	NR	720	38	NR	850	1	NR	980	0	NR
465	429	NR	595	571	NR	725	32	NR	855	1	NR	985	0	NR
470	316	NR	600	560	NR	730	28	NR	860	1	NR	990	0	NR
475	236	NR	605	545	NR	735	24	NR	865	1	NR	995	0	NR
480	224	NR	610	524	NR	740	20	NR	870	0	NR	1000	0	NR
485	235	NR	615	501	NR	745	17	NR	875	0	NR			

REPORT NUMBER: SP1-2506-458-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 4.11


λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	262	NR	620	472	NR	750	15	NR	880	0	NR
365	0	NR	495	307	NR	625	443	NR	755	13	NR	885	0	NR
370	0	NR	500	358	NR	630	412	NR	760	11	NR	890	0	NR
375	0	NR	505	403	NR	635	379	NR	765	9	NR	895	0	NR
380	0	NR	510	440	NR	640	346	NR	770	8	NR	900	0	NR
385	1	NR	515	471	NR	645	313	NR	775	7	NR	905	0	NR
390	3	NR	520	490	NR	650	282	NR	780	6	NR	910	0	NR
395	4	NR	525	504	NR	655	252	NR	785	5	NR	915	0	NR
400	6	NR	530	515	NR	660	223	NR	790	4	NR	920	0	NR
405	9	NR	535	524	NR	665	197	NR	795	4	NR	925	0	NR
410	12	NR	540	530	NR	670	171	NR	800	3	NR	930	0	NR
415	20	NR	545	539	NR	675	149	NR	805	3	NR	935	0	NR
420	36	NR	550	545	NR	680	130	NR	810	2	NR	940	0	NR
425	64	NR	555	554	NR	685	112	NR	815	2	NR	945	0	NR
430	117	NR	560	562	NR	690	97	NR	820	2	NR	950	0	NR
435	212	NR	565	567	NR	695	83	NR	825	2	NR	955	0	NR
440	378	NR	570	571	NR	700	71	NR	830	1	NR	960	0	NR
445	709	NR	575	574	NR	705	61	NR	835	1	NR	965	0	NR
450	1000	NR	580	579	NR	710	52	NR	840	1	NR	970	0	NR
455	789	NR	585	578	NR	715	44	NR	845	1	NR	975	0	NR
460	519	NR	590	578	NR	720	38	NR	850	1	NR	980	0	NR
465	429	NR	595	571	NR	725	32	NR	855	1	NR	985	0	NR
470	316	NR	600	560	NR	730	28	NR	860	1	NR	990	0	NR
475	236	NR	605	545	NR	735	24	NR	865	1	NR	995	0	NR
480	224	NR	610	524	NR	740	20	NR	870	0	NR	1000	0	NR
485	235	NR	615	501	NR	745	17	NR	875	0	NR			

REPORT NUMBER: SP1-2506-458-7





TM-30-18

Summary

$R_f = 84$
 $R_g = 96.2$
 $\text{CIE } R_a = 83.1$
 $R_9 = 10.3$







Color Vector Graphics





Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 85	CES26 = 80	CES51 = 95	CES76 = 72
CES02 = 60	CES27 = 93	CES52 = 95	CES77 = 81
CES03 = 30	CES28 = 90	CES53 = 89	CES78 = 71
CES04 = 69	CES29 = 85	CES54 = 90	CES79 = 91
CES05 = 47	CES30 = 97	CES55 = 89	CES80 = 87
CES06 = 50	CES31 = 87	CES56 = 86	CES81 = 84
CES07 = 40	CES32 = 79	CES57 = 85	CES82 = 95
CES08 = 39	CES33 = 92	CES58 = 85	CES83 = 95
CES09 = 29	CES34 = 84	CES59 = 92	CES84 = 90
CES10 = 73	CES35 = 91	CES60 = 91	CES85 = 81
CES11 = 56	CES36 = 83	CES61 = 88	CES86 = 79
CES12 = 62	CES37 = 90	CES62 = 85	CES87 = 84
CES13 = 42	CES38 = 93	CES63 = 85	CES88 = 89
CES14 = 74	CES39 = 98	CES64 = 79	CES89 = 79
CES15 = 71	CES40 = 94	CES65 = 76	CES90 = 89
CES16 = 46	CES41 = 99	CES66 = 75	CES91 = 72
CES17 = 48	CES42 = 89	CES67 = 73	CES92 = 67
CES18 = 55	CES43 = 88	CES68 = 78	CES93 = 80
CES19 = 70	CES44 = 99	CES69 = 82	CES94 = 65
CES20 = 64	CES45 = 93	CES70 = 73	CES95 = 73
CES21 = 85	CES46 = 91	CES71 = 67	CES96 = 84
CES22 = 77	CES47 = 96	CES72 = 89	CES97 = 92
CES23 = 91	CES48 = 87	CES73 = 66	CES98 = 86
CES24 = 90	CES49 = 90	CES74 = 92	CES99 = 77
CES25 = 71	CES50 = 95	CES75 = 68	



Color Rendition by Hue-Angle Bin


Measure Comparisons



(END OF REPORT)