

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1216064

Luminaire Tested: 24-ID2-55-CNC-L950-U

Issue Date: 12/5/2025


Test Information

Test Method: LM-79-2019
Report Number: P1216064
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2508-510-9)
Test Lab: INNOVATION CENTER
Issue Date: 12/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 24-ID2-55-CNC-L950-U
Description: 2X4 IN DEPTH TROFFER WITH 2INCH CURVE REGRESSED
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4998.4 lumens
Efficiency: N/A
Efficacy: 105.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.19 / 1.29
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 47.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1216064
CATALOG NUMBER: 24-ID2-55-CNC-L950-U

Luminous Intensity Polar Plot



TEST NUMBER: P1216064

CATALOG NUMBER: 24-ID2-55-CNC-L950-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	109	105	100	97	106	102	99	95	98	95	92		94	92	89		85
2	100	92	85	79	97	90	84	78	86	81	77		83	79	75		71
3	91	81	73	67	89	79	72	66	76	70	65		74	68	64		60
4	84	72	63	57	81	71	63	56	68	61	56		66	60	55		52
5	77	64	56	49	75	63	55	49	61	54	48		59	53	48		45
6	71	58	49	43	69	57	49	43	55	48	42		54	47	42		40
7	66	53	44	38	64	52	44	38	51	43	38		49	42	37		35
8	62	48	40	34	60	48	40	34	46	39	34		45	38	34		32
9	58	44	36	31	56	44	36	31	43	36	31		42	35	30		29
10	54	41	33	28	53	41	33	28	40	33	28		39	32	28		26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2658	2658	2658
5°	2668	2654	2656
10°	2651	2637	2637
15°	2625	2610	2607
20°	2586	2568	2565
25°	2535	2512	2511
30°	2473	2450	2437
35°	2401	2374	2355
40°	2323	2290	2271
45°	2236	2205	2174
50°	2147	2108	2078
55°	2047	1999	1973
60°	1946	1894	1875
65°	1812	1779	1775
70°	1658	1650	1645
75°	1481	1506	1517
80°	1208	1315	1379
85°	831	1054	1054

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2236 cd/sqm

TEST NUMBER: P1216064
 CATALOG NUMBER: 24-ID2-55-CNC-L950-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.6	3.7
10°-20°	528.3	10.6
20°-30°	780.2	15.6
30°-40°	904.5	18.1
40°-50°	893.5	17.9
50°-60°	765.5	15.3
60°-70°	555.5	11.1
70°-80°	306.6	6.1
80°-90°	77.7	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1495.1	29.9
0°-40°	2399.6	48.0
0°-60°	4058.7	81.2
0°-90°	4998.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4998.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1976	1976	1976	1976	1976	
5°	1975	1968	1965	1961	1966	187
15°	1885	1878	1874	1870	1872	531
25°	1708	1701	1692	1689	1692	786
35°	1462	1456	1445	1438	1434	915
45°	1175	1167	1159	1147	1142	907
55°	873	864	852	845	841	781
65°	569	564	559	556	557	563
75°	285	284	290	292	292	301
85°	54	59	68	69	68	68
90°	0	0	0	0	0	

TEST NUMBER: P1216064

CATALOG NUMBER: 24-ID2-55-CNC-L950-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1975.8	1975.8	1975.8	1975.8	1975.8
2.5°	1982.7	1975.8	1972.4	1969.6	1973.7
5°	1975.1	1967.5	1964.8	1961.3	1966.2
7.5°	1960.0	1953.7	1950.3	1947.5	1950.3
10°	1940.6	1933.7	1930.3	1928.2	1930.3
12.5°	1915.1	1910.3	1904.8	1900.6	1904.8
15°	1884.8	1877.9	1873.7	1869.6	1871.6
17.5°	1847.5	1841.3	1835.8	1832.3	1834.4
20°	1806.1	1798.5	1793.7	1790.2	1791.6
22.5°	1762.6	1753.0	1746.8	1741.3	1741.9
25°	1707.5	1700.6	1692.3	1688.8	1691.6
27.5°	1650.9	1643.3	1636.4	1630.9	1629.5
30°	1591.6	1584.7	1577.1	1570.9	1568.8
32.5°	1532.2	1520.5	1512.2	1506.0	1505.3
35°	1461.9	1456.3	1445.3	1438.4	1433.6
37.5°	1394.9	1386.7	1375.6	1369.4	1364.6
40°	1322.5	1314.2	1303.9	1294.9	1292.8
42.5°	1249.4	1243.2	1229.4	1223.8	1220.4
45°	1174.9	1167.3	1159.0	1147.3	1142.4
47.5°	1103.8	1096.2	1082.4	1072.1	1069.3
50°	1025.9	1016.9	1007.2	994.8	992.7
52.5°	952.0	941.7	929.3	923.8	919.6
55°	872.7	864.4	852.0	845.1	841.0
57.5°	794.1	789.2	780.9	771.3	770.6
60°	723.0	713.3	703.7	696.8	696.8
62.5°	643.7	640.2	630.6	626.4	624.3
65°	569.2	564.3	558.8	556.0	557.4
67.5°	492.6	491.9	487.7	488.4	487.1
70°	421.5	418.8	419.4	420.8	418.1
72.5°	352.5	350.5	353.9	354.6	356.0
75°	284.9	283.5	289.7	291.8	291.8
77.5°	217.3	221.5	228.4	233.9	233.9
80°	155.9	161.4	169.7	174.5	178.0
82.5°	100.0	109.0	116.6	120.0	120.0
85°	53.8	59.3	68.3	69.0	68.3
87.5°	16.6	20.7	24.8	26.2	26.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1216064

CATALOG NUMBER: 24-ID2-55-CNC-L950-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.43	16.03	14.80	16.34	16.66	14.26	15.86	14.63	16.18	16.49
	3H	16.07	17.51	16.45	17.84	18.20	15.95	17.40	16.33	17.72	18.08
	4H	16.66	18.01	17.05	18.36	18.74	16.58	17.94	16.98	18.29	18.66
	6H	17.04	18.30	17.45	18.66	19.05	17.05	18.31	17.47	18.68	19.07
	8H	17.14	18.34	17.56	18.73	19.13	17.20	18.40	17.62	18.79	19.19
	12H	17.19	18.34	17.62	18.72	19.15	17.28	18.43	17.71	18.81	19.24
4H	2H	15.00	16.36	15.40	16.70	17.08	14.86	16.22	15.26	16.57	16.94
	3H	16.86	17.99	17.27	18.39	18.79	16.77	17.91	17.18	18.30	18.70
	4H	17.56	18.58	17.99	19.00	19.44	17.53	18.55	17.96	18.97	19.40
	6H	18.06	18.96	18.52	19.40	19.85	18.13	19.02	18.58	19.46	19.92
	8H	18.20	19.04	18.66	19.48	19.94	18.31	19.15	18.77	19.59	20.06
	12H	18.28	19.03	18.76	19.51	19.98	18.44	19.19	18.92	19.66	20.13
8H	4H	17.84	18.68	18.30	19.12	19.58	17.81	18.65	18.27	19.09	19.56
	6H	18.45	19.14	18.94	19.63	20.11	18.52	19.22	19.02	19.71	20.18
	8H	18.65	19.27	19.16	19.78	20.26	18.78	19.40	19.29	19.91	20.40
	12H	18.78	19.33	19.29	19.82	20.38	18.97	19.52	19.47	20.01	20.57
12H	4H	17.87	18.62	18.35	19.09	19.56	17.84	18.59	18.32	19.06	19.53
	6H	18.50	19.12	19.01	19.63	20.11	18.56	19.19	19.08	19.70	20.18
	8H	18.75	19.30	19.26	19.79	20.35	18.87	19.42	19.38	19.92	20.48

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-13

Test Date: 08/27/2025

Luminaire Tested: 22ID2-55-CFR1-L950-U

Data in this report applies to families of products including 22ID2-55-CFR1-L950-U


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-13
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L950-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 5000K 90CRI

Spectral Parameters

CCT (K): 4919
 CIE u' : 0.2096
 CIE v' : 0.4901
 Duv: 0.0038
 CIE x: 0.3483
 CIE y: 0.3619
 CIE z: 0.2898
 Peak Wavelength (nm): 453
 Dominant Wavelength (nm): 570
 Purity: 13.10873
 R_f: 90.8
 R_g: 97.4

CRI (Ra): 94.0
 R1: 94.8
 R2: 97.7
 R3: 98.4
 R4: 90.8
 R5: 92.2
 R6: 94.3
 R7: 94.0
 R8: 90.0
 R9: 77.7
 R10: 93.1
 R11: 92.0
 R12: 65.9
 R13: 95.9
 R14: 99.0
 R15: 91.4



Test Conditions


Stabilization Time: M
 Operation Time: 1H 0M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-458-13


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-13

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-13

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	419	NR	620	583	NR	750	44	NR	880	1	NR
365	0	NR	495	441	NR	625	580	NR	755	37	NR	885	1	NR
370	0	NR	500	472	NR	630	572	NR	760	32	NR	890	1	NR
375	0	NR	505	501	NR	635	559	NR	765	27	NR	895	0	NR
380	0	NR	510	524	NR	640	543	NR	770	23	NR	900	0	NR
385	0	NR	515	545	NR	645	522	NR	775	20	NR	905	0	NR
390	1	NR	520	559	NR	650	496	NR	780	17	NR	910	0	NR
395	3	NR	525	572	NR	655	468	NR	785	14	NR	915	0	NR
400	4	NR	530	581	NR	660	435	NR	790	12	NR	920	0	NR
405	7	NR	535	590	NR	665	403	NR	795	10	NR	925	0	NR
410	9	NR	540	595	NR	670	368	NR	800	9	NR	930	0	NR
415	14	NR	545	599	NR	675	335	NR	805	8	NR	935	0	NR
420	23	NR	550	599	NR	680	304	NR	810	6	NR	940	0	NR
425	40	NR	555	599	NR	685	271	NR	815	6	NR	945	0	NR
430	72	NR	560	595	NR	690	243	NR	820	5	NR	950	0	NR
435	132	NR	565	589	NR	695	215	NR	825	4	NR	955	0	NR
440	243	NR	570	581	NR	700	189	NR	830	3	NR	960	0	NR
445	488	NR	575	575	NR	705	165	NR	835	3	NR	965	0	NR
450	879	NR	580	573	NR	710	144	NR	840	3	NR	970	0	NR
455	974	NR	585	570	NR	715	124	NR	845	2	NR	975	0	NR
460	726	NR	590	572	NR	720	108	NR	850	2	NR	980	0	NR
465	627	NR	595	574	NR	725	93	NR	855	2	NR	985	0	NR
470	546	NR	600	576	NR	730	80	NR	860	1	NR	990	0	NR
475	434	NR	605	581	NR	735	69	NR	865	1	NR	995	0	NR
480	395	NR	610	582	NR	740	59	NR	870	1	NR	1000	0	NR
485	403	NR	615	586	NR	745	51	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-13

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 2.09

λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)
360	0	NR	490	419	NR	620	583	NR	750	44	NR	880	1	NR
365	0	NR	495	441	NR	625	580	NR	755	37	NR	885	1	NR
370	0	NR	500	472	NR	630	572	NR	760	32	NR	890	1	NR
375	0	NR	505	501	NR	635	559	NR	765	27	NR	895	0	NR
380	0	NR	510	524	NR	640	543	NR	770	23	NR	900	0	NR
385	0	NR	515	545	NR	645	522	NR	775	20	NR	905	0	NR
390	1	NR	520	559	NR	650	496	NR	780	17	NR	910	0	NR
395	3	NR	525	572	NR	655	468	NR	785	14	NR	915	0	NR
400	4	NR	530	581	NR	660	435	NR	790	12	NR	920	0	NR
405	7	NR	535	590	NR	665	403	NR	795	10	NR	925	0	NR
410	9	NR	540	595	NR	670	368	NR	800	9	NR	930	0	NR
415	14	NR	545	599	NR	675	335	NR	805	8	NR	935	0	NR
420	23	NR	550	599	NR	680	304	NR	810	6	NR	940	0	NR
425	40	NR	555	599	NR	685	271	NR	815	6	NR	945	0	NR
430	72	NR	560	595	NR	690	243	NR	820	5	NR	950	0	NR
435	132	NR	565	589	NR	695	215	NR	825	4	NR	955	0	NR
440	243	NR	570	581	NR	700	189	NR	830	3	NR	960	0	NR
445	488	NR	575	575	NR	705	165	NR	835	3	NR	965	0	NR
450	879	NR	580	573	NR	710	144	NR	840	3	NR	970	0	NR
455	974	NR	585	570	NR	715	124	NR	845	2	NR	975	0	NR
460	726	NR	590	572	NR	720	108	NR	850	2	NR	980	0	NR
465	627	NR	595	574	NR	725	93	NR	855	2	NR	985	0	NR
470	546	NR	600	576	NR	730	80	NR	860	1	NR	990	0	NR
475	434	NR	605	581	NR	735	69	NR	865	1	NR	995	0	NR
480	395	NR	610	582	NR	740	59	NR	870	1	NR	1000	0	NR
485	403	NR	615	586	NR	745	51	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-13

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 4.55


λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	419	NR	620	583	NR	750	44	NR	880	1	NR
365	0	NR	495	441	NR	625	580	NR	755	37	NR	885	1	NR
370	0	NR	500	472	NR	630	572	NR	760	32	NR	890	1	NR
375	0	NR	505	501	NR	635	559	NR	765	27	NR	895	0	NR
380	0	NR	510	524	NR	640	543	NR	770	23	NR	900	0	NR
385	0	NR	515	545	NR	645	522	NR	775	20	NR	905	0	NR
390	1	NR	520	559	NR	650	496	NR	780	17	NR	910	0	NR
395	3	NR	525	572	NR	655	468	NR	785	14	NR	915	0	NR
400	4	NR	530	581	NR	660	435	NR	790	12	NR	920	0	NR
405	7	NR	535	590	NR	665	403	NR	795	10	NR	925	0	NR
410	9	NR	540	595	NR	670	368	NR	800	9	NR	930	0	NR
415	14	NR	545	599	NR	675	335	NR	805	8	NR	935	0	NR
420	23	NR	550	599	NR	680	304	NR	810	6	NR	940	0	NR
425	40	NR	555	599	NR	685	271	NR	815	6	NR	945	0	NR
430	72	NR	560	595	NR	690	243	NR	820	5	NR	950	0	NR
435	132	NR	565	589	NR	695	215	NR	825	4	NR	955	0	NR
440	243	NR	570	581	NR	700	189	NR	830	3	NR	960	0	NR
445	488	NR	575	575	NR	705	165	NR	835	3	NR	965	0	NR
450	879	NR	580	573	NR	710	144	NR	840	3	NR	970	0	NR
455	974	NR	585	570	NR	715	124	NR	845	2	NR	975	0	NR
460	726	NR	590	572	NR	720	108	NR	850	2	NR	980	0	NR
465	627	NR	595	574	NR	725	93	NR	855	2	NR	985	0	NR
470	546	NR	600	576	NR	730	80	NR	860	1	NR	990	0	NR
475	434	NR	605	581	NR	735	69	NR	865	1	NR	995	0	NR
480	395	NR	610	582	NR	740	59	NR	870	1	NR	1000	0	NR
485	403	NR	615	586	NR	745	51	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-13





TM-30-18

Summary

$R_f = 90.8$
 $R_g = 97.4$
 $CIE R_a = 94.0$
 $R_9 = 77.7$







Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 85	CES26 = 98	CES51 = 93	CES76 = 91
CES02 = 61	CES27 = 86	CES52 = 96	CES77 = 89
CES03 = 31	CES28 = 98	CES53 = 93	CES78 = 87
CES04 = 68	CES29 = 90	CES54 = 89	CES79 = 97
CES05 = 48	CES30 = 80	CES55 = 86	CES80 = 94
CES06 = 50	CES31 = 92	CES56 = 89	CES81 = 89
CES07 = 41	CES32 = 97	CES57 = 87	CES82 = 97
CES08 = 40	CES33 = 89	CES58 = 87	CES83 = 96
CES09 = 29	CES34 = 98	CES59 = 96	CES84 = 94
CES10 = 73	CES35 = 98	CES60 = 89	CES85 = 84
CES11 = 56	CES36 = 74	CES61 = 90	CES86 = 90
CES12 = 62	CES37 = 97	CES62 = 78	CES87 = 92
CES13 = 42	CES38 = 75	CES63 = 89	CES88 = 95
CES14 = 74	CES39 = 97	CES64 = 85	CES89 = 90
CES15 = 71	CES40 = 97	CES65 = 87	CES90 = 92
CES16 = 47	CES41 = 91	CES66 = 82	CES91 = 69
CES17 = 48	CES42 = 99	CES67 = 82	CES92 = 81
CES18 = 56	CES43 = 97	CES68 = 86	CES93 = 88
CES19 = 70	CES44 = 99	CES69 = 87	CES94 = 86
CES20 = 65	CES45 = 97	CES70 = 86	CES95 = 83
CES21 = 84	CES46 = 94	CES71 = 77	CES96 = 94
CES22 = 77	CES47 = 90	CES72 = 93	CES97 = 97
CES23 = 91	CES48 = 83	CES73 = 82	CES98 = 94
CES24 = 89	CES49 = 95	CES74 = 89	CES99 = 92
CES25 = 70	CES50 = 94	CES75 = 81	



Color Rendition by Hue-Angle Bin


Measure Comparisons


(END OF REPORT)