

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1216184

Luminaire Tested: 24-ID2-55-CNV-L950-U


Issue Date: 12/5/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P1216184  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2508-510-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/5/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: 24-ID2-55-CNV-L950-U  
Description: 2X4 IN DEPTH TROFFER WITH 2INCH CURVE DROP  
Light Source: 5000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5032.3 lumens  
Efficiency: N/A  
Efficacy: 105.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.2 / 1.31  
Luminous Opening: Rectangular w/ Sides (W: 2' x L: 4' x H: 0.16')  
CIE Type: Direct  
  
Input Watts (W): 47.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P1216184  
CATALOG NUMBER: 24-ID2-55-CNV-L950-U

### Luminous Intensity Polar Plot





TEST NUMBER: P1216184  
 CATALOG NUMBER: 24-ID2-55-CNV-L950-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	110	110	110	106	106	106	101	101	101
1	108	104	99	95	105	101	97	94	97	93	90	93	90	87	89	87	85
2	99	90	84	78	96	88	82	77	85	79	75	81	77	73	78	74	71
3	90	80	71	65	87	78	70	64	75	68	63	72	66	62	69	65	61
4	83	71	62	55	80	69	61	55	67	60	54	64	58	53	62	57	52
5	76	63	54	48	74	62	54	47	60	52	47	58	51	46	56	50	46
6	70	57	48	42	68	56	48	42	54	47	41	52	46	41	51	45	40
7	65	52	43	37	63	51	43	37	49	42	36	48	41	36	46	40	36
8	61	47	39	33	59	47	39	33	45	38	33	44	37	32	43	37	32
9	57	44	35	30	55	43	35	30	42	35	30	40	34	29	39	33	29
10	53	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2535	2535	2535
5°	2533	2511	2516
10°	2512	2479	2485
15°	2479	2438	2444
20°	2432	2385	2391
25°	2377	2321	2329
30°	2318	2251	2254
35°	2247	2167	2173
40°	2169	2079	2082
45°	2089	1990	1986
50°	1997	1886	1887
55°	1908	1784	1766
60°	1809	1666	1653
65°	1699	1537	1519
70°	1568	1385	1391
75°	1411	1226	1249
80°	1194	1061	1144
85°	958	936	1096

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2089 cd/sqm



TEST NUMBER: P1216184  
 CATALOG NUMBER: 24-ID2-55-CNV-L950-U

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	178.0	3.5
10°-20°	505.0	10.0
20°-30°	749.1	14.9
30°-40°	875.3	17.4
40°-50°	874.9	17.4
50°-60°	761.7	15.1
60°-70°	564.6	11.2
70°-80°	331.6	6.6
80°-90°	133.1	2.6
90°-100°	34.8	0.7
100°-110°	11.4	0.2
110°-120°	6.6	0.1
120°-130°	3.6	0.1
130°-140°	1.8	0.0
140°-150°	0.9	0.0
150°-160°	0.1	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1432.1	28.5
0°-40°	2307.3	45.9
0°-60°	3943.8	78.4
0°-90°	4973.2	98.8
90°-120°	52.7	1.0
90°-150°	59.0	1.2
90°-180°	59.0	1.2
0°-180°	5032.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1884	1884	1884	1884	1884	
5°	1882	1877	1873	1871	1876	179
15°	1799	1792	1790	1789	1792	507
25°	1631	1628	1626	1624	1628	752
35°	1406	1403	1398	1397	1397	879
45°	1142	1140	1134	1130	1127	881
55°	860	858	853	849	839	768
65°	580	575	571	562	559	573
75°	312	309	310	312	312	330
85°	90	102	119	133	136	95
90°	37	47	61	72	74	22
95°	31	26	26	31	33	25
105°	21	18	10	3	0	23
115°	14	12	6	1	0	14
125°	9	7	4	1	0	8
135°	5	4	2	1	0	4
145°	3	2	1	1	1	2
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P1216184  
 CATALOG NUMBER: 24-ID2-55-CNV-L950-U

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1884.2	1884.2	1884.2	1884.2	1884.2
2.5°	1890.5	1883.6	1880.8	1878.7	1882.2
5°	1882.2	1876.7	1873.2	1871.1	1876.0
7.5°	1869.8	1863.5	1860.1	1858.7	1862.9
10°	1851.8	1844.2	1841.5	1840.1	1844.2
12.5°	1827.7	1821.5	1818.7	1817.3	1821.5
15°	1798.7	1792.5	1789.7	1789.0	1792.5
17.5°	1764.9	1758.7	1755.2	1755.2	1759.4
20°	1723.5	1719.3	1717.3	1716.6	1718.7
22.5°	1682.1	1675.9	1675.2	1672.4	1677.3
25°	1631.0	1628.3	1625.5	1624.1	1627.6
27.5°	1583.4	1575.8	1572.4	1573.1	1575.1
30°	1526.2	1521.3	1520.0	1516.5	1517.9
32.5°	1466.8	1463.4	1462.0	1457.9	1457.9
35°	1406.1	1402.7	1397.8	1397.1	1397.1
37.5°	1343.3	1339.9	1335.7	1332.3	1333.7
40°	1276.4	1273.0	1268.1	1267.4	1264.7
42.5°	1210.9	1207.4	1201.9	1201.2	1198.4
45°	1141.9	1139.8	1134.3	1130.1	1127.4
47.5°	1072.9	1069.4	1063.2	1059.1	1057.0
50°	999.7	996.3	992.1	988.0	987.3
52.5°	929.4	928.7	922.5	919.0	915.6
55°	859.7	857.6	852.8	849.3	839.0
57.5°	787.2	785.8	783.1	775.5	769.3
60°	718.9	714.8	710.0	701.0	699.6
62.5°	646.5	646.5	638.9	632.0	629.2
65°	579.6	574.7	570.6	562.3	558.9
67.5°	509.9	509.2	501.6	496.8	490.6
70°	442.3	440.2	434.0	432.6	431.2
72.5°	374.6	374.0	372.6	371.2	367.7
75°	311.9	309.1	310.5	312.5	311.9
77.5°	248.4	251.8	253.2	259.4	260.1
80°	189.0	194.6	202.8	212.5	214.6
82.5°	135.2	142.8	158.7	171.1	173.9
85°	90.4	102.1	119.4	133.2	135.9
87.5°	55.9	69.0	87.6	100.7	102.8
90°	36.6	46.9	60.7	71.8	74.5
92.5°	33.8	33.1	40.7	49.0	51.7
95°	31.0	26.2	26.2	31.0	33.1
97.5°	29.0	24.1	16.6	17.2	17.9
100°	26.2	22.1	12.4	7.6	7.6
102.5°	24.1	20.0	11.0	2.8	0.7
105°	21.4	17.9	10.3	2.8	0.0
107.5°	19.3	16.6	9.0	2.1	0.0
110°	17.2	14.5	8.3	2.1	0.0



TEST NUMBER: P1216184  
 CATALOG NUMBER: 24-ID2-55-CNV-L950-U

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	15.9	13.1	7.6	1.4	0.0
115°	13.8	11.7	6.2	1.4	0.0
117.5°	12.4	10.3	5.5	0.7	0.0
120°	11.0	9.0	4.8	0.7	0.0
122.5°	9.7	8.3	4.1	0.7	0.0
125°	9.0	6.9	4.1	0.7	0.0
127.5°	7.6	6.2	3.4	0.0	0.0
130°	6.9	5.5	2.8	0.0	0.0
132.5°	6.2	4.8	2.1	0.7	0.0
135°	4.8	4.1	2.1	0.7	0.0
137.5°	4.1	3.4	1.4	0.7	0.7
140°	3.4	2.8	1.4	0.7	0.7
142.5°	3.4	2.8	1.4	0.7	0.7
145°	2.8	2.1	0.7	0.7	0.7
147.5°	2.1	1.4	0.7	0.7	0.7
150°	1.4	1.4	0.7	0.7	0.7
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1216184  
 CATALOG NUMBER: 24-ID2-55-CNV-L950-U

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.85	15.44	14.23	15.78	16.13	13.87	15.46	14.25	15.80	16.14
	3H	15.52	16.96	15.91	17.31	17.70	15.54	16.99	15.94	17.34	17.73
	4H	16.12	17.47	16.53	17.85	18.25	16.20	17.56	16.61	17.93	18.33
	6H	16.54	17.80	16.97	18.19	18.61	16.74	18.00	17.17	18.39	18.81
	8H	16.66	17.86	17.10	18.28	18.71	16.97	18.17	17.41	18.58	19.01
	12H	16.74	17.90	17.19	18.30	18.76	17.18	18.33	17.62	18.74	19.19
4H	2H	14.42	15.78	14.84	16.15	16.56	14.43	15.79	14.85	16.17	16.57
	3H	16.30	17.44	16.73	17.86	18.29	16.33	17.47	16.76	17.89	18.32
	4H	17.02	18.05	17.47	18.49	18.95	17.11	18.14	17.56	18.58	19.04
	6H	17.56	18.47	18.03	18.93	19.41	17.79	18.69	18.26	19.16	19.64
	8H	17.73	18.58	18.21	19.04	19.54	18.08	18.93	18.56	19.39	19.88
	12H	17.85	18.62	18.35	19.11	19.61	18.36	19.12	18.86	19.62	20.12
8H	4H	17.30	18.15	17.78	18.61	19.11	17.38	18.23	17.86	18.69	19.19
	6H	17.96	18.67	18.47	19.18	19.68	18.19	18.90	18.70	19.41	19.91
	8H	18.20	18.84	18.72	19.36	19.87	18.57	19.21	19.10	19.74	20.25
	12H	18.39	18.96	18.92	19.47	20.06	18.97	19.53	19.49	20.04	20.63
12H	4H	17.33	18.10	17.83	18.60	19.09	17.40	18.17	17.90	18.67	19.16
	6H	18.02	18.66	18.55	19.19	19.70	18.24	18.88	18.77	19.41	19.92
	8H	18.32	18.89	18.85	19.40	19.98	18.69	19.25	19.21	19.77	20.35



Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-13

Test Date: 08/27/2025

Luminaire Tested: 22ID2-55-CFR1-L950-U

Data in this report applies to families of products including 22ID2-55-CFR1-L950-U


**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2506-458-13  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 08/27/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Corelite  
 Catalog Number: **22ID2-55-CFR1-L950-U**  
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 5000K 90CRI

**Spectral Parameters**

CCT (K): 4919  
 CIE u': 0.2096  
 CIE v': 0.4901  
 Duv: 0.0038  
 CIE x: 0.3483  
 CIE y: 0.3619  
 CIE z: 0.2898  
 Peak Wavelength (nm): 453  
 Dominant Wavelength (nm): 570  
 Purity: 13.10873  
 Rf: 90.8  
 Rg: 97.4

CRI (Ra):	94.0		
R1:	94.8	R9:	77.7
R2:	97.7	R10:	93.1
R3:	98.4	R11:	92.0
R4:	90.8	R12:	65.9
R5:	92.2	R13:	95.9
R6:	94.3	R14:	99.0
R7:	94.0	R15:	91.4
R8:	90.0		



**Test Conditions**


Stabilization Time: M  
 Operation Time: 1H 0M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-458-13


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-13

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-13

**Photopic Flux vs. Wavelength**




**Photopic Lumens: NR**

$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)
360	0	NR	490	419	NR	620	583	NR	750	44	NR	880	1	NR
365	0	NR	495	441	NR	625	580	NR	755	37	NR	885	1	NR
370	0	NR	500	472	NR	630	572	NR	760	32	NR	890	1	NR
375	0	NR	505	501	NR	635	559	NR	765	27	NR	895	0	NR
380	0	NR	510	524	NR	640	543	NR	770	23	NR	900	0	NR
385	0	NR	515	545	NR	645	522	NR	775	20	NR	905	0	NR
390	1	NR	520	559	NR	650	496	NR	780	17	NR	910	0	NR
395	3	NR	525	572	NR	655	468	NR	785	14	NR	915	0	NR
400	4	NR	530	581	NR	660	435	NR	790	12	NR	920	0	NR
405	7	NR	535	590	NR	665	403	NR	795	10	NR	925	0	NR
410	9	NR	540	595	NR	670	368	NR	800	9	NR	930	0	NR
415	14	NR	545	599	NR	675	335	NR	805	8	NR	935	0	NR
420	23	NR	550	599	NR	680	304	NR	810	6	NR	940	0	NR
425	40	NR	555	599	NR	685	271	NR	815	6	NR	945	0	NR
430	72	NR	560	595	NR	690	243	NR	820	5	NR	950	0	NR
435	132	NR	565	589	NR	695	215	NR	825	4	NR	955	0	NR
440	243	NR	570	581	NR	700	189	NR	830	3	NR	960	0	NR
445	488	NR	575	575	NR	705	165	NR	835	3	NR	965	0	NR
450	879	NR	580	573	NR	710	144	NR	840	3	NR	970	0	NR
455	974	NR	585	570	NR	715	124	NR	845	2	NR	975	0	NR
460	726	NR	590	572	NR	720	108	NR	850	2	NR	980	0	NR
465	627	NR	595	574	NR	725	93	NR	855	2	NR	985	0	NR
470	546	NR	600	576	NR	730	80	NR	860	1	NR	990	0	NR
475	434	NR	605	581	NR	735	69	NR	865	1	NR	995	0	NR
480	395	NR	610	582	NR	740	59	NR	870	1	NR	1000	0	NR
485	403	NR	615	586	NR	745	51	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-13

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 2.09

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	419	NR	620	583	NR	750	44	NR	880	1	NR
365	0	NR	495	441	NR	625	580	NR	755	37	NR	885	1	NR
370	0	NR	500	472	NR	630	572	NR	760	32	NR	890	1	NR
375	0	NR	505	501	NR	635	559	NR	765	27	NR	895	0	NR
380	0	NR	510	524	NR	640	543	NR	770	23	NR	900	0	NR
385	0	NR	515	545	NR	645	522	NR	775	20	NR	905	0	NR
390	1	NR	520	559	NR	650	496	NR	780	17	NR	910	0	NR
395	3	NR	525	572	NR	655	468	NR	785	14	NR	915	0	NR
400	4	NR	530	581	NR	660	435	NR	790	12	NR	920	0	NR
405	7	NR	535	590	NR	665	403	NR	795	10	NR	925	0	NR
410	9	NR	540	595	NR	670	368	NR	800	9	NR	930	0	NR
415	14	NR	545	599	NR	675	335	NR	805	8	NR	935	0	NR
420	23	NR	550	599	NR	680	304	NR	810	6	NR	940	0	NR
425	40	NR	555	599	NR	685	271	NR	815	6	NR	945	0	NR
430	72	NR	560	595	NR	690	243	NR	820	5	NR	950	0	NR
435	132	NR	565	589	NR	695	215	NR	825	4	NR	955	0	NR
440	243	NR	570	581	NR	700	189	NR	830	3	NR	960	0	NR
445	488	NR	575	575	NR	705	165	NR	835	3	NR	965	0	NR
450	879	NR	580	573	NR	710	144	NR	840	3	NR	970	0	NR
455	974	NR	585	570	NR	715	124	NR	845	2	NR	975	0	NR
460	726	NR	590	572	NR	720	108	NR	850	2	NR	980	0	NR
465	627	NR	595	574	NR	725	93	NR	855	2	NR	985	0	NR
470	546	NR	600	576	NR	730	80	NR	860	1	NR	990	0	NR
475	434	NR	605	581	NR	735	69	NR	865	1	NR	995	0	NR
480	395	NR	610	582	NR	740	59	NR	870	1	NR	1000	0	NR
485	403	NR	615	586	NR	745	51	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-13

Melanopic Flux vs. Wavelength




Melanopic Lumens: NR

M/P: 4.55





λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	419	NR	620	583	NR	750	44	NR	880	1	NR
365	0	NR	495	441	NR	625	580	NR	755	37	NR	885	1	NR
370	0	NR	500	472	NR	630	572	NR	760	32	NR	890	1	NR
375	0	NR	505	501	NR	635	559	NR	765	27	NR	895	0	NR
380	0	NR	510	524	NR	640	543	NR	770	23	NR	900	0	NR
385	0	NR	515	545	NR	645	522	NR	775	20	NR	905	0	NR
390	1	NR	520	559	NR	650	496	NR	780	17	NR	910	0	NR
395	3	NR	525	572	NR	655	468	NR	785	14	NR	915	0	NR
400	4	NR	530	581	NR	660	435	NR	790	12	NR	920	0	NR
405	7	NR	535	590	NR	665	403	NR	795	10	NR	925	0	NR
410	9	NR	540	595	NR	670	368	NR	800	9	NR	930	0	NR
415	14	NR	545	599	NR	675	335	NR	805	8	NR	935	0	NR
420	23	NR	550	599	NR	680	304	NR	810	6	NR	940	0	NR
425	40	NR	555	599	NR	685	271	NR	815	6	NR	945	0	NR
430	72	NR	560	595	NR	690	243	NR	820	5	NR	950	0	NR
435	132	NR	565	589	NR	695	215	NR	825	4	NR	955	0	NR
440	243	NR	570	581	NR	700	189	NR	830	3	NR	960	0	NR
445	488	NR	575	575	NR	705	165	NR	835	3	NR	965	0	NR
450	879	NR	580	573	NR	710	144	NR	840	3	NR	970	0	NR
455	974	NR	585	570	NR	715	124	NR	845	2	NR	975	0	NR
460	726	NR	590	572	NR	720	108	NR	850	2	NR	980	0	NR
465	627	NR	595	574	NR	725	93	NR	855	2	NR	985	0	NR
470	546	NR	600	576	NR	730	80	NR	860	1	NR	990	0	NR
475	434	NR	605	581	NR	735	69	NR	865	1	NR	995	0	NR
480	395	NR	610	582	NR	740	59	NR	870	1	NR	1000	0	NR
485	403	NR	615	586	NR	745	51	NR	875	1	NR			

**Summary**

$R_f = 90.8$   
 $R_g = 97.4$   
 $CIE R_a = 94.0$   
 $R_9 = 77.7$




**Color Vector Graphics**








**Individual Sample Fidelity Index ( $R_{f,i}$ )**



CES01 = 85	CES26 = 98	CES51 = 93	CES76 = 91
CES02 = 61	CES27 = 86	CES52 = 96	CES77 = 89
CES03 = 31	CES28 = 98	CES53 = 93	CES78 = 87
CES04 = 68	CES29 = 90	CES54 = 89	CES79 = 97
CES05 = 48	CES30 = 80	CES55 = 86	CES80 = 94
CES06 = 50	CES31 = 92	CES56 = 89	CES81 = 89
CES07 = 41	CES32 = 97	CES57 = 87	CES82 = 97
CES08 = 40	CES33 = 89	CES58 = 87	CES83 = 96
CES09 = 29	CES34 = 98	CES59 = 96	CES84 = 94
CES10 = 73	CES35 = 98	CES60 = 89	CES85 = 84
CES11 = 56	CES36 = 74	CES61 = 90	CES86 = 90
CES12 = 62	CES37 = 97	CES62 = 78	CES87 = 92
CES13 = 42	CES38 = 75	CES63 = 89	CES88 = 95
CES14 = 74	CES39 = 97	CES64 = 85	CES89 = 90
CES15 = 71	CES40 = 97	CES65 = 87	CES90 = 92
CES16 = 47	CES41 = 91	CES66 = 82	CES91 = 69
CES17 = 48	CES42 = 99	CES67 = 82	CES92 = 81
CES18 = 56	CES43 = 97	CES68 = 86	CES93 = 88
CES19 = 70	CES44 = 99	CES69 = 87	CES94 = 86
CES20 = 65	CES45 = 97	CES70 = 86	CES95 = 83
CES21 = 84	CES46 = 94	CES71 = 77	CES96 = 94
CES22 = 77	CES47 = 90	CES72 = 93	CES97 = 97
CES23 = 91	CES48 = 83	CES73 = 82	CES98 = 94
CES24 = 89	CES49 = 95	CES74 = 89	CES99 = 92
CES25 = 70	CES50 = 94	CES75 = 81	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)