

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1216314

Luminaire Tested: 24-ID2-65-DBD-L835-U

Issue Date: 12/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1216314
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2508-510-11)
Test Lab: INNOVATION CENTER
Issue Date: 12/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 24-ID2-65-DBD-L835-U
Description: 2X4 IN DEPTH TROFFER WITH 2INCH DOUBLE BARREL DROP
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6789.9 lumens
Efficiency: N/A
Efficacy: 121.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.21 / 1.31
Luminous Opening: Rectangular w/ Sides (W: 2' x L: 4' x H: 0.15')
CIE Type: Direct

Input Watts (W): 56.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1216314
CATALOG NUMBER: 24-ID2-65-DBD-L835-U

Luminous Intensity Polar Plot



TEST NUMBER: P1216314

CATALOG NUMBER: 24-ID2-65-DBD-L835-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101
1	108	103	99	95	105	101	97	93	96	93	90	92	90	87	88	86	84
2	98	90	83	77	96	88	82	76	84	79	74	81	76	73	78	74	71
3	90	79	71	65	87	78	70	64	74	68	63	71	66	61	69	64	60
4	82	70	62	55	80	69	61	54	66	59	54	64	58	53	61	56	52
5	76	63	54	47	74	62	53	47	60	52	46	57	51	46	55	50	45
6	70	57	48	41	68	56	47	41	54	46	41	52	45	40	50	44	40
7	65	52	43	37	63	51	42	37	49	42	36	47	41	36	46	40	35
8	61	47	39	33	59	46	38	33	45	38	32	44	37	32	42	36	32
9	57	43	35	30	55	43	35	29	41	34	29	40	34	29	39	33	29
10	53	40	32	27	52	39	32	27	38	31	27	37	31	26	36	31	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3385	3385	3385
5°	3386	3356	3358
10°	3353	3315	3322
15°	3305	3259	3270
20°	3242	3190	3208
25°	3164	3112	3132
30°	3074	3017	3046
35°	2971	2910	2949
40°	2858	2799	2838
45°	2734	2677	2725
50°	2618	2546	2603
55°	2477	2406	2458
60°	2343	2268	2335
65°	2191	2111	2167
70°	2037	1940	2009
75°	1844	1771	1870
80°	1643	1602	1737
85°	1470	1454	1657

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2734 cd/sqm

TEST NUMBER: P1216314
 CATALOG NUMBER: 24-ID2-65-DBD-L835-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	237.7	3.5
10°-20°	674.1	9.9
20°-30°	1000.6	14.7
30°-40°	1170.0	17.2
40°-50°	1170.6	17.2
50°-60°	1021.3	15.0
60°-70°	764.7	11.3
70°-80°	465.9	6.9
80°-90°	196.5	2.9
90°-100°	58.0	0.9
100°-110°	17.9	0.3
110°-120°	6.8	0.1
120°-130°	3.4	0.1
130°-140°	1.6	0.0
140°-150°	0.8	0.0
150°-160°	0.1	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1912.4	28.2
0°-40°	3082.4	45.4
0°-60°	5274.2	77.7
0°-90°	6701.4	98.7
90°-120°	82.7	1.2
90°-150°	88.5	1.3
90°-180°	89.0	1.3
0°-180°	6789.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2516	2516	2516	2516	2516	
5°	2515	2507	2502	2498	2503	239
15°	2397	2391	2389	2390	2395	676
25°	2168	2168	2174	2178	2183	999
35°	1856	1858	1870	1883	1890	1161
45°	1491	1499	1519	1535	1539	1152
55°	1113	1120	1142	1158	1160	997
65°	744	753	776	787	790	737
75°	404	419	442	458	460	430
85°	136	155	180	198	199	135
90°	45	68	88	103	107	29
95°	37	36	51	64	68	29
105°	24	20	11	11	14	26
115°	15	12	6	1	0	15
125°	8	8	4	0	0	8
135°	5	4	1	1	0	4
145°	2	2	1	1	1	1
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1216314

CATALOG NUMBER: 24-ID2-65-DBD-L835-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2516.0	2516.0	2516.0	2516.0	2516.0
2.5°	2525.3	2516.9	2511.3	2508.5	2512.2
5°	2515.0	2506.7	2502.0	2498.3	2502.9
7.5°	2496.4	2488.0	2484.3	2482.4	2486.2
10°	2470.3	2461.9	2460.1	2457.3	2463.8
12.5°	2438.6	2430.2	2428.4	2427.4	2434.0
15°	2396.7	2391.1	2389.2	2390.2	2394.8
17.5°	2351.0	2344.5	2343.6	2345.4	2351.0
20°	2295.1	2291.4	2292.3	2297.0	2301.6
22.5°	2235.5	2231.8	2235.5	2237.4	2244.8
25°	2168.4	2167.5	2174.0	2177.7	2183.3
27.5°	2099.4	2099.4	2103.2	2109.7	2118.1
30°	2021.2	2022.1	2031.4	2037.0	2045.4
32.5°	1942.0	1943.8	1952.2	1961.5	1967.1
35°	1856.2	1858.1	1870.2	1883.3	1889.8
37.5°	1768.6	1773.3	1787.3	1799.4	1804.0
40°	1678.2	1683.8	1699.7	1714.6	1717.4
42.5°	1586.9	1592.5	1611.2	1627.0	1629.8
45°	1490.9	1499.3	1518.9	1534.7	1539.4
47.5°	1398.7	1407.1	1426.6	1443.4	1445.3
50°	1306.4	1312.0	1331.6	1347.4	1354.9
52.5°	1214.2	1219.8	1238.4	1258.0	1257.1
55°	1112.6	1120.1	1142.4	1158.3	1160.1
57.5°	1017.6	1027.8	1051.1	1067.0	1072.5
60°	927.2	935.6	958.9	971.9	980.3
62.5°	833.1	843.3	865.7	880.6	884.3
65°	743.6	752.9	776.2	787.4	790.2
67.5°	651.4	664.4	685.8	699.8	701.7
70°	571.2	580.5	601.0	615.0	615.9
72.5°	484.6	497.6	518.1	534.9	539.5
75°	404.4	419.3	441.7	458.5	460.3
77.5°	328.0	343.8	371.8	388.6	389.5
80°	257.2	274.9	300.1	319.6	319.6
82.5°	191.0	211.5	240.4	258.1	257.2
85°	136.0	154.7	179.8	197.6	199.4
87.5°	84.8	104.4	128.6	143.5	147.2
90°	44.7	68.0	88.5	103.4	107.2
92.5°	41.0	49.4	69.0	82.9	85.7
95°	37.3	36.3	51.3	64.3	68.0
97.5°	33.5	28.0	36.3	47.5	51.3
100°	29.8	25.2	26.1	33.5	36.3
102.5°	27.0	22.4	15.8	21.4	24.2
105°	24.2	19.6	11.2	11.2	14.0
107.5°	21.4	17.7	10.3	4.7	6.5
110°	18.6	15.8	8.4	1.9	0.9

TEST NUMBER: P1216314

CATALOG NUMBER: 24-ID2-65-DBD-L835-U

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	16.8	14.0	7.5	0.9	0.0
115°	14.9	12.1	6.5	0.9	0.0
117.5°	13.0	11.2	5.6	0.0	0.0
120°	11.2	9.3	4.7	0.0	0.0
122.5°	10.3	8.4	3.7	0.0	0.0
125°	8.4	7.5	3.7	0.0	0.0
127.5°	7.5	6.5	2.8	0.0	0.0
130°	6.5	5.6	1.9	0.0	0.0
132.5°	5.6	4.7	1.9	0.0	0.0
135°	4.7	3.7	0.9	0.9	0.0
137.5°	3.7	2.8	0.9	0.9	0.0
140°	2.8	2.8	0.9	0.9	0.0
142.5°	2.8	1.9	0.9	0.9	0.0
145°	1.9	1.9	0.9	0.9	0.9
147.5°	1.9	0.9	0.9	0.9	0.9
150°	0.9	0.9	0.9	0.9	0.9
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1216314

CATALOG NUMBER: 24-ID2-65-DBD-L835-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.67	16.27	15.06	16.61	16.96	15.07	16.67	15.45	17.01	17.36
	3H	16.33	17.77	16.72	18.13	18.52	16.84	18.28	17.23	18.64	19.03
	4H	16.94	18.30	17.36	18.68	19.09	17.56	18.92	17.98	19.29	19.70
	6H	17.39	18.66	17.83	19.05	19.47	18.17	19.44	18.60	19.83	20.25
	8H	17.54	18.75	17.99	19.17	19.60	18.42	19.63	18.87	20.05	20.48
	12H	17.65	18.81	18.10	19.22	19.68	18.65	19.81	19.10	20.22	20.68
4H	2H	15.30	16.67	15.72	17.04	17.45	15.62	16.98	16.04	17.36	17.77
	3H	17.18	18.32	17.61	18.75	19.18	17.61	18.76	18.04	19.18	19.61
	4H	17.92	18.96	18.37	19.40	19.86	18.47	19.51	18.92	19.95	20.42
	6H	18.50	19.41	18.98	19.88	20.36	19.24	20.15	19.72	20.62	21.10
	8H	18.70	19.56	19.18	20.02	20.52	19.56	20.42	20.04	20.88	21.38
	12H	18.86	19.63	19.36	20.13	20.63	19.86	20.63	20.36	21.13	21.63
8H	4H	18.26	19.12	18.74	19.59	20.08	18.76	19.61	19.24	20.08	20.57
	6H	18.98	19.70	19.50	20.21	20.71	19.67	20.38	20.18	20.89	21.40
	8H	19.27	19.91	19.79	20.44	20.95	20.09	20.73	20.62	21.26	21.78
	12H	19.51	20.08	20.04	20.60	21.18	20.51	21.08	21.04	21.60	22.18
12H	4H	18.32	19.09	18.82	19.59	20.09	18.78	19.55	19.28	20.05	20.55
	6H	19.07	19.72	19.60	20.25	20.76	19.72	20.37	20.25	20.90	21.41
	8H	19.42	20.00	19.95	20.51	21.10	20.22	20.79	20.74	21.30	21.89

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-1

Test Date: 07/23/2025

Luminaire Tested: 22ID2-55-CFR1-L835-U

Data in this report applies to families of products including 22ID2-55-CFR1-L835-U

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-1
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L835-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 3500K 80CRI

Spectral Parameters

CCT (K): 3440
 CIE u' : 0.2370
 CIE v' : 0.5132
 Duv: 0.0005
 CIE x: 0.4093
 CIE y: 0.3940
 CIE z: 0.1967
 Peak Wavelength (nm): 599
 Dominant Wavelength (nm): 580
 Purity: 41.09375
 Rf: 84.9
 Rg: 94.6

CRI (Ra): 84.2
 R1: 82.8
 R2: 91.7
 R3: 96.7
 R4: 81.9
 R5: 82.6
 R6: 88.8
 R7: 85.0
 R8: 63.7
 R9: 13.6
 R10: 80.1
 R11: 81.1
 R12: 65.8
 R13: 85.2
 R14: 98.7
 R15: 76.2



Test Conditions

Stabilization Time: 36M
 Operation Time: 1H 36M
 Sphere Temperature (°C): 24.0

REPORT NUMBER: SP1-2506-458-1

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-1

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	295	NR	620	910	NR	750	30	NR	880	1	NR
365	0	NR	495	335	NR	625	862	NR	755	25	NR	885	1	NR
370	0	NR	500	390	NR	630	809	NR	760	21	NR	890	1	NR
375	0	NR	505	445	NR	635	752	NR	765	18	NR	895	0	NR
380	0	NR	510	490	NR	640	694	NR	770	16	NR	900	0	NR
385	0	NR	515	532	NR	645	630	NR	775	13	NR	905	0	NR
390	0	NR	520	563	NR	650	571	NR	780	12	NR	910	0	NR
395	2	NR	525	588	NR	655	512	NR	785	10	NR	915	0	NR
400	3	NR	530	609	NR	660	453	NR	790	8	NR	920	0	NR
405	5	NR	535	631	NR	665	401	NR	795	7	NR	925	0	NR
410	8	NR	540	654	NR	670	351	NR	800	6	NR	930	0	NR
415	13	NR	545	677	NR	675	306	NR	805	5	NR	935	0	NR
420	23	NR	550	702	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	734	NR	685	230	NR	815	4	NR	945	0	NR
430	70	NR	560	767	NR	690	199	NR	820	4	NR	950	0	NR
435	126	NR	565	802	NR	695	171	NR	825	3	NR	955	0	NR
440	221	NR	570	838	NR	700	146	NR	830	3	NR	960	0	NR
445	418	NR	575	875	NR	705	125	NR	835	2	NR	965	0	NR
450	729	NR	580	913	NR	710	107	NR	840	2	NR	970	0	NR
455	816	NR	585	946	NR	715	90	NR	845	2	NR	975	0	NR
460	578	NR	590	976	NR	720	77	NR	850	1	NR	980	0	NR
465	458	NR	595	992	NR	725	66	NR	855	1	NR	985	0	NR
470	390	NR	600	999	NR	730	56	NR	860	1	NR	990	0	NR
475	299	NR	605	995	NR	735	47	NR	865	1	NR	995	0	NR
480	260	NR	610	975	NR	740	40	NR	870	1	NR	1000	0	NR
485	271	NR	615	948	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-1

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.53

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	295	NR	620	910	NR	750	30	NR	880	1	NR
365	0	NR	495	335	NR	625	862	NR	755	25	NR	885	1	NR
370	0	NR	500	390	NR	630	809	NR	760	21	NR	890	1	NR
375	0	NR	505	445	NR	635	752	NR	765	18	NR	895	0	NR
380	0	NR	510	490	NR	640	694	NR	770	16	NR	900	0	NR
385	0	NR	515	532	NR	645	630	NR	775	13	NR	905	0	NR
390	0	NR	520	563	NR	650	571	NR	780	12	NR	910	0	NR
395	2	NR	525	588	NR	655	512	NR	785	10	NR	915	0	NR
400	3	NR	530	609	NR	660	453	NR	790	8	NR	920	0	NR
405	5	NR	535	631	NR	665	401	NR	795	7	NR	925	0	NR
410	8	NR	540	654	NR	670	351	NR	800	6	NR	930	0	NR
415	13	NR	545	677	NR	675	306	NR	805	5	NR	935	0	NR
420	23	NR	550	702	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	734	NR	685	230	NR	815	4	NR	945	0	NR
430	70	NR	560	767	NR	690	199	NR	820	4	NR	950	0	NR
435	126	NR	565	802	NR	695	171	NR	825	3	NR	955	0	NR
440	221	NR	570	838	NR	700	146	NR	830	3	NR	960	0	NR
445	418	NR	575	875	NR	705	125	NR	835	2	NR	965	0	NR
450	729	NR	580	913	NR	710	107	NR	840	2	NR	970	0	NR
455	816	NR	585	946	NR	715	90	NR	845	2	NR	975	0	NR
460	578	NR	590	976	NR	720	77	NR	850	1	NR	980	0	NR
465	458	NR	595	992	NR	725	66	NR	855	1	NR	985	0	NR
470	390	NR	600	999	NR	730	56	NR	860	1	NR	990	0	NR
475	299	NR	605	995	NR	735	47	NR	865	1	NR	995	0	NR
480	260	NR	610	975	NR	740	40	NR	870	1	NR	1000	0	NR
485	271	NR	615	948	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.07

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	295	NR	620	910	NR	750	30	NR	880	1	NR
365	0	NR	495	335	NR	625	862	NR	755	25	NR	885	1	NR
370	0	NR	500	390	NR	630	809	NR	760	21	NR	890	1	NR
375	0	NR	505	445	NR	635	752	NR	765	18	NR	895	0	NR
380	0	NR	510	490	NR	640	694	NR	770	16	NR	900	0	NR
385	0	NR	515	532	NR	645	630	NR	775	13	NR	905	0	NR
390	0	NR	520	563	NR	650	571	NR	780	12	NR	910	0	NR
395	2	NR	525	588	NR	655	512	NR	785	10	NR	915	0	NR
400	3	NR	530	609	NR	660	453	NR	790	8	NR	920	0	NR
405	5	NR	535	631	NR	665	401	NR	795	7	NR	925	0	NR
410	8	NR	540	654	NR	670	351	NR	800	6	NR	930	0	NR
415	13	NR	545	677	NR	675	306	NR	805	5	NR	935	0	NR
420	23	NR	550	702	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	734	NR	685	230	NR	815	4	NR	945	0	NR
430	70	NR	560	767	NR	690	199	NR	820	4	NR	950	0	NR
435	126	NR	565	802	NR	695	171	NR	825	3	NR	955	0	NR
440	221	NR	570	838	NR	700	146	NR	830	3	NR	960	0	NR
445	418	NR	575	875	NR	705	125	NR	835	2	NR	965	0	NR
450	729	NR	580	913	NR	710	107	NR	840	2	NR	970	0	NR
455	816	NR	585	946	NR	715	90	NR	845	2	NR	975	0	NR
460	578	NR	590	976	NR	720	77	NR	850	1	NR	980	0	NR
465	458	NR	595	992	NR	725	66	NR	855	1	NR	985	0	NR
470	390	NR	600	999	NR	730	56	NR	860	1	NR	990	0	NR
475	299	NR	605	995	NR	735	47	NR	865	1	NR	995	0	NR
480	260	NR	610	975	NR	740	40	NR	870	1	NR	1000	0	NR
485	271	NR	615	948	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-1

TM-30-18

Summary

$R_f = 84.9$
 $R_g = 94.6$
 $\text{CIE } R_a = 84.2$
 $R_9 = 13.6$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 87	CES51 = 92	CES76 = 81
CES02 = 62	CES27 = 91	CES52 = 93	CES77 = 85
CES03 = 31	CES28 = 94	CES53 = 90	CES78 = 80
CES04 = 70	CES29 = 92	CES54 = 89	CES79 = 92
CES05 = 49	CES30 = 89	CES55 = 86	CES80 = 90
CES06 = 51	CES31 = 94	CES56 = 85	CES81 = 77
CES07 = 41	CES32 = 86	CES57 = 83	CES82 = 96
CES08 = 40	CES33 = 97	CES58 = 84	CES83 = 96
CES09 = 29	CES34 = 91	CES59 = 91	CES84 = 91
CES10 = 75	CES35 = 95	CES60 = 89	CES85 = 76
CES11 = 58	CES36 = 79	CES61 = 87	CES86 = 73
CES12 = 64	CES37 = 95	CES62 = 81	CES87 = 85
CES13 = 43	CES38 = 84	CES63 = 85	CES88 = 89
CES14 = 74	CES39 = 98	CES64 = 78	CES89 = 78
CES15 = 71	CES40 = 97	CES65 = 78	CES90 = 90
CES16 = 47	CES41 = 95	CES66 = 75	CES91 = 71
CES17 = 50	CES42 = 96	CES67 = 74	CES92 = 65
CES18 = 56	CES43 = 92	CES68 = 79	CES93 = 79
CES19 = 72	CES44 = 99	CES69 = 83	CES94 = 64
CES20 = 66	CES45 = 95	CES70 = 77	CES95 = 74
CES21 = 86	CES46 = 91	CES71 = 71	CES96 = 85
CES22 = 78	CES47 = 94	CES72 = 90	CES97 = 90
CES23 = 92	CES48 = 83	CES73 = 72	CES98 = 86
CES24 = 90	CES49 = 92	CES74 = 90	CES99 = 79
CES25 = 72	CES50 = 93	CES75 = 75	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)