

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1216266

Luminaire Tested: 24-ID2-35-DBD-L835-U

Issue Date: 12/5/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P1216266  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2508-510-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/5/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: 24-ID2-35-DBD-L835-U  
Description: 2X4 IN DEPTH TROFFER WITH 2INCH DOUBLE BARREL DROP  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3724.1 lumens  
Efficiency: N/A  
Efficacy: 122.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.21 / 1.31  
Luminous Opening: Rectangular w/ Sides (W: 2' x L: 4' x H: 0.15')  
CIE Type: Direct  
  
Input Watts (W): 30.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P1216266  
CATALOG NUMBER: 24-ID2-35-DBD-L835-U

### Luminous Intensity Polar Plot





TEST NUMBER: P1216266  
 CATALOG NUMBER: 24-ID2-35-DBD-L835-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101	99
1	108	103	99	95	105	101	97	93	96	93	90	92	90	87	88	86	84	82
2	98	90	83	77	96	88	82	76	84	79	74	81	76	73	78	74	71	68
3	90	79	71	65	87	78	70	64	74	68	63	71	66	61	69	64	60	58
4	82	70	62	55	80	69	61	54	66	59	54	64	58	53	61	56	52	50
5	76	63	54	47	74	62	53	47	60	52	46	57	51	46	55	50	45	43
6	70	57	48	41	68	56	47	41	54	46	41	52	45	40	50	44	40	38
7	65	52	43	37	63	51	42	37	49	42	36	47	41	36	46	40	35	33
8	61	47	39	33	59	46	38	33	45	38	32	44	37	32	42	36	32	30
9	57	43	35	30	55	43	35	29	41	34	29	40	34	29	39	33	29	27
10	53	40	32	27	52	39	32	27	38	31	27	37	31	26	36	31	26	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1857	1857	1857
5°	1857	1841	1842
10°	1839	1818	1822
15°	1813	1787	1794
20°	1778	1750	1760
25°	1735	1707	1718
30°	1686	1655	1671
35°	1629	1596	1618
40°	1567	1535	1556
45°	1500	1468	1494
50°	1436	1396	1428
55°	1359	1320	1348
60°	1285	1244	1281
65°	1202	1158	1189
70°	1117	1064	1102
75°	1011	971	1026
80°	902	879	953
85°	806	797	909

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1500 cd/sqm



TEST NUMBER: P1216266  
 CATALOG NUMBER: 24-ID2-35-DBD-L835-U

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	130.4	3.5
10°-20°	369.7	9.9
20°-30°	548.8	14.7
30°-40°	641.7	17.2
40°-50°	642.1	17.2
50°-60°	560.1	15.0
60°-70°	419.4	11.3
70°-80°	255.5	6.9
80°-90°	107.8	2.9
90°-100°	31.8	0.9
100°-110°	9.8	0.3
110°-120°	3.7	0.1
120°-130°	1.9	0.1
130°-140°	0.9	0.0
140°-150°	0.4	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1048.9	28.2
0°-40°	1690.6	45.4
0°-60°	2892.8	77.7
0°-90°	3675.6	98.7
90°-120°	45.4	1.2
90°-150°	48.5	1.3
90°-180°	49.0	1.3
0°-180°	3724.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1380	1380	1380	1380	1380	
5°	1379	1375	1372	1370	1373	131
15°	1314	1312	1310	1311	1314	371
25°	1189	1189	1192	1194	1198	548
35°	1018	1019	1026	1033	1036	637
45°	818	822	833	842	844	632
55°	610	614	627	635	636	547
65°	408	413	426	432	433	404
75°	222	230	242	252	252	236
85°	75	85	99	108	109	74
90°	24	37	49	57	59	16
95°	20	20	28	35	37	16
105°	13	11	6	6	8	14
115°	8	7	4	0	0	8
125°	5	4	2	0	0	4
135°	3	2	0	0	0	2
145°	1	1	0	0	0	1
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P1216266  
 CATALOG NUMBER: 24-ID2-35-DBD-L835-U

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1380.0	1380.0	1380.0	1380.0	1380.0
2.5°	1385.1	1380.5	1377.4	1375.9	1377.9
5°	1379.4	1374.8	1372.3	1370.2	1372.8
7.5°	1369.2	1364.6	1362.6	1361.6	1363.6
10°	1354.9	1350.3	1349.3	1347.8	1351.3
12.5°	1337.5	1332.9	1331.9	1331.4	1335.0
15°	1314.5	1311.5	1310.4	1311.0	1313.5
17.5°	1289.5	1285.9	1285.4	1286.4	1289.5
20°	1258.8	1256.8	1257.3	1259.9	1262.4
22.5°	1226.1	1224.1	1226.1	1227.1	1231.2
25°	1189.3	1188.8	1192.4	1194.4	1197.5
27.5°	1151.5	1151.5	1153.5	1157.1	1161.7
30°	1108.6	1109.1	1114.2	1117.3	1121.9
32.5°	1065.1	1066.1	1070.7	1075.9	1078.9
35°	1018.1	1019.1	1025.8	1032.9	1036.5
37.5°	970.1	972.6	980.3	986.9	989.5
40°	920.5	923.6	932.2	940.4	941.9
42.5°	870.4	873.5	883.7	892.4	893.9
45°	817.8	822.4	833.1	841.8	844.3
47.5°	767.2	771.8	782.5	791.7	792.7
50°	716.6	719.6	730.4	739.0	743.1
52.5°	666.0	669.0	679.2	690.0	689.5
55°	610.2	614.3	626.6	635.3	636.3
57.5°	558.1	563.7	576.5	585.2	588.3
60°	508.5	513.1	525.9	533.1	537.7
62.5°	456.9	462.5	474.8	483.0	485.0
65°	407.9	413.0	425.7	431.9	433.4
67.5°	357.3	364.4	376.2	383.8	384.9
70°	313.3	318.4	329.7	337.3	337.8
72.5°	265.8	272.9	284.2	293.4	295.9
75°	221.8	230.0	242.3	251.5	252.5
77.5°	179.9	188.6	203.9	213.1	213.6
80°	141.1	150.8	164.6	175.3	175.3
82.5°	104.8	116.0	131.9	141.6	141.1
85°	74.6	84.8	98.6	108.4	109.4
87.5°	46.5	57.2	70.5	78.7	80.8
90°	24.5	37.3	48.6	56.7	58.8
92.5°	22.5	27.1	37.8	45.5	47.0
95°	20.4	19.9	28.1	35.3	37.3
97.5°	18.4	15.3	19.9	26.1	28.1
100°	16.4	13.8	14.3	18.4	19.9
102.5°	14.8	12.3	8.7	11.8	13.3
105°	13.3	10.7	6.1	6.1	7.7
107.5°	11.8	9.7	5.6	2.6	3.6
110°	10.2	8.7	4.6	1.0	0.5



TEST NUMBER: P1216266  
 CATALOG NUMBER: 24-ID2-35-DBD-L835-U

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	9.2	7.7	4.1	0.5	0.0
115°	8.2	6.6	3.6	0.5	0.0
117.5°	7.2	6.1	3.1	0.0	0.0
120°	6.1	5.1	2.6	0.0	0.0
122.5°	5.6	4.6	2.0	0.0	0.0
125°	4.6	4.1	2.0	0.0	0.0
127.5°	4.1	3.6	1.5	0.0	0.0
130°	3.6	3.1	1.0	0.0	0.0
132.5°	3.1	2.6	1.0	0.0	0.0
135°	2.6	2.0	0.5	0.5	0.0
137.5°	2.0	1.5	0.5	0.5	0.0
140°	1.5	1.5	0.5	0.5	0.0
142.5°	1.5	1.0	0.5	0.5	0.0
145°	1.0	1.0	0.5	0.5	0.5
147.5°	1.0	0.5	0.5	0.5	0.5
150°	0.5	0.5	0.5	0.5	0.5
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1216266  
 CATALOG NUMBER: 24-ID2-35-DBD-L835-U

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.59	14.18	12.97	14.53	14.87	12.98	14.58	13.37	14.92	15.27
	3H	14.24	15.69	14.64	16.04	16.43	14.75	16.20	15.15	16.55	16.94
	4H	14.85	16.22	15.27	16.59	17.00	15.47	16.83	15.89	17.21	17.62
	6H	15.31	16.57	15.74	16.96	17.39	16.08	17.35	16.52	17.74	18.16
	8H	15.46	16.67	15.90	17.08	17.51	16.34	17.55	16.78	17.96	18.39
	12H	15.57	16.73	16.02	17.14	17.60	16.56	17.72	17.01	18.13	18.59
4H	2H	13.22	14.58	13.64	14.96	15.36	13.53	14.90	13.95	15.27	15.68
	3H	15.09	16.24	15.52	16.66	17.09	15.52	16.67	15.96	17.10	17.53
	4H	15.83	16.87	16.28	17.31	17.78	16.39	17.43	16.84	17.86	18.33
	6H	16.41	17.33	16.89	17.79	18.28	17.15	18.07	17.63	18.53	19.02
	8H	16.62	17.47	17.10	17.94	18.43	17.47	18.33	17.96	18.80	19.29
	12H	16.77	17.55	17.28	18.04	18.54	17.78	18.55	18.28	19.05	19.54
8H	4H	16.18	17.03	16.66	17.50	17.99	16.67	17.52	17.15	17.99	18.49
	6H	16.90	17.61	17.41	18.12	18.63	17.58	18.30	18.09	18.81	19.31
	8H	17.18	17.82	17.71	18.35	18.87	18.00	18.65	18.53	19.18	19.69
	12H	17.42	18.00	17.95	18.51	19.10	18.42	19.00	18.95	19.51	20.10
12H	4H	16.23	17.00	16.73	17.50	18.00	16.70	17.47	17.20	17.97	18.47
	6H	16.99	17.63	17.51	18.16	18.68	17.64	18.28	18.17	18.81	19.33
	8H	17.34	17.91	17.86	18.42	19.01	18.13	18.70	18.66	19.21	19.80



Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-1

Test Date: 07/23/2025

Luminaire Tested: 22ID2-55-CFR1-L835-U

Data in this report applies to families of products including 22ID2-55-CFR1-L835-U


**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2506-458-1  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 08/27/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Corelite  
 Catalog Number: **22ID2-55-CFR1-L835-U**  
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 3500K 80CRI

**Spectral Parameters**

CCT (K): 3440  
 CIE u': 0.2370  
 CIE v': 0.5132  
 Duv: 0.0005  
 CIE x: 0.4093  
 CIE y: 0.3940  
 CIE z: 0.1967  
 Peak Wavelength (nm): 599  
 Dominant Wavelength (nm): 580  
 Purity: 41.09375  
 Rf: 84.9  
 Rg: 94.6

CRI (Ra):	84.2		
R1:	82.8	R9:	13.6
R2:	91.7	R10:	80.1
R3:	96.7	R11:	81.1
R4:	81.9	R12:	65.8
R5:	82.6	R13:	85.2
R6:	88.8	R14:	98.7
R7:	85.0	R15:	76.2
R8:	63.7		



**Test Conditions**


Stabilization Time: 36M  
 Operation Time: 1H 36M  
 Sphere Temperature (°C): 24.0

REPORT NUMBER: SP1-2506-458-1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-1

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-1

**Photopic Flux vs. Wavelength**




**Photopic Lumens: NR**

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	295	NR	620	910	NR	750	30	NR	880	1	NR
365	0	NR	495	335	NR	625	862	NR	755	25	NR	885	1	NR
370	0	NR	500	390	NR	630	809	NR	760	21	NR	890	1	NR
375	0	NR	505	445	NR	635	752	NR	765	18	NR	895	0	NR
380	0	NR	510	490	NR	640	694	NR	770	16	NR	900	0	NR
385	0	NR	515	532	NR	645	630	NR	775	13	NR	905	0	NR
390	0	NR	520	563	NR	650	571	NR	780	12	NR	910	0	NR
395	2	NR	525	588	NR	655	512	NR	785	10	NR	915	0	NR
400	3	NR	530	609	NR	660	453	NR	790	8	NR	920	0	NR
405	5	NR	535	631	NR	665	401	NR	795	7	NR	925	0	NR
410	8	NR	540	654	NR	670	351	NR	800	6	NR	930	0	NR
415	13	NR	545	677	NR	675	306	NR	805	5	NR	935	0	NR
420	23	NR	550	702	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	734	NR	685	230	NR	815	4	NR	945	0	NR
430	70	NR	560	767	NR	690	199	NR	820	4	NR	950	0	NR
435	126	NR	565	802	NR	695	171	NR	825	3	NR	955	0	NR
440	221	NR	570	838	NR	700	146	NR	830	3	NR	960	0	NR
445	418	NR	575	875	NR	705	125	NR	835	2	NR	965	0	NR
450	729	NR	580	913	NR	710	107	NR	840	2	NR	970	0	NR
455	816	NR	585	946	NR	715	90	NR	845	2	NR	975	0	NR
460	578	NR	590	976	NR	720	77	NR	850	1	NR	980	0	NR
465	458	NR	595	992	NR	725	66	NR	855	1	NR	985	0	NR
470	390	NR	600	999	NR	730	56	NR	860	1	NR	990	0	NR
475	299	NR	605	995	NR	735	47	NR	865	1	NR	995	0	NR
480	260	NR	610	975	NR	740	40	NR	870	1	NR	1000	0	NR
485	271	NR	615	948	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-1

**Scotopic Flux vs. Wavelength**




**Scotopic Lumens: NR**

**S/P: 1.53**

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	295	NR	620	910	NR	750	30	NR	880	1	NR
365	0	NR	495	335	NR	625	862	NR	755	25	NR	885	1	NR
370	0	NR	500	390	NR	630	809	NR	760	21	NR	890	1	NR
375	0	NR	505	445	NR	635	752	NR	765	18	NR	895	0	NR
380	0	NR	510	490	NR	640	694	NR	770	16	NR	900	0	NR
385	0	NR	515	532	NR	645	630	NR	775	13	NR	905	0	NR
390	0	NR	520	563	NR	650	571	NR	780	12	NR	910	0	NR
395	2	NR	525	588	NR	655	512	NR	785	10	NR	915	0	NR
400	3	NR	530	609	NR	660	453	NR	790	8	NR	920	0	NR
405	5	NR	535	631	NR	665	401	NR	795	7	NR	925	0	NR
410	8	NR	540	654	NR	670	351	NR	800	6	NR	930	0	NR
415	13	NR	545	677	NR	675	306	NR	805	5	NR	935	0	NR
420	23	NR	550	702	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	734	NR	685	230	NR	815	4	NR	945	0	NR
430	70	NR	560	767	NR	690	199	NR	820	4	NR	950	0	NR
435	126	NR	565	802	NR	695	171	NR	825	3	NR	955	0	NR
440	221	NR	570	838	NR	700	146	NR	830	3	NR	960	0	NR
445	418	NR	575	875	NR	705	125	NR	835	2	NR	965	0	NR
450	729	NR	580	913	NR	710	107	NR	840	2	NR	970	0	NR
455	816	NR	585	946	NR	715	90	NR	845	2	NR	975	0	NR
460	578	NR	590	976	NR	720	77	NR	850	1	NR	980	0	NR
465	458	NR	595	992	NR	725	66	NR	855	1	NR	985	0	NR
470	390	NR	600	999	NR	730	56	NR	860	1	NR	990	0	NR
475	299	NR	605	995	NR	735	47	NR	865	1	NR	995	0	NR
480	260	NR	610	975	NR	740	40	NR	870	1	NR	1000	0	NR
485	271	NR	615	948	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-1

**Melanopic Flux vs. Wavelength**




**Melanopic Lumens: NR**

**M/P: 3.07**





λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	295	NR	620	910	NR	750	30	NR	880	1	NR
365	0	NR	495	335	NR	625	862	NR	755	25	NR	885	1	NR
370	0	NR	500	390	NR	630	809	NR	760	21	NR	890	1	NR
375	0	NR	505	445	NR	635	752	NR	765	18	NR	895	0	NR
380	0	NR	510	490	NR	640	694	NR	770	16	NR	900	0	NR
385	0	NR	515	532	NR	645	630	NR	775	13	NR	905	0	NR
390	0	NR	520	563	NR	650	571	NR	780	12	NR	910	0	NR
395	2	NR	525	588	NR	655	512	NR	785	10	NR	915	0	NR
400	3	NR	530	609	NR	660	453	NR	790	8	NR	920	0	NR
405	5	NR	535	631	NR	665	401	NR	795	7	NR	925	0	NR
410	8	NR	540	654	NR	670	351	NR	800	6	NR	930	0	NR
415	13	NR	545	677	NR	675	306	NR	805	5	NR	935	0	NR
420	23	NR	550	702	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	734	NR	685	230	NR	815	4	NR	945	0	NR
430	70	NR	560	767	NR	690	199	NR	820	4	NR	950	0	NR
435	126	NR	565	802	NR	695	171	NR	825	3	NR	955	0	NR
440	221	NR	570	838	NR	700	146	NR	830	3	NR	960	0	NR
445	418	NR	575	875	NR	705	125	NR	835	2	NR	965	0	NR
450	729	NR	580	913	NR	710	107	NR	840	2	NR	970	0	NR
455	816	NR	585	946	NR	715	90	NR	845	2	NR	975	0	NR
460	578	NR	590	976	NR	720	77	NR	850	1	NR	980	0	NR
465	458	NR	595	992	NR	725	66	NR	855	1	NR	985	0	NR
470	390	NR	600	999	NR	730	56	NR	860	1	NR	990	0	NR
475	299	NR	605	995	NR	735	47	NR	865	1	NR	995	0	NR
480	260	NR	610	975	NR	740	40	NR	870	1	NR	1000	0	NR
485	271	NR	615	948	NR	745	34	NR	875	1	NR			

**Summary**

$R_f = 84.9$   
 $R_g = 94.6$   
 CIE  $R_a = 84.2$   
 $R_9 = 13.6$




**Color Vector Graphics**








**Individual Sample Fidelity Index ( $R_{f,i}$ )**



CES01 = 86	CES26 = 87	CES51 = 92	CES76 = 81
CES02 = 62	CES27 = 91	CES52 = 93	CES77 = 85
CES03 = 31	CES28 = 94	CES53 = 90	CES78 = 80
CES04 = 70	CES29 = 92	CES54 = 89	CES79 = 92
CES05 = 49	CES30 = 89	CES55 = 86	CES80 = 90
CES06 = 51	CES31 = 94	CES56 = 85	CES81 = 77
CES07 = 41	CES32 = 86	CES57 = 83	CES82 = 96
CES08 = 40	CES33 = 97	CES58 = 84	CES83 = 96
CES09 = 29	CES34 = 91	CES59 = 91	CES84 = 91
CES10 = 75	CES35 = 95	CES60 = 89	CES85 = 76
CES11 = 58	CES36 = 79	CES61 = 87	CES86 = 73
CES12 = 64	CES37 = 95	CES62 = 81	CES87 = 85
CES13 = 43	CES38 = 84	CES63 = 85	CES88 = 89
CES14 = 74	CES39 = 98	CES64 = 78	CES89 = 78
CES15 = 71	CES40 = 97	CES65 = 78	CES90 = 90
CES16 = 47	CES41 = 95	CES66 = 75	CES91 = 71
CES17 = 50	CES42 = 96	CES67 = 74	CES92 = 65
CES18 = 56	CES43 = 92	CES68 = 79	CES93 = 79
CES19 = 72	CES44 = 99	CES69 = 83	CES94 = 64
CES20 = 66	CES45 = 95	CES70 = 77	CES95 = 74
CES21 = 86	CES46 = 91	CES71 = 71	CES96 = 85
CES22 = 78	CES47 = 94	CES72 = 90	CES97 = 90
CES23 = 92	CES48 = 83	CES73 = 72	CES98 = 86
CES24 = 90	CES49 = 92	CES74 = 90	CES99 = 79
CES25 = 72	CES50 = 93	CES75 = 75	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)