

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1215913

Luminaire Tested: 24-ID2-40-CFD2-L830-U

Issue Date: 12/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1215913
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2506-458-28)
Test Lab: INNOVATION CENTER
Issue Date: 12/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 24-ID2-40-CFD2-L830-U
Description: 2X4 IN DEPTH TROFFER WITH 2INCH CUBE DROP LENS
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4079.2 lumens
Efficiency: N/A
Efficacy: 117.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.32
Luminous Opening: Rectangular w/ Sides (W: 2' x L: 4' x H: 0.16')
CIE Type: Direct

Input Watts (W): 34.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1215913
CATALOG NUMBER: 24-ID2-40-CFD2-L830-U

Luminous Intensity Polar Plot



TEST NUMBER: P1215913

CATALOG NUMBER: 24-ID2-40-CFD2-L830-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	108	103	99	95	106	101	97	93		97	94	90			93	90	88			83
2	99	90	83	77	96	88	82	76		85	79	75			81	77	73			69
3	90	79	71	64	87	78	70	64		75	68	63			72	66	61			58
4	82	70	61	55	80	69	61	54		66	59	53			64	58	53			50
5	76	63	54	47	74	62	53	47		60	52	46			58	51	46			43
6	70	57	48	41	68	56	47	41		54	46	41			52	45	40			38
7	65	51	43	36	63	51	42	36		49	42	36			48	41	36			34
8	61	47	38	33	59	46	38	32		45	38	32			44	37	32			30
9	57	43	35	29	55	43	35	29		41	34	29			40	34	29			27
10	53	40	32	27	52	39	32	27		38	31	26			37	31	26			24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2023	2023	2023
5°	2022	2004	2008
10°	2004	1980	1987
15°	1979	1950	1956
20°	1944	1909	1915
25°	1902	1861	1864
30°	1850	1804	1807
35°	1795	1742	1748
40°	1734	1677	1680
45°	1668	1609	1621
50°	1599	1541	1551
55°	1526	1467	1489
60°	1451	1394	1422
65°	1382	1313	1357
70°	1285	1230	1276
75°	1177	1111	1188
80°	1040	990	1082
85°	909	865	978

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1668 cd/sqm

TEST NUMBER: P1215913
 CATALOG NUMBER: 24-ID2-40-CFD2-L830-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.1	3.5
10°-20°	403.7	9.9
20°-30°	599.9	14.7
30°-40°	702.8	17.2
40°-50°	707.4	17.3
50°-60°	627.0	15.4
60°-70°	482.4	11.8
70°-80°	298.3	7.3
80°-90°	115.6	2.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1145.7	28.1
0°-40°	1848.5	45.3
0°-60°	3182.9	78.0
0°-90°	4079.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4079.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1504	1504	1504	1504	1504	
5°	1502	1498	1495	1494	1497	143
15°	1436	1432	1432	1431	1434	405
25°	1305	1303	1303	1302	1302	601
35°	1123	1124	1123	1124	1124	702
45°	912	915	917	919	920	703
55°	688	696	701	708	708	616
65°	471	478	487	496	499	466
75°	260	269	281	295	297	275
85°	86	97	110	120	121	95
90°	0	0	0	0	0	

TEST NUMBER: P1215913

CATALOG NUMBER: 24-ID2-40-CFD2-L830-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1503.7	1503.7	1503.7	1503.7	1503.7
2.5°	1508.3	1503.7	1500.8	1499.1	1502.0
5°	1502.5	1498.0	1495.1	1494.0	1496.8
7.5°	1492.2	1487.7	1485.4	1484.8	1487.7
10°	1477.4	1472.8	1471.1	1470.5	1474.5
12.5°	1458.5	1454.5	1453.3	1453.9	1456.2
15°	1436.2	1432.2	1431.6	1431.0	1434.5
17.5°	1408.7	1405.3	1405.3	1404.2	1407.6
20°	1377.8	1373.8	1374.4	1373.8	1376.1
22.5°	1342.4	1340.1	1341.8	1341.2	1341.8
25°	1305.2	1302.9	1302.9	1302.3	1302.3
27.5°	1262.9	1262.3	1262.3	1260.6	1261.2
30°	1218.3	1218.8	1218.3	1217.7	1216.6
32.5°	1173.7	1172.5	1172.5	1172.5	1170.8
35°	1123.3	1123.9	1123.3	1123.9	1123.9
37.5°	1071.9	1075.3	1074.1	1075.3	1072.4
40°	1020.4	1021.5	1022.7	1022.7	1020.9
42.5°	964.3	970.6	971.2	971.2	971.2
45°	911.7	914.6	917.4	918.6	920.3
47.5°	855.7	860.8	865.9	864.8	867.1
50°	800.2	807.0	810.5	813.3	811.6
52.5°	746.4	750.4	756.1	759.6	759.0
55°	687.5	695.5	701.2	707.5	707.5
57.5°	633.7	642.9	647.5	654.9	656.0
60°	576.5	586.8	594.3	601.1	601.7
62.5°	525.6	532.5	540.5	550.2	548.5
65°	471.3	478.2	487.3	496.5	499.3
67.5°	415.2	425.0	435.8	445.0	449.0
70°	362.6	372.9	385.5	394.7	395.8
72.5°	311.1	322.0	332.3	343.7	346.6
75°	260.2	269.4	281.4	295.1	296.8
77.5°	209.3	221.9	233.9	246.5	247.1
80°	164.7	175.0	189.3	200.8	203.0
82.5°	121.3	132.7	146.4	158.4	159.6
85°	85.8	96.7	110.4	120.1	121.3
87.5°	57.8	68.6	81.2	90.9	92.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1215913

CATALOG NUMBER: 24-ID2-40-CFD2-L830-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.18	14.82	13.55	15.14	15.45	13.46	15.10	13.82	15.41	15.73
	3H	14.90	16.38	15.27	16.71	17.07	15.35	16.83	15.73	17.16	17.52
	4H	15.53	16.93	15.93	17.28	17.66	16.11	17.51	16.51	17.86	18.24
	6H	16.00	17.30	16.41	17.66	18.05	16.74	18.04	17.15	18.40	18.79
	8H	16.15	17.39	16.57	17.78	18.18	16.98	18.23	17.41	18.62	19.01
	12H	16.25	17.45	16.68	17.83	18.26	17.20	18.39	17.63	18.77	19.20
4H	2H	13.82	15.22	14.22	15.57	15.95	14.04	15.44	14.44	15.79	16.16
	3H	15.76	16.94	16.17	17.34	17.74	16.16	17.34	16.56	17.73	18.13
	4H	16.53	17.60	16.96	18.01	18.45	17.06	18.13	17.49	18.54	18.98
	6H	17.12	18.06	17.57	18.50	18.95	17.83	18.77	18.28	19.21	19.66
	8H	17.32	18.20	17.78	18.64	19.11	18.14	19.02	18.60	19.46	19.93
	12H	17.48	18.27	17.96	18.74	19.21	18.42	19.22	18.90	19.69	20.16
8H	4H	16.88	17.76	17.34	18.20	18.67	17.35	18.23	17.81	18.67	19.13
	6H	17.60	18.34	18.10	18.83	19.30	18.26	18.99	18.75	19.48	19.96
	8H	17.88	18.54	18.39	19.05	19.53	18.66	19.33	19.17	19.83	20.32
	12H	18.12	18.71	18.63	19.20	19.76	19.06	19.65	19.56	20.14	20.69
12H	4H	16.93	17.73	17.41	18.20	18.67	17.38	18.17	17.86	18.65	19.12
	6H	17.69	18.35	18.20	18.86	19.34	18.31	18.98	18.82	19.48	19.97
	8H	18.03	18.62	18.54	19.11	19.67	18.78	19.37	19.29	19.86	20.42

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-3

Test Date: 07/24/2025

Luminaire Tested: 22ID2-55-CFR1-L830-U

Data in this report applies to families of products including 22ID2-55-CFR1-L830-U


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-3
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L830-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 3000K 80CRI

Spectral Parameters

CCT (K): 3031
 CIE u' : 0.2493
 CIE v' : 0.5215
 Duv: 0.0005
 CIE x: 0.4355
 CIE y: 0.4049
 CIE z: 0.1596
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 582
 Purity: 52.24762
 R_f: 84.8
 R_g: 95.8

CRI (Ra): 82.5
 R1: 80.7
 R2: 90.5
 R3: 96.7
 R4: 80.7
 R5: 80.9
 R6: 88.5
 R7: 83.0
 R8: 58.8
 R9: 5.8
 R10: 78.6
 R11: 80.2
 R12: 69.8
 R13: 83.0
 R14: 98.8
 R15: 73.0



Test Conditions


Stabilization Time: 38M
 Operation Time: 1H 38M
 Sphere Temperature (°C): 24.0

REPORT NUMBER: SP1-2506-458-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-3

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	229	NR	620	922	NR	750	29	NR	880	1	NR
365	0	NR	495	275	NR	625	875	NR	755	25	NR	885	1	NR
370	0	NR	500	326	NR	630	822	NR	760	21	NR	890	1	NR
375	0	NR	505	372	NR	635	764	NR	765	18	NR	895	0	NR
380	0	NR	510	411	NR	640	704	NR	770	15	NR	900	0	NR
385	0	NR	515	447	NR	645	638	NR	775	13	NR	905	0	NR
390	0	NR	520	473	NR	650	577	NR	780	11	NR	910	0	NR
395	1	NR	525	495	NR	655	517	NR	785	10	NR	915	0	NR
400	3	NR	530	515	NR	660	457	NR	790	8	NR	920	0	NR
405	4	NR	535	537	NR	665	404	NR	795	7	NR	925	0	NR
410	7	NR	540	559	NR	670	353	NR	800	6	NR	930	0	NR
415	12	NR	545	584	NR	675	307	NR	805	5	NR	935	0	NR
420	22	NR	550	612	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	648	NR	685	230	NR	815	4	NR	945	0	NR
430	69	NR	560	688	NR	690	199	NR	820	3	NR	950	0	NR
435	120	NR	565	730	NR	695	170	NR	825	3	NR	955	0	NR
440	212	NR	570	777	NR	700	145	NR	830	3	NR	960	0	NR
445	400	NR	575	824	NR	705	124	NR	835	2	NR	965	0	NR
450	578	NR	580	873	NR	710	106	NR	840	2	NR	970	0	NR
455	478	NR	585	918	NR	715	90	NR	845	2	NR	975	0	NR
460	332	NR	590	958	NR	720	76	NR	850	1	NR	980	0	NR
465	295	NR	595	983	NR	725	65	NR	855	1	NR	985	0	NR
470	231	NR	600	997	NR	730	55	NR	860	1	NR	990	0	NR
475	183	NR	605	998	NR	735	47	NR	865	1	NR	995	0	NR
480	184	NR	610	982	NR	740	40	NR	870	1	NR	1000	0	NR
485	201	NR	615	958	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.35

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	229	NR	620	922	NR	750	29	NR	880	1	NR
365	0	NR	495	275	NR	625	875	NR	755	25	NR	885	1	NR
370	0	NR	500	326	NR	630	822	NR	760	21	NR	890	1	NR
375	0	NR	505	372	NR	635	764	NR	765	18	NR	895	0	NR
380	0	NR	510	411	NR	640	704	NR	770	15	NR	900	0	NR
385	0	NR	515	447	NR	645	638	NR	775	13	NR	905	0	NR
390	0	NR	520	473	NR	650	577	NR	780	11	NR	910	0	NR
395	1	NR	525	495	NR	655	517	NR	785	10	NR	915	0	NR
400	3	NR	530	515	NR	660	457	NR	790	8	NR	920	0	NR
405	4	NR	535	537	NR	665	404	NR	795	7	NR	925	0	NR
410	7	NR	540	559	NR	670	353	NR	800	6	NR	930	0	NR
415	12	NR	545	584	NR	675	307	NR	805	5	NR	935	0	NR
420	22	NR	550	612	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	648	NR	685	230	NR	815	4	NR	945	0	NR
430	69	NR	560	688	NR	690	199	NR	820	3	NR	950	0	NR
435	120	NR	565	730	NR	695	170	NR	825	3	NR	955	0	NR
440	212	NR	570	777	NR	700	145	NR	830	3	NR	960	0	NR
445	400	NR	575	824	NR	705	124	NR	835	2	NR	965	0	NR
450	578	NR	580	873	NR	710	106	NR	840	2	NR	970	0	NR
455	478	NR	585	918	NR	715	90	NR	845	2	NR	975	0	NR
460	332	NR	590	958	NR	720	76	NR	850	1	NR	980	0	NR
465	295	NR	595	983	NR	725	65	NR	855	1	NR	985	0	NR
470	231	NR	600	997	NR	730	55	NR	860	1	NR	990	0	NR
475	183	NR	605	998	NR	735	47	NR	865	1	NR	995	0	NR
480	184	NR	610	982	NR	740	40	NR	870	1	NR	1000	0	NR
485	201	NR	615	958	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-3

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 2.59


λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	229	NR	620	922	NR	750	29	NR	880	1	NR
365	0	NR	495	275	NR	625	875	NR	755	25	NR	885	1	NR
370	0	NR	500	326	NR	630	822	NR	760	21	NR	890	1	NR
375	0	NR	505	372	NR	635	764	NR	765	18	NR	895	0	NR
380	0	NR	510	411	NR	640	704	NR	770	15	NR	900	0	NR
385	0	NR	515	447	NR	645	638	NR	775	13	NR	905	0	NR
390	0	NR	520	473	NR	650	577	NR	780	11	NR	910	0	NR
395	1	NR	525	495	NR	655	517	NR	785	10	NR	915	0	NR
400	3	NR	530	515	NR	660	457	NR	790	8	NR	920	0	NR
405	4	NR	535	537	NR	665	404	NR	795	7	NR	925	0	NR
410	7	NR	540	559	NR	670	353	NR	800	6	NR	930	0	NR
415	12	NR	545	584	NR	675	307	NR	805	5	NR	935	0	NR
420	22	NR	550	612	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	648	NR	685	230	NR	815	4	NR	945	0	NR
430	69	NR	560	688	NR	690	199	NR	820	3	NR	950	0	NR
435	120	NR	565	730	NR	695	170	NR	825	3	NR	955	0	NR
440	212	NR	570	777	NR	700	145	NR	830	3	NR	960	0	NR
445	400	NR	575	824	NR	705	124	NR	835	2	NR	965	0	NR
450	578	NR	580	873	NR	710	106	NR	840	2	NR	970	0	NR
455	478	NR	585	918	NR	715	90	NR	845	2	NR	975	0	NR
460	332	NR	590	958	NR	720	76	NR	850	1	NR	980	0	NR
465	295	NR	595	983	NR	725	65	NR	855	1	NR	985	0	NR
470	231	NR	600	997	NR	730	55	NR	860	1	NR	990	0	NR
475	183	NR	605	998	NR	735	47	NR	865	1	NR	995	0	NR
480	184	NR	610	982	NR	740	40	NR	870	1	NR	1000	0	NR
485	201	NR	615	958	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-3





TM-30-18

Summary

$R_f = 84.8$
 $R_g = 95.8$
 $CIE R_a = 82.5$
 $R_9 = 5.8$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 84	CES51 = 94	CES76 = 80
CES02 = 63	CES27 = 94	CES52 = 94	CES77 = 85
CES03 = 31	CES28 = 93	CES53 = 89	CES78 = 79
CES04 = 70	CES29 = 87	CES54 = 91	CES79 = 91
CES05 = 50	CES30 = 96	CES55 = 90	CES80 = 90
CES06 = 51	CES31 = 89	CES56 = 87	CES81 = 74
CES07 = 42	CES32 = 82	CES57 = 86	CES82 = 95
CES08 = 41	CES33 = 92	CES58 = 87	CES83 = 94
CES09 = 29	CES34 = 90	CES59 = 91	CES84 = 92
CES10 = 76	CES35 = 94	CES60 = 92	CES85 = 77
CES11 = 59	CES36 = 86	CES61 = 88	CES86 = 69
CES12 = 65	CES37 = 94	CES62 = 90	CES87 = 84
CES13 = 43	CES38 = 95	CES63 = 87	CES88 = 88
CES14 = 74	CES39 = 98	CES64 = 81	CES89 = 75
CES15 = 72	CES40 = 95	CES65 = 79	CES90 = 89
CES16 = 47	CES41 = 97	CES66 = 79	CES91 = 77
CES17 = 50	CES42 = 95	CES67 = 78	CES92 = 65
CES18 = 56	CES43 = 90	CES68 = 81	CES93 = 79
CES19 = 72	CES44 = 99	CES69 = 86	CES94 = 62
CES20 = 67	CES45 = 93	CES70 = 78	CES95 = 74
CES21 = 87	CES46 = 90	CES71 = 75	CES96 = 84
CES22 = 79	CES47 = 94	CES72 = 91	CES97 = 89
CES23 = 92	CES48 = 85	CES73 = 73	CES98 = 85
CES24 = 91	CES49 = 90	CES74 = 92	CES99 = 77
CES25 = 72	CES50 = 94	CES75 = 78	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)