

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1215918

Luminaire Tested: 24-ID2-40-CFD2-L935-U

Issue Date: 12/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1215918
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2506-458-28)
Test Lab: INNOVATION CENTER
Issue Date: 12/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 24-ID2-40-CFD2-L935-U
Description: 2X4 IN DEPTH TROFFER WITH 2INCH CUBE DROP LENS
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3526.2 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.32
Luminous Opening: Rectangular w/ Sides (W: 2' x L: 4' x H: 0.16')
CIE Type: Direct

Input Watts (W): 34.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1215918
CATALOG NUMBER: 24-ID2-40-CFD2-L935-U

Luminous Intensity Polar Plot



TEST NUMBER: P1215918
 CATALOG NUMBER: 24-ID2-40-CFD2-L935-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	108	103	99	95	106	101	97	93		97	94	90		93	90	88		89	87	85
2	99	90	83	77	96	88	82	76		85	79	75		81	77	73		78	75	71
3	90	79	71	64	87	78	70	64		75	68	63		72	66	61		69	64	60
4	82	70	61	55	80	69	61	54		66	59	53		64	58	53		62	56	52
5	76	63	54	47	74	62	53	47		60	52	46		58	51	46		56	50	45
6	70	57	48	41	68	56	47	41		54	46	41		52	45	40		51	45	40
7	65	51	43	36	63	51	42	36		49	42	36		48	41	36		46	40	36
8	61	47	38	33	59	46	38	32		45	38	32		44	37	32		43	36	32
9	57	43	35	29	55	43	35	29		41	34	29		40	34	29		39	33	29
10	53	40	32	27	52	39	32	27		38	31	26		37	31	26		37	31	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1749	1749	1749
5°	1748	1733	1735
10°	1733	1712	1717
15°	1711	1685	1691
20°	1681	1650	1655
25°	1644	1608	1611
30°	1599	1560	1562
35°	1551	1505	1511
40°	1499	1449	1453
45°	1442	1391	1402
50°	1382	1332	1341
55°	1319	1268	1288
60°	1254	1205	1229
65°	1195	1135	1173
70°	1111	1063	1103
75°	1018	961	1027
80°	899	856	935
85°	786	748	845

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1442 cd/sqm

TEST NUMBER: P1215918
 CATALOG NUMBER: 24-ID2-40-CFD2-L935-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.8	3.5
10°-20°	349.0	9.9
20°-30°	518.6	14.7
30°-40°	607.5	17.2
40°-50°	611.5	17.3
50°-60°	542.0	15.4
60°-70°	417.0	11.8
70°-80°	257.8	7.3
80°-90°	100.0	2.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	990.4	28.1
0°-40°	1597.9	45.3
0°-60°	2751.4	78.0
0°-90°	3526.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3526.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1300	1300	1300	1300	1300	
5°	1299	1295	1292	1291	1294	123
15°	1242	1238	1238	1237	1240	350
25°	1128	1126	1126	1126	1126	519
35°	971	972	971	972	972	607
45°	788	791	793	794	796	608
55°	594	601	606	612	612	533
65°	407	413	421	429	432	402
75°	225	233	243	255	257	238
85°	74	84	95	104	105	82
90°	0	0	0	0	0	

TEST NUMBER: P1215918

CATALOG NUMBER: 24-ID2-40-CFD2-L935-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1299.8	1299.8	1299.8	1299.8	1299.8
2.5°	1303.8	1299.8	1297.4	1295.9	1298.3
5°	1298.8	1294.9	1292.4	1291.4	1293.9
7.5°	1289.9	1286.0	1284.0	1283.5	1286.0
10°	1277.1	1273.1	1271.6	1271.2	1274.6
12.5°	1260.8	1257.3	1256.3	1256.8	1258.8
15°	1241.5	1238.0	1237.5	1237.0	1240.0
17.5°	1217.8	1214.8	1214.8	1213.8	1216.8
20°	1191.1	1187.6	1188.1	1187.6	1189.6
22.5°	1160.4	1158.4	1159.9	1159.4	1159.9
25°	1128.3	1126.3	1126.3	1125.8	1125.8
27.5°	1091.7	1091.2	1091.2	1089.7	1090.2
30°	1053.1	1053.6	1053.1	1052.6	1051.6
32.5°	1014.6	1013.6	1013.6	1013.6	1012.1
35°	971.0	971.5	971.0	971.5	971.5
37.5°	926.5	929.5	928.5	929.5	927.0
40°	882.0	883.0	884.0	884.0	882.5
42.5°	833.6	839.0	839.5	839.5	839.5
45°	788.1	790.6	793.1	794.0	795.5
47.5°	739.7	744.1	748.6	747.6	749.5
50°	691.7	697.6	700.6	703.1	701.6
52.5°	645.2	648.7	653.6	656.6	656.1
55°	594.3	601.2	606.2	611.6	611.6
57.5°	547.8	555.7	559.7	566.1	567.1
60°	498.4	507.3	513.7	519.6	520.1
62.5°	454.4	460.3	467.2	475.6	474.1
65°	407.4	413.3	421.2	429.2	431.6
67.5°	358.9	367.4	376.7	384.7	388.1
70°	313.5	322.4	333.2	341.2	342.1
72.5°	269.0	278.4	287.3	297.1	299.6
75°	225.0	232.9	243.3	255.1	256.6
77.5°	181.0	191.8	202.2	213.1	213.6
80°	142.4	151.3	163.7	173.5	175.5
82.5°	104.8	114.7	126.6	137.0	137.9
85°	74.2	83.6	95.4	103.8	104.8
87.5°	49.9	59.3	70.2	78.6	79.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1215918

CATALOG NUMBER: 24-ID2-40-CFD2-L935-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.68	14.32	13.04	14.63	14.94	12.95	14.59	13.32	14.91	15.22
	3H	14.39	15.87	14.77	16.20	16.56	14.84	16.33	15.22	16.65	17.01
	4H	15.03	16.43	15.42	16.77	17.15	15.61	17.01	16.00	17.35	17.73
	6H	15.49	16.79	15.90	17.15	17.55	16.23	17.53	16.64	17.90	18.29
	8H	15.64	16.88	16.06	17.27	17.67	16.48	17.72	16.90	18.11	18.51
	12H	15.75	16.94	16.18	17.32	17.75	16.69	17.88	17.12	18.26	18.69
4H	2H	13.32	14.72	13.71	15.06	15.44	13.53	14.94	13.93	15.28	15.66
	3H	15.26	16.44	15.67	16.83	17.23	15.65	16.83	16.06	17.23	17.63
	4H	16.02	17.09	16.45	17.51	17.94	16.55	17.62	16.98	18.03	18.47
	6H	16.61	17.55	17.07	17.99	18.45	17.32	18.26	17.78	18.70	19.16
	8H	16.81	17.69	17.27	18.14	18.60	17.63	18.51	18.09	18.96	19.42
	12H	16.97	17.76	17.45	18.24	18.71	17.92	18.71	18.39	19.18	19.65
8H	4H	16.37	17.25	16.83	17.70	18.16	16.84	17.72	17.30	18.16	18.63
	6H	17.10	17.83	17.59	18.32	18.80	17.75	18.49	18.24	18.97	19.45
	8H	17.38	18.04	17.88	18.54	19.03	18.16	18.82	18.66	19.32	19.81
	12H	17.61	18.20	18.12	18.69	19.25	18.55	19.14	19.06	19.63	20.19
12H	4H	16.43	17.22	16.91	17.70	18.16	16.87	17.67	17.35	18.14	18.61
	6H	17.18	17.85	17.69	18.35	18.84	17.81	18.47	18.31	18.98	19.46
	8H	17.53	18.12	18.03	18.61	19.16	18.28	18.87	18.78	19.36	19.91

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-10

Test Date: 08/26/2025

Luminaire Tested: 22ID2-55-CFR1-L935-U

Data in this report applies to families of products including 22ID2-55-CFR1-L935-U

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-10
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L935-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 3500K 90CRI

Spectral Parameters

CCT (K): 3377
 CIE u' : 0.2392
 CIE v' : 0.5128
 Duv: -0.0007
 CIE x: 0.4116
 CIE y: 0.3922
 CIE z: 0.1962
 Peak Wavelength (nm): 618
 Dominant Wavelength (nm): 581
 Purity: 41.24368
 R_f: 91.8
 R_g: 99.6

CRI (Ra): 93.6
 R1: 94.1
 R2: 96.6
 R3: 97.5
 R4: 94.0
 R5: 93.6
 R6: 94.8
 R7: 93.4
 R8: 84.8
 R9: 64.2
 R10: 91.1
 R11: 94.7
 R12: 78.5
 R13: 95.0
 R14: 98.1
 R15: 91.0



Test Conditions

Stabilization Time: 32M
 Operation Time: 1H 32M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2506-458-10

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-10

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-10

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	362	NR	620	996	NR	750	68	NR	880	1	NR
365	0	NR	495	412	NR	625	989	NR	755	58	NR	885	1	NR
370	0	NR	500	463	NR	630	973	NR	760	49	NR	890	1	NR
375	0	NR	505	509	NR	635	947	NR	765	42	NR	895	1	NR
380	0	NR	510	548	NR	640	914	NR	770	36	NR	900	1	NR
385	0	NR	515	582	NR	645	872	NR	775	31	NR	905	1	NR
390	1	NR	520	605	NR	650	822	NR	780	26	NR	910	1	NR
395	2	NR	525	626	NR	655	770	NR	785	22	NR	915	1	NR
400	4	NR	530	646	NR	660	712	NR	790	19	NR	920	0	NR
405	6	NR	535	666	NR	665	656	NR	795	16	NR	925	0	NR
410	9	NR	540	683	NR	670	596	NR	800	14	NR	930	0	NR
415	15	NR	545	702	NR	675	538	NR	805	12	NR	935	0	NR
420	27	NR	550	720	NR	680	486	NR	810	10	NR	940	0	NR
425	48	NR	555	740	NR	685	432	NR	815	9	NR	945	0	NR
430	85	NR	560	757	NR	690	385	NR	820	7	NR	950	0	NR
435	152	NR	565	776	NR	695	339	NR	825	6	NR	955	0	NR
440	274	NR	570	794	NR	700	297	NR	830	5	NR	960	0	NR
445	536	NR	575	816	NR	705	260	NR	835	5	NR	965	0	NR
450	793	NR	580	842	NR	710	225	NR	840	4	NR	970	0	NR
455	659	NR	585	867	NR	715	194	NR	845	3	NR	975	0	NR
460	484	NR	590	899	NR	720	169	NR	850	3	NR	980	0	NR
465	441	NR	595	927	NR	725	146	NR	855	2	NR	985	0	NR
470	353	NR	600	950	NR	730	125	NR	860	2	NR	990	0	NR
475	293	NR	605	974	NR	735	107	NR	865	2	NR	995	0	NR
480	300	NR	610	986	NR	740	92	NR	870	2	NR	1000	0	NR
485	325	NR	615	998	NR	745	79	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-10

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.58

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	362	NR	620	996	NR	750	68	NR	880	1	NR
365	0	NR	495	412	NR	625	989	NR	755	58	NR	885	1	NR
370	0	NR	500	463	NR	630	973	NR	760	49	NR	890	1	NR
375	0	NR	505	509	NR	635	947	NR	765	42	NR	895	1	NR
380	0	NR	510	548	NR	640	914	NR	770	36	NR	900	1	NR
385	0	NR	515	582	NR	645	872	NR	775	31	NR	905	1	NR
390	1	NR	520	605	NR	650	822	NR	780	26	NR	910	1	NR
395	2	NR	525	626	NR	655	770	NR	785	22	NR	915	1	NR
400	4	NR	530	646	NR	660	712	NR	790	19	NR	920	0	NR
405	6	NR	535	666	NR	665	656	NR	795	16	NR	925	0	NR
410	9	NR	540	683	NR	670	596	NR	800	14	NR	930	0	NR
415	15	NR	545	702	NR	675	538	NR	805	12	NR	935	0	NR
420	27	NR	550	720	NR	680	486	NR	810	10	NR	940	0	NR
425	48	NR	555	740	NR	685	432	NR	815	9	NR	945	0	NR
430	85	NR	560	757	NR	690	385	NR	820	7	NR	950	0	NR
435	152	NR	565	776	NR	695	339	NR	825	6	NR	955	0	NR
440	274	NR	570	794	NR	700	297	NR	830	5	NR	960	0	NR
445	536	NR	575	816	NR	705	260	NR	835	5	NR	965	0	NR
450	793	NR	580	842	NR	710	225	NR	840	4	NR	970	0	NR
455	659	NR	585	867	NR	715	194	NR	845	3	NR	975	0	NR
460	484	NR	590	899	NR	720	169	NR	850	3	NR	980	0	NR
465	441	NR	595	927	NR	725	146	NR	855	2	NR	985	0	NR
470	353	NR	600	950	NR	730	125	NR	860	2	NR	990	0	NR
475	293	NR	605	974	NR	735	107	NR	865	2	NR	995	0	NR
480	300	NR	610	986	NR	740	92	NR	870	2	NR	1000	0	NR
485	325	NR	615	998	NR	745	79	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-10

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 3.19

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	362	NR	620	996	NR	750	68	NR	880	1	NR
365	0	NR	495	412	NR	625	989	NR	755	58	NR	885	1	NR
370	0	NR	500	463	NR	630	973	NR	760	49	NR	890	1	NR
375	0	NR	505	509	NR	635	947	NR	765	42	NR	895	1	NR
380	0	NR	510	548	NR	640	914	NR	770	36	NR	900	1	NR
385	0	NR	515	582	NR	645	872	NR	775	31	NR	905	1	NR
390	1	NR	520	605	NR	650	822	NR	780	26	NR	910	1	NR
395	2	NR	525	626	NR	655	770	NR	785	22	NR	915	1	NR
400	4	NR	530	646	NR	660	712	NR	790	19	NR	920	0	NR
405	6	NR	535	666	NR	665	656	NR	795	16	NR	925	0	NR
410	9	NR	540	683	NR	670	596	NR	800	14	NR	930	0	NR
415	15	NR	545	702	NR	675	538	NR	805	12	NR	935	0	NR
420	27	NR	550	720	NR	680	486	NR	810	10	NR	940	0	NR
425	48	NR	555	740	NR	685	432	NR	815	9	NR	945	0	NR
430	85	NR	560	757	NR	690	385	NR	820	7	NR	950	0	NR
435	152	NR	565	776	NR	695	339	NR	825	6	NR	955	0	NR
440	274	NR	570	794	NR	700	297	NR	830	5	NR	960	0	NR
445	536	NR	575	816	NR	705	260	NR	835	5	NR	965	0	NR
450	793	NR	580	842	NR	710	225	NR	840	4	NR	970	0	NR
455	659	NR	585	867	NR	715	194	NR	845	3	NR	975	0	NR
460	484	NR	590	899	NR	720	169	NR	850	3	NR	980	0	NR
465	441	NR	595	927	NR	725	146	NR	855	2	NR	985	0	NR
470	353	NR	600	950	NR	730	125	NR	860	2	NR	990	0	NR
475	293	NR	605	974	NR	735	107	NR	865	2	NR	995	0	NR
480	300	NR	610	986	NR	740	92	NR	870	2	NR	1000	0	NR
485	325	NR	615	998	NR	745	79	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-10

TM-30-18

Summary

$R_f = 91.8$
 $R_g = 99.6$
 $CIE R_a = 93.6$
 $R_9 = 64.2$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 94	CES51 = 97	CES76 = 88
CES02 = 62	CES27 = 92	CES52 = 99	CES77 = 89
CES03 = 31	CES28 = 96	CES53 = 97	CES78 = 85
CES04 = 70	CES29 = 96	CES54 = 93	CES79 = 95
CES05 = 50	CES30 = 92	CES55 = 92	CES80 = 93
CES06 = 51	CES31 = 97	CES56 = 95	CES81 = 86
CES07 = 43	CES32 = 91	CES57 = 93	CES82 = 97
CES08 = 42	CES33 = 99	CES58 = 94	CES83 = 97
CES09 = 29	CES34 = 94	CES59 = 97	CES84 = 94
CES10 = 75	CES35 = 96	CES60 = 92	CES85 = 83
CES11 = 58	CES36 = 82	CES61 = 92	CES86 = 86
CES12 = 64	CES37 = 95	CES62 = 87	CES87 = 91
CES13 = 43	CES38 = 87	CES63 = 93	CES88 = 97
CES14 = 74	CES39 = 99	CES64 = 90	CES89 = 87
CES15 = 72	CES40 = 98	CES65 = 89	CES90 = 96
CES16 = 48	CES41 = 97	CES66 = 88	CES91 = 75
CES17 = 50	CES42 = 95	CES67 = 87	CES92 = 80
CES18 = 56	CES43 = 94	CES68 = 88	CES93 = 88
CES19 = 71	CES44 = 99	CES69 = 89	CES94 = 81
CES20 = 67	CES45 = 97	CES70 = 86	CES95 = 84
CES21 = 86	CES46 = 97	CES71 = 82	CES96 = 92
CES22 = 78	CES47 = 96	CES72 = 94	CES97 = 96
CES23 = 91	CES48 = 92	CES73 = 82	CES98 = 95
CES24 = 90	CES49 = 96	CES74 = 92	CES99 = 92
CES25 = 71	CES50 = 98	CES75 = 84	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)