

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1216408

Luminaire Tested: 24-ID2-45-DBR-L950-U

Issue Date: 12/5/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P1216408  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2508-510-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/5/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: 24-ID2-45-DBR-L950-U  
Description: 2X4 IN DEPTH TROFFER WITH 2INCH DOUBLE BARREL REGRESSED  
Light Source: 5000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4116.0 lumens  
Efficiency: N/A  
Efficacy: 105.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 39  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P1216408  
CATALOG NUMBER: 24-ID2-45-DBR-L950-U

### Luminous Intensity Polar Plot



TEST NUMBER: P1216408

CATALOG NUMBER: 24-ID2-45-DBR-L950-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 100 |
| 1   | 109 | 104 | 100 | 96  | 106 | 102 | 98  | 95  | 98  | 95  | 92  |  | 94  | 91  | 89  |  | 84  |
| 2   | 99  | 91  | 85  | 79  | 97  | 89  | 83  | 78  | 86  | 81  | 76  |  | 83  | 78  | 74  |  | 71  |
| 3   | 91  | 80  | 72  | 66  | 88  | 79  | 71  | 65  | 76  | 70  | 64  |  | 73  | 68  | 63  |  | 60  |
| 4   | 83  | 71  | 63  | 56  | 81  | 70  | 62  | 56  | 68  | 61  | 55  |  | 65  | 59  | 54  |  | 51  |
| 5   | 77  | 64  | 55  | 49  | 75  | 63  | 55  | 48  | 61  | 53  | 48  |  | 59  | 52  | 47  |  | 45  |
| 6   | 71  | 58  | 49  | 43  | 69  | 57  | 48  | 42  | 55  | 48  | 42  |  | 53  | 47  | 42  |  | 39  |
| 7   | 66  | 52  | 44  | 38  | 64  | 52  | 43  | 38  | 50  | 43  | 37  |  | 49  | 42  | 37  |  | 35  |
| 8   | 61  | 48  | 40  | 34  | 60  | 47  | 39  | 34  | 46  | 39  | 33  |  | 45  | 38  | 33  |  | 31  |
| 9   | 57  | 44  | 36  | 31  | 56  | 44  | 36  | 30  | 42  | 35  | 30  |  | 41  | 35  | 30  |  | 28  |
| 10  | 54  | 41  | 33  | 28  | 53  | 40  | 33  | 28  | 39  | 32  | 28  |  | 38  | 32  | 27  |  | 26  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 2153 | 2153 | 2153 |
| 5°  | 2161 | 2149 | 2149 |
| 10° | 2147 | 2135 | 2137 |
| 15° | 2124 | 2113 | 2114 |
| 20° | 2090 | 2079 | 2080 |
| 25° | 2046 | 2040 | 2041 |
| 30° | 1993 | 1987 | 1996 |
| 35° | 1934 | 1931 | 1941 |
| 40° | 1862 | 1873 | 1886 |
| 45° | 1794 | 1807 | 1823 |
| 50° | 1710 | 1737 | 1762 |
| 55° | 1628 | 1666 | 1699 |
| 60° | 1528 | 1594 | 1619 |
| 65° | 1430 | 1504 | 1547 |
| 70° | 1316 | 1421 | 1445 |
| 75° | 1186 | 1322 | 1334 |
| 80° | 1007 | 1179 | 1192 |
| 85° | 772  | 973  | 999  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 67.5°

Vertical Angle: 45°

Luminance: 1823 cd/sqm

TEST NUMBER: P1216408  
 CATALOG NUMBER: 24-ID2-45-DBR-L950-U

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 151.1  | 3.7       |
| 10°-20°   | 427.8  | 10.4      |
| 20°-30°   | 632.7  | 15.4      |
| 30°-40°   | 736.4  | 17.9      |
| 40°-50°   | 732.7  | 17.8      |
| 50°-60°   | 634.1  | 15.4      |
| 60°-70°   | 466.3  | 11.3      |
| 70°-80°   | 263.4  | 6.4       |
| 80°-90°   | 71.5   | 1.7       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1211.6 | 29.4      |
| 0°-40°    | 1948.0 | 47.3      |
| 0°-60°    | 3314.8 | 80.5      |
| 0°-90°    | 4116.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 4116.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|-----|------|-------|------|-------|------|------|
| 0°  | 1600 | 1600  | 1600 | 1600  | 1600 |      |
| 5°  | 1600 | 1594  | 1591 | 1588  | 1591 | 152  |
| 15° | 1525 | 1520  | 1517 | 1514  | 1518 | 430  |
| 25° | 1378 | 1374  | 1374 | 1372  | 1375 | 635  |
| 35° | 1178 | 1175  | 1176 | 1181  | 1182 | 736  |
| 45° | 943  | 943   | 950  | 958   | 958  | 726  |
| 55° | 694  | 697   | 710  | 720   | 724  | 620  |
| 65° | 449  | 458   | 472  | 481   | 486  | 446  |
| 75° | 228  | 241   | 254  | 256   | 257  | 242  |
| 85° | 50   | 59    | 63   | 64    | 65   | 60   |
| 90° | 0    | 0     | 0    | 0     | 0    |      |

TEST NUMBER: P1216408

CATALOG NUMBER: 24-ID2-45-DBR-L950-U

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|-------|--------|--------|--------|--------|--------|
| 0°    | 1600.5 | 1600.5 | 1600.5 | 1600.5 | 1600.5 |
| 2.5°  | 1606.7 | 1600.5 | 1597.1 | 1595.4 | 1597.6 |
| 5°    | 1599.9 | 1594.2 | 1590.8 | 1588.5 | 1591.4 |
| 7.5°  | 1588.5 | 1582.3 | 1578.9 | 1576.6 | 1580.6 |
| 10°   | 1571.5 | 1565.3 | 1562.4 | 1560.7 | 1564.1 |
| 12.5° | 1550.5 | 1545.4 | 1542.0 | 1539.7 | 1542.0 |
| 15°   | 1525.0 | 1520.4 | 1517.0 | 1514.2 | 1517.6 |
| 17.5° | 1494.9 | 1489.2 | 1488.1 | 1484.6 | 1487.5 |
| 20°   | 1459.7 | 1455.1 | 1452.3 | 1450.6 | 1452.9 |
| 22.5° | 1423.3 | 1417.1 | 1415.4 | 1413.7 | 1415.9 |
| 25°   | 1378.5 | 1374.5 | 1373.9 | 1372.2 | 1375.1 |
| 27.5° | 1333.1 | 1330.8 | 1327.9 | 1329.1 | 1329.7 |
| 30°   | 1283.1 | 1280.3 | 1279.1 | 1281.4 | 1284.8 |
| 32.5° | 1231.4 | 1229.2 | 1229.7 | 1232.0 | 1238.2 |
| 35°   | 1177.5 | 1175.2 | 1175.8 | 1180.9 | 1182.0 |
| 37.5° | 1122.4 | 1118.5 | 1122.4 | 1125.8 | 1128.7 |
| 40°   | 1060.0 | 1060.5 | 1066.2 | 1070.8 | 1073.6 |
| 42.5° | 1002.1 | 1002.1 | 1007.7 | 1014.6 | 1018.0 |
| 45°   | 943.0  | 943.0  | 949.8  | 957.8  | 957.8  |
| 47.5° | 880.6  | 879.4  | 891.9  | 900.4  | 903.3  |
| 50°   | 817.0  | 819.3  | 830.0  | 838.6  | 842.0  |
| 52.5° | 757.4  | 758.5  | 770.4  | 779.5  | 781.2  |
| 55°   | 693.8  | 697.2  | 710.2  | 719.9  | 724.4  |
| 57.5° | 631.3  | 637.0  | 650.1  | 662.0  | 663.1  |
| 60°   | 567.7  | 576.8  | 592.2  | 598.4  | 601.8  |
| 62.5° | 509.8  | 518.9  | 531.4  | 541.6  | 543.9  |
| 65°   | 449.1  | 458.2  | 472.4  | 481.4  | 486.0  |
| 67.5° | 392.3  | 403.1  | 417.3  | 424.1  | 424.1  |
| 70°   | 334.4  | 346.3  | 361.1  | 366.8  | 367.3  |
| 72.5° | 279.9  | 293.5  | 306.6  | 311.1  | 312.3  |
| 75°   | 228.2  | 240.7  | 254.3  | 256.1  | 256.6  |
| 77.5° | 177.7  | 190.8  | 201.0  | 204.4  | 202.7  |
| 80°   | 130.0  | 143.1  | 152.2  | 154.4  | 153.9  |
| 82.5° | 88.6   | 99.4   | 107.9  | 107.9  | 107.9  |
| 85°   | 50.0   | 59.0   | 63.0   | 64.2   | 64.7   |
| 87.5° | 16.5   | 23.3   | 26.7   | 26.7   | 26.7   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

TEST NUMBER: P1216408

CATALOG NUMBER: 24-ID2-45-DBR-L950-U

**CIE UGR TABLE:**

| Reflectances:   |      |                  |       |       |       |       |                |       |       |       |       |
|-----------------|------|------------------|-------|-------|-------|-------|----------------|-------|-------|-------|-------|
| Ceiling         |      | 0.7              | 0.7   | 0.5   | 0.5   | 0.3   | 0.7            | 0.7   | 0.5   | 0.5   | 0.3   |
| Wall            |      | 0.5              | 0.3   | 0.5   | 0.3   | 0.3   | 0.5            | 0.3   | 0.5   | 0.3   | 0.3   |
| Reference plane |      | 0.2              | 0.2   | 0.2   | 0.2   | 0.2   | 0.2            | 0.2   | 0.2   | 0.2   | 0.2   |
| Room dimensions |      | Viewed crosswise |       |       |       |       | Viewed endwise |       |       |       |       |
| X=2H            | Y=2H | 13.59            | 15.19 | 13.95 | 15.51 | 15.82 | 13.87          | 15.48 | 14.23 | 15.79 | 16.10 |
|                 | 3H   | 15.24            | 16.69 | 15.62 | 17.02 | 17.38 | 15.60          | 17.05 | 15.98 | 17.38 | 17.74 |
|                 | 4H   | 15.84            | 17.20 | 16.24 | 17.55 | 17.93 | 16.25          | 17.62 | 16.65 | 17.97 | 18.34 |
|                 | 6H   | 16.25            | 17.52 | 16.66 | 17.88 | 18.27 | 16.73          | 17.99 | 17.14 | 18.36 | 18.75 |
|                 | 8H   | 16.37            | 17.58 | 16.79 | 17.97 | 18.37 | 16.88          | 18.09 | 17.30 | 18.48 | 18.87 |
|                 | 12H  | 16.44            | 17.60 | 16.87 | 17.98 | 18.41 | 16.98          | 18.13 | 17.41 | 18.52 | 18.95 |
| 4H              | 2H   | 14.22            | 15.59 | 14.62 | 15.94 | 16.31 | 14.45          | 15.81 | 14.84 | 16.16 | 16.54 |
|                 | 3H   | 16.11            | 17.25 | 16.51 | 17.65 | 18.05 | 16.41          | 17.55 | 16.82 | 17.95 | 18.35 |
|                 | 4H   | 16.83            | 17.87 | 17.26 | 18.28 | 18.72 | 17.19          | 18.22 | 17.62 | 18.64 | 19.07 |
|                 | 6H   | 17.37            | 18.27 | 17.82 | 18.71 | 19.17 | 17.80          | 18.70 | 18.25 | 19.14 | 19.60 |
|                 | 8H   | 17.53            | 18.38 | 17.99 | 18.82 | 19.29 | 18.00          | 18.84 | 18.46 | 19.28 | 19.75 |
|                 | 12H  | 17.64            | 18.40 | 18.12 | 18.87 | 19.34 | 18.14          | 18.90 | 18.62 | 19.37 | 19.84 |
| 8H              | 4H   | 17.16            | 18.01 | 17.62 | 18.45 | 18.91 | 17.48          | 18.32 | 17.94 | 18.77 | 19.23 |
|                 | 6H   | 17.82            | 18.53 | 18.32 | 19.02 | 19.49 | 18.21          | 18.91 | 18.70 | 19.40 | 19.87 |
|                 | 8H   | 18.06            | 18.69 | 18.57 | 19.20 | 19.68 | 18.48          | 19.11 | 18.99 | 19.62 | 20.10 |
|                 | 12H  | 18.23            | 18.79 | 18.74 | 19.28 | 19.84 | 18.69          | 19.25 | 19.20 | 19.74 | 20.30 |
| 12H             | 4H   | 17.20            | 17.96 | 17.68 | 18.43 | 18.90 | 17.51          | 18.26 | 17.99 | 18.74 | 19.21 |
|                 | 6H   | 17.89            | 18.52 | 18.40 | 19.03 | 19.51 | 18.26          | 18.89 | 18.77 | 19.39 | 19.88 |
|                 | 8H   | 18.18            | 18.74 | 18.69 | 19.23 | 19.79 | 18.59          | 19.14 | 19.09 | 19.63 | 20.20 |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-13

Test Date: 08/27/2025

Luminaire Tested: 22ID2-55-CFR1-L950-U

Data in this report applies to families of products including 22ID2-55-CFR1-L950-U

### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2506-458-13  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 08/27/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Corelite  
 Catalog Number: **22ID2-55-CFR1-L950-U**  
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 5000K 90CRI

### Spectral Parameters

CCT (K): 4919  
 CIE  $u'$ : 0.2096  
 CIE  $v'$ : 0.4901  
 Duv: 0.0038  
 CIE x: 0.3483  
 CIE y: 0.3619  
 CIE z: 0.2898  
 Peak Wavelength (nm): 453  
 Dominant Wavelength (nm): 570  
 Purity: 13.10873  
 R<sub>f</sub>: 90.8  
 R<sub>g</sub>: 97.4

CRI (Ra): 94.0  
 R1: 94.8  
 R2: 97.7  
 R3: 98.4  
 R4: 90.8  
 R5: 92.2  
 R6: 94.3  
 R7: 94.0  
 R8: 90.0  
 R9: 77.7  
 R10: 93.1  
 R11: 92.0  
 R12: 65.9  
 R13: 95.9  
 R14: 99.0  
 R15: 91.4



### Test Conditions

Stabilization Time: M  
 Operation Time: 1H 0M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-458-13

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | 76INCH SPHERE IN0058  | 6/16/2025        | 12/16/2025           |
| Power Meter                    | XITRON INXT2011004    | 1/21/2025        | 1/21/2026            |
| AC Power Source                | CHROMA 61603 IN0063   | 10/22/2024       | 10/22/2025           |
| DC Power Source                | AGILENT E3634A IN0208 | 10/22/2024       | 10/22/2025           |
| Sphere Thermometer             | ONSET IN0085          | 10/22/2024       | 10/22/2025           |
| Room Thermometer               | ONSET IN0046          | 10/22/2024       | 10/22/2025           |

REPORT NUMBER: SP1-2506-458-13

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-13

### Photopic Flux vs. Wavelength



### Photopic Lumens: NR

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 419                      | NR            | 620    | 583                      | NR            | 750    | 44                       | NR            | 880    | 1                        | NR            |
| 365    | 0                        | NR            | 495    | 441                      | NR            | 625    | 580                      | NR            | 755    | 37                       | NR            | 885    | 1                        | NR            |
| 370    | 0                        | NR            | 500    | 472                      | NR            | 630    | 572                      | NR            | 760    | 32                       | NR            | 890    | 1                        | NR            |
| 375    | 0                        | NR            | 505    | 501                      | NR            | 635    | 559                      | NR            | 765    | 27                       | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 524                      | NR            | 640    | 543                      | NR            | 770    | 23                       | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 545                      | NR            | 645    | 522                      | NR            | 775    | 20                       | NR            | 905    | 0                        | NR            |
| 390    | 1                        | NR            | 520    | 559                      | NR            | 650    | 496                      | NR            | 780    | 17                       | NR            | 910    | 0                        | NR            |
| 395    | 3                        | NR            | 525    | 572                      | NR            | 655    | 468                      | NR            | 785    | 14                       | NR            | 915    | 0                        | NR            |
| 400    | 4                        | NR            | 530    | 581                      | NR            | 660    | 435                      | NR            | 790    | 12                       | NR            | 920    | 0                        | NR            |
| 405    | 7                        | NR            | 535    | 590                      | NR            | 665    | 403                      | NR            | 795    | 10                       | NR            | 925    | 0                        | NR            |
| 410    | 9                        | NR            | 540    | 595                      | NR            | 670    | 368                      | NR            | 800    | 9                        | NR            | 930    | 0                        | NR            |
| 415    | 14                       | NR            | 545    | 599                      | NR            | 675    | 335                      | NR            | 805    | 8                        | NR            | 935    | 0                        | NR            |
| 420    | 23                       | NR            | 550    | 599                      | NR            | 680    | 304                      | NR            | 810    | 6                        | NR            | 940    | 0                        | NR            |
| 425    | 40                       | NR            | 555    | 599                      | NR            | 685    | 271                      | NR            | 815    | 6                        | NR            | 945    | 0                        | NR            |
| 430    | 72                       | NR            | 560    | 595                      | NR            | 690    | 243                      | NR            | 820    | 5                        | NR            | 950    | 0                        | NR            |
| 435    | 132                      | NR            | 565    | 589                      | NR            | 695    | 215                      | NR            | 825    | 4                        | NR            | 955    | 0                        | NR            |
| 440    | 243                      | NR            | 570    | 581                      | NR            | 700    | 189                      | NR            | 830    | 3                        | NR            | 960    | 0                        | NR            |
| 445    | 488                      | NR            | 575    | 575                      | NR            | 705    | 165                      | NR            | 835    | 3                        | NR            | 965    | 0                        | NR            |
| 450    | 879                      | NR            | 580    | 573                      | NR            | 710    | 144                      | NR            | 840    | 3                        | NR            | 970    | 0                        | NR            |
| 455    | 974                      | NR            | 585    | 570                      | NR            | 715    | 124                      | NR            | 845    | 2                        | NR            | 975    | 0                        | NR            |
| 460    | 726                      | NR            | 590    | 572                      | NR            | 720    | 108                      | NR            | 850    | 2                        | NR            | 980    | 0                        | NR            |
| 465    | 627                      | NR            | 595    | 574                      | NR            | 725    | 93                       | NR            | 855    | 2                        | NR            | 985    | 0                        | NR            |
| 470    | 546                      | NR            | 600    | 576                      | NR            | 730    | 80                       | NR            | 860    | 1                        | NR            | 990    | 0                        | NR            |
| 475    | 434                      | NR            | 605    | 581                      | NR            | 735    | 69                       | NR            | 865    | 1                        | NR            | 995    | 0                        | NR            |
| 480    | 395                      | NR            | 610    | 582                      | NR            | 740    | 59                       | NR            | 870    | 1                        | NR            | 1000   | 0                        | NR            |
| 485    | 403                      | NR            | 615    | 586                      | NR            | 745    | 51                       | NR            | 875    | 1                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2506-458-13

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 2.09

| λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 419                         | NR               | 620       | 583                         | NR               | 750       | 44                          | NR               | 880       | 1                           | NR               |
| 365       | 0                           | NR               | 495       | 441                         | NR               | 625       | 580                         | NR               | 755       | 37                          | NR               | 885       | 1                           | NR               |
| 370       | 0                           | NR               | 500       | 472                         | NR               | 630       | 572                         | NR               | 760       | 32                          | NR               | 890       | 1                           | NR               |
| 375       | 0                           | NR               | 505       | 501                         | NR               | 635       | 559                         | NR               | 765       | 27                          | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 524                         | NR               | 640       | 543                         | NR               | 770       | 23                          | NR               | 900       | 0                           | NR               |
| 385       | 0                           | NR               | 515       | 545                         | NR               | 645       | 522                         | NR               | 775       | 20                          | NR               | 905       | 0                           | NR               |
| 390       | 1                           | NR               | 520       | 559                         | NR               | 650       | 496                         | NR               | 780       | 17                          | NR               | 910       | 0                           | NR               |
| 395       | 3                           | NR               | 525       | 572                         | NR               | 655       | 468                         | NR               | 785       | 14                          | NR               | 915       | 0                           | NR               |
| 400       | 4                           | NR               | 530       | 581                         | NR               | 660       | 435                         | NR               | 790       | 12                          | NR               | 920       | 0                           | NR               |
| 405       | 7                           | NR               | 535       | 590                         | NR               | 665       | 403                         | NR               | 795       | 10                          | NR               | 925       | 0                           | NR               |
| 410       | 9                           | NR               | 540       | 595                         | NR               | 670       | 368                         | NR               | 800       | 9                           | NR               | 930       | 0                           | NR               |
| 415       | 14                          | NR               | 545       | 599                         | NR               | 675       | 335                         | NR               | 805       | 8                           | NR               | 935       | 0                           | NR               |
| 420       | 23                          | NR               | 550       | 599                         | NR               | 680       | 304                         | NR               | 810       | 6                           | NR               | 940       | 0                           | NR               |
| 425       | 40                          | NR               | 555       | 599                         | NR               | 685       | 271                         | NR               | 815       | 6                           | NR               | 945       | 0                           | NR               |
| 430       | 72                          | NR               | 560       | 595                         | NR               | 690       | 243                         | NR               | 820       | 5                           | NR               | 950       | 0                           | NR               |
| 435       | 132                         | NR               | 565       | 589                         | NR               | 695       | 215                         | NR               | 825       | 4                           | NR               | 955       | 0                           | NR               |
| 440       | 243                         | NR               | 570       | 581                         | NR               | 700       | 189                         | NR               | 830       | 3                           | NR               | 960       | 0                           | NR               |
| 445       | 488                         | NR               | 575       | 575                         | NR               | 705       | 165                         | NR               | 835       | 3                           | NR               | 965       | 0                           | NR               |
| 450       | 879                         | NR               | 580       | 573                         | NR               | 710       | 144                         | NR               | 840       | 3                           | NR               | 970       | 0                           | NR               |
| 455       | 974                         | NR               | 585       | 570                         | NR               | 715       | 124                         | NR               | 845       | 2                           | NR               | 975       | 0                           | NR               |
| 460       | 726                         | NR               | 590       | 572                         | NR               | 720       | 108                         | NR               | 850       | 2                           | NR               | 980       | 0                           | NR               |
| 465       | 627                         | NR               | 595       | 574                         | NR               | 725       | 93                          | NR               | 855       | 2                           | NR               | 985       | 0                           | NR               |
| 470       | 546                         | NR               | 600       | 576                         | NR               | 730       | 80                          | NR               | 860       | 1                           | NR               | 990       | 0                           | NR               |
| 475       | 434                         | NR               | 605       | 581                         | NR               | 735       | 69                          | NR               | 865       | 1                           | NR               | 995       | 0                           | NR               |
| 480       | 395                         | NR               | 610       | 582                         | NR               | 740       | 59                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 403                         | NR               | 615       | 586                         | NR               | 745       | 51                          | NR               | 875       | 1                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2506-458-13

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 4.55

| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 419                         | NR               | 620       | 583                         | NR               | 750       | 44                          | NR               | 880       | 1                           | NR               |
| 365       | 0                           | NR               | 495       | 441                         | NR               | 625       | 580                         | NR               | 755       | 37                          | NR               | 885       | 1                           | NR               |
| 370       | 0                           | NR               | 500       | 472                         | NR               | 630       | 572                         | NR               | 760       | 32                          | NR               | 890       | 1                           | NR               |
| 375       | 0                           | NR               | 505       | 501                         | NR               | 635       | 559                         | NR               | 765       | 27                          | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 524                         | NR               | 640       | 543                         | NR               | 770       | 23                          | NR               | 900       | 0                           | NR               |
| 385       | 0                           | NR               | 515       | 545                         | NR               | 645       | 522                         | NR               | 775       | 20                          | NR               | 905       | 0                           | NR               |
| 390       | 1                           | NR               | 520       | 559                         | NR               | 650       | 496                         | NR               | 780       | 17                          | NR               | 910       | 0                           | NR               |
| 395       | 3                           | NR               | 525       | 572                         | NR               | 655       | 468                         | NR               | 785       | 14                          | NR               | 915       | 0                           | NR               |
| 400       | 4                           | NR               | 530       | 581                         | NR               | 660       | 435                         | NR               | 790       | 12                          | NR               | 920       | 0                           | NR               |
| 405       | 7                           | NR               | 535       | 590                         | NR               | 665       | 403                         | NR               | 795       | 10                          | NR               | 925       | 0                           | NR               |
| 410       | 9                           | NR               | 540       | 595                         | NR               | 670       | 368                         | NR               | 800       | 9                           | NR               | 930       | 0                           | NR               |
| 415       | 14                          | NR               | 545       | 599                         | NR               | 675       | 335                         | NR               | 805       | 8                           | NR               | 935       | 0                           | NR               |
| 420       | 23                          | NR               | 550       | 599                         | NR               | 680       | 304                         | NR               | 810       | 6                           | NR               | 940       | 0                           | NR               |
| 425       | 40                          | NR               | 555       | 599                         | NR               | 685       | 271                         | NR               | 815       | 6                           | NR               | 945       | 0                           | NR               |
| 430       | 72                          | NR               | 560       | 595                         | NR               | 690       | 243                         | NR               | 820       | 5                           | NR               | 950       | 0                           | NR               |
| 435       | 132                         | NR               | 565       | 589                         | NR               | 695       | 215                         | NR               | 825       | 4                           | NR               | 955       | 0                           | NR               |
| 440       | 243                         | NR               | 570       | 581                         | NR               | 700       | 189                         | NR               | 830       | 3                           | NR               | 960       | 0                           | NR               |
| 445       | 488                         | NR               | 575       | 575                         | NR               | 705       | 165                         | NR               | 835       | 3                           | NR               | 965       | 0                           | NR               |
| 450       | 879                         | NR               | 580       | 573                         | NR               | 710       | 144                         | NR               | 840       | 3                           | NR               | 970       | 0                           | NR               |
| 455       | 974                         | NR               | 585       | 570                         | NR               | 715       | 124                         | NR               | 845       | 2                           | NR               | 975       | 0                           | NR               |
| 460       | 726                         | NR               | 590       | 572                         | NR               | 720       | 108                         | NR               | 850       | 2                           | NR               | 980       | 0                           | NR               |
| 465       | 627                         | NR               | 595       | 574                         | NR               | 725       | 93                          | NR               | 855       | 2                           | NR               | 985       | 0                           | NR               |
| 470       | 546                         | NR               | 600       | 576                         | NR               | 730       | 80                          | NR               | 860       | 1                           | NR               | 990       | 0                           | NR               |
| 475       | 434                         | NR               | 605       | 581                         | NR               | 735       | 69                          | NR               | 865       | 1                           | NR               | 995       | 0                           | NR               |
| 480       | 395                         | NR               | 610       | 582                         | NR               | 740       | 59                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 403                         | NR               | 615       | 586                         | NR               | 745       | 51                          | NR               | 875       | 1                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2506-458-13

TM-30-18

### Summary

$R_f = 90.8$   
 $R_g = 97.4$   
 $CIE R_a = 94.0$   
 $R_9 = 77.7$




### Color Vector Graphics




**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 98 | CES51 = 93 | CES76 = 91 |
| CES02 = 61 | CES27 = 86 | CES52 = 96 | CES77 = 89 |
| CES03 = 31 | CES28 = 98 | CES53 = 93 | CES78 = 87 |
| CES04 = 68 | CES29 = 90 | CES54 = 89 | CES79 = 97 |
| CES05 = 48 | CES30 = 80 | CES55 = 86 | CES80 = 94 |
| CES06 = 50 | CES31 = 92 | CES56 = 89 | CES81 = 89 |
| CES07 = 41 | CES32 = 97 | CES57 = 87 | CES82 = 97 |
| CES08 = 40 | CES33 = 89 | CES58 = 87 | CES83 = 96 |
| CES09 = 29 | CES34 = 98 | CES59 = 96 | CES84 = 94 |
| CES10 = 73 | CES35 = 98 | CES60 = 89 | CES85 = 84 |
| CES11 = 56 | CES36 = 74 | CES61 = 90 | CES86 = 90 |
| CES12 = 62 | CES37 = 97 | CES62 = 78 | CES87 = 92 |
| CES13 = 42 | CES38 = 75 | CES63 = 89 | CES88 = 95 |
| CES14 = 74 | CES39 = 97 | CES64 = 85 | CES89 = 90 |
| CES15 = 71 | CES40 = 97 | CES65 = 87 | CES90 = 92 |
| CES16 = 47 | CES41 = 91 | CES66 = 82 | CES91 = 69 |
| CES17 = 48 | CES42 = 99 | CES67 = 82 | CES92 = 81 |
| CES18 = 56 | CES43 = 97 | CES68 = 86 | CES93 = 88 |
| CES19 = 70 | CES44 = 99 | CES69 = 87 | CES94 = 86 |
| CES20 = 65 | CES45 = 97 | CES70 = 86 | CES95 = 83 |
| CES21 = 84 | CES46 = 94 | CES71 = 77 | CES96 = 94 |
| CES22 = 77 | CES47 = 90 | CES72 = 93 | CES97 = 97 |
| CES23 = 91 | CES48 = 83 | CES73 = 82 | CES98 = 94 |
| CES24 = 89 | CES49 = 95 | CES74 = 89 | CES99 = 92 |
| CES25 = 70 | CES50 = 94 | CES75 = 81 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)