

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1216103

Luminaire Tested: 24-ID2-80-CNC-L940-U

Issue Date: 12/5/2025


Test Information

Test Method: LM-79-2019
Report Number: P1216103
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2508-510-9)
Test Lab: INNOVATION CENTER
Issue Date: 12/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 24-ID2-80-CNC-L940-U
Description: 2X4 IN DEPTH TROFFER WITH 2INCH CURVE REGRESSED
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7387.5 lumens
Efficiency: N/A
Efficacy: 106.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.19 / 1.29
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 69.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1216103
CATALOG NUMBER: 24-ID2-80-CNC-L940-U

Luminous Intensity Polar Plot



TEST NUMBER: P1216103

CATALOG NUMBER: 24-ID2-80-CNC-L940-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	109	105	100	97	106	102	99	95	98	95	92		94	92	89		85
2	100	92	85	79	97	90	84	78	86	81	77		83	79	75		71
3	91	81	73	67	89	79	72	66	76	70	65		74	68	64		60
4	84	72	63	57	81	71	63	56	68	61	56		66	60	55		52
5	77	64	56	49	75	63	55	49	61	54	48		59	53	48		45
6	71	58	49	43	69	57	49	43	55	48	42		54	47	42		40
7	66	53	44	38	64	52	44	38	51	43	38		49	42	37		35
8	62	48	40	34	60	48	40	34	46	39	34		45	38	34		32
9	58	44	36	31	56	44	36	31	43	36	31		42	35	30		29
10	54	41	33	28	53	41	33	28	40	33	28		39	32	28		26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3929	3929	3929
5°	3943	3922	3925
10°	3919	3898	3898
15°	3880	3858	3853
20°	3822	3796	3792
25°	3746	3713	3712
30°	3655	3621	3602
35°	3549	3509	3480
40°	3433	3385	3356
45°	3304	3260	3213
50°	3174	3116	3071
55°	3026	2954	2916
60°	2876	2799	2771
65°	2678	2629	2623
70°	2451	2439	2431
75°	2189	2226	2242
80°	1785	1943	2039
85°	1227	1558	1558

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3304 cd/sqm

TEST NUMBER: P1216103
 CATALOG NUMBER: 24-ID2-80-CNC-L940-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	275.7	3.7
10°-20°	780.8	10.6
20°-30°	1153.1	15.6
30°-40°	1336.9	18.1
40°-50°	1320.6	17.9
50°-60°	1131.4	15.3
60°-70°	821.0	11.1
70°-80°	453.1	6.1
80°-90°	114.9	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2209.7	29.9
0°-40°	3546.5	48.0
0°-60°	5998.6	81.2
0°-90°	7387.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7387.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2920	2920	2920	2920	2920	
5°	2919	2908	2904	2899	2906	277
15°	2786	2775	2769	2763	2766	785
25°	2524	2513	2501	2496	2500	1162
35°	2161	2152	2136	2126	2119	1352
45°	1736	1725	1713	1696	1688	1341
55°	1290	1278	1259	1249	1243	1154
65°	841	834	826	822	824	833
75°	421	419	428	431	431	445
85°	80	88	101	102	101	100
90°	0	0	0	0	0	

TEST NUMBER: P1216103

CATALOG NUMBER: 24-ID2-80-CNC-L940-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2920.2	2920.2	2920.2	2920.2	2920.2
2.5°	2930.4	2920.2	2915.1	2911.0	2917.1
5°	2919.2	2908.0	2903.9	2898.8	2905.9
7.5°	2896.7	2887.6	2882.5	2878.4	2882.5
10°	2868.2	2858.0	2852.9	2849.8	2852.9
12.5°	2830.5	2823.3	2815.2	2809.1	2815.2
15°	2785.6	2775.4	2769.3	2763.2	2766.2
17.5°	2730.5	2721.4	2713.2	2708.1	2711.2
20°	2669.4	2658.1	2651.0	2645.9	2648.0
22.5°	2605.1	2590.9	2581.7	2573.5	2574.5
25°	2523.6	2513.4	2501.1	2496.0	2500.1
27.5°	2439.9	2428.7	2418.5	2410.4	2408.3
30°	2352.3	2342.1	2330.9	2321.7	2318.6
32.5°	2264.6	2247.2	2235.0	2225.8	2224.8
35°	2160.6	2152.4	2136.1	2125.9	2118.8
37.5°	2061.7	2049.4	2033.1	2023.9	2016.8
40°	1954.6	1942.4	1927.1	1913.8	1910.8
42.5°	1846.5	1837.4	1817.0	1808.8	1803.7
45°	1736.4	1725.2	1713.0	1695.6	1688.5
47.5°	1631.4	1620.2	1599.8	1584.5	1580.4
50°	1516.2	1502.9	1488.6	1470.3	1467.2
52.5°	1407.1	1391.8	1373.4	1365.3	1359.2
55°	1289.8	1277.6	1259.2	1249.0	1242.9
57.5°	1173.6	1166.4	1154.2	1139.9	1138.9
60°	1068.6	1054.3	1040.0	1029.8	1029.8
62.5°	951.3	946.2	931.9	925.8	922.8
65°	841.2	834.0	825.9	821.8	823.9
67.5°	728.0	727.0	720.9	721.9	719.9
70°	623.0	618.9	619.9	622.0	617.9
72.5°	521.0	518.0	523.1	524.1	526.1
75°	421.1	419.1	428.2	431.3	431.3
77.5°	321.2	327.3	337.5	345.7	345.7
80°	230.4	238.6	250.8	258.0	263.1
82.5°	147.8	161.1	172.3	177.4	177.4
85°	79.5	87.7	100.9	102.0	100.9
87.5°	24.5	30.6	36.7	38.7	39.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1216103

CATALOG NUMBER: 24-ID2-80-CNC-L940-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.79	17.39	16.15	17.70	18.02	15.62	17.22	15.98	17.53	17.85
	3H	17.43	18.87	17.81	19.20	19.56	17.31	18.75	17.69	19.08	19.44
	4H	18.01	19.37	18.41	19.72	20.09	17.94	19.30	18.34	19.65	20.02
	6H	18.40	19.65	18.81	20.02	20.41	18.41	19.67	18.82	20.03	20.42
	8H	18.50	19.70	18.92	20.08	20.48	18.56	19.75	18.98	20.14	20.54
	12H	18.55	19.69	18.98	20.08	20.50	18.64	19.79	19.07	20.17	20.60
4H	2H	16.36	17.71	16.75	18.06	18.44	16.22	17.58	16.62	17.92	18.30
	3H	18.21	19.35	18.62	19.75	20.15	18.13	19.26	18.54	19.66	20.06
	4H	18.92	19.94	19.35	20.36	20.79	18.89	19.91	19.32	20.32	20.76
	6H	19.42	20.31	19.88	20.75	21.21	19.48	20.38	19.94	20.82	21.27
	8H	19.56	20.39	20.02	20.84	21.30	19.67	20.51	20.13	20.95	21.42
	12H	19.64	20.39	20.12	20.86	21.33	19.79	20.54	20.27	21.02	21.49
8H	4H	19.20	20.03	19.66	20.48	20.94	19.17	20.01	19.63	20.45	20.91
	6H	19.81	20.50	20.30	20.99	21.47	19.88	20.57	20.37	21.06	21.54
	8H	20.01	20.63	20.52	21.13	21.62	20.14	20.76	20.65	21.27	21.75
	12H	20.14	20.69	20.65	21.18	21.74	20.32	20.87	20.83	21.37	21.93
12H	4H	19.23	19.97	19.71	20.45	20.92	19.19	19.94	19.67	20.42	20.89
	6H	19.85	20.48	20.36	20.98	21.47	19.92	20.55	20.43	21.05	21.54
	8H	20.11	20.65	20.61	21.15	21.71	20.23	20.78	20.74	21.27	21.83

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-11

Test Date: 08/26/2025

Luminaire Tested: 22ID2-55-CFR1-L940-U

Data in this report applies to families of products including 22ID2-55-CFR1-L940-U


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-11
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L940-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 4000K 90CRI

Spectral Parameters

CCT (K): 3910
 CIE u' : 0.2263
 CIE v' : 0.5043
 Duv: 0.0008
 CIE x: 0.3851
 CIE y: 0.3813
 CIE z: 0.2336
 Peak Wavelength (nm): 451
 Dominant Wavelength (nm): 578
 Purity: 30.01895
 R_f: 90.8
 R_g: 98.8

CRI (Ra): 92.4
 R1: 92.5
 R2: 94.9
 R3: 95.8
 R4: 92.7
 R5: 91.7
 R6: 92.1
 R7: 94.3
 R8: 85.2
 R9: 62.0
 R10: 87.0
 R11: 92.8
 R12: 71.7
 R13: 93.2
 R14: 97.3
 R15: 89.6



Test Conditions


Stabilization Time: 31M
 Operation Time: 1H 31M
 Sphere Temperature (°C): 25.2.

REPORT NUMBER: SP1-2506-458-11


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-11

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-11

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	394	NR	620	868	NR	750	58	NR	880	1	NR
365	0	NR	495	449	NR	625	858	NR	755	49	NR	885	1	NR
370	0	NR	500	505	NR	630	839	NR	760	42	NR	890	1	NR
375	0	NR	505	553	NR	635	813	NR	765	36	NR	895	1	NR
380	0	NR	510	593	NR	640	783	NR	770	31	NR	900	1	NR
385	0	NR	515	628	NR	645	746	NR	775	26	NR	905	1	NR
390	1	NR	520	651	NR	650	702	NR	780	22	NR	910	0	NR
395	4	NR	525	670	NR	655	657	NR	785	19	NR	915	0	NR
400	5	NR	530	687	NR	660	607	NR	790	16	NR	920	0	NR
405	8	NR	535	705	NR	665	559	NR	795	14	NR	925	0	NR
410	12	NR	540	717	NR	670	507	NR	800	12	NR	930	0	NR
415	19	NR	545	731	NR	675	458	NR	805	10	NR	935	0	NR
420	34	NR	550	745	NR	680	413	NR	810	9	NR	940	0	NR
425	60	NR	555	757	NR	685	367	NR	815	7	NR	945	0	NR
430	107	NR	560	767	NR	690	328	NR	820	6	NR	950	0	NR
435	194	NR	565	777	NR	695	289	NR	825	5	NR	955	0	NR
440	349	NR	570	785	NR	700	253	NR	830	5	NR	960	0	NR
445	678	NR	575	794	NR	705	221	NR	835	4	NR	965	0	NR
450	997	NR	580	809	NR	710	192	NR	840	3	NR	970	0	NR
455	819	NR	585	820	NR	715	165	NR	845	3	NR	975	0	NR
460	581	NR	590	838	NR	720	144	NR	850	2	NR	980	0	NR
465	517	NR	595	851	NR	725	124	NR	855	2	NR	985	0	NR
470	406	NR	600	861	NR	730	107	NR	860	2	NR	990	0	NR
475	327	NR	605	873	NR	735	91	NR	865	2	NR	995	0	NR
480	330	NR	610	875	NR	740	78	NR	870	1	NR	1000	0	NR
485	356	NR	615	877	NR	745	67	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-11

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.75

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	394	NR	620	868	NR	750	58	NR	880	1	NR
365	0	NR	495	449	NR	625	858	NR	755	49	NR	885	1	NR
370	0	NR	500	505	NR	630	839	NR	760	42	NR	890	1	NR
375	0	NR	505	553	NR	635	813	NR	765	36	NR	895	1	NR
380	0	NR	510	593	NR	640	783	NR	770	31	NR	900	1	NR
385	0	NR	515	628	NR	645	746	NR	775	26	NR	905	1	NR
390	1	NR	520	651	NR	650	702	NR	780	22	NR	910	0	NR
395	4	NR	525	670	NR	655	657	NR	785	19	NR	915	0	NR
400	5	NR	530	687	NR	660	607	NR	790	16	NR	920	0	NR
405	8	NR	535	705	NR	665	559	NR	795	14	NR	925	0	NR
410	12	NR	540	717	NR	670	507	NR	800	12	NR	930	0	NR
415	19	NR	545	731	NR	675	458	NR	805	10	NR	935	0	NR
420	34	NR	550	745	NR	680	413	NR	810	9	NR	940	0	NR
425	60	NR	555	757	NR	685	367	NR	815	7	NR	945	0	NR
430	107	NR	560	767	NR	690	328	NR	820	6	NR	950	0	NR
435	194	NR	565	777	NR	695	289	NR	825	5	NR	955	0	NR
440	349	NR	570	785	NR	700	253	NR	830	5	NR	960	0	NR
445	678	NR	575	794	NR	705	221	NR	835	4	NR	965	0	NR
450	997	NR	580	809	NR	710	192	NR	840	3	NR	970	0	NR
455	819	NR	585	820	NR	715	165	NR	845	3	NR	975	0	NR
460	581	NR	590	838	NR	720	144	NR	850	2	NR	980	0	NR
465	517	NR	595	851	NR	725	124	NR	855	2	NR	985	0	NR
470	406	NR	600	861	NR	730	107	NR	860	2	NR	990	0	NR
475	327	NR	605	873	NR	735	91	NR	865	2	NR	995	0	NR
480	330	NR	610	875	NR	740	78	NR	870	1	NR	1000	0	NR
485	356	NR	615	877	NR	745	67	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-11

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 3.61


λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	394	NR	620	868	NR	750	58	NR	880	1	NR
365	0	NR	495	449	NR	625	858	NR	755	49	NR	885	1	NR
370	0	NR	500	505	NR	630	839	NR	760	42	NR	890	1	NR
375	0	NR	505	553	NR	635	813	NR	765	36	NR	895	1	NR
380	0	NR	510	593	NR	640	783	NR	770	31	NR	900	1	NR
385	0	NR	515	628	NR	645	746	NR	775	26	NR	905	1	NR
390	1	NR	520	651	NR	650	702	NR	780	22	NR	910	0	NR
395	4	NR	525	670	NR	655	657	NR	785	19	NR	915	0	NR
400	5	NR	530	687	NR	660	607	NR	790	16	NR	920	0	NR
405	8	NR	535	705	NR	665	559	NR	795	14	NR	925	0	NR
410	12	NR	540	717	NR	670	507	NR	800	12	NR	930	0	NR
415	19	NR	545	731	NR	675	458	NR	805	10	NR	935	0	NR
420	34	NR	550	745	NR	680	413	NR	810	9	NR	940	0	NR
425	60	NR	555	757	NR	685	367	NR	815	7	NR	945	0	NR
430	107	NR	560	767	NR	690	328	NR	820	6	NR	950	0	NR
435	194	NR	565	777	NR	695	289	NR	825	5	NR	955	0	NR
440	349	NR	570	785	NR	700	253	NR	830	5	NR	960	0	NR
445	678	NR	575	794	NR	705	221	NR	835	4	NR	965	0	NR
450	997	NR	580	809	NR	710	192	NR	840	3	NR	970	0	NR
455	819	NR	585	820	NR	715	165	NR	845	3	NR	975	0	NR
460	581	NR	590	838	NR	720	144	NR	850	2	NR	980	0	NR
465	517	NR	595	851	NR	725	124	NR	855	2	NR	985	0	NR
470	406	NR	600	861	NR	730	107	NR	860	2	NR	990	0	NR
475	327	NR	605	873	NR	735	91	NR	865	2	NR	995	0	NR
480	330	NR	610	875	NR	740	78	NR	870	1	NR	1000	0	NR
485	356	NR	615	877	NR	745	67	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-11





TM-30-18

Summary

$R_f = 90.8$
 $R_g = 98.8$
 $CIE R_a = 92.4$
 $R_9 = 62.0$




Color Vector Graphics







Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 93	CES51 = 96	CES76 = 85
CES02 = 62	CES27 = 90	CES52 = 98	CES77 = 88
CES03 = 31	CES28 = 96	CES53 = 96	CES78 = 82
CES04 = 69	CES29 = 96	CES54 = 92	CES79 = 96
CES05 = 49	CES30 = 90	CES55 = 90	CES80 = 93
CES06 = 50	CES31 = 97	CES56 = 93	CES81 = 89
CES07 = 42	CES32 = 91	CES57 = 91	CES82 = 97
CES08 = 41	CES33 = 98	CES58 = 92	CES83 = 98
CES09 = 29	CES34 = 93	CES59 = 96	CES84 = 93
CES10 = 74	CES35 = 96	CES60 = 91	CES85 = 83
CES11 = 57	CES36 = 79	CES61 = 91	CES86 = 88
CES12 = 63	CES37 = 95	CES62 = 84	CES87 = 91
CES13 = 43	CES38 = 85	CES63 = 91	CES88 = 96
CES14 = 74	CES39 = 99	CES64 = 87	CES89 = 87
CES15 = 71	CES40 = 98	CES65 = 87	CES90 = 96
CES16 = 47	CES41 = 96	CES66 = 84	CES91 = 71
CES17 = 49	CES42 = 95	CES67 = 83	CES92 = 79
CES18 = 56	CES43 = 95	CES68 = 86	CES93 = 87
CES19 = 71	CES44 = 99	CES69 = 87	CES94 = 81
CES20 = 66	CES45 = 98	CES70 = 84	CES95 = 82
CES21 = 85	CES46 = 97	CES71 = 77	CES96 = 91
CES22 = 78	CES47 = 97	CES72 = 93	CES97 = 96
CES23 = 91	CES48 = 90	CES73 = 78	CES98 = 94
CES24 = 90	CES49 = 96	CES74 = 91	CES99 = 91
CES25 = 71	CES50 = 97	CES75 = 80	



Color Rendition by Hue-Angle Bin



Measure Comparisons


(END OF REPORT)