

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1216218

Luminaire Tested: 24-ID2-80-CNV-L835-U

Issue Date: 12/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1216218
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2508-510-5)
Test Lab: INNOVATION CENTER
Issue Date: 12/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 24-ID2-80-CNV-L835-U
Description: 2X4 IN DEPTH TROFFER WITH 2INCH CURVE DROP
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8287.1 lumens
Efficiency: N/A
Efficacy: 119.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.2 / 1.31
Luminous Opening: Rectangular w/ Sides (W: 2' x L: 4' x H: 0.16')
CIE Type: Direct

Input Watts (W): 69.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1216218
CATALOG NUMBER: 24-ID2-80-CNV-L835-U

Luminous Intensity Polar Plot



TEST NUMBER: P1216218

CATALOG NUMBER: 24-ID2-80-CNV-L835-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	110	110	110	106	106	106	101	101	101
1	108	104	99	95	105	101	97	94	97	93	90	93	90	87	89	87	85
2	99	90	84	78	96	88	82	77	85	79	75	81	77	73	78	74	71
3	90	80	71	65	87	78	70	64	75	68	63	72	66	62	69	65	61
4	83	71	62	55	80	69	61	55	67	60	54	64	58	53	62	57	52
5	76	63	54	48	74	62	54	47	60	52	47	58	51	46	56	50	46
6	70	57	48	42	68	56	48	42	54	47	41	52	46	41	51	45	40
7	65	52	43	37	63	51	43	37	49	42	36	48	41	36	46	40	36
8	61	47	39	33	59	47	39	33	45	38	33	44	37	32	43	37	32
9	57	44	35	30	55	43	35	30	42	35	30	40	34	29	39	33	29
10	53	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4175	4175	4175
5°	4172	4136	4143
10°	4137	4082	4092
15°	4082	4014	4026
20°	4006	3928	3938
25°	3915	3823	3836
30°	3817	3707	3712
35°	3700	3569	3579
40°	3572	3424	3428
45°	3440	3276	3271
50°	3289	3106	3107
55°	3141	2938	2909
60°	2979	2743	2723
65°	2798	2531	2501
70°	2581	2280	2290
75°	2323	2019	2056
80°	1966	1747	1884
85°	1576	1541	1805

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3440 cd/sqm

TEST NUMBER: P1216218
 CATALOG NUMBER: 24-ID2-80-CNV-L835-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	293.1	3.5
10°-20°	831.6	10.0
20°-30°	1233.6	14.9
30°-40°	1441.4	17.4
40°-50°	1440.7	17.4
50°-60°	1254.3	15.1
60°-70°	929.8	11.2
70°-80°	546.1	6.6
80°-90°	219.2	2.6
90°-100°	57.3	0.7
100°-110°	18.7	0.2
110°-120°	10.8	0.1
120°-130°	5.9	0.1
130°-140°	3.0	0.0
140°-150°	1.4	0.0
150°-160°	0.1	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2358.3	28.5
0°-40°	3799.7	45.9
0°-60°	6494.7	78.4
0°-90°	8189.9	98.8
90°-120°	86.8	1.0
90°-150°	97.1	1.2
90°-180°	97.0	1.2
0°-180°	8287.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3103	3103	3103	3103	3103	
5°	3100	3090	3085	3081	3089	294
15°	2962	2952	2947	2946	2952	835
25°	2686	2681	2677	2675	2680	1238
35°	2316	2310	2302	2301	2301	1448
45°	1880	1877	1868	1861	1857	1450
55°	1416	1412	1404	1399	1382	1265
65°	954	946	940	926	920	944
75°	514	509	511	515	514	543
85°	149	168	197	219	224	156
90°	60	77	100	118	123	37
95°	51	43	43	51	54	40
105°	35	30	17	4	0	38
115°	23	19	10	2	0	23
125°	15	11	7	1	0	13
135°	8	7	3	1	0	7
145°	4	3	1	1	1	3
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1216218

CATALOG NUMBER: 24-ID2-80-CNV-L835-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3103.0	3103.0	3103.0	3103.0	3103.0
2.5°	3113.2	3101.8	3097.3	3093.9	3099.6
5°	3099.6	3090.5	3084.8	3081.4	3089.3
7.5°	3079.1	3068.9	3063.2	3060.9	3067.8
10°	3049.6	3037.1	3032.5	3030.3	3037.1
12.5°	3009.8	2999.6	2995.0	2992.8	2999.6
15°	2962.1	2951.9	2947.3	2946.2	2951.9
17.5°	2906.4	2896.2	2890.5	2890.5	2897.3
20°	2838.2	2831.4	2828.0	2826.9	2830.3
22.5°	2770.1	2759.8	2758.7	2754.2	2762.1
25°	2686.0	2681.4	2676.9	2674.6	2680.3
27.5°	2607.6	2595.1	2589.4	2590.5	2594.0
30°	2513.3	2505.3	2503.1	2497.4	2499.7
32.5°	2415.6	2409.9	2407.6	2400.8	2400.8
35°	2315.6	2309.9	2302.0	2300.8	2300.8
37.5°	2212.2	2206.5	2199.7	2194.0	2196.3
40°	2102.0	2096.3	2088.3	2087.2	2082.7
42.5°	1994.0	1988.4	1979.3	1978.1	1973.6
45°	1880.4	1877.0	1867.9	1861.1	1856.6
47.5°	1766.8	1761.1	1750.9	1744.1	1740.7
50°	1646.4	1640.7	1633.9	1627.0	1625.9
52.5°	1530.5	1529.3	1519.1	1513.4	1507.7
55°	1415.7	1412.3	1404.4	1398.7	1381.6
57.5°	1296.4	1294.1	1289.6	1277.1	1266.9
60°	1183.9	1177.1	1169.2	1154.4	1152.1
62.5°	1064.6	1064.6	1052.1	1040.8	1036.2
65°	954.4	946.5	939.6	926.0	920.3
67.5°	839.7	838.5	826.0	818.1	807.8
70°	728.3	724.9	714.7	712.4	710.1
72.5°	617.0	615.8	613.6	611.3	605.6
75°	513.6	509.0	511.3	514.7	513.6
77.5°	409.0	414.7	417.0	427.2	428.3
80°	311.3	320.4	334.0	350.0	353.4
82.5°	222.7	235.2	261.3	281.8	286.3
85°	148.8	168.2	196.6	219.3	223.8
87.5°	92.0	113.6	144.3	165.9	169.3
90°	60.2	77.3	100.0	118.2	122.7
92.5°	55.7	54.5	67.0	80.7	85.2
95°	51.1	43.2	43.2	51.1	54.5
97.5°	47.7	39.8	27.3	28.4	29.5
100°	43.2	36.4	20.5	12.5	12.5
102.5°	39.8	32.9	18.2	4.5	1.1
105°	35.2	29.5	17.0	4.5	0.0
107.5°	31.8	27.3	14.8	3.4	0.0
110°	28.4	23.9	13.6	3.4	0.0

TEST NUMBER: P1216218

CATALOG NUMBER: 24-ID2-80-CNV-L835-U

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	26.1	21.6	12.5	2.3	0.0
115°	22.7	19.3	10.2	2.3	0.0
117.5°	20.5	17.0	9.1	1.1	0.0
120°	18.2	14.8	8.0	1.1	0.0
122.5°	15.9	13.6	6.8	1.1	0.0
125°	14.8	11.4	6.8	1.1	0.0
127.5°	12.5	10.2	5.7	0.0	0.0
130°	11.4	9.1	4.5	0.0	0.0
132.5°	10.2	8.0	3.4	1.1	0.0
135°	8.0	6.8	3.4	1.1	0.0
137.5°	6.8	5.7	2.3	1.1	1.1
140°	5.7	4.5	2.3	1.1	1.1
142.5°	5.7	4.5	2.3	1.1	1.1
145°	4.5	3.4	1.1	1.1	1.1
147.5°	3.4	2.3	1.1	1.1	1.1
150°	2.3	2.3	1.1	1.1	1.1
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1216218

CATALOG NUMBER: 24-ID2-80-CNV-L835-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.58	17.18	15.97	17.52	17.86	15.60	17.19	15.98	17.53	17.88
	3H	17.25	18.69	17.65	19.04	19.43	17.28	18.72	17.67	19.07	19.46
	4H	17.85	19.21	18.27	19.58	19.98	17.93	19.29	18.35	19.66	20.07
	6H	18.27	19.53	18.70	19.92	20.34	18.47	19.73	18.90	20.12	20.54
	8H	18.39	19.60	18.84	20.01	20.44	18.70	19.90	19.14	20.32	20.74
	12H	18.47	19.63	18.92	20.03	20.49	18.91	20.06	19.36	20.47	20.93
4H	2H	16.15	17.51	16.57	17.89	18.29	16.17	17.53	16.58	17.90	18.30
	3H	18.03	19.17	18.46	19.59	20.02	18.06	19.20	18.49	19.62	20.05
	4H	18.75	19.79	19.20	20.22	20.69	18.84	19.87	19.29	20.31	20.77
	6H	19.29	20.20	19.77	20.66	21.15	19.52	20.43	19.99	20.89	21.37
	8H	19.46	20.31	19.94	20.78	21.27	19.81	20.66	20.29	21.12	21.62
	12H	19.59	20.35	20.08	20.85	21.34	20.09	20.85	20.59	21.35	21.85
8H	4H	19.03	19.88	19.51	20.35	20.84	19.11	19.96	19.59	20.43	20.92
	6H	19.69	20.40	20.20	20.91	21.41	19.92	20.63	20.44	21.14	21.64
	8H	19.93	20.57	20.46	21.09	21.61	20.31	20.95	20.84	21.47	21.98
	12H	20.13	20.69	20.65	21.20	21.79	20.70	21.27	21.23	21.78	22.36
12H	4H	19.07	19.83	19.57	20.33	20.83	19.14	19.90	19.64	20.40	20.90
	6H	19.75	20.39	20.28	20.92	21.43	19.97	20.61	20.50	21.14	21.65
	8H	20.05	20.62	20.58	21.13	21.72	20.42	20.99	20.95	21.50	22.09

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-1

Test Date: 07/23/2025

Luminaire Tested: 22ID2-55-CFR1-L835-U

Data in this report applies to families of products including 22ID2-55-CFR1-L835-U


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-1
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L835-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 3500K 80CRI

Spectral Parameters

CCT (K): 3440
 CIE u' : 0.2370
 CIE v' : 0.5132
 Duv: 0.0005
 CIE x: 0.4093
 CIE y: 0.3940
 CIE z: 0.1967
 Peak Wavelength (nm): 599
 Dominant Wavelength (nm): 580
 Purity: 41.09375
 R_f: 84.9
 R_g: 94.6

CRI (Ra): 84.2
 R1: 82.8
 R2: 91.7
 R3: 96.7
 R4: 81.9
 R5: 82.6
 R6: 88.8
 R7: 85.0
 R8: 63.7
 R9: 13.6
 R10: 80.1
 R11: 81.1
 R12: 65.8
 R13: 85.2
 R14: 98.7
 R15: 76.2



Test Conditions


Stabilization Time: 36M
 Operation Time: 1H 36M
 Sphere Temperature (°C): 24.0

REPORT NUMBER: SP1-2506-458-1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-1

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-1

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	295	NR	620	910	NR	750	30	NR	880	1	NR
365	0	NR	495	335	NR	625	862	NR	755	25	NR	885	1	NR
370	0	NR	500	390	NR	630	809	NR	760	21	NR	890	1	NR
375	0	NR	505	445	NR	635	752	NR	765	18	NR	895	0	NR
380	0	NR	510	490	NR	640	694	NR	770	16	NR	900	0	NR
385	0	NR	515	532	NR	645	630	NR	775	13	NR	905	0	NR
390	0	NR	520	563	NR	650	571	NR	780	12	NR	910	0	NR
395	2	NR	525	588	NR	655	512	NR	785	10	NR	915	0	NR
400	3	NR	530	609	NR	660	453	NR	790	8	NR	920	0	NR
405	5	NR	535	631	NR	665	401	NR	795	7	NR	925	0	NR
410	8	NR	540	654	NR	670	351	NR	800	6	NR	930	0	NR
415	13	NR	545	677	NR	675	306	NR	805	5	NR	935	0	NR
420	23	NR	550	702	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	734	NR	685	230	NR	815	4	NR	945	0	NR
430	70	NR	560	767	NR	690	199	NR	820	4	NR	950	0	NR
435	126	NR	565	802	NR	695	171	NR	825	3	NR	955	0	NR
440	221	NR	570	838	NR	700	146	NR	830	3	NR	960	0	NR
445	418	NR	575	875	NR	705	125	NR	835	2	NR	965	0	NR
450	729	NR	580	913	NR	710	107	NR	840	2	NR	970	0	NR
455	816	NR	585	946	NR	715	90	NR	845	2	NR	975	0	NR
460	578	NR	590	976	NR	720	77	NR	850	1	NR	980	0	NR
465	458	NR	595	992	NR	725	66	NR	855	1	NR	985	0	NR
470	390	NR	600	999	NR	730	56	NR	860	1	NR	990	0	NR
475	299	NR	605	995	NR	735	47	NR	865	1	NR	995	0	NR
480	260	NR	610	975	NR	740	40	NR	870	1	NR	1000	0	NR
485	271	NR	615	948	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-1

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.53

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	295	NR	620	910	NR	750	30	NR	880	1	NR
365	0	NR	495	335	NR	625	862	NR	755	25	NR	885	1	NR
370	0	NR	500	390	NR	630	809	NR	760	21	NR	890	1	NR
375	0	NR	505	445	NR	635	752	NR	765	18	NR	895	0	NR
380	0	NR	510	490	NR	640	694	NR	770	16	NR	900	0	NR
385	0	NR	515	532	NR	645	630	NR	775	13	NR	905	0	NR
390	0	NR	520	563	NR	650	571	NR	780	12	NR	910	0	NR
395	2	NR	525	588	NR	655	512	NR	785	10	NR	915	0	NR
400	3	NR	530	609	NR	660	453	NR	790	8	NR	920	0	NR
405	5	NR	535	631	NR	665	401	NR	795	7	NR	925	0	NR
410	8	NR	540	654	NR	670	351	NR	800	6	NR	930	0	NR
415	13	NR	545	677	NR	675	306	NR	805	5	NR	935	0	NR
420	23	NR	550	702	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	734	NR	685	230	NR	815	4	NR	945	0	NR
430	70	NR	560	767	NR	690	199	NR	820	4	NR	950	0	NR
435	126	NR	565	802	NR	695	171	NR	825	3	NR	955	0	NR
440	221	NR	570	838	NR	700	146	NR	830	3	NR	960	0	NR
445	418	NR	575	875	NR	705	125	NR	835	2	NR	965	0	NR
450	729	NR	580	913	NR	710	107	NR	840	2	NR	970	0	NR
455	816	NR	585	946	NR	715	90	NR	845	2	NR	975	0	NR
460	578	NR	590	976	NR	720	77	NR	850	1	NR	980	0	NR
465	458	NR	595	992	NR	725	66	NR	855	1	NR	985	0	NR
470	390	NR	600	999	NR	730	56	NR	860	1	NR	990	0	NR
475	299	NR	605	995	NR	735	47	NR	865	1	NR	995	0	NR
480	260	NR	610	975	NR	740	40	NR	870	1	NR	1000	0	NR
485	271	NR	615	948	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.07


λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	295	NR	620	910	NR	750	30	NR	880	1	NR
365	0	NR	495	335	NR	625	862	NR	755	25	NR	885	1	NR
370	0	NR	500	390	NR	630	809	NR	760	21	NR	890	1	NR
375	0	NR	505	445	NR	635	752	NR	765	18	NR	895	0	NR
380	0	NR	510	490	NR	640	694	NR	770	16	NR	900	0	NR
385	0	NR	515	532	NR	645	630	NR	775	13	NR	905	0	NR
390	0	NR	520	563	NR	650	571	NR	780	12	NR	910	0	NR
395	2	NR	525	588	NR	655	512	NR	785	10	NR	915	0	NR
400	3	NR	530	609	NR	660	453	NR	790	8	NR	920	0	NR
405	5	NR	535	631	NR	665	401	NR	795	7	NR	925	0	NR
410	8	NR	540	654	NR	670	351	NR	800	6	NR	930	0	NR
415	13	NR	545	677	NR	675	306	NR	805	5	NR	935	0	NR
420	23	NR	550	702	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	734	NR	685	230	NR	815	4	NR	945	0	NR
430	70	NR	560	767	NR	690	199	NR	820	4	NR	950	0	NR
435	126	NR	565	802	NR	695	171	NR	825	3	NR	955	0	NR
440	221	NR	570	838	NR	700	146	NR	830	3	NR	960	0	NR
445	418	NR	575	875	NR	705	125	NR	835	2	NR	965	0	NR
450	729	NR	580	913	NR	710	107	NR	840	2	NR	970	0	NR
455	816	NR	585	946	NR	715	90	NR	845	2	NR	975	0	NR
460	578	NR	590	976	NR	720	77	NR	850	1	NR	980	0	NR
465	458	NR	595	992	NR	725	66	NR	855	1	NR	985	0	NR
470	390	NR	600	999	NR	730	56	NR	860	1	NR	990	0	NR
475	299	NR	605	995	NR	735	47	NR	865	1	NR	995	0	NR
480	260	NR	610	975	NR	740	40	NR	870	1	NR	1000	0	NR
485	271	NR	615	948	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-1





TM-30-18

Summary

$R_f = 84.9$
 $R_g = 94.6$
 $CIE R_a = 84.2$
 $R_9 = 13.6$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 87	CES51 = 92	CES76 = 81
CES02 = 62	CES27 = 91	CES52 = 93	CES77 = 85
CES03 = 31	CES28 = 94	CES53 = 90	CES78 = 80
CES04 = 70	CES29 = 92	CES54 = 89	CES79 = 92
CES05 = 49	CES30 = 89	CES55 = 86	CES80 = 90
CES06 = 51	CES31 = 94	CES56 = 85	CES81 = 77
CES07 = 41	CES32 = 86	CES57 = 83	CES82 = 96
CES08 = 40	CES33 = 97	CES58 = 84	CES83 = 96
CES09 = 29	CES34 = 91	CES59 = 91	CES84 = 91
CES10 = 75	CES35 = 95	CES60 = 89	CES85 = 76
CES11 = 58	CES36 = 79	CES61 = 87	CES86 = 73
CES12 = 64	CES37 = 95	CES62 = 81	CES87 = 85
CES13 = 43	CES38 = 84	CES63 = 85	CES88 = 89
CES14 = 74	CES39 = 98	CES64 = 78	CES89 = 78
CES15 = 71	CES40 = 97	CES65 = 78	CES90 = 90
CES16 = 47	CES41 = 95	CES66 = 75	CES91 = 71
CES17 = 50	CES42 = 96	CES67 = 74	CES92 = 65
CES18 = 56	CES43 = 92	CES68 = 79	CES93 = 79
CES19 = 72	CES44 = 99	CES69 = 83	CES94 = 64
CES20 = 66	CES45 = 95	CES70 = 77	CES95 = 74
CES21 = 86	CES46 = 91	CES71 = 71	CES96 = 85
CES22 = 78	CES47 = 94	CES72 = 90	CES97 = 90
CES23 = 92	CES48 = 83	CES73 = 72	CES98 = 86
CES24 = 90	CES49 = 92	CES74 = 90	CES99 = 79
CES25 = 72	CES50 = 93	CES75 = 75	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)