

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1216060

Luminaire Tested: 24-ID2-55-CNC-L850-U

Issue Date: 12/5/2025


Test Information

Test Method: LM-79-2019
Report Number: P1216060
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2508-510-9)
Test Lab: INNOVATION CENTER
Issue Date: 12/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 24-ID2-55-CNC-L850-U
Description: 2X4 IN DEPTH TROFFER WITH 2INCH CURVE REGRESSED
Light Source: 5000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5898.2 lumens
Efficiency: N/A
Efficacy: 124.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.19 / 1.29
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 47.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1216060
CATALOG NUMBER: 24-ID2-55-CNC-L850-U

Luminous Intensity Polar Plot



TEST NUMBER: P1216060

CATALOG NUMBER: 24-ID2-55-CNC-L850-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	109	105	100	97	106	102	99	95	98	95	92		94	92	89		85
2	100	92	85	79	97	90	84	78	86	81	77		83	79	75		71
3	91	81	73	67	89	79	72	66	76	70	65		74	68	64		60
4	84	72	63	57	81	71	63	56	68	61	56		66	60	55		52
5	77	64	56	49	75	63	55	49	61	54	48		59	53	48		45
6	71	58	49	43	69	57	49	43	55	48	42		54	47	42		40
7	66	53	44	38	64	52	44	38	51	43	38		49	42	37		35
8	62	48	40	34	60	48	40	34	46	39	34		45	38	34		32
9	58	44	36	31	56	44	36	31	43	36	31		42	35	30		29
10	54	41	33	28	53	41	33	28	40	33	28		39	32	28		26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3137	3137	3137
5°	3148	3131	3134
10°	3129	3112	3112
15°	3098	3080	3076
20°	3052	3031	3027
25°	2991	2965	2963
30°	2918	2891	2876
35°	2833	2801	2779
40°	2741	2702	2680
45°	2638	2602	2565
50°	2534	2488	2452
55°	2416	2358	2328
60°	2296	2235	2213
65°	2138	2099	2094
70°	1957	1947	1941
75°	1748	1777	1790
80°	1426	1552	1627
85°	980	1244	1244

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2638 cd/sqm

TEST NUMBER: P1216060
 CATALOG NUMBER: 24-ID2-55-CNC-L850-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	220.2	3.7
10°-20°	623.4	10.6
20°-30°	920.7	15.6
30°-40°	1067.4	18.1
40°-50°	1054.4	17.9
50°-60°	903.3	15.3
60°-70°	655.5	11.1
70°-80°	361.8	6.1
80°-90°	91.7	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1764.2	29.9
0°-40°	2831.6	48.0
0°-60°	4789.3	81.2
0°-90°	5898.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5898.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2332	2332	2332	2332	2332	
5°	2331	2322	2318	2314	2320	221
15°	2224	2216	2211	2206	2209	627
25°	2015	2007	1997	1993	1996	928
35°	1725	1718	1706	1697	1692	1079
45°	1386	1377	1368	1354	1348	1071
55°	1030	1020	1005	997	992	921
65°	672	666	659	656	658	665
75°	336	335	342	344	344	356
85°	64	70	81	81	81	80
90°	0	0	0	0	0	

TEST NUMBER: P1216060

CATALOG NUMBER: 24-ID2-55-CNC-L850-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2331.5	2331.5	2331.5	2331.5	2331.5
2.5°	2339.6	2331.5	2327.4	2324.2	2329.1
5°	2330.7	2321.7	2318.5	2314.4	2320.1
7.5°	2312.8	2305.4	2301.4	2298.1	2301.4
10°	2290.0	2281.8	2277.8	2275.3	2277.8
12.5°	2259.9	2254.2	2247.6	2242.8	2247.6
15°	2224.0	2215.9	2211.0	2206.1	2208.6
17.5°	2180.1	2172.8	2166.2	2162.2	2164.6
20°	2131.2	2122.3	2116.6	2112.5	2114.1
22.5°	2079.9	2068.6	2061.2	2054.7	2055.5
25°	2014.8	2006.7	1996.9	1992.8	1996.1
27.5°	1948.1	1939.1	1931.0	1924.5	1922.8
30°	1878.1	1869.9	1861.0	1853.6	1851.2
32.5°	1808.1	1794.2	1784.4	1777.1	1776.3
35°	1725.0	1718.5	1705.5	1697.3	1691.6
37.5°	1646.1	1636.3	1623.3	1615.9	1610.2
40°	1560.6	1550.8	1538.6	1528.0	1525.6
42.5°	1474.3	1467.0	1450.7	1444.2	1440.1
45°	1386.4	1377.4	1367.6	1353.8	1348.1
47.5°	1302.5	1293.6	1277.3	1265.1	1261.8
50°	1210.5	1199.9	1188.5	1173.9	1171.4
52.5°	1123.4	1111.2	1096.6	1090.0	1085.2
55°	1029.8	1020.0	1005.4	997.2	992.4
57.5°	937.0	931.3	921.5	910.1	909.3
60°	853.1	841.7	830.4	822.2	822.2
62.5°	759.5	755.5	744.1	739.2	736.7
65°	671.6	665.9	659.4	656.1	657.8
67.5°	581.2	580.4	575.5	576.4	574.7
70°	497.4	494.1	495.0	496.6	493.3
72.5°	416.0	413.5	417.6	418.4	420.1
75°	336.2	334.6	341.9	344.4	344.4
77.5°	256.4	261.3	269.5	276.0	276.0
80°	184.0	190.5	200.3	206.0	210.0
82.5°	118.0	128.6	137.6	141.6	141.6
85°	63.5	70.0	80.6	81.4	80.6
87.5°	19.5	24.4	29.3	30.9	31.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1216060

CATALOG NUMBER: 24-ID2-55-CNC-L850-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.01	16.61	15.37	16.92	17.23	14.84	16.44	15.20	16.75	17.06
	3H	16.65	18.09	17.02	18.42	18.78	16.53	17.97	16.91	18.30	18.66
	4H	17.23	18.59	17.63	18.94	19.31	17.16	18.52	17.56	18.86	19.24
	6H	17.62	18.87	18.03	19.24	19.63	17.63	18.89	18.04	19.25	19.64
	8H	17.71	18.91	18.14	19.30	19.70	17.77	18.97	18.20	19.36	19.76
	12H	17.76	18.91	18.19	19.29	19.72	17.86	19.01	18.29	19.39	19.82
4H	2H	15.57	16.93	15.97	17.28	17.65	15.44	16.79	15.84	17.14	17.52
	3H	17.43	18.57	17.84	18.96	19.36	17.35	18.48	17.76	18.88	19.28
	4H	18.14	19.16	18.57	19.57	20.01	18.10	19.13	18.54	19.54	19.98
	6H	18.64	19.53	19.09	19.97	20.43	18.70	19.59	19.16	20.04	20.49
	8H	18.78	19.61	19.24	20.05	20.52	18.89	19.72	19.35	20.17	20.63
	12H	18.86	19.61	19.34	20.08	20.55	19.01	19.76	19.49	20.24	20.71
8H	4H	18.42	19.25	18.88	19.69	20.16	18.39	19.22	18.85	19.67	20.13
	6H	19.03	19.72	19.52	20.21	20.68	19.10	19.79	19.59	20.28	20.76
	8H	19.22	19.85	19.73	20.35	20.84	19.35	19.98	19.87	20.48	20.97
	12H	19.36	19.91	19.86	20.40	20.96	19.54	20.09	20.05	20.58	21.14
12H	4H	18.44	19.19	18.92	19.67	20.14	18.41	19.16	18.89	19.64	20.11
	6H	19.07	19.70	19.58	20.20	20.69	19.14	19.76	19.65	20.27	20.76
	8H	19.32	19.87	19.83	20.36	20.93	19.45	20.00	19.96	20.49	21.05

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-7

Test Date: 08/26/2025

Luminaire Tested: 22ID2-55-CFR1-L850-U

Data in this report applies to families of products including 22ID2-55-CFR1-L850-U

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L850-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 5000K 80CRI

Spectral Parameters

CCT (K): 4966
 CIE u' : 0.2093
 CIE v' : 0.4890
 Duv: 0.0036
 CIE x: 0.3468
 CIE y: 0.3601
 CIE z: 0.2931
 Peak Wavelength (nm): 450
 Dominant Wavelength (nm): 570
 Purity: 12.1135
 R_f: 84
 R_g: 96.2

CRI (Ra): 83.1
 R1: 81.0
 R2: 87.8
 R3: 92.7
 R4: 82.4
 R5: 81.0
 R6: 82.6
 R7: 88.5
 R8: 68.6
 R9: 10.3
 R10: 70.9
 R11: 81.3
 R12: 55.9
 R13: 82.8
 R14: 96.1
 R15: 75.1



Test Conditions


Stabilization Time: 37M
 Operation Time: 1H 37M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2506-458-7

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-7

Photopic Flux vs. Wavelength

Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	262	NR	620	472	NR	750	15	NR	880	0	NR
365	0	NR	495	307	NR	625	443	NR	755	13	NR	885	0	NR
370	0	NR	500	358	NR	630	412	NR	760	11	NR	890	0	NR
375	0	NR	505	403	NR	635	379	NR	765	9	NR	895	0	NR
380	0	NR	510	440	NR	640	346	NR	770	8	NR	900	0	NR
385	1	NR	515	471	NR	645	313	NR	775	7	NR	905	0	NR
390	3	NR	520	490	NR	650	282	NR	780	6	NR	910	0	NR
395	4	NR	525	504	NR	655	252	NR	785	5	NR	915	0	NR
400	6	NR	530	515	NR	660	223	NR	790	4	NR	920	0	NR
405	9	NR	535	524	NR	665	197	NR	795	4	NR	925	0	NR
410	12	NR	540	530	NR	670	171	NR	800	3	NR	930	0	NR
415	20	NR	545	539	NR	675	149	NR	805	3	NR	935	0	NR
420	36	NR	550	545	NR	680	130	NR	810	2	NR	940	0	NR
425	64	NR	555	554	NR	685	112	NR	815	2	NR	945	0	NR
430	117	NR	560	562	NR	690	97	NR	820	2	NR	950	0	NR
435	212	NR	565	567	NR	695	83	NR	825	2	NR	955	0	NR
440	378	NR	570	571	NR	700	71	NR	830	1	NR	960	0	NR
445	709	NR	575	574	NR	705	61	NR	835	1	NR	965	0	NR
450	1000	NR	580	579	NR	710	52	NR	840	1	NR	970	0	NR
455	789	NR	585	578	NR	715	44	NR	845	1	NR	975	0	NR
460	519	NR	590	578	NR	720	38	NR	850	1	NR	980	0	NR
465	429	NR	595	571	NR	725	32	NR	855	1	NR	985	0	NR
470	316	NR	600	560	NR	730	28	NR	860	1	NR	990	0	NR
475	236	NR	605	545	NR	735	24	NR	865	1	NR	995	0	NR
480	224	NR	610	524	NR	740	20	NR	870	0	NR	1000	0	NR
485	235	NR	615	501	NR	745	17	NR	875	0	NR			

REPORT NUMBER: SP1-2506-458-7

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.94

λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)
360	0	NR	490	262	NR	620	472	NR	750	15	NR	880	0	NR
365	0	NR	495	307	NR	625	443	NR	755	13	NR	885	0	NR
370	0	NR	500	358	NR	630	412	NR	760	11	NR	890	0	NR
375	0	NR	505	403	NR	635	379	NR	765	9	NR	895	0	NR
380	0	NR	510	440	NR	640	346	NR	770	8	NR	900	0	NR
385	1	NR	515	471	NR	645	313	NR	775	7	NR	905	0	NR
390	3	NR	520	490	NR	650	282	NR	780	6	NR	910	0	NR
395	4	NR	525	504	NR	655	252	NR	785	5	NR	915	0	NR
400	6	NR	530	515	NR	660	223	NR	790	4	NR	920	0	NR
405	9	NR	535	524	NR	665	197	NR	795	4	NR	925	0	NR
410	12	NR	540	530	NR	670	171	NR	800	3	NR	930	0	NR
415	20	NR	545	539	NR	675	149	NR	805	3	NR	935	0	NR
420	36	NR	550	545	NR	680	130	NR	810	2	NR	940	0	NR
425	64	NR	555	554	NR	685	112	NR	815	2	NR	945	0	NR
430	117	NR	560	562	NR	690	97	NR	820	2	NR	950	0	NR
435	212	NR	565	567	NR	695	83	NR	825	2	NR	955	0	NR
440	378	NR	570	571	NR	700	71	NR	830	1	NR	960	0	NR
445	709	NR	575	574	NR	705	61	NR	835	1	NR	965	0	NR
450	1000	NR	580	579	NR	710	52	NR	840	1	NR	970	0	NR
455	789	NR	585	578	NR	715	44	NR	845	1	NR	975	0	NR
460	519	NR	590	578	NR	720	38	NR	850	1	NR	980	0	NR
465	429	NR	595	571	NR	725	32	NR	855	1	NR	985	0	NR
470	316	NR	600	560	NR	730	28	NR	860	1	NR	990	0	NR
475	236	NR	605	545	NR	735	24	NR	865	1	NR	995	0	NR
480	224	NR	610	524	NR	740	20	NR	870	0	NR	1000	0	NR
485	235	NR	615	501	NR	745	17	NR	875	0	NR			

REPORT NUMBER: SP1-2506-458-7

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 4.11

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	262	NR	620	472	NR	750	15	NR	880	0	NR
365	0	NR	495	307	NR	625	443	NR	755	13	NR	885	0	NR
370	0	NR	500	358	NR	630	412	NR	760	11	NR	890	0	NR
375	0	NR	505	403	NR	635	379	NR	765	9	NR	895	0	NR
380	0	NR	510	440	NR	640	346	NR	770	8	NR	900	0	NR
385	1	NR	515	471	NR	645	313	NR	775	7	NR	905	0	NR
390	3	NR	520	490	NR	650	282	NR	780	6	NR	910	0	NR
395	4	NR	525	504	NR	655	252	NR	785	5	NR	915	0	NR
400	6	NR	530	515	NR	660	223	NR	790	4	NR	920	0	NR
405	9	NR	535	524	NR	665	197	NR	795	4	NR	925	0	NR
410	12	NR	540	530	NR	670	171	NR	800	3	NR	930	0	NR
415	20	NR	545	539	NR	675	149	NR	805	3	NR	935	0	NR
420	36	NR	550	545	NR	680	130	NR	810	2	NR	940	0	NR
425	64	NR	555	554	NR	685	112	NR	815	2	NR	945	0	NR
430	117	NR	560	562	NR	690	97	NR	820	2	NR	950	0	NR
435	212	NR	565	567	NR	695	83	NR	825	2	NR	955	0	NR
440	378	NR	570	571	NR	700	71	NR	830	1	NR	960	0	NR
445	709	NR	575	574	NR	705	61	NR	835	1	NR	965	0	NR
450	1000	NR	580	579	NR	710	52	NR	840	1	NR	970	0	NR
455	789	NR	585	578	NR	715	44	NR	845	1	NR	975	0	NR
460	519	NR	590	578	NR	720	38	NR	850	1	NR	980	0	NR
465	429	NR	595	571	NR	725	32	NR	855	1	NR	985	0	NR
470	316	NR	600	560	NR	730	28	NR	860	1	NR	990	0	NR
475	236	NR	605	545	NR	735	24	NR	865	1	NR	995	0	NR
480	224	NR	610	524	NR	740	20	NR	870	0	NR	1000	0	NR
485	235	NR	615	501	NR	745	17	NR	875	0	NR			

REPORT NUMBER: SP1-2506-458-7


TM-30-18

Summary

$R_f = 84$
 $R_g = 96.2$
 $\text{CIE } R_a = 83.1$
 $R_9 = 10.3$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 85	CES26 = 80	CES51 = 95	CES76 = 72
CES02 = 60	CES27 = 93	CES52 = 95	CES77 = 81
CES03 = 30	CES28 = 90	CES53 = 89	CES78 = 71
CES04 = 69	CES29 = 85	CES54 = 90	CES79 = 91
CES05 = 47	CES30 = 97	CES55 = 89	CES80 = 87
CES06 = 50	CES31 = 87	CES56 = 86	CES81 = 84
CES07 = 40	CES32 = 79	CES57 = 85	CES82 = 95
CES08 = 39	CES33 = 92	CES58 = 85	CES83 = 95
CES09 = 29	CES34 = 84	CES59 = 92	CES84 = 90
CES10 = 73	CES35 = 91	CES60 = 91	CES85 = 81
CES11 = 56	CES36 = 83	CES61 = 88	CES86 = 79
CES12 = 62	CES37 = 90	CES62 = 85	CES87 = 84
CES13 = 42	CES38 = 93	CES63 = 85	CES88 = 89
CES14 = 74	CES39 = 98	CES64 = 79	CES89 = 79
CES15 = 71	CES40 = 94	CES65 = 76	CES90 = 89
CES16 = 46	CES41 = 99	CES66 = 75	CES91 = 72
CES17 = 48	CES42 = 89	CES67 = 73	CES92 = 67
CES18 = 55	CES43 = 88	CES68 = 78	CES93 = 80
CES19 = 70	CES44 = 99	CES69 = 82	CES94 = 65
CES20 = 64	CES45 = 93	CES70 = 73	CES95 = 73
CES21 = 85	CES46 = 91	CES71 = 67	CES96 = 84
CES22 = 77	CES47 = 96	CES72 = 89	CES97 = 92
CES23 = 91	CES48 = 87	CES73 = 66	CES98 = 86
CES24 = 90	CES49 = 90	CES74 = 92	CES99 = 77
CES25 = 71	CES50 = 95	CES75 = 68	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)