

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1216463

Luminaire Tested: 24-ID2-80-DBR-L940-U

Issue Date: 12/5/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P1216463  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2508-510-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/5/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: 24-ID2-80-DBR-L940-U  
Description: 2X4 IN DEPTH TROFFER WITH 2INCH DOUBLE BARREL REGRESSED  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7392.6 lumens  
Efficiency: N/A  
Efficacy: 107.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 69.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P1216463  
CATALOG NUMBER: 24-ID2-80-DBR-L940-U

### Luminous Intensity Polar Plot



TEST NUMBER: P1216463

CATALOG NUMBER: 24-ID2-80-DBR-L940-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 100 |
| 1   | 109 | 104 | 100 | 96  | 106 | 102 | 98  | 95  | 98  | 95  | 92  |  | 94  | 91  | 89  |  | 84  |
| 2   | 99  | 91  | 85  | 79  | 97  | 89  | 83  | 78  | 86  | 81  | 76  |  | 83  | 78  | 74  |  | 71  |
| 3   | 91  | 80  | 72  | 66  | 88  | 79  | 71  | 65  | 76  | 70  | 64  |  | 73  | 68  | 63  |  | 60  |
| 4   | 83  | 71  | 63  | 56  | 81  | 70  | 62  | 56  | 68  | 61  | 55  |  | 65  | 59  | 54  |  | 51  |
| 5   | 77  | 64  | 55  | 49  | 75  | 63  | 55  | 48  | 61  | 53  | 48  |  | 59  | 52  | 47  |  | 45  |
| 6   | 71  | 58  | 49  | 43  | 69  | 57  | 48  | 42  | 55  | 48  | 42  |  | 53  | 47  | 42  |  | 39  |
| 7   | 66  | 52  | 44  | 38  | 64  | 52  | 43  | 38  | 50  | 43  | 37  |  | 49  | 42  | 37  |  | 35  |
| 8   | 61  | 48  | 40  | 34  | 60  | 47  | 39  | 34  | 46  | 39  | 33  |  | 45  | 38  | 33  |  | 31  |
| 9   | 57  | 44  | 36  | 31  | 56  | 44  | 36  | 30  | 42  | 35  | 30  |  | 41  | 35  | 30  |  | 28  |
| 10  | 54  | 41  | 33  | 28  | 53  | 40  | 33  | 28  | 39  | 32  | 28  |  | 38  | 32  | 27  |  | 26  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 3868 | 3868 | 3868 |
| 5°  | 3881 | 3859 | 3861 |
| 10° | 3856 | 3834 | 3838 |
| 15° | 3815 | 3795 | 3797 |
| 20° | 3754 | 3735 | 3736 |
| 25° | 3676 | 3664 | 3667 |
| 30° | 3581 | 3569 | 3585 |
| 35° | 3474 | 3469 | 3487 |
| 40° | 3344 | 3364 | 3387 |
| 45° | 3223 | 3246 | 3273 |
| 50° | 3072 | 3121 | 3165 |
| 55° | 2923 | 2993 | 3052 |
| 60° | 2744 | 2862 | 2909 |
| 65° | 2568 | 2701 | 2779 |
| 70° | 2363 | 2551 | 2596 |
| 75° | 2131 | 2375 | 2396 |
| 80° | 1809 | 2118 | 2141 |
| 85° | 1385 | 1748 | 1794 |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 67.5°

Vertical Angle: 45°

Luminance: 3273 cd/sqm

TEST NUMBER: P1216463  
 CATALOG NUMBER: 24-ID2-80-DBR-L940-U

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 271.4  | 3.7       |
| 10°-20°   | 768.3  | 10.4      |
| 20°-30°   | 1136.4 | 15.4      |
| 30°-40°   | 1322.7 | 17.9      |
| 40°-50°   | 1316.1 | 17.8      |
| 50°-60°   | 1138.9 | 15.4      |
| 60°-70°   | 837.5  | 11.3      |
| 70°-80°   | 473.0  | 6.4       |
| 80°-90°   | 128.3  | 1.7       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 2176.1 | 29.4      |
| 0°-40°    | 3498.8 | 47.3      |
| 0°-60°    | 5953.8 | 80.5      |
| 0°-90°    | 7392.6 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 7392.6 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|-----|------|-------|------|-------|------|------|
| 0°  | 2875 | 2875  | 2875 | 2875  | 2875 |      |
| 5°  | 2874 | 2863  | 2857 | 2853  | 2858 | 273  |
| 15° | 2739 | 2731  | 2725 | 2720  | 2726 | 772  |
| 25° | 2476 | 2469  | 2468 | 2465  | 2470 | 1140 |
| 35° | 2115 | 2111  | 2112 | 2121  | 2123 | 1322 |
| 45° | 1694 | 1694  | 1706 | 1720  | 1720 | 1304 |
| 55° | 1246 | 1252  | 1276 | 1293  | 1301 | 1114 |
| 65° | 807  | 823   | 848  | 865   | 873  | 801  |
| 75° | 410  | 432   | 457  | 460   | 461  | 435  |
| 85° | 90   | 106   | 113  | 115   | 116  | 107  |
| 90° | 0    | 0     | 0    | 0     | 0    |      |

TEST NUMBER: P1216463

CATALOG NUMBER: 24-ID2-80-DBR-L940-U

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|-------|--------|--------|--------|--------|--------|
| 0°    | 2874.6 | 2874.6 | 2874.6 | 2874.6 | 2874.6 |
| 2.5°  | 2885.8 | 2874.6 | 2868.5 | 2865.4 | 2869.5 |
| 5°    | 2873.6 | 2863.4 | 2857.3 | 2853.2 | 2858.3 |
| 7.5°  | 2853.2 | 2842.0 | 2835.8 | 2831.8 | 2838.9 |
| 10°   | 2822.6 | 2811.4 | 2806.3 | 2803.2 | 2809.3 |
| 12.5° | 2784.9 | 2775.7 | 2769.6 | 2765.5 | 2769.6 |
| 15°   | 2739.0 | 2730.8 | 2724.7 | 2719.6 | 2725.7 |
| 17.5° | 2684.9 | 2674.7 | 2672.7 | 2666.6 | 2671.7 |
| 20°   | 2621.7 | 2613.5 | 2608.4 | 2605.4 | 2609.5 |
| 22.5° | 2556.4 | 2545.2 | 2542.2 | 2539.1 | 2543.2 |
| 25°   | 2475.9 | 2468.7 | 2467.7 | 2464.7 | 2469.8 |
| 27.5° | 2394.3 | 2390.2 | 2385.1 | 2387.2 | 2388.2 |
| 30°   | 2304.6 | 2299.5 | 2297.4 | 2301.5 | 2307.6 |
| 32.5° | 2211.8 | 2207.7 | 2208.7 | 2212.8 | 2224.0 |
| 35°   | 2114.9 | 2110.8 | 2111.8 | 2121.0 | 2123.1 |
| 37.5° | 2016.0 | 2008.8 | 2016.0 | 2022.1 | 2027.2 |
| 40°   | 1903.8 | 1904.8 | 1915.0 | 1923.2 | 1928.3 |
| 42.5° | 1799.8 | 1799.8 | 1810.0 | 1822.2 | 1828.4 |
| 45°   | 1693.8 | 1693.8 | 1706.0 | 1720.3 | 1720.3 |
| 47.5° | 1581.6 | 1579.5 | 1602.0 | 1617.3 | 1622.4 |
| 50°   | 1467.4 | 1471.5 | 1490.8 | 1506.1 | 1512.2 |
| 52.5° | 1360.3 | 1362.3 | 1383.8 | 1400.1 | 1403.1 |
| 55°   | 1246.1 | 1252.2 | 1275.7 | 1293.0 | 1301.2 |
| 57.5° | 1133.9 | 1144.1 | 1167.6 | 1189.0 | 1191.0 |
| 60°   | 1019.7 | 1036.0 | 1063.6 | 1074.8 | 1080.9 |
| 62.5° | 915.7  | 932.0  | 954.5  | 972.8  | 976.9  |
| 65°   | 806.6  | 822.9  | 848.4  | 864.7  | 872.9  |
| 67.5° | 704.6  | 724.0  | 749.5  | 761.7  | 761.7  |
| 70°   | 600.6  | 622.0  | 648.5  | 658.7  | 659.8  |
| 72.5° | 502.7  | 527.2  | 550.6  | 558.8  | 560.8  |
| 75°   | 409.9  | 432.4  | 456.8  | 459.9  | 460.9  |
| 77.5° | 319.2  | 342.6  | 361.0  | 367.1  | 364.0  |
| 80°   | 233.5  | 257.0  | 273.3  | 277.4  | 276.3  |
| 82.5° | 159.1  | 178.5  | 193.7  | 193.7  | 193.7  |
| 85°   | 89.7   | 106.1  | 113.2  | 115.2  | 116.2  |
| 87.5° | 29.6   | 41.8   | 47.9   | 47.9   | 47.9   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

TEST NUMBER: P1216463

CATALOG NUMBER: 24-ID2-80-DBR-L940-U

**CIE UGR TABLE:**

| Reflectances:   |      |                  |       |       |       |       |                |       |       |       |       |
|-----------------|------|------------------|-------|-------|-------|-------|----------------|-------|-------|-------|-------|
| Ceiling         |      | 0.7              | 0.7   | 0.5   | 0.5   | 0.3   | 0.7            | 0.7   | 0.5   | 0.5   | 0.3   |
| Wall            |      | 0.5              | 0.3   | 0.5   | 0.3   | 0.3   | 0.5            | 0.3   | 0.5   | 0.3   | 0.3   |
| Reference plane |      | 0.2              | 0.2   | 0.2   | 0.2   | 0.2   | 0.2            | 0.2   | 0.2   | 0.2   | 0.2   |
| Room dimensions |      | Viewed crosswise |       |       |       |       | Viewed endwise |       |       |       |       |
| X=2H            | Y=2H | 15.62            | 17.23 | 15.99 | 17.54 | 17.86 | 15.90          | 17.51 | 16.27 | 17.82 | 18.14 |
|                 | 3H   | 17.27            | 18.73 | 17.65 | 19.05 | 19.41 | 17.64          | 19.09 | 18.01 | 19.41 | 19.78 |
|                 | 4H   | 17.87            | 19.24 | 18.27 | 19.59 | 19.96 | 18.29          | 19.65 | 18.68 | 20.00 | 20.38 |
|                 | 6H   | 18.28            | 19.55 | 18.70 | 19.92 | 20.31 | 18.76          | 20.03 | 19.17 | 20.39 | 20.78 |
|                 | 8H   | 18.40            | 19.61 | 18.83 | 20.00 | 20.40 | 18.91          | 20.12 | 19.34 | 20.51 | 20.91 |
|                 | 12H  | 18.47            | 19.63 | 18.90 | 20.01 | 20.44 | 19.01          | 20.17 | 19.44 | 20.55 | 20.98 |
| 4H              | 2H   | 16.26            | 17.62 | 16.65 | 17.97 | 18.35 | 16.48          | 17.85 | 16.88 | 18.19 | 18.57 |
|                 | 3H   | 18.14            | 19.28 | 18.55 | 19.68 | 20.08 | 18.44          | 19.59 | 18.85 | 19.99 | 20.39 |
|                 | 4H   | 18.87            | 19.90 | 19.30 | 20.31 | 20.75 | 19.23          | 20.26 | 19.66 | 20.67 | 21.11 |
|                 | 6H   | 19.41            | 20.31 | 19.86 | 20.75 | 21.21 | 19.83          | 20.73 | 20.29 | 21.17 | 21.63 |
|                 | 8H   | 19.57            | 20.41 | 20.03 | 20.86 | 21.32 | 20.03          | 20.88 | 20.49 | 21.32 | 21.78 |
|                 | 12H  | 19.67            | 20.43 | 20.16 | 20.91 | 21.38 | 20.17          | 20.93 | 20.65 | 21.41 | 21.88 |
| 8H              | 4H   | 19.20            | 20.04 | 19.66 | 20.48 | 20.95 | 19.51          | 20.36 | 19.97 | 20.80 | 21.27 |
|                 | 6H   | 19.86            | 20.56 | 20.35 | 21.05 | 21.53 | 20.24          | 20.94 | 20.74 | 21.43 | 21.91 |
|                 | 8H   | 20.09            | 20.72 | 20.60 | 21.23 | 21.72 | 20.52          | 21.15 | 21.03 | 21.65 | 22.14 |
|                 | 12H  | 20.27            | 20.82 | 20.77 | 21.31 | 21.88 | 20.73          | 21.29 | 21.24 | 21.78 | 22.34 |
| 12H             | 4H   | 19.23            | 19.99 | 19.71 | 20.47 | 20.94 | 19.54          | 20.30 | 20.02 | 20.77 | 21.24 |
|                 | 6H   | 19.92            | 20.55 | 20.43 | 21.06 | 21.55 | 20.29          | 20.92 | 20.80 | 21.43 | 21.91 |
|                 | 8H   | 20.22            | 20.77 | 20.72 | 21.26 | 21.83 | 20.62          | 21.18 | 21.13 | 21.67 | 22.23 |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-11

Test Date: 08/26/2025

Luminaire Tested: 22ID2-55-CFR1-L940-U

Data in this report applies to families of products including 22ID2-55-CFR1-L940-U




### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2506-458-11  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 08/27/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Corelite  
 Catalog Number: **22ID2-55-CFR1-L940-U**  
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 4000K 90CRI

### Spectral Parameters

CCT (K): 3910  
 CIE  $u'$ : 0.2263  
 CIE  $v'$ : 0.5043  
 Duv: 0.0008  
 CIE x: 0.3851  
 CIE y: 0.3813  
 CIE z: 0.2336  
 Peak Wavelength (nm): 451  
 Dominant Wavelength (nm): 578  
 Purity: 30.01895  
 R<sub>f</sub>: 90.8  
 R<sub>g</sub>: 98.8

CRI (Ra): 92.4  
 R1: 92.5  
 R2: 94.9  
 R3: 95.8  
 R4: 92.7  
 R5: 91.7  
 R6: 92.1  
 R7: 94.3  
 R8: 85.2  
 R9: 62.0  
 R10: 87.0  
 R11: 92.8  
 R12: 71.7  
 R13: 93.2  
 R14: 97.3  
 R15: 89.6



### Test Conditions


Stabilization Time: 31M  
 Operation Time: 1H 31M  
 Sphere Temperature (°C): 25.2.

REPORT NUMBER: SP1-2506-458-11


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | 76INCH SPHERE IN0058  | 6/16/2025        | 12/16/2025           |
| Power Meter                    | XITRON INXT2011004    | 1/21/2025        | 1/21/2026            |
| AC Power Source                | CHROMA 61603 IN0063   | 10/22/2024       | 10/22/2025           |
| DC Power Source                | AGILENT E3634A IN0208 | 10/22/2024       | 10/22/2025           |
| Sphere Thermometer             | ONSET IN0085          | 10/22/2024       | 10/22/2025           |
| Room Thermometer               | ONSET IN0046          | 10/22/2024       | 10/22/2025           |

REPORT NUMBER: SP1-2506-458-11

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-11

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 394                         | NR               | 620       | 868                         | NR               | 750       | 58                          | NR               | 880       | 1                           | NR               |
| 365       | 0                           | NR               | 495       | 449                         | NR               | 625       | 858                         | NR               | 755       | 49                          | NR               | 885       | 1                           | NR               |
| 370       | 0                           | NR               | 500       | 505                         | NR               | 630       | 839                         | NR               | 760       | 42                          | NR               | 890       | 1                           | NR               |
| 375       | 0                           | NR               | 505       | 553                         | NR               | 635       | 813                         | NR               | 765       | 36                          | NR               | 895       | 1                           | NR               |
| 380       | 0                           | NR               | 510       | 593                         | NR               | 640       | 783                         | NR               | 770       | 31                          | NR               | 900       | 1                           | NR               |
| 385       | 0                           | NR               | 515       | 628                         | NR               | 645       | 746                         | NR               | 775       | 26                          | NR               | 905       | 1                           | NR               |
| 390       | 1                           | NR               | 520       | 651                         | NR               | 650       | 702                         | NR               | 780       | 22                          | NR               | 910       | 0                           | NR               |
| 395       | 4                           | NR               | 525       | 670                         | NR               | 655       | 657                         | NR               | 785       | 19                          | NR               | 915       | 0                           | NR               |
| 400       | 5                           | NR               | 530       | 687                         | NR               | 660       | 607                         | NR               | 790       | 16                          | NR               | 920       | 0                           | NR               |
| 405       | 8                           | NR               | 535       | 705                         | NR               | 665       | 559                         | NR               | 795       | 14                          | NR               | 925       | 0                           | NR               |
| 410       | 12                          | NR               | 540       | 717                         | NR               | 670       | 507                         | NR               | 800       | 12                          | NR               | 930       | 0                           | NR               |
| 415       | 19                          | NR               | 545       | 731                         | NR               | 675       | 458                         | NR               | 805       | 10                          | NR               | 935       | 0                           | NR               |
| 420       | 34                          | NR               | 550       | 745                         | NR               | 680       | 413                         | NR               | 810       | 9                           | NR               | 940       | 0                           | NR               |
| 425       | 60                          | NR               | 555       | 757                         | NR               | 685       | 367                         | NR               | 815       | 7                           | NR               | 945       | 0                           | NR               |
| 430       | 107                         | NR               | 560       | 767                         | NR               | 690       | 328                         | NR               | 820       | 6                           | NR               | 950       | 0                           | NR               |
| 435       | 194                         | NR               | 565       | 777                         | NR               | 695       | 289                         | NR               | 825       | 5                           | NR               | 955       | 0                           | NR               |
| 440       | 349                         | NR               | 570       | 785                         | NR               | 700       | 253                         | NR               | 830       | 5                           | NR               | 960       | 0                           | NR               |
| 445       | 678                         | NR               | 575       | 794                         | NR               | 705       | 221                         | NR               | 835       | 4                           | NR               | 965       | 0                           | NR               |
| 450       | 997                         | NR               | 580       | 809                         | NR               | 710       | 192                         | NR               | 840       | 3                           | NR               | 970       | 0                           | NR               |
| 455       | 819                         | NR               | 585       | 820                         | NR               | 715       | 165                         | NR               | 845       | 3                           | NR               | 975       | 0                           | NR               |
| 460       | 581                         | NR               | 590       | 838                         | NR               | 720       | 144                         | NR               | 850       | 2                           | NR               | 980       | 0                           | NR               |
| 465       | 517                         | NR               | 595       | 851                         | NR               | 725       | 124                         | NR               | 855       | 2                           | NR               | 985       | 0                           | NR               |
| 470       | 406                         | NR               | 600       | 861                         | NR               | 730       | 107                         | NR               | 860       | 2                           | NR               | 990       | 0                           | NR               |
| 475       | 327                         | NR               | 605       | 873                         | NR               | 735       | 91                          | NR               | 865       | 2                           | NR               | 995       | 0                           | NR               |
| 480       | 330                         | NR               | 610       | 875                         | NR               | 740       | 78                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 356                         | NR               | 615       | 877                         | NR               | 745       | 67                          | NR               | 875       | 1                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2506-458-11

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.75

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 394                      | NR            | 620    | 868                      | NR            | 750    | 58                       | NR            | 880    | 1                        | NR            |
| 365    | 0                        | NR            | 495    | 449                      | NR            | 625    | 858                      | NR            | 755    | 49                       | NR            | 885    | 1                        | NR            |
| 370    | 0                        | NR            | 500    | 505                      | NR            | 630    | 839                      | NR            | 760    | 42                       | NR            | 890    | 1                        | NR            |
| 375    | 0                        | NR            | 505    | 553                      | NR            | 635    | 813                      | NR            | 765    | 36                       | NR            | 895    | 1                        | NR            |
| 380    | 0                        | NR            | 510    | 593                      | NR            | 640    | 783                      | NR            | 770    | 31                       | NR            | 900    | 1                        | NR            |
| 385    | 0                        | NR            | 515    | 628                      | NR            | 645    | 746                      | NR            | 775    | 26                       | NR            | 905    | 1                        | NR            |
| 390    | 1                        | NR            | 520    | 651                      | NR            | 650    | 702                      | NR            | 780    | 22                       | NR            | 910    | 0                        | NR            |
| 395    | 4                        | NR            | 525    | 670                      | NR            | 655    | 657                      | NR            | 785    | 19                       | NR            | 915    | 0                        | NR            |
| 400    | 5                        | NR            | 530    | 687                      | NR            | 660    | 607                      | NR            | 790    | 16                       | NR            | 920    | 0                        | NR            |
| 405    | 8                        | NR            | 535    | 705                      | NR            | 665    | 559                      | NR            | 795    | 14                       | NR            | 925    | 0                        | NR            |
| 410    | 12                       | NR            | 540    | 717                      | NR            | 670    | 507                      | NR            | 800    | 12                       | NR            | 930    | 0                        | NR            |
| 415    | 19                       | NR            | 545    | 731                      | NR            | 675    | 458                      | NR            | 805    | 10                       | NR            | 935    | 0                        | NR            |
| 420    | 34                       | NR            | 550    | 745                      | NR            | 680    | 413                      | NR            | 810    | 9                        | NR            | 940    | 0                        | NR            |
| 425    | 60                       | NR            | 555    | 757                      | NR            | 685    | 367                      | NR            | 815    | 7                        | NR            | 945    | 0                        | NR            |
| 430    | 107                      | NR            | 560    | 767                      | NR            | 690    | 328                      | NR            | 820    | 6                        | NR            | 950    | 0                        | NR            |
| 435    | 194                      | NR            | 565    | 777                      | NR            | 695    | 289                      | NR            | 825    | 5                        | NR            | 955    | 0                        | NR            |
| 440    | 349                      | NR            | 570    | 785                      | NR            | 700    | 253                      | NR            | 830    | 5                        | NR            | 960    | 0                        | NR            |
| 445    | 678                      | NR            | 575    | 794                      | NR            | 705    | 221                      | NR            | 835    | 4                        | NR            | 965    | 0                        | NR            |
| 450    | 997                      | NR            | 580    | 809                      | NR            | 710    | 192                      | NR            | 840    | 3                        | NR            | 970    | 0                        | NR            |
| 455    | 819                      | NR            | 585    | 820                      | NR            | 715    | 165                      | NR            | 845    | 3                        | NR            | 975    | 0                        | NR            |
| 460    | 581                      | NR            | 590    | 838                      | NR            | 720    | 144                      | NR            | 850    | 2                        | NR            | 980    | 0                        | NR            |
| 465    | 517                      | NR            | 595    | 851                      | NR            | 725    | 124                      | NR            | 855    | 2                        | NR            | 985    | 0                        | NR            |
| 470    | 406                      | NR            | 600    | 861                      | NR            | 730    | 107                      | NR            | 860    | 2                        | NR            | 990    | 0                        | NR            |
| 475    | 327                      | NR            | 605    | 873                      | NR            | 735    | 91                       | NR            | 865    | 2                        | NR            | 995    | 0                        | NR            |
| 480    | 330                      | NR            | 610    | 875                      | NR            | 740    | 78                       | NR            | 870    | 1                        | NR            | 1000   | 0                        | NR            |
| 485    | 356                      | NR            | 615    | 877                      | NR            | 745    | 67                       | NR            | 875    | 1                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2506-458-11

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.61


| λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 394                         | NR               | 620       | 868                         | NR               | 750       | 58                          | NR               | 880       | 1                           | NR               |
| 365       | 0                           | NR               | 495       | 449                         | NR               | 625       | 858                         | NR               | 755       | 49                          | NR               | 885       | 1                           | NR               |
| 370       | 0                           | NR               | 500       | 505                         | NR               | 630       | 839                         | NR               | 760       | 42                          | NR               | 890       | 1                           | NR               |
| 375       | 0                           | NR               | 505       | 553                         | NR               | 635       | 813                         | NR               | 765       | 36                          | NR               | 895       | 1                           | NR               |
| 380       | 0                           | NR               | 510       | 593                         | NR               | 640       | 783                         | NR               | 770       | 31                          | NR               | 900       | 1                           | NR               |
| 385       | 0                           | NR               | 515       | 628                         | NR               | 645       | 746                         | NR               | 775       | 26                          | NR               | 905       | 1                           | NR               |
| 390       | 1                           | NR               | 520       | 651                         | NR               | 650       | 702                         | NR               | 780       | 22                          | NR               | 910       | 0                           | NR               |
| 395       | 4                           | NR               | 525       | 670                         | NR               | 655       | 657                         | NR               | 785       | 19                          | NR               | 915       | 0                           | NR               |
| 400       | 5                           | NR               | 530       | 687                         | NR               | 660       | 607                         | NR               | 790       | 16                          | NR               | 920       | 0                           | NR               |
| 405       | 8                           | NR               | 535       | 705                         | NR               | 665       | 559                         | NR               | 795       | 14                          | NR               | 925       | 0                           | NR               |
| 410       | 12                          | NR               | 540       | 717                         | NR               | 670       | 507                         | NR               | 800       | 12                          | NR               | 930       | 0                           | NR               |
| 415       | 19                          | NR               | 545       | 731                         | NR               | 675       | 458                         | NR               | 805       | 10                          | NR               | 935       | 0                           | NR               |
| 420       | 34                          | NR               | 550       | 745                         | NR               | 680       | 413                         | NR               | 810       | 9                           | NR               | 940       | 0                           | NR               |
| 425       | 60                          | NR               | 555       | 757                         | NR               | 685       | 367                         | NR               | 815       | 7                           | NR               | 945       | 0                           | NR               |
| 430       | 107                         | NR               | 560       | 767                         | NR               | 690       | 328                         | NR               | 820       | 6                           | NR               | 950       | 0                           | NR               |
| 435       | 194                         | NR               | 565       | 777                         | NR               | 695       | 289                         | NR               | 825       | 5                           | NR               | 955       | 0                           | NR               |
| 440       | 349                         | NR               | 570       | 785                         | NR               | 700       | 253                         | NR               | 830       | 5                           | NR               | 960       | 0                           | NR               |
| 445       | 678                         | NR               | 575       | 794                         | NR               | 705       | 221                         | NR               | 835       | 4                           | NR               | 965       | 0                           | NR               |
| 450       | 997                         | NR               | 580       | 809                         | NR               | 710       | 192                         | NR               | 840       | 3                           | NR               | 970       | 0                           | NR               |
| 455       | 819                         | NR               | 585       | 820                         | NR               | 715       | 165                         | NR               | 845       | 3                           | NR               | 975       | 0                           | NR               |
| 460       | 581                         | NR               | 590       | 838                         | NR               | 720       | 144                         | NR               | 850       | 2                           | NR               | 980       | 0                           | NR               |
| 465       | 517                         | NR               | 595       | 851                         | NR               | 725       | 124                         | NR               | 855       | 2                           | NR               | 985       | 0                           | NR               |
| 470       | 406                         | NR               | 600       | 861                         | NR               | 730       | 107                         | NR               | 860       | 2                           | NR               | 990       | 0                           | NR               |
| 475       | 327                         | NR               | 605       | 873                         | NR               | 735       | 91                          | NR               | 865       | 2                           | NR               | 995       | 0                           | NR               |
| 480       | 330                         | NR               | 610       | 875                         | NR               | 740       | 78                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 356                         | NR               | 615       | 877                         | NR               | 745       | 67                          | NR               | 875       | 1                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2506-458-11





TM-30-18

### Summary

$R_f = 90.8$   
 $R_g = 98.8$   
 $CIE R_a = 92.4$   
 $R_9 = 62.0$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**



|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 93 | CES51 = 96 | CES76 = 85 |
| CES02 = 62 | CES27 = 90 | CES52 = 98 | CES77 = 88 |
| CES03 = 31 | CES28 = 96 | CES53 = 96 | CES78 = 82 |
| CES04 = 69 | CES29 = 96 | CES54 = 92 | CES79 = 96 |
| CES05 = 49 | CES30 = 90 | CES55 = 90 | CES80 = 93 |
| CES06 = 50 | CES31 = 97 | CES56 = 93 | CES81 = 89 |
| CES07 = 42 | CES32 = 91 | CES57 = 91 | CES82 = 97 |
| CES08 = 41 | CES33 = 98 | CES58 = 92 | CES83 = 98 |
| CES09 = 29 | CES34 = 93 | CES59 = 96 | CES84 = 93 |
| CES10 = 74 | CES35 = 96 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 79 | CES61 = 91 | CES86 = 88 |
| CES12 = 63 | CES37 = 95 | CES62 = 84 | CES87 = 91 |
| CES13 = 43 | CES38 = 85 | CES63 = 91 | CES88 = 96 |
| CES14 = 74 | CES39 = 99 | CES64 = 87 | CES89 = 87 |
| CES15 = 71 | CES40 = 98 | CES65 = 87 | CES90 = 96 |
| CES16 = 47 | CES41 = 96 | CES66 = 84 | CES91 = 71 |
| CES17 = 49 | CES42 = 95 | CES67 = 83 | CES92 = 79 |
| CES18 = 56 | CES43 = 95 | CES68 = 86 | CES93 = 87 |
| CES19 = 71 | CES44 = 99 | CES69 = 87 | CES94 = 81 |
| CES20 = 66 | CES45 = 98 | CES70 = 84 | CES95 = 82 |
| CES21 = 85 | CES46 = 97 | CES71 = 77 | CES96 = 91 |
| CES22 = 78 | CES47 = 97 | CES72 = 93 | CES97 = 96 |
| CES23 = 91 | CES48 = 90 | CES73 = 78 | CES98 = 94 |
| CES24 = 90 | CES49 = 96 | CES74 = 91 | CES99 = 91 |
| CES25 = 71 | CES50 = 97 | CES75 = 80 |            |





**Color Rendition by Hue-Angle Bin**


**Measure Comparisons**



(END OF REPORT)