

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1216228

Luminaire Tested: 24-ID2-90-CNV-L850-U

Issue Date: 12/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1216228
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2508-510-5)
Test Lab: INNOVATION CENTER
Issue Date: 12/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 24-ID2-90-CNV-L850-U
Description: 2X4 IN DEPTH TROFFER WITH 2INCH CURVE DROP
Light Source: 5000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9471.9 lumens
Efficiency: N/A
Efficacy: 121.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.2 / 1.31
Luminous Opening: Rectangular w/ Sides (W: 2' x L: 4' x H: 0.16')
CIE Type: Direct

Input Watts (W): 78
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1216228
CATALOG NUMBER: 24-ID2-90-CNV-L850-U

Luminous Intensity Polar Plot



TEST NUMBER: P1216228

CATALOG NUMBER: 24-ID2-90-CNV-L850-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	110	110	110		106	106	106		99
1	108	104	99	95	105	101	97	94	97	93	90		93	90	87		82
2	99	90	84	78	96	88	82	77	85	79	75		81	77	73		69
3	90	80	71	65	87	78	70	64	75	68	63		72	66	62		58
4	83	71	62	55	80	69	61	55	67	60	54		64	58	53		50
5	76	63	54	48	74	62	54	47	60	52	47		58	51	46		43
6	70	57	48	42	68	56	48	42	54	47	41		52	46	41		38
7	65	52	43	37	63	51	43	37	49	42	36		48	41	36		34
8	61	47	39	33	59	47	39	33	45	38	33		44	37	32		30
9	57	44	35	30	55	43	35	30	42	35	30		40	34	29		27
10	53	40	32	27	52	40	32	27	39	32	27		38	31	27		25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4772	4772	4772
5°	4768	4727	4736
10°	4729	4666	4677
15°	4666	4588	4601
20°	4578	4489	4501
25°	4474	4369	4384
30°	4362	4237	4243
35°	4229	4079	4090
40°	4083	3914	3918
45°	3932	3745	3739
50°	3760	3550	3551
55°	3591	3358	3325
60°	3405	3135	3112
65°	3199	2893	2859
70°	2950	2606	2618
75°	2655	2307	2350
80°	2247	1997	2153
85°	1802	1761	2063

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3932 cd/sqm

TEST NUMBER: P1216228
 CATALOG NUMBER: 24-ID2-90-CNV-L850-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	335.0	3.5
10°-20°	950.5	10.0
20°-30°	1410.0	14.9
30°-40°	1647.5	17.4
40°-50°	1646.7	17.4
50°-60°	1433.6	15.1
60°-70°	1062.8	11.2
70°-80°	624.2	6.6
80°-90°	250.6	2.6
90°-100°	65.5	0.7
100°-110°	21.4	0.2
110°-120°	12.4	0.1
120°-130°	6.7	0.1
130°-140°	3.4	0.0
140°-150°	1.6	0.0
150°-160°	0.1	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2695.5	28.5
0°-40°	4342.9	45.9
0°-60°	7423.2	78.4
0°-90°	9360.7	98.8
90°-120°	99.3	1.0
90°-150°	111.1	1.2
90°-180°	111.0	1.2
0°-180°	9471.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3547	3547	3547	3547	3547	
5°	3543	3532	3526	3522	3531	336
15°	3386	3374	3369	3367	3374	954
25°	3070	3065	3060	3057	3064	1415
35°	2647	2640	2631	2630	2630	1655
45°	2149	2145	2135	2127	2122	1658
55°	1618	1614	1605	1599	1579	1446
65°	1091	1082	1074	1058	1052	1079
75°	587	582	584	588	587	621
85°	170	192	225	251	256	178
90°	69	88	114	135	140	42
95°	58	49	49	58	62	46
105°	40	34	20	5	0	43
115°	26	22	12	3	0	26
125°	17	13	8	1	0	15
135°	9	8	4	1	0	7
145°	5	4	1	1	1	3
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1216228

CATALOG NUMBER: 24-ID2-90-CNV-L850-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3546.6	3546.6	3546.6	3546.6	3546.6
2.5°	3558.3	3545.3	3540.1	3536.2	3542.7
5°	3542.7	3532.3	3525.8	3521.9	3531.0
7.5°	3519.3	3507.6	3501.1	3498.5	3506.3
10°	3485.6	3471.3	3466.1	3463.5	3471.3
12.5°	3440.1	3428.4	3423.2	3420.6	3428.4
15°	3385.6	3373.9	3368.7	3367.4	3373.9
17.5°	3321.9	3310.2	3303.7	3303.7	3311.5
20°	3244.0	3236.2	3232.3	3231.0	3234.9
22.5°	3166.1	3154.4	3153.1	3147.9	3157.0
25°	3070.0	3064.8	3059.6	3057.0	3063.5
27.5°	2980.4	2966.1	2959.6	2960.9	2964.8
30°	2872.6	2863.5	2860.9	2854.4	2857.0
32.5°	2760.9	2754.4	2751.8	2744.0	2744.0
35°	2646.6	2640.1	2631.1	2629.8	2629.8
37.5°	2528.5	2522.0	2514.2	2507.7	2510.3
40°	2402.5	2396.0	2386.9	2385.6	2380.4
42.5°	2279.1	2272.6	2262.2	2260.9	2255.7
45°	2149.3	2145.4	2135.0	2127.2	2122.0
47.5°	2019.4	2012.9	2001.2	1993.4	1989.5
50°	1881.7	1875.2	1867.4	1859.7	1858.4
52.5°	1749.3	1748.0	1736.3	1729.8	1723.3
55°	1618.1	1614.2	1605.1	1598.6	1579.2
57.5°	1481.8	1479.2	1474.0	1459.7	1448.0
60°	1353.2	1345.4	1336.3	1319.4	1316.8
62.5°	1216.8	1216.8	1202.5	1189.6	1184.4
65°	1090.9	1081.8	1074.0	1058.4	1051.9
67.5°	959.7	958.4	944.1	935.0	923.3
70°	832.4	828.5	816.8	814.2	811.7
72.5°	705.2	703.9	701.3	698.7	692.2
75°	587.0	581.8	584.4	588.3	587.0
77.5°	467.5	474.0	476.6	488.3	489.6
80°	355.8	366.2	381.8	400.0	403.9
82.5°	254.5	268.8	298.7	322.1	327.3
85°	170.1	192.2	224.7	250.6	255.8
87.5°	105.2	129.9	164.9	189.6	193.5
90°	68.8	88.3	114.3	135.1	140.3
92.5°	63.6	62.3	76.6	92.2	97.4
95°	58.4	49.3	49.3	58.4	62.3
97.5°	54.5	45.5	31.2	32.5	33.8
100°	49.3	41.6	23.4	14.3	14.3
102.5°	45.5	37.7	20.8	5.2	1.3
105°	40.3	33.8	19.5	5.2	0.0
107.5°	36.4	31.2	16.9	3.9	0.0
110°	32.5	27.3	15.6	3.9	0.0

TEST NUMBER: P1216228

CATALOG NUMBER: 24-ID2-90-CNV-L850-U

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	29.9	24.7	14.3	2.6	0.0
115°	26.0	22.1	11.7	2.6	0.0
117.5°	23.4	19.5	10.4	1.3	0.0
120°	20.8	16.9	9.1	1.3	0.0
122.5°	18.2	15.6	7.8	1.3	0.0
125°	16.9	13.0	7.8	1.3	0.0
127.5°	14.3	11.7	6.5	0.0	0.0
130°	13.0	10.4	5.2	0.0	0.0
132.5°	11.7	9.1	3.9	1.3	0.0
135°	9.1	7.8	3.9	1.3	0.0
137.5°	7.8	6.5	2.6	1.3	1.3
140°	6.5	5.2	2.6	1.3	1.3
142.5°	6.5	5.2	2.6	1.3	1.3
145°	5.2	3.9	1.3	1.3	1.3
147.5°	3.9	2.6	1.3	1.3	1.3
150°	2.6	2.6	1.3	1.3	1.3
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1216228

CATALOG NUMBER: 24-ID2-90-CNV-L850-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.05	17.64	16.43	17.98	18.32	16.06	17.66	16.45	18.00	18.34
	3H	17.71	19.16	18.11	19.51	19.90	17.74	19.18	18.14	19.54	19.93
	4H	18.31	19.67	18.73	20.04	20.45	18.39	19.75	18.81	20.12	20.53
	6H	18.73	19.99	19.16	20.38	20.80	18.94	20.20	19.37	20.59	21.01
	8H	18.86	20.06	19.30	20.47	20.90	19.16	20.37	19.61	20.78	21.21
	12H	18.94	20.09	19.39	20.50	20.96	19.37	20.53	19.82	20.93	21.39
4H	2H	16.62	17.98	17.04	18.35	18.75	16.63	17.99	17.05	18.36	18.77
	3H	18.50	19.64	18.92	20.06	20.49	18.52	19.67	18.95	20.09	20.52
	4H	19.21	20.25	19.67	20.69	21.15	19.30	20.34	19.75	20.77	21.24
	6H	19.76	20.66	20.23	21.13	21.61	19.99	20.89	20.46	21.35	21.84
	8H	19.93	20.78	20.41	21.24	21.73	20.28	21.12	20.75	21.59	22.08
	12H	20.05	20.81	20.55	21.31	21.81	20.55	21.32	21.05	21.82	22.31
8H	4H	19.50	20.35	19.98	20.81	21.30	19.58	20.43	20.06	20.89	21.38
	6H	20.16	20.87	20.67	21.38	21.88	20.39	21.10	20.90	21.61	22.11
	8H	20.39	21.03	20.92	21.56	22.07	20.77	21.41	21.30	21.94	22.45
	12H	20.59	21.16	21.12	21.67	22.25	21.17	21.73	21.69	22.24	22.83
12H	4H	19.53	20.30	20.03	20.79	21.29	19.60	20.37	20.10	20.86	21.36
	6H	20.22	20.86	20.75	21.38	21.90	20.44	21.08	20.97	21.60	22.12
	8H	20.52	21.08	21.04	21.59	22.18	20.89	21.45	21.41	21.96	22.55

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-7

Test Date: 08/26/2025

Luminaire Tested: 22ID2-55-CFR1-L850-U

Data in this report applies to families of products including 22ID2-55-CFR1-L850-U

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L850-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 5000K 80CRI

Spectral Parameters

CCT (K): 4966
 CIE u' : 0.2093
 CIE v' : 0.4890
 Duv: 0.0036
 CIE x: 0.3468
 CIE y: 0.3601
 CIE z: 0.2931
 Peak Wavelength (nm): 450
 Dominant Wavelength (nm): 570
 Purity: 12.1135
 R_f: 84
 R_g: 96.2

CRI (Ra): 83.1
 R1: 81.0
 R2: 87.8
 R3: 92.7
 R4: 82.4
 R5: 81.0
 R6: 82.6
 R7: 88.5
 R8: 68.6
 R9: 10.3
 R10: 70.9
 R11: 81.3
 R12: 55.9
 R13: 82.8
 R14: 96.1
 R15: 75.1



Test Conditions

Stabilization Time: 37M
 Operation Time: 1H 37M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2506-458-7

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-7

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	262	NR	620	472	NR	750	15	NR	880	0	NR
365	0	NR	495	307	NR	625	443	NR	755	13	NR	885	0	NR
370	0	NR	500	358	NR	630	412	NR	760	11	NR	890	0	NR
375	0	NR	505	403	NR	635	379	NR	765	9	NR	895	0	NR
380	0	NR	510	440	NR	640	346	NR	770	8	NR	900	0	NR
385	1	NR	515	471	NR	645	313	NR	775	7	NR	905	0	NR
390	3	NR	520	490	NR	650	282	NR	780	6	NR	910	0	NR
395	4	NR	525	504	NR	655	252	NR	785	5	NR	915	0	NR
400	6	NR	530	515	NR	660	223	NR	790	4	NR	920	0	NR
405	9	NR	535	524	NR	665	197	NR	795	4	NR	925	0	NR
410	12	NR	540	530	NR	670	171	NR	800	3	NR	930	0	NR
415	20	NR	545	539	NR	675	149	NR	805	3	NR	935	0	NR
420	36	NR	550	545	NR	680	130	NR	810	2	NR	940	0	NR
425	64	NR	555	554	NR	685	112	NR	815	2	NR	945	0	NR
430	117	NR	560	562	NR	690	97	NR	820	2	NR	950	0	NR
435	212	NR	565	567	NR	695	83	NR	825	2	NR	955	0	NR
440	378	NR	570	571	NR	700	71	NR	830	1	NR	960	0	NR
445	709	NR	575	574	NR	705	61	NR	835	1	NR	965	0	NR
450	1000	NR	580	579	NR	710	52	NR	840	1	NR	970	0	NR
455	789	NR	585	578	NR	715	44	NR	845	1	NR	975	0	NR
460	519	NR	590	578	NR	720	38	NR	850	1	NR	980	0	NR
465	429	NR	595	571	NR	725	32	NR	855	1	NR	985	0	NR
470	316	NR	600	560	NR	730	28	NR	860	1	NR	990	0	NR
475	236	NR	605	545	NR	735	24	NR	865	1	NR	995	0	NR
480	224	NR	610	524	NR	740	20	NR	870	0	NR	1000	0	NR
485	235	NR	615	501	NR	745	17	NR	875	0	NR			

REPORT NUMBER: SP1-2506-458-7

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.94

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	262	NR	620	472	NR	750	15	NR	880	0	NR
365	0	NR	495	307	NR	625	443	NR	755	13	NR	885	0	NR
370	0	NR	500	358	NR	630	412	NR	760	11	NR	890	0	NR
375	0	NR	505	403	NR	635	379	NR	765	9	NR	895	0	NR
380	0	NR	510	440	NR	640	346	NR	770	8	NR	900	0	NR
385	1	NR	515	471	NR	645	313	NR	775	7	NR	905	0	NR
390	3	NR	520	490	NR	650	282	NR	780	6	NR	910	0	NR
395	4	NR	525	504	NR	655	252	NR	785	5	NR	915	0	NR
400	6	NR	530	515	NR	660	223	NR	790	4	NR	920	0	NR
405	9	NR	535	524	NR	665	197	NR	795	4	NR	925	0	NR
410	12	NR	540	530	NR	670	171	NR	800	3	NR	930	0	NR
415	20	NR	545	539	NR	675	149	NR	805	3	NR	935	0	NR
420	36	NR	550	545	NR	680	130	NR	810	2	NR	940	0	NR
425	64	NR	555	554	NR	685	112	NR	815	2	NR	945	0	NR
430	117	NR	560	562	NR	690	97	NR	820	2	NR	950	0	NR
435	212	NR	565	567	NR	695	83	NR	825	2	NR	955	0	NR
440	378	NR	570	571	NR	700	71	NR	830	1	NR	960	0	NR
445	709	NR	575	574	NR	705	61	NR	835	1	NR	965	0	NR
450	1000	NR	580	579	NR	710	52	NR	840	1	NR	970	0	NR
455	789	NR	585	578	NR	715	44	NR	845	1	NR	975	0	NR
460	519	NR	590	578	NR	720	38	NR	850	1	NR	980	0	NR
465	429	NR	595	571	NR	725	32	NR	855	1	NR	985	0	NR
470	316	NR	600	560	NR	730	28	NR	860	1	NR	990	0	NR
475	236	NR	605	545	NR	735	24	NR	865	1	NR	995	0	NR
480	224	NR	610	524	NR	740	20	NR	870	0	NR	1000	0	NR
485	235	NR	615	501	NR	745	17	NR	875	0	NR			

REPORT NUMBER: SP1-2506-458-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 4.11

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	262	NR	620	472	NR	750	15	NR	880	0	NR
365	0	NR	495	307	NR	625	443	NR	755	13	NR	885	0	NR
370	0	NR	500	358	NR	630	412	NR	760	11	NR	890	0	NR
375	0	NR	505	403	NR	635	379	NR	765	9	NR	895	0	NR
380	0	NR	510	440	NR	640	346	NR	770	8	NR	900	0	NR
385	1	NR	515	471	NR	645	313	NR	775	7	NR	905	0	NR
390	3	NR	520	490	NR	650	282	NR	780	6	NR	910	0	NR
395	4	NR	525	504	NR	655	252	NR	785	5	NR	915	0	NR
400	6	NR	530	515	NR	660	223	NR	790	4	NR	920	0	NR
405	9	NR	535	524	NR	665	197	NR	795	4	NR	925	0	NR
410	12	NR	540	530	NR	670	171	NR	800	3	NR	930	0	NR
415	20	NR	545	539	NR	675	149	NR	805	3	NR	935	0	NR
420	36	NR	550	545	NR	680	130	NR	810	2	NR	940	0	NR
425	64	NR	555	554	NR	685	112	NR	815	2	NR	945	0	NR
430	117	NR	560	562	NR	690	97	NR	820	2	NR	950	0	NR
435	212	NR	565	567	NR	695	83	NR	825	2	NR	955	0	NR
440	378	NR	570	571	NR	700	71	NR	830	1	NR	960	0	NR
445	709	NR	575	574	NR	705	61	NR	835	1	NR	965	0	NR
450	1000	NR	580	579	NR	710	52	NR	840	1	NR	970	0	NR
455	789	NR	585	578	NR	715	44	NR	845	1	NR	975	0	NR
460	519	NR	590	578	NR	720	38	NR	850	1	NR	980	0	NR
465	429	NR	595	571	NR	725	32	NR	855	1	NR	985	0	NR
470	316	NR	600	560	NR	730	28	NR	860	1	NR	990	0	NR
475	236	NR	605	545	NR	735	24	NR	865	1	NR	995	0	NR
480	224	NR	610	524	NR	740	20	NR	870	0	NR	1000	0	NR
485	235	NR	615	501	NR	745	17	NR	875	0	NR			

REPORT NUMBER: SP1-2506-458-7




TM-30-18

Summary

$R_f = 84$
 $R_g = 96.2$
 $\text{CIE } R_a = 83.1$
 $R_9 = 10.3$




Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 85	CES26 = 80	CES51 = 95	CES76 = 72
CES02 = 60	CES27 = 93	CES52 = 95	CES77 = 81
CES03 = 30	CES28 = 90	CES53 = 89	CES78 = 71
CES04 = 69	CES29 = 85	CES54 = 90	CES79 = 91
CES05 = 47	CES30 = 97	CES55 = 89	CES80 = 87
CES06 = 50	CES31 = 87	CES56 = 86	CES81 = 84
CES07 = 40	CES32 = 79	CES57 = 85	CES82 = 95
CES08 = 39	CES33 = 92	CES58 = 85	CES83 = 95
CES09 = 29	CES34 = 84	CES59 = 92	CES84 = 90
CES10 = 73	CES35 = 91	CES60 = 91	CES85 = 81
CES11 = 56	CES36 = 83	CES61 = 88	CES86 = 79
CES12 = 62	CES37 = 90	CES62 = 85	CES87 = 84
CES13 = 42	CES38 = 93	CES63 = 85	CES88 = 89
CES14 = 74	CES39 = 98	CES64 = 79	CES89 = 79
CES15 = 71	CES40 = 94	CES65 = 76	CES90 = 89
CES16 = 46	CES41 = 99	CES66 = 75	CES91 = 72
CES17 = 48	CES42 = 89	CES67 = 73	CES92 = 67
CES18 = 55	CES43 = 88	CES68 = 78	CES93 = 80
CES19 = 70	CES44 = 99	CES69 = 82	CES94 = 65
CES20 = 64	CES45 = 93	CES70 = 73	CES95 = 73
CES21 = 85	CES46 = 91	CES71 = 67	CES96 = 84
CES22 = 77	CES47 = 96	CES72 = 89	CES97 = 92
CES23 = 91	CES48 = 87	CES73 = 66	CES98 = 86
CES24 = 90	CES49 = 90	CES74 = 92	CES99 = 77
CES25 = 71	CES50 = 95	CES75 = 68	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)