

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P413100

Luminaire Tested: **22PD-55-PC3-L830**

Issue Date: 9/15/2020

Test Information

Test Method: LM-79-08
Report Number: P413100
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2008-911-15)
Test Lab: INNOVATION CENTER
Issue Date: 9/15/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: 22PD-55-PC3-L830
Description: 5500 LUMEN 2X2 PERCEIVE LED TROFFER WITH PYRAMID PATTERN OPTICS AND 80 CRI, 3000 CCT LEDS
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5204.0 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.37
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')
CIE Type: Direct

Input Watts (W): 45.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P413100
CATALOG NUMBER: 22PD-55-PC3-L830

Luminous Intensity Polar Plot





TEST NUMBER: P413100

CATALOG NUMBER: 22PD-55-PC3-L830

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	105	101	97	107	103	99	96	99	96	93	95	92	90	91	89	87	85			
2	100	92	86	80	97	90	84	79	87	82	77	83	79	76	80	77	74	72			
3	91	81	73	67	89	80	72	67	77	70	65	74	69	64	71	67	63	61			
4	84	72	64	57	82	71	63	57	68	61	56	66	60	55	64	59	54	52			
5	77	65	56	49	75	63	55	49	61	54	49	59	53	48	58	52	47	45			
6	71	58	49	43	69	57	49	43	55	48	43	54	47	42	52	46	42	40			
7	66	53	44	38	64	52	44	38	50	43	38	49	42	37	48	42	37	35			
8	62	48	40	34	60	48	40	34	46	39	34	45	38	34	44	38	33	31			
9	58	44	36	31	56	44	36	31	43	35	30	41	35	30	40	34	30	28			
10	54	41	33	28	53	40	33	28	39	32	28	38	32	28	38	32	27	26			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5213	5213	5213
5°	5219	5216	5223
10°	5232	5231	5232
15°	5239	5246	5237
20°	5212	5255	5208
25°	5152	5236	5148
30°	5075	5175	5068
35°	4987	5086	4987
40°	4894	4980	4894
45°	4765	4858	4771
50°	4602	4692	4620
55°	4388	4475	4388
60°	4092	4195	4066
65°	3672	3801	3625
70°	3142	3253	3049
75°	2492	2563	2364
80°	1785	1852	1700
85°	1179	1216	1102



TEST NUMBER: P413100

CATALOG NUMBER: 22PD-55-PC3-L830

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.8	3.5
10°-20°	530.9	10.2
20°-30°	805.4	15.5
30°-40°	961.9	18.5
40°-50°	978.2	18.8
50°-60°	846.1	16.3
60°-70°	582.2	11.2
70°-80°	264.3	5.1
80°-90°	51.2	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1520.1	29.2
0°-40°	2482.0	47.7
0°-60°	4306.4	82.8
0°-90°	5204.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5204.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1937	1937	1937	1937	1937	
5°	1932	1930	1931	1931	1933	184
15°	1880	1882	1883	1880	1880	530
25°	1735	1750	1763	1747	1734	799
35°	1518	1545	1548	1543	1518	950
45°	1252	1275	1277	1275	1254	966
55°	935	951	954	952	935	836
65°	577	593	597	592	569	572
75°	240	249	246	244	227	258
85°	38	41	39	38	36	50
90°	0	0	0	0	0	



TEST NUMBER: P413100

CATALOG NUMBER: 22PD-55-PC3-L830

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1937.1	1937.1	1937.1	1937.1	<i>1937.1</i>
2.5°	<i>1937.1</i>	<i>1934.7</i>	<i>1935.3</i>	<i>1935.9</i>	<i>1939.6</i>
5°	1932.2	1930.4	1931.0	1931.0	<i>1933.4</i>
7.5°	1924.2	1923.6	1923.6	1923.0	<i>1924.8</i>
10°	1914.9	1913.7	1914.3	1913.7	<i>1914.9</i>
12.5°	1900.8	1900.8	1901.4	1899.5	<i>1900.8</i>
15°	1880.4	1881.7	1882.9	1879.8	<i>1879.8</i>
17.5°	1854.6	1857.6	1860.7	1855.2	<i>1852.1</i>
20°	1820.1	1827.5	1834.9	1826.2	<i>1818.8</i>
22.5°	1780.0	1792.3	1803.4	1789.9	<i>1780.0</i>
25°	1735.0	1750.4	1763.4	1747.4	<i>1733.8</i>
27.5°	1686.4	1703.6	1715.9	1702.4	<i>1683.9</i>
30°	1633.4	1654.3	1665.4	1652.5	<i>1630.9</i>
32.5°	1576.7	1601.3	1608.1	1600.1	<i>1575.5</i>
35°	1518.2	1545.3	1548.3	1542.8	<i>1518.2</i>
37.5°	1457.2	1483.0	1485.5	1482.4	<i>1457.2</i>
40°	1393.1	1417.1	1417.7	1417.7	<i>1393.1</i>
42.5°	1324.7	1348.1	1348.1	1347.5	<i>1326.5</i>
45°	1252.0	1274.8	1276.6	1275.4	<i>1253.8</i>
47.5°	1179.9	1197.2	1200.2	1197.8	<i>1178.7</i>
50°	1099.2	1117.1	1120.7	1118.3	<i>1103.5</i>
52.5°	1019.1	1035.7	1039.4	1037.6	<i>1020.9</i>
55°	935.3	951.3	953.8	951.9	<i>935.3</i>
57.5°	854.6	865.1	867.5	863.8	<i>842.9</i>
60°	760.3	775.1	779.4	775.1	<i>755.4</i>
62.5°	669.1	685.1	688.8	682.7	<i>661.7</i>
65°	576.7	592.7	597.0	592.1	<i>569.3</i>
67.5°	489.2	500.9	504.6	499.1	<i>478.1</i>
70°	399.3	414.0	413.4	406.0	<i>387.5</i>
72.5°	310.5	330.9	327.2	322.9	<i>302.5</i>
75°	239.7	248.9	246.5	244.0	<i>227.4</i>
77.5°	171.3	182.4	176.2	176.8	<i>162.7</i>
80°	115.2	125.7	119.5	117.1	<i>109.7</i>
82.5°	73.3	77.6	76.4	75.2	<i>68.4</i>
85°	38.2	40.7	39.4	38.2	<i>35.7</i>
87.5°	14.8	16.0	14.8	14.8	<i>13.6</i>
90°	0.0	0.0	0.0	0.0	<i>0.0</i>



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)