

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P413103

Luminaire Tested: **22PD-55-PC3-L850**

Issue Date: 9/15/2020

Test Information

Test Method: LM-79-08
Report Number: P413103
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2008-911-15)
Test Lab: INNOVATION CENTER
Issue Date: 9/15/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: 22PD-55-PC3-L850
Description: 5500 LUMEN 2X2 PERCEIVE LED TROFFER WITH PYRAMID PATTERN OPTICS AND 80 CRI, 5000 CCT LEDS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5610.0 lumens
Efficiency: N/A
Efficacy: 123.6 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.37
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')
CIE Type: Direct

Input Watts (W): 45.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P413103

CATALOG NUMBER: 22PD-55-PC3-L850

Luminous Intensity Polar Plot





TEST NUMBER: P413103

CATALOG NUMBER: 22PD-55-PC3-L850

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	105	101	97	107	103	99	96	99	96	93	95	92	90	91	89	87	85								
2	100	92	86	80	97	90	84	79	87	82	77	83	79	76	80	77	74	72								
3	91	81	73	67	89	80	72	67	77	70	65	74	69	64	71	67	63	61								
4	84	72	64	57	82	71	63	57	68	61	56	66	60	55	64	59	54	52								
5	77	65	56	49	75	63	55	49	61	54	49	59	53	48	58	52	47	45								
6	71	58	49	43	69	57	49	43	55	48	43	54	47	42	52	46	42	40								
7	66	53	44	38	64	52	44	38	50	43	38	49	42	37	48	42	37	35								
8	62	48	40	34	60	48	40	34	46	39	34	45	38	34	44	38	33	31								
9	58	44	36	31	56	44	36	31	43	35	30	41	35	30	40	34	30	28								
10	54	41	33	28	53	40	33	28	39	32	28	38	32	28	38	32	27	26								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5620	5620	5620
5°	5626	5623	5630
10°	5641	5639	5641
15°	5648	5655	5646
20°	5619	5664	5615
25°	5554	5644	5550
30°	5471	5578	5463
35°	5376	5483	5376
40°	5276	5369	5276
45°	5136	5237	5144
50°	4960	5058	4980
55°	4731	4824	4731
60°	4411	4522	4383
65°	3959	4098	3908
70°	3386	3507	3287
75°	2687	2763	2548
80°	1925	1998	1832
85°	1272	1312	1189



TEST NUMBER: P413103

CATALOG NUMBER: 22PD-55-PC3-L850

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	198.1	3.5
10°-20°	572.3	10.2
20°-30°	868.3	15.5
30°-40°	1036.9	18.5
40°-50°	1054.5	18.8
50°-60°	912.2	16.3
60°-70°	627.7	11.2
70°-80°	284.9	5.1
80°-90°	55.1	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1638.7	29.2
0°-40°	2675.6	47.7
0°-60°	4642.3	82.8
0°-90°	5610.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5610.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2088	2088	2088	2088	2088	
5°	2083	2081	2082	2082	2084	198
15°	2027	2028	2030	2026	2026	572
25°	1870	1887	1901	1884	1869	862
35°	1637	1666	1669	1663	1637	1024
45°	1350	1374	1376	1375	1352	1041
55°	1008	1026	1028	1026	1008	901
65°	622	639	644	638	614	617
75°	258	268	266	263	245	278
85°	41	44	42	41	38	54
90°	0	0	0	0	0	



TEST NUMBER: P413103

CATALOG NUMBER: 22PD-55-PC3-L850

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2088.3	2088.3	2088.3	2088.3	<i>2088.3</i>
2.5°	<i>2088.3</i>	<i>2085.6</i>	<i>2086.3</i>	<i>2086.9</i>	<i>2090.9</i>
5°	2082.9	2081.0	2081.6	2081.6	<i>2084.3</i>
7.5°	2074.3	2073.6	2073.6	2073.0	<i>2075.0</i>
10°	2064.3	2063.0	2063.7	2063.0	<i>2064.3</i>
12.5°	2049.1	2049.1	2049.7	2047.7	<i>2049.1</i>
15°	2027.2	2028.5	2029.8	2026.5	<i>2026.5</i>
17.5°	1999.3	2002.6	2005.9	1999.9	<i>1996.6</i>
20°	1962.1	1970.0	1978.0	1968.7	<i>1960.7</i>
22.5°	1918.9	1932.2	1944.1	1929.5	<i>1918.9</i>
25°	1870.4	1887.0	1901.0	1883.7	<i>1869.1</i>
27.5°	1817.9	1836.5	1849.8	1835.2	<i>1815.3</i>
30°	1760.8	1783.4	1795.3	1781.4	<i>1758.1</i>
32.5°	1699.7	1726.3	1733.6	1724.9	<i>1698.4</i>
35°	1636.6	1665.8	1669.1	1663.2	<i>1636.6</i>
37.5°	1570.8	1598.7	1601.4	1598.1	<i>1570.8</i>
40°	1501.8	1527.7	1528.3	1528.3	<i>1501.8</i>
42.5°	1428.0	1453.3	1453.3	1452.6	<i>1430.0</i>
45°	1349.7	1374.2	1376.2	1374.9	<i>1351.7</i>
47.5°	1272.0	1290.5	1293.9	1291.2	<i>1270.6</i>
50°	1184.9	1204.2	1208.2	1205.5	<i>1189.6</i>
52.5°	1098.6	1116.5	1120.5	1118.5	<i>1100.6</i>
55°	1008.3	1025.5	1028.2	1026.2	<i>1008.3</i>
57.5°	921.3	932.5	935.2	931.2	<i>908.6</i>
60°	819.6	835.6	840.2	835.6	<i>814.3</i>
62.5°	721.3	738.6	742.6	735.9	<i>713.4</i>
65°	621.7	639.0	643.6	638.3	<i>613.7</i>
67.5°	527.4	540.0	544.0	538.0	<i>515.4</i>
70°	430.4	446.3	445.7	437.7	<i>417.8</i>
72.5°	334.8	356.7	352.7	348.0	<i>326.1</i>
75°	258.4	268.3	265.7	263.0	<i>245.1</i>
77.5°	184.6	196.6	190.0	190.6	<i>175.3</i>
80°	124.2	135.5	128.9	126.2	<i>118.2</i>
82.5°	79.0	83.7	82.4	81.0	<i>73.7</i>
85°	41.2	43.8	42.5	41.2	<i>38.5</i>
87.5°	15.9	17.3	15.9	15.9	<i>14.6</i>
90°	0.0	0.0	0.0	0.0	<i>0.0</i>



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)