

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1216093

Luminaire Tested: 24-ID2-72-CNC-L930-U

Issue Date: 12/5/2025


Test Information

Test Method: LM-79-2019
Report Number: P1216093
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2508-510-9)
Test Lab: INNOVATION CENTER
Issue Date: 12/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 24-ID2-72-CNC-L930-U
Description: 2X4 IN DEPTH TROFFER WITH 2INCH CURVE REGRESSED
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6454.3 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.19 / 1.29
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 64.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1216093
CATALOG NUMBER: 24-ID2-72-CNC-L930-U

Luminous Intensity Polar Plot



TEST NUMBER: P1216093

CATALOG NUMBER: 24-ID2-72-CNC-L930-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	109	105	100	97	106	102	99	95	98	95	92		94	92	89		85
2	100	92	85	79	97	90	84	78	86	81	77		83	79	75		71
3	91	81	73	67	89	79	72	66	76	70	65		74	68	64		60
4	84	72	63	57	81	71	63	56	68	61	56		66	60	55		52
5	77	64	56	49	75	63	55	49	61	54	48		59	53	48		45
6	71	58	49	43	69	57	49	43	55	48	42		54	47	42		40
7	66	53	44	38	64	52	44	38	51	43	38		49	42	37		35
8	62	48	40	34	60	48	40	34	46	39	34		45	38	34		32
9	58	44	36	31	56	44	36	31	43	36	31		42	35	30		29
10	54	41	33	28	53	41	33	28	40	33	28		39	32	28		26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3433	3433	3433
5°	3445	3427	3429
10°	3424	3405	3405
15°	3390	3370	3366
20°	3339	3316	3313
25°	3273	3244	3243
30°	3193	3164	3147
35°	3100	3065	3041
40°	2999	2957	2932
45°	2887	2848	2807
50°	2773	2722	2683
55°	2643	2581	2547
60°	2512	2445	2421
65°	2340	2297	2292
70°	2141	2131	2124
75°	1913	1945	1959
80°	1560	1698	1781
85°	1073	1362	1362

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2887 cd/sqm

TEST NUMBER: P1216093
 CATALOG NUMBER: 24-ID2-72-CNC-L930-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	240.9	3.7
10°-20°	682.2	10.6
20°-30°	1007.5	15.6
30°-40°	1168.0	18.1
40°-50°	1153.8	17.9
50°-60°	988.5	15.3
60°-70°	717.3	11.1
70°-80°	395.9	6.1
80°-90°	100.4	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1930.5	29.9
0°-40°	3098.5	48.0
0°-60°	5240.8	81.2
0°-90°	6454.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6454.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2551	2551	2551	2551	2551	
5°	2550	2541	2537	2533	2539	242
15°	2434	2425	2420	2414	2417	686
25°	2205	2196	2185	2181	2184	1015
35°	1888	1880	1866	1857	1851	1181
45°	1517	1507	1497	1481	1475	1172
55°	1127	1116	1100	1091	1086	1008
65°	735	729	722	718	720	727
75°	368	366	374	377	377	389
85°	70	77	88	89	88	87
90°	0	0	0	0	0	

TEST NUMBER: P1216093

CATALOG NUMBER: 24-ID2-72-CNC-L930-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2551.3	2551.3	2551.3	2551.3	2551.3
2.5°	2560.2	2551.3	2546.9	2543.3	2548.6
5°	2550.4	2540.6	2537.1	2532.6	2538.8
7.5°	2530.8	2522.8	2518.3	2514.8	2518.3
10°	2505.9	2497.0	2492.5	2489.8	2492.5
12.5°	2472.9	2466.7	2459.6	2454.2	2459.6
15°	2433.7	2424.8	2419.5	2414.1	2416.8
17.5°	2385.6	2377.6	2370.5	2366.0	2368.7
20°	2332.2	2322.4	2316.1	2311.7	2313.5
22.5°	2276.0	2263.6	2255.6	2248.4	2249.3
25°	2204.8	2195.9	2185.2	2180.7	2184.3
27.5°	2131.7	2121.9	2113.0	2105.9	2104.1
30°	2055.1	2046.2	2036.4	2028.4	2025.7
32.5°	1978.5	1963.4	1952.7	1944.7	1943.8
35°	1887.6	1880.5	1866.3	1857.4	1851.1
37.5°	1801.2	1790.5	1776.3	1768.3	1762.0
40°	1707.7	1697.0	1683.6	1672.1	1669.4
42.5°	1613.3	1605.3	1587.4	1580.3	1575.9
45°	1517.1	1507.3	1496.6	1481.4	1475.2
47.5°	1425.3	1415.5	1397.7	1384.3	1380.8
50°	1324.6	1313.1	1300.6	1284.6	1281.9
52.5°	1229.3	1216.0	1199.9	1192.8	1187.5
55°	1126.9	1116.2	1100.2	1091.3	1085.9
57.5°	1025.3	1019.1	1008.4	995.9	995.0
60°	933.6	921.1	908.6	899.7	899.7
62.5°	831.1	826.7	814.2	808.9	806.2
65°	734.9	728.7	721.6	718.0	719.8
67.5°	636.0	635.2	629.8	630.7	628.9
70°	544.3	540.7	541.6	543.4	539.8
72.5°	455.2	452.5	457.0	457.9	459.7
75°	367.9	366.1	374.1	376.8	376.8
77.5°	280.6	286.0	294.9	302.0	302.0
80°	201.3	208.5	219.1	225.4	229.8
82.5°	129.2	140.7	150.5	155.0	155.0
85°	69.5	76.6	88.2	89.1	88.2
87.5°	21.4	26.7	32.1	33.9	34.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1216093

CATALOG NUMBER: 24-ID2-72-CNC-L930-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.32	16.92	15.68	17.23	17.55	15.15	16.75	15.52	17.06	17.38
	3H	16.96	18.40	17.34	18.73	19.09	16.84	18.28	17.22	18.61	18.97
	4H	17.54	18.90	17.94	19.25	19.63	17.47	18.83	17.87	19.18	19.55
	6H	17.93	19.18	18.34	19.55	19.94	17.94	19.20	18.35	19.56	19.95
	8H	18.03	19.23	18.45	19.62	20.01	18.09	19.29	18.51	19.67	20.07
	12H	18.08	19.22	18.51	19.61	20.04	18.17	19.32	18.60	19.70	20.13
4H	2H	15.89	17.24	16.29	17.59	17.97	15.75	17.11	16.15	17.46	17.83
	3H	17.75	18.88	18.16	19.28	19.68	17.66	18.79	18.07	19.19	19.59
	4H	18.45	19.47	18.88	19.89	20.32	18.42	19.44	18.85	19.85	20.29
	6H	18.95	19.84	19.41	20.29	20.74	19.01	19.91	19.47	20.35	20.80
	8H	19.09	19.92	19.55	20.37	20.83	19.20	20.04	19.66	20.48	20.95
	12H	19.17	19.92	19.65	20.40	20.86	19.32	20.07	19.81	20.55	21.02
8H	4H	18.73	19.56	19.19	20.01	20.47	18.70	19.54	19.16	19.98	20.44
	6H	19.34	20.03	19.83	20.52	21.00	19.41	20.10	19.91	20.59	21.07
	8H	19.54	20.16	20.05	20.67	21.15	19.67	20.29	20.18	20.80	21.28
	12H	19.67	20.22	20.18	20.71	21.27	19.86	20.41	20.36	20.90	21.46
12H	4H	18.76	19.51	19.24	19.98	20.45	18.72	19.47	19.20	19.95	20.42
	6H	19.38	20.01	19.90	20.52	21.00	19.45	20.08	19.96	20.58	21.07
	8H	19.64	20.19	20.14	20.68	21.24	19.76	20.31	20.27	20.80	21.37

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-9

Test Date: 08/26/2025

Luminaire Tested: 22ID2-55-CFR1-L930-U

Data in this report applies to families of products including 22ID2-55-CFR1-L930-U


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L930-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 3000K 90CRI

Spectral Parameters

CCT (K): 3003
 CIE u' : 0.2507
 CIE v' : 0.5202
 Duv: -0.0008
 CIE x: 0.4356
 CIE y: 0.4017
 CIE z: 0.1627
 Peak Wavelength (nm): 618
 Dominant Wavelength (nm): 583
 Purity: 51.31044
 R_f: 91.9
 R_g: 99.2

CRI (Ra): 93.2
 R1: 93.7
 R2: 97.2
 R3: 98.7
 R4: 93.5
 R5: 93.6
 R6: 96.3
 R7: 91.5
 R8: 81.5
 R9: 59.0
 R10: 92.7
 R11: 94.9
 R12: 82.6
 R13: 94.8
 R14: 99.1
 R15: 89.5



Test Conditions


Stabilization Time: 32M
 Operation Time: 1H 32M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2506-458-9


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-9

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-9

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	296	NR	620	997	NR	750	66	NR	880	1	NR
365	0	NR	495	338	NR	625	992	NR	755	56	NR	885	1	NR
370	0	NR	500	381	NR	630	975	NR	760	48	NR	890	1	NR
375	0	NR	505	421	NR	635	949	NR	765	41	NR	895	1	NR
380	0	NR	510	456	NR	640	916	NR	770	35	NR	900	1	NR
385	0	NR	515	487	NR	645	871	NR	775	30	NR	905	1	NR
390	0	NR	520	508	NR	650	821	NR	780	26	NR	910	1	NR
395	1	NR	525	529	NR	655	769	NR	785	22	NR	915	0	NR
400	2	NR	530	548	NR	660	709	NR	790	18	NR	920	0	NR
405	4	NR	535	568	NR	665	652	NR	795	16	NR	925	0	NR
410	6	NR	540	585	NR	670	591	NR	800	13	NR	930	0	NR
415	11	NR	545	607	NR	675	534	NR	805	11	NR	935	0	NR
420	19	NR	550	627	NR	680	480	NR	810	10	NR	940	0	NR
425	33	NR	555	649	NR	685	427	NR	815	8	NR	945	0	NR
430	58	NR	560	673	NR	690	380	NR	820	7	NR	950	0	NR
435	103	NR	565	697	NR	695	334	NR	825	6	NR	955	0	NR
440	184	NR	570	723	NR	700	292	NR	830	5	NR	960	0	NR
445	360	NR	575	753	NR	705	255	NR	835	4	NR	965	0	NR
450	557	NR	580	789	NR	710	221	NR	840	4	NR	970	0	NR
455	486	NR	585	825	NR	715	190	NR	845	3	NR	975	0	NR
460	362	NR	590	864	NR	720	166	NR	850	3	NR	980	0	NR
465	337	NR	595	902	NR	725	143	NR	855	2	NR	985	0	NR
470	279	NR	600	932	NR	730	122	NR	860	2	NR	990	0	NR
475	233	NR	605	963	NR	735	105	NR	865	2	NR	995	0	NR
480	241	NR	610	981	NR	740	90	NR	870	1	NR	1000	0	NR
485	264	NR	615	997	NR	745	77	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-9

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.43

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	296	NR	620	997	NR	750	66	NR	880	1	NR
365	0	NR	495	338	NR	625	992	NR	755	56	NR	885	1	NR
370	0	NR	500	381	NR	630	975	NR	760	48	NR	890	1	NR
375	0	NR	505	421	NR	635	949	NR	765	41	NR	895	1	NR
380	0	NR	510	456	NR	640	916	NR	770	35	NR	900	1	NR
385	0	NR	515	487	NR	645	871	NR	775	30	NR	905	1	NR
390	0	NR	520	508	NR	650	821	NR	780	26	NR	910	1	NR
395	1	NR	525	529	NR	655	769	NR	785	22	NR	915	0	NR
400	2	NR	530	548	NR	660	709	NR	790	18	NR	920	0	NR
405	4	NR	535	568	NR	665	652	NR	795	16	NR	925	0	NR
410	6	NR	540	585	NR	670	591	NR	800	13	NR	930	0	NR
415	11	NR	545	607	NR	675	534	NR	805	11	NR	935	0	NR
420	19	NR	550	627	NR	680	480	NR	810	10	NR	940	0	NR
425	33	NR	555	649	NR	685	427	NR	815	8	NR	945	0	NR
430	58	NR	560	673	NR	690	380	NR	820	7	NR	950	0	NR
435	103	NR	565	697	NR	695	334	NR	825	6	NR	955	0	NR
440	184	NR	570	723	NR	700	292	NR	830	5	NR	960	0	NR
445	360	NR	575	753	NR	705	255	NR	835	4	NR	965	0	NR
450	557	NR	580	789	NR	710	221	NR	840	4	NR	970	0	NR
455	486	NR	585	825	NR	715	190	NR	845	3	NR	975	0	NR
460	362	NR	590	864	NR	720	166	NR	850	3	NR	980	0	NR
465	337	NR	595	902	NR	725	143	NR	855	2	NR	985	0	NR
470	279	NR	600	932	NR	730	122	NR	860	2	NR	990	0	NR
475	233	NR	605	963	NR	735	105	NR	865	2	NR	995	0	NR
480	241	NR	610	981	NR	740	90	NR	870	1	NR	1000	0	NR
485	264	NR	615	997	NR	745	77	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.82


λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	296	NR	620	997	NR	750	66	NR	880	1	NR
365	0	NR	495	338	NR	625	992	NR	755	56	NR	885	1	NR
370	0	NR	500	381	NR	630	975	NR	760	48	NR	890	1	NR
375	0	NR	505	421	NR	635	949	NR	765	41	NR	895	1	NR
380	0	NR	510	456	NR	640	916	NR	770	35	NR	900	1	NR
385	0	NR	515	487	NR	645	871	NR	775	30	NR	905	1	NR
390	0	NR	520	508	NR	650	821	NR	780	26	NR	910	1	NR
395	1	NR	525	529	NR	655	769	NR	785	22	NR	915	0	NR
400	2	NR	530	548	NR	660	709	NR	790	18	NR	920	0	NR
405	4	NR	535	568	NR	665	652	NR	795	16	NR	925	0	NR
410	6	NR	540	585	NR	670	591	NR	800	13	NR	930	0	NR
415	11	NR	545	607	NR	675	534	NR	805	11	NR	935	0	NR
420	19	NR	550	627	NR	680	480	NR	810	10	NR	940	0	NR
425	33	NR	555	649	NR	685	427	NR	815	8	NR	945	0	NR
430	58	NR	560	673	NR	690	380	NR	820	7	NR	950	0	NR
435	103	NR	565	697	NR	695	334	NR	825	6	NR	955	0	NR
440	184	NR	570	723	NR	700	292	NR	830	5	NR	960	0	NR
445	360	NR	575	753	NR	705	255	NR	835	4	NR	965	0	NR
450	557	NR	580	789	NR	710	221	NR	840	4	NR	970	0	NR
455	486	NR	585	825	NR	715	190	NR	845	3	NR	975	0	NR
460	362	NR	590	864	NR	720	166	NR	850	3	NR	980	0	NR
465	337	NR	595	902	NR	725	143	NR	855	2	NR	985	0	NR
470	279	NR	600	932	NR	730	122	NR	860	2	NR	990	0	NR
475	233	NR	605	963	NR	735	105	NR	865	2	NR	995	0	NR
480	241	NR	610	981	NR	740	90	NR	870	1	NR	1000	0	NR
485	264	NR	615	997	NR	745	77	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-9





TM-30-18

Summary

$R_f = 91.9$
 $R_g = 99.2$
 $\text{CIE } R_a = 93.2$
 $R_9 = 59.0$







Color Vector Graphics





Individual Sample Fidelity Index (R_{fi})

CES01 = 86	CES26 = 94	CES51 = 97	CES76 = 90
CES02 = 63	CES27 = 92	CES52 = 99	CES77 = 89
CES03 = 32	CES28 = 97	CES53 = 97	CES78 = 87
CES04 = 70	CES29 = 97	CES54 = 94	CES79 = 93
CES05 = 51	CES30 = 93	CES55 = 92	CES80 = 93
CES06 = 51	CES31 = 97	CES56 = 95	CES81 = 82
CES07 = 43	CES32 = 91	CES57 = 94	CES82 = 97
CES08 = 42	CES33 = 99	CES58 = 94	CES83 = 96
CES09 = 29	CES34 = 95	CES59 = 97	CES84 = 95
CES10 = 76	CES35 = 97	CES60 = 93	CES85 = 82
CES11 = 59	CES36 = 83	CES61 = 93	CES86 = 83
CES12 = 65	CES37 = 97	CES62 = 88	CES87 = 91
CES13 = 44	CES38 = 89	CES63 = 94	CES88 = 96
CES14 = 74	CES39 = 99	CES64 = 91	CES89 = 85
CES15 = 72	CES40 = 98	CES65 = 90	CES90 = 96
CES16 = 48	CES41 = 97	CES66 = 90	CES91 = 78
CES17 = 50	CES42 = 96	CES67 = 89	CES92 = 79
CES18 = 57	CES43 = 94	CES68 = 90	CES93 = 87
CES19 = 72	CES44 = 99	CES69 = 91	CES94 = 79
CES20 = 67	CES45 = 98	CES70 = 88	CES95 = 84
CES21 = 86	CES46 = 96	CES71 = 85	CES96 = 92
CES22 = 79	CES47 = 94	CES72 = 95	CES97 = 96
CES23 = 92	CES48 = 91	CES73 = 84	CES98 = 94
CES24 = 91	CES49 = 96	CES74 = 91	CES99 = 91
CES25 = 72	CES50 = 98	CES75 = 87	



Color Rendition by Hue-Angle Bin


Measure Comparisons



(END OF REPORT)