

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1216215

Luminaire Tested: 24-ID2-72-CNV-L940-U

Issue Date: 12/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1216215
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2508-510-5)
Test Lab: INNOVATION CENTER
Issue Date: 12/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 24-ID2-72-CNV-L940-U
Description: 2X4 IN DEPTH TROFFER WITH 2INCH CURVE DROP
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6994.5 lumens
Efficiency: N/A
Efficacy: 108.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.2 / 1.31
Luminous Opening: Rectangular w/ Sides (W: 2' x L: 4' x H: 0.16')
CIE Type: Direct

Input Watts (W): 64.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1216215
CATALOG NUMBER: 24-ID2-72-CNV-L940-U

Luminous Intensity Polar Plot



TEST NUMBER: P1216215

CATALOG NUMBER: 24-ID2-72-CNV-L940-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	110	110	110	106	106	106	101	101	101
1	108	104	99	95	105	101	97	94	97	93	90	93	90	87	89	87	85
2	99	90	84	78	96	88	82	77	85	79	75	81	77	73	78	74	71
3	90	80	71	65	87	78	70	64	75	68	63	72	66	62	69	65	61
4	83	71	62	55	80	69	61	55	67	60	54	64	58	53	62	57	52
5	76	63	54	48	74	62	54	47	60	52	47	58	51	46	56	50	46
6	70	57	48	42	68	56	48	42	54	47	41	52	46	41	51	45	40
7	65	52	43	37	63	51	43	37	49	42	36	48	41	36	46	40	36
8	61	47	39	33	59	47	39	33	45	38	33	44	37	32	43	37	32
9	57	44	35	30	55	43	35	30	42	35	30	40	34	29	39	33	29
10	53	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3524	3524	3524
5°	3521	3491	3497
10°	3492	3445	3453
15°	3446	3388	3398
20°	3381	3315	3324
25°	3304	3227	3238
30°	3221	3129	3133
35°	3123	3012	3020
40°	3015	2890	2893
45°	2904	2765	2761
50°	2776	2621	2622
55°	2652	2480	2455
60°	2515	2315	2298
65°	2362	2136	2111
70°	2179	1924	1933
75°	1961	1704	1735
80°	1660	1475	1589
85°	1331	1300	1523

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2904 cd/sqm

TEST NUMBER: P1216215
 CATALOG NUMBER: 24-ID2-72-CNV-L940-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	247.4	3.5
10°-20°	701.9	10.0
20°-30°	1041.2	14.9
30°-40°	1216.6	17.4
40°-50°	1216.0	17.4
50°-60°	1058.7	15.1
60°-70°	784.8	11.2
70°-80°	460.9	6.6
80°-90°	185.0	2.6
90°-100°	48.4	0.7
100°-110°	15.8	0.2
110°-120°	9.1	0.1
120°-130°	5.0	0.1
130°-140°	2.5	0.0
140°-150°	1.2	0.0
150°-160°	0.1	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1990.4	28.5
0°-40°	3207.0	45.9
0°-60°	5481.6	78.4
0°-90°	6912.4	98.8
90°-120°	73.3	1.0
90°-150°	82.0	1.2
90°-180°	82.0	1.2
0°-180°	6994.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2619	2619	2619	2619	2619	
5°	2616	2608	2604	2601	2608	248
15°	2500	2491	2488	2487	2491	705
25°	2267	2263	2259	2257	2262	1045
35°	1954	1950	1943	1942	1942	1222
45°	1587	1584	1577	1571	1567	1224
55°	1195	1192	1185	1180	1166	1068
65°	806	799	793	782	777	797
75°	434	430	432	434	434	458
85°	126	142	166	185	189	132
90°	51	65	84	100	104	31
95°	43	36	36	43	46	34
105°	30	25	14	4	0	32
115°	19	16	9	2	0	19
125°	12	10	6	1	0	11
135°	7	6	3	1	0	6
145°	4	3	1	1	1	2
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1216215

CATALOG NUMBER: 24-ID2-72-CNV-L940-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2619.0	2619.0	2619.0	2619.0	2619.0
2.5°	2627.6	2618.0	2614.2	2611.3	2616.1
5°	2616.1	2608.4	2603.6	2600.7	2607.5
7.5°	2598.8	2590.2	2585.4	2583.5	2589.2
10°	2573.9	2563.3	2559.5	2557.6	2563.3
12.5°	2540.3	2531.7	2527.9	2525.9	2531.7
15°	2500.1	2491.4	2487.6	2486.6	2491.4
17.5°	2453.1	2444.4	2439.6	2439.6	2445.4
20°	2395.5	2389.8	2386.9	2385.9	2388.8
22.5°	2338.0	2329.4	2328.4	2324.6	2331.3
25°	2267.0	2263.2	2259.4	2257.4	2262.2
27.5°	2200.9	2190.3	2185.5	2186.5	2189.3
30°	2121.3	2114.5	2112.6	2107.8	2109.8
32.5°	2038.8	2034.0	2032.1	2026.3	2026.3
35°	1954.4	1949.6	1942.9	1941.9	1941.9
37.5°	1867.1	1862.3	1856.6	1851.8	1853.7
40°	1774.1	1769.3	1762.6	1761.6	1757.8
42.5°	1683.0	1678.2	1670.5	1669.6	1665.7
45°	1587.1	1584.2	1576.6	1570.8	1567.0
47.5°	1491.2	1486.4	1477.8	1472.0	1469.2
50°	1389.6	1384.8	1379.0	1373.3	1372.3
52.5°	1291.7	1290.8	1282.2	1277.4	1272.6
55°	1194.9	1192.0	1185.3	1180.5	1166.1
57.5°	1094.2	1092.3	1088.4	1077.9	1069.3
60°	999.3	993.5	986.8	974.3	972.4
62.5°	898.6	898.6	888.0	878.4	874.6
65°	805.5	798.8	793.1	781.6	776.8
67.5°	708.7	707.7	697.2	690.5	681.8
70°	614.7	611.8	603.2	601.3	599.4
72.5°	520.7	519.8	517.8	515.9	511.1
75°	433.5	429.6	431.5	434.4	433.5
77.5°	345.2	350.0	351.9	360.6	361.5
80°	262.8	270.4	281.9	295.4	298.2
82.5°	188.0	198.5	220.6	237.8	241.7
85°	125.6	141.9	165.9	185.1	188.9
87.5°	77.7	95.9	121.8	140.0	142.9
90°	50.8	65.2	84.4	99.7	103.6
92.5°	47.0	46.0	56.6	68.1	71.9
95°	43.2	36.4	36.4	43.2	46.0
97.5°	40.3	33.6	23.0	24.0	24.9
100°	36.4	30.7	17.3	10.5	10.5
102.5°	33.6	27.8	15.3	3.8	1.0
105°	29.7	24.9	14.4	3.8	0.0
107.5°	26.9	23.0	12.5	2.9	0.0
110°	24.0	20.1	11.5	2.9	0.0

TEST NUMBER: P1216215

CATALOG NUMBER: 24-ID2-72-CNV-L940-U

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	22.1	18.2	10.5	1.9	0.0
115°	19.2	16.3	8.6	1.9	0.0
117.5°	17.3	14.4	7.7	1.0	0.0
120°	15.3	12.5	6.7	1.0	0.0
122.5°	13.4	11.5	5.8	1.0	0.0
125°	12.5	9.6	5.8	1.0	0.0
127.5°	10.5	8.6	4.8	0.0	0.0
130°	9.6	7.7	3.8	0.0	0.0
132.5°	8.6	6.7	2.9	1.0	0.0
135°	6.7	5.8	2.9	1.0	0.0
137.5°	5.8	4.8	1.9	1.0	1.0
140°	4.8	3.8	1.9	1.0	1.0
142.5°	4.8	3.8	1.9	1.0	1.0
145°	3.8	2.9	1.0	1.0	1.0
147.5°	2.9	1.9	1.0	1.0	1.0
150°	1.9	1.9	1.0	1.0	1.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1216215

CATALOG NUMBER: 24-ID2-72-CNV-L940-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.99	16.59	15.38	16.93	17.27	15.01	16.60	15.39	16.94	17.29
	3H	16.66	18.10	17.06	18.45	18.84	16.69	18.13	17.08	18.48	18.87
	4H	17.26	18.62	17.68	18.99	19.40	17.34	18.70	17.76	19.07	19.48
	6H	17.68	18.94	18.11	19.33	19.75	17.88	19.14	18.31	19.53	19.95
	8H	17.80	19.01	18.25	19.42	19.85	18.11	19.32	18.55	19.73	20.16
	12H	17.89	19.04	18.33	19.45	19.90	18.32	19.47	18.77	19.88	20.34
4H	2H	15.56	16.92	15.98	17.30	17.70	15.58	16.94	16.00	17.31	17.71
	3H	17.44	18.58	17.87	19.01	19.43	17.47	18.61	17.90	19.03	19.46
	4H	18.16	19.20	18.61	19.63	20.10	18.25	19.28	18.70	19.72	20.18
	6H	18.70	19.61	19.18	20.07	20.56	18.93	19.84	19.40	20.30	20.78
	8H	18.87	19.72	19.35	20.19	20.68	19.22	20.07	19.70	20.54	21.03
	12H	19.00	19.76	19.50	20.26	20.75	19.50	20.27	20.00	20.76	21.26
8H	4H	18.44	19.29	18.92	19.76	20.25	18.52	19.37	19.00	19.84	20.33
	6H	19.10	19.81	19.61	20.32	20.82	19.33	20.04	19.85	20.55	21.06
	8H	19.34	19.98	19.87	20.51	21.02	19.72	20.36	20.25	20.88	21.40
	12H	19.54	20.10	20.06	20.61	21.20	20.11	20.68	20.64	21.19	21.78
12H	4H	18.48	19.24	18.98	19.74	20.24	18.55	19.31	19.05	19.81	20.31
	6H	19.17	19.80	19.69	20.33	20.84	19.39	20.02	19.91	20.55	21.06
	8H	19.46	20.03	19.99	20.54	21.13	19.83	20.40	20.36	20.91	21.50

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-11

Test Date: 08/26/2025

Luminaire Tested: 22ID2-55-CFR1-L940-U

Data in this report applies to families of products including 22ID2-55-CFR1-L940-U

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-11
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L940-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 4000K 90CRI

Spectral Parameters

CCT (K): 3910
 CIE u' : 0.2263
 CIE v' : 0.5043
 Duv: 0.0008
 CIE x: 0.3851
 CIE y: 0.3813
 CIE z: 0.2336
 Peak Wavelength (nm): 451
 Dominant Wavelength (nm): 578
 Purity: 30.01895
 R_f: 90.8
 R_g: 98.8

CRI (Ra): 92.4
 R1: 92.5
 R2: 94.9
 R3: 95.8
 R4: 92.7
 R5: 91.7
 R6: 92.1
 R7: 94.3
 R8: 85.2
 R9: 62.0
 R10: 87.0
 R11: 92.8
 R12: 71.7
 R13: 93.2
 R14: 97.3
 R15: 89.6



Test Conditions

Stabilization Time: 31M
 Operation Time: 1H 31M
 Sphere Temperature (°C): 25.2.

REPORT NUMBER: SP1-2506-458-11

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-11

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-11

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	394	NR	620	868	NR	750	58	NR	880	1	NR
365	0	NR	495	449	NR	625	858	NR	755	49	NR	885	1	NR
370	0	NR	500	505	NR	630	839	NR	760	42	NR	890	1	NR
375	0	NR	505	553	NR	635	813	NR	765	36	NR	895	1	NR
380	0	NR	510	593	NR	640	783	NR	770	31	NR	900	1	NR
385	0	NR	515	628	NR	645	746	NR	775	26	NR	905	1	NR
390	1	NR	520	651	NR	650	702	NR	780	22	NR	910	0	NR
395	4	NR	525	670	NR	655	657	NR	785	19	NR	915	0	NR
400	5	NR	530	687	NR	660	607	NR	790	16	NR	920	0	NR
405	8	NR	535	705	NR	665	559	NR	795	14	NR	925	0	NR
410	12	NR	540	717	NR	670	507	NR	800	12	NR	930	0	NR
415	19	NR	545	731	NR	675	458	NR	805	10	NR	935	0	NR
420	34	NR	550	745	NR	680	413	NR	810	9	NR	940	0	NR
425	60	NR	555	757	NR	685	367	NR	815	7	NR	945	0	NR
430	107	NR	560	767	NR	690	328	NR	820	6	NR	950	0	NR
435	194	NR	565	777	NR	695	289	NR	825	5	NR	955	0	NR
440	349	NR	570	785	NR	700	253	NR	830	5	NR	960	0	NR
445	678	NR	575	794	NR	705	221	NR	835	4	NR	965	0	NR
450	997	NR	580	809	NR	710	192	NR	840	3	NR	970	0	NR
455	819	NR	585	820	NR	715	165	NR	845	3	NR	975	0	NR
460	581	NR	590	838	NR	720	144	NR	850	2	NR	980	0	NR
465	517	NR	595	851	NR	725	124	NR	855	2	NR	985	0	NR
470	406	NR	600	861	NR	730	107	NR	860	2	NR	990	0	NR
475	327	NR	605	873	NR	735	91	NR	865	2	NR	995	0	NR
480	330	NR	610	875	NR	740	78	NR	870	1	NR	1000	0	NR
485	356	NR	615	877	NR	745	67	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-11

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.75

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	394	NR	620	868	NR	750	58	NR	880	1	NR
365	0	NR	495	449	NR	625	858	NR	755	49	NR	885	1	NR
370	0	NR	500	505	NR	630	839	NR	760	42	NR	890	1	NR
375	0	NR	505	553	NR	635	813	NR	765	36	NR	895	1	NR
380	0	NR	510	593	NR	640	783	NR	770	31	NR	900	1	NR
385	0	NR	515	628	NR	645	746	NR	775	26	NR	905	1	NR
390	1	NR	520	651	NR	650	702	NR	780	22	NR	910	0	NR
395	4	NR	525	670	NR	655	657	NR	785	19	NR	915	0	NR
400	5	NR	530	687	NR	660	607	NR	790	16	NR	920	0	NR
405	8	NR	535	705	NR	665	559	NR	795	14	NR	925	0	NR
410	12	NR	540	717	NR	670	507	NR	800	12	NR	930	0	NR
415	19	NR	545	731	NR	675	458	NR	805	10	NR	935	0	NR
420	34	NR	550	745	NR	680	413	NR	810	9	NR	940	0	NR
425	60	NR	555	757	NR	685	367	NR	815	7	NR	945	0	NR
430	107	NR	560	767	NR	690	328	NR	820	6	NR	950	0	NR
435	194	NR	565	777	NR	695	289	NR	825	5	NR	955	0	NR
440	349	NR	570	785	NR	700	253	NR	830	5	NR	960	0	NR
445	678	NR	575	794	NR	705	221	NR	835	4	NR	965	0	NR
450	997	NR	580	809	NR	710	192	NR	840	3	NR	970	0	NR
455	819	NR	585	820	NR	715	165	NR	845	3	NR	975	0	NR
460	581	NR	590	838	NR	720	144	NR	850	2	NR	980	0	NR
465	517	NR	595	851	NR	725	124	NR	855	2	NR	985	0	NR
470	406	NR	600	861	NR	730	107	NR	860	2	NR	990	0	NR
475	327	NR	605	873	NR	735	91	NR	865	2	NR	995	0	NR
480	330	NR	610	875	NR	740	78	NR	870	1	NR	1000	0	NR
485	356	NR	615	877	NR	745	67	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-11

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.61


λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	394	NR	620	868	NR	750	58	NR	880	1	NR
365	0	NR	495	449	NR	625	858	NR	755	49	NR	885	1	NR
370	0	NR	500	505	NR	630	839	NR	760	42	NR	890	1	NR
375	0	NR	505	553	NR	635	813	NR	765	36	NR	895	1	NR
380	0	NR	510	593	NR	640	783	NR	770	31	NR	900	1	NR
385	0	NR	515	628	NR	645	746	NR	775	26	NR	905	1	NR
390	1	NR	520	651	NR	650	702	NR	780	22	NR	910	0	NR
395	4	NR	525	670	NR	655	657	NR	785	19	NR	915	0	NR
400	5	NR	530	687	NR	660	607	NR	790	16	NR	920	0	NR
405	8	NR	535	705	NR	665	559	NR	795	14	NR	925	0	NR
410	12	NR	540	717	NR	670	507	NR	800	12	NR	930	0	NR
415	19	NR	545	731	NR	675	458	NR	805	10	NR	935	0	NR
420	34	NR	550	745	NR	680	413	NR	810	9	NR	940	0	NR
425	60	NR	555	757	NR	685	367	NR	815	7	NR	945	0	NR
430	107	NR	560	767	NR	690	328	NR	820	6	NR	950	0	NR
435	194	NR	565	777	NR	695	289	NR	825	5	NR	955	0	NR
440	349	NR	570	785	NR	700	253	NR	830	5	NR	960	0	NR
445	678	NR	575	794	NR	705	221	NR	835	4	NR	965	0	NR
450	997	NR	580	809	NR	710	192	NR	840	3	NR	970	0	NR
455	819	NR	585	820	NR	715	165	NR	845	3	NR	975	0	NR
460	581	NR	590	838	NR	720	144	NR	850	2	NR	980	0	NR
465	517	NR	595	851	NR	725	124	NR	855	2	NR	985	0	NR
470	406	NR	600	861	NR	730	107	NR	860	2	NR	990	0	NR
475	327	NR	605	873	NR	735	91	NR	865	2	NR	995	0	NR
480	330	NR	610	875	NR	740	78	NR	870	1	NR	1000	0	NR
485	356	NR	615	877	NR	745	67	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-11


TM-30-18

Summary

$R_f = 90.8$
 $R_g = 98.8$
 $CIE R_a = 92.4$
 $R_9 = 62.0$




Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 93	CES51 = 96	CES76 = 85
CES02 = 62	CES27 = 90	CES52 = 98	CES77 = 88
CES03 = 31	CES28 = 96	CES53 = 96	CES78 = 82
CES04 = 69	CES29 = 96	CES54 = 92	CES79 = 96
CES05 = 49	CES30 = 90	CES55 = 90	CES80 = 93
CES06 = 50	CES31 = 97	CES56 = 93	CES81 = 89
CES07 = 42	CES32 = 91	CES57 = 91	CES82 = 97
CES08 = 41	CES33 = 98	CES58 = 92	CES83 = 98
CES09 = 29	CES34 = 93	CES59 = 96	CES84 = 93
CES10 = 74	CES35 = 96	CES60 = 91	CES85 = 83
CES11 = 57	CES36 = 79	CES61 = 91	CES86 = 88
CES12 = 63	CES37 = 95	CES62 = 84	CES87 = 91
CES13 = 43	CES38 = 85	CES63 = 91	CES88 = 96
CES14 = 74	CES39 = 99	CES64 = 87	CES89 = 87
CES15 = 71	CES40 = 98	CES65 = 87	CES90 = 96
CES16 = 47	CES41 = 96	CES66 = 84	CES91 = 71
CES17 = 49	CES42 = 95	CES67 = 83	CES92 = 79
CES18 = 56	CES43 = 95	CES68 = 86	CES93 = 87
CES19 = 71	CES44 = 99	CES69 = 87	CES94 = 81
CES20 = 66	CES45 = 98	CES70 = 84	CES95 = 82
CES21 = 85	CES46 = 97	CES71 = 77	CES96 = 91
CES22 = 78	CES47 = 97	CES72 = 93	CES97 = 96
CES23 = 91	CES48 = 90	CES73 = 78	CES98 = 94
CES24 = 90	CES49 = 96	CES74 = 91	CES99 = 91
CES25 = 71	CES50 = 97	CES75 = 80	



Color Rendition by Hue-Angle Bin


Measure Comparisons


(END OF REPORT)