

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1216338

Luminaire Tested: 24-ID2-80-DBD-L835-U

Issue Date: 12/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1216338
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2508-510-11)
Test Lab: INNOVATION CENTER
Issue Date: 12/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 24-ID2-80-DBD-L835-U
Description: 2X4 IN DEPTH TROFFER WITH 2INCH DOUBLE BARREL DROP
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8279.1 lumens
Efficiency: N/A
Efficacy: 119.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.21 / 1.31
Luminous Opening: Rectangular w/ Sides (W: 2' x L: 4' x H: 0.15')
CIE Type: Direct

Input Watts (W): 69.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1216338
CATALOG NUMBER: 24-ID2-80-DBD-L835-U

Luminous Intensity Polar Plot



TEST NUMBER: P1216338

CATALOG NUMBER: 24-ID2-80-DBD-L835-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		99
1	108	103	99	95	105	101	97	93	96	93	90		92	90	87		82
2	98	90	83	77	96	88	82	76	84	79	74		81	76	73		68
3	90	79	71	65	87	78	70	64	74	68	63		71	66	61		58
4	82	70	62	55	80	69	61	54	66	59	54		64	58	53		50
5	76	63	54	47	74	62	53	47	60	52	46		57	51	46		43
6	70	57	48	41	68	56	47	41	54	46	41		52	45	40		38
7	65	52	43	37	63	51	42	37	49	42	36		47	41	36		33
8	61	47	39	33	59	46	38	33	45	38	32		44	37	32		30
9	57	43	35	30	55	43	35	29	41	34	29		40	34	29		27
10	53	40	32	27	52	39	32	27	38	31	27		37	31	26		25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4128	4128	4128
5°	4128	4092	4095
10°	4088	4042	4051
15°	4030	3973	3987
20°	3953	3890	3912
25°	3858	3795	3819
30°	3748	3679	3714
35°	3622	3548	3596
40°	3485	3412	3460
45°	3334	3264	3322
50°	3192	3104	3174
55°	3021	2934	2997
60°	2857	2765	2847
65°	2672	2574	2642
70°	2484	2366	2450
75°	2249	2159	2280
80°	2004	1954	2118
85°	1793	1773	2021

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3334 cd/sqm

TEST NUMBER: P1216338
 CATALOG NUMBER: 24-ID2-80-DBD-L835-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	289.8	3.5
10°-20°	822.0	9.9
20°-30°	1220.1	14.7
30°-40°	1426.6	17.2
40°-50°	1427.3	17.2
50°-60°	1245.2	15.0
60°-70°	932.5	11.3
70°-80°	568.1	6.9
80°-90°	239.6	2.9
90°-100°	70.8	0.9
100°-110°	21.8	0.3
110°-120°	8.3	0.1
120°-130°	4.2	0.1
130°-140°	1.9	0.0
140°-150°	0.9	0.0
150°-160°	0.1	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2331.8	28.2
0°-40°	3758.4	45.4
0°-60°	6431.0	77.7
0°-90°	8171.2	98.7
90°-120°	100.9	1.2
90°-150°	107.9	1.3
90°-180°	108.0	1.3
0°-180°	8279.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3068	3068	3068	3068	3068	
5°	3067	3056	3051	3046	3052	291
15°	2922	2916	2913	2914	2920	824
25°	2644	2643	2651	2655	2662	1218
35°	2263	2266	2280	2296	2304	1415
45°	1818	1828	1852	1871	1877	1404
55°	1357	1366	1393	1412	1415	1216
65°	907	918	946	960	964	898
75°	493	511	539	559	561	525
85°	166	189	219	241	243	165
90°	54	83	108	126	131	36
95°	45	44	62	78	83	35
105°	30	24	14	14	17	31
115°	18	15	8	1	0	18
125°	10	9	4	0	0	10
135°	6	4	1	1	0	4
145°	2	2	1	1	1	2
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1216338

CATALOG NUMBER: 24-ID2-80-DBD-L835-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3067.8	3067.8	3067.8	3067.8	3067.8
2.5°	3079.1	3068.9	3062.1	3058.7	3063.2
5°	3066.6	3056.4	3050.7	3046.2	3051.9
7.5°	3043.9	3033.7	3029.1	3026.9	3031.4
10°	3012.1	3001.9	2999.6	2996.2	3004.1
12.5°	2973.5	2963.2	2961.0	2959.8	2967.8
15°	2922.3	2915.5	2913.3	2914.4	2920.1
17.5°	2866.7	2858.7	2857.6	2859.8	2866.7
20°	2798.5	2793.9	2795.1	2800.8	2806.4
22.5°	2725.8	2721.2	2725.8	2728.0	2737.1
25°	2644.0	2642.8	2650.8	2655.3	2662.1
27.5°	2559.9	2559.9	2564.4	2572.4	2582.6
30°	2464.4	2465.6	2476.9	2483.8	2494.0
32.5°	2367.9	2370.1	2380.4	2391.7	2398.5
35°	2263.3	2265.6	2280.4	2296.3	2304.2
37.5°	2156.5	2162.2	2179.3	2194.0	2199.7
40°	2046.3	2053.1	2072.5	2090.6	2094.0
42.5°	1935.0	1941.8	1964.5	1983.8	1987.2
45°	1817.9	1828.2	1852.0	1871.3	1877.0
47.5°	1705.5	1715.7	1739.5	1760.0	1762.3
50°	1593.0	1599.8	1623.6	1643.0	1652.1
52.5°	1480.5	1487.3	1510.0	1533.9	1532.8
55°	1356.6	1365.7	1393.0	1412.3	1414.6
57.5°	1240.7	1253.2	1281.6	1301.0	1307.8
60°	1130.5	1140.8	1169.2	1185.1	1195.3
62.5°	1015.8	1028.3	1055.5	1073.7	1078.3
65°	906.7	918.1	946.5	960.1	963.5
67.5°	794.2	810.1	836.3	853.3	855.6
70°	696.5	707.9	732.9	749.9	751.0
72.5°	590.8	606.7	631.7	652.2	657.9
75°	493.1	511.3	538.6	559.0	561.3
77.5°	399.9	419.3	453.3	473.8	474.9
80°	313.6	335.2	365.9	389.7	389.7
82.5°	232.9	257.9	293.1	314.7	313.6
85°	165.9	188.6	219.3	240.9	243.1
87.5°	103.4	127.3	156.8	175.0	179.5
90°	54.5	82.9	107.9	126.1	130.7
92.5°	50.0	60.2	84.1	101.1	104.5
95°	45.4	44.3	62.5	78.4	82.9
97.5°	40.9	34.1	44.3	57.9	62.5
100°	36.4	30.7	31.8	40.9	44.3
102.5°	33.0	27.3	19.3	26.1	29.5
105°	29.5	23.9	13.6	13.6	17.0
107.5°	26.1	21.6	12.5	5.7	8.0
110°	22.7	19.3	10.2	2.3	1.1

TEST NUMBER: P1216338

CATALOG NUMBER: 24-ID2-80-DBD-L835-U

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	20.5	17.0	9.1	1.1	0.0
115°	18.2	14.8	8.0	1.1	0.0
117.5°	15.9	13.6	6.8	0.0	0.0
120°	13.6	11.4	5.7	0.0	0.0
122.5°	12.5	10.2	4.5	0.0	0.0
125°	10.2	9.1	4.5	0.0	0.0
127.5°	9.1	8.0	3.4	0.0	0.0
130°	8.0	6.8	2.3	0.0	0.0
132.5°	6.8	5.7	2.3	0.0	0.0
135°	5.7	4.5	1.1	1.1	0.0
137.5°	4.5	3.4	1.1	1.1	0.0
140°	3.4	3.4	1.1	1.1	0.0
142.5°	3.4	2.3	1.1	1.1	0.0
145°	2.3	2.3	1.1	1.1	1.1
147.5°	2.3	1.1	1.1	1.1	1.1
150°	1.1	1.1	1.1	1.1	1.1
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1216338

CATALOG NUMBER: 24-ID2-80-DBD-L835-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.36	16.96	15.75	17.30	17.65	15.76	17.36	16.14	17.70	18.05
	3H	17.02	18.46	17.41	18.82	19.21	17.53	18.97	17.92	19.33	19.72
	4H	17.63	18.99	18.05	19.37	19.78	18.24	19.61	18.66	19.98	20.39
	6H	18.08	19.35	18.52	19.74	20.16	18.86	20.13	19.29	20.52	20.94
	8H	18.23	19.44	18.68	19.86	20.29	19.11	20.32	19.56	20.74	21.17
	12H	18.34	19.50	18.79	19.91	20.37	19.34	20.50	19.79	20.91	21.37
4H	2H	15.99	17.36	16.41	17.73	18.14	16.31	17.67	16.73	18.05	18.45
	3H	17.87	19.01	18.30	19.44	19.87	18.30	19.45	18.73	19.87	20.30
	4H	18.61	19.65	19.06	20.09	20.55	19.16	20.20	19.61	20.64	21.11
	6H	19.19	20.10	19.66	20.57	21.05	19.93	20.84	20.40	21.31	21.79
	8H	19.39	20.25	19.87	20.71	21.21	20.25	21.11	20.73	21.57	22.07
	12H	19.55	20.32	20.05	20.82	21.32	20.55	21.32	21.05	21.82	22.32
8H	4H	18.95	19.81	19.43	20.27	20.77	19.44	20.30	19.92	20.77	21.26
	6H	19.67	20.39	20.18	20.90	21.40	20.36	21.07	20.87	21.58	22.09
	8H	19.95	20.60	20.48	21.13	21.64	20.78	21.42	21.31	21.95	22.47
	12H	20.20	20.77	20.73	21.28	21.87	21.20	21.77	21.73	22.29	22.87
12H	4H	19.01	19.78	19.51	20.28	20.78	19.47	20.24	19.97	20.74	21.24
	6H	19.76	20.41	20.29	20.94	21.45	20.41	21.06	20.94	21.59	22.10
	8H	20.11	20.69	20.64	21.20	21.79	20.90	21.48	21.43	21.99	22.58

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-1

Test Date: 07/23/2025

Luminaire Tested: 22ID2-55-CFR1-L835-U

Data in this report applies to families of products including 22ID2-55-CFR1-L835-U


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-1
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L835-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 3500K 80CRI

Spectral Parameters

CCT (K): 3440
 CIE u' : 0.2370
 CIE v' : 0.5132
 Duv: 0.0005
 CIE x: 0.4093
 CIE y: 0.3940
 CIE z: 0.1967
 Peak Wavelength (nm): 599
 Dominant Wavelength (nm): 580
 Purity: 41.09375
 R_f: 84.9
 R_g: 94.6

CRI (Ra): 84.2
 R1: 82.8
 R2: 91.7
 R3: 96.7
 R4: 81.9
 R5: 82.6
 R6: 88.8
 R7: 85.0
 R8: 63.7
 R9: 13.6
 R10: 80.1
 R11: 81.1
 R12: 65.8
 R13: 85.2
 R14: 98.7
 R15: 76.2



Test Conditions


Stabilization Time: 36M
 Operation Time: 1H 36M
 Sphere Temperature (°C): 24.0

REPORT NUMBER: SP1-2506-458-1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-1

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-1

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)
360	0	NR	490	295	NR	620	910	NR	750	30	NR	880	1	NR
365	0	NR	495	335	NR	625	862	NR	755	25	NR	885	1	NR
370	0	NR	500	390	NR	630	809	NR	760	21	NR	890	1	NR
375	0	NR	505	445	NR	635	752	NR	765	18	NR	895	0	NR
380	0	NR	510	490	NR	640	694	NR	770	16	NR	900	0	NR
385	0	NR	515	532	NR	645	630	NR	775	13	NR	905	0	NR
390	0	NR	520	563	NR	650	571	NR	780	12	NR	910	0	NR
395	2	NR	525	588	NR	655	512	NR	785	10	NR	915	0	NR
400	3	NR	530	609	NR	660	453	NR	790	8	NR	920	0	NR
405	5	NR	535	631	NR	665	401	NR	795	7	NR	925	0	NR
410	8	NR	540	654	NR	670	351	NR	800	6	NR	930	0	NR
415	13	NR	545	677	NR	675	306	NR	805	5	NR	935	0	NR
420	23	NR	550	702	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	734	NR	685	230	NR	815	4	NR	945	0	NR
430	70	NR	560	767	NR	690	199	NR	820	4	NR	950	0	NR
435	126	NR	565	802	NR	695	171	NR	825	3	NR	955	0	NR
440	221	NR	570	838	NR	700	146	NR	830	3	NR	960	0	NR
445	418	NR	575	875	NR	705	125	NR	835	2	NR	965	0	NR
450	729	NR	580	913	NR	710	107	NR	840	2	NR	970	0	NR
455	816	NR	585	946	NR	715	90	NR	845	2	NR	975	0	NR
460	578	NR	590	976	NR	720	77	NR	850	1	NR	980	0	NR
465	458	NR	595	992	NR	725	66	NR	855	1	NR	985	0	NR
470	390	NR	600	999	NR	730	56	NR	860	1	NR	990	0	NR
475	299	NR	605	995	NR	735	47	NR	865	1	NR	995	0	NR
480	260	NR	610	975	NR	740	40	NR	870	1	NR	1000	0	NR
485	271	NR	615	948	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-1

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.53

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	295	NR	620	910	NR	750	30	NR	880	1	NR
365	0	NR	495	335	NR	625	862	NR	755	25	NR	885	1	NR
370	0	NR	500	390	NR	630	809	NR	760	21	NR	890	1	NR
375	0	NR	505	445	NR	635	752	NR	765	18	NR	895	0	NR
380	0	NR	510	490	NR	640	694	NR	770	16	NR	900	0	NR
385	0	NR	515	532	NR	645	630	NR	775	13	NR	905	0	NR
390	0	NR	520	563	NR	650	571	NR	780	12	NR	910	0	NR
395	2	NR	525	588	NR	655	512	NR	785	10	NR	915	0	NR
400	3	NR	530	609	NR	660	453	NR	790	8	NR	920	0	NR
405	5	NR	535	631	NR	665	401	NR	795	7	NR	925	0	NR
410	8	NR	540	654	NR	670	351	NR	800	6	NR	930	0	NR
415	13	NR	545	677	NR	675	306	NR	805	5	NR	935	0	NR
420	23	NR	550	702	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	734	NR	685	230	NR	815	4	NR	945	0	NR
430	70	NR	560	767	NR	690	199	NR	820	4	NR	950	0	NR
435	126	NR	565	802	NR	695	171	NR	825	3	NR	955	0	NR
440	221	NR	570	838	NR	700	146	NR	830	3	NR	960	0	NR
445	418	NR	575	875	NR	705	125	NR	835	2	NR	965	0	NR
450	729	NR	580	913	NR	710	107	NR	840	2	NR	970	0	NR
455	816	NR	585	946	NR	715	90	NR	845	2	NR	975	0	NR
460	578	NR	590	976	NR	720	77	NR	850	1	NR	980	0	NR
465	458	NR	595	992	NR	725	66	NR	855	1	NR	985	0	NR
470	390	NR	600	999	NR	730	56	NR	860	1	NR	990	0	NR
475	299	NR	605	995	NR	735	47	NR	865	1	NR	995	0	NR
480	260	NR	610	975	NR	740	40	NR	870	1	NR	1000	0	NR
485	271	NR	615	948	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.07


λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	295	NR	620	910	NR	750	30	NR	880	1	NR
365	0	NR	495	335	NR	625	862	NR	755	25	NR	885	1	NR
370	0	NR	500	390	NR	630	809	NR	760	21	NR	890	1	NR
375	0	NR	505	445	NR	635	752	NR	765	18	NR	895	0	NR
380	0	NR	510	490	NR	640	694	NR	770	16	NR	900	0	NR
385	0	NR	515	532	NR	645	630	NR	775	13	NR	905	0	NR
390	0	NR	520	563	NR	650	571	NR	780	12	NR	910	0	NR
395	2	NR	525	588	NR	655	512	NR	785	10	NR	915	0	NR
400	3	NR	530	609	NR	660	453	NR	790	8	NR	920	0	NR
405	5	NR	535	631	NR	665	401	NR	795	7	NR	925	0	NR
410	8	NR	540	654	NR	670	351	NR	800	6	NR	930	0	NR
415	13	NR	545	677	NR	675	306	NR	805	5	NR	935	0	NR
420	23	NR	550	702	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	734	NR	685	230	NR	815	4	NR	945	0	NR
430	70	NR	560	767	NR	690	199	NR	820	4	NR	950	0	NR
435	126	NR	565	802	NR	695	171	NR	825	3	NR	955	0	NR
440	221	NR	570	838	NR	700	146	NR	830	3	NR	960	0	NR
445	418	NR	575	875	NR	705	125	NR	835	2	NR	965	0	NR
450	729	NR	580	913	NR	710	107	NR	840	2	NR	970	0	NR
455	816	NR	585	946	NR	715	90	NR	845	2	NR	975	0	NR
460	578	NR	590	976	NR	720	77	NR	850	1	NR	980	0	NR
465	458	NR	595	992	NR	725	66	NR	855	1	NR	985	0	NR
470	390	NR	600	999	NR	730	56	NR	860	1	NR	990	0	NR
475	299	NR	605	995	NR	735	47	NR	865	1	NR	995	0	NR
480	260	NR	610	975	NR	740	40	NR	870	1	NR	1000	0	NR
485	271	NR	615	948	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-1





TM-30-18

Summary

$R_f = 84.9$
 $R_g = 94.6$
 $CIE R_a = 84.2$
 $R_9 = 13.6$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 87	CES51 = 92	CES76 = 81
CES02 = 62	CES27 = 91	CES52 = 93	CES77 = 85
CES03 = 31	CES28 = 94	CES53 = 90	CES78 = 80
CES04 = 70	CES29 = 92	CES54 = 89	CES79 = 92
CES05 = 49	CES30 = 89	CES55 = 86	CES80 = 90
CES06 = 51	CES31 = 94	CES56 = 85	CES81 = 77
CES07 = 41	CES32 = 86	CES57 = 83	CES82 = 96
CES08 = 40	CES33 = 97	CES58 = 84	CES83 = 96
CES09 = 29	CES34 = 91	CES59 = 91	CES84 = 91
CES10 = 75	CES35 = 95	CES60 = 89	CES85 = 76
CES11 = 58	CES36 = 79	CES61 = 87	CES86 = 73
CES12 = 64	CES37 = 95	CES62 = 81	CES87 = 85
CES13 = 43	CES38 = 84	CES63 = 85	CES88 = 89
CES14 = 74	CES39 = 98	CES64 = 78	CES89 = 78
CES15 = 71	CES40 = 97	CES65 = 78	CES90 = 90
CES16 = 47	CES41 = 95	CES66 = 75	CES91 = 71
CES17 = 50	CES42 = 96	CES67 = 74	CES92 = 65
CES18 = 56	CES43 = 92	CES68 = 79	CES93 = 79
CES19 = 72	CES44 = 99	CES69 = 83	CES94 = 64
CES20 = 66	CES45 = 95	CES70 = 77	CES95 = 74
CES21 = 86	CES46 = 91	CES71 = 71	CES96 = 85
CES22 = 78	CES47 = 94	CES72 = 90	CES97 = 90
CES23 = 92	CES48 = 83	CES73 = 72	CES98 = 86
CES24 = 90	CES49 = 92	CES74 = 90	CES99 = 79
CES25 = 72	CES50 = 93	CES75 = 75	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)