

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P413135

Luminaire Tested: **22PD-70-PC3-L950**

Issue Date: 9/15/2020



Test Information

Test Method: LM-79-08
Report Number: P413135
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2008-911-15)
Test Lab: INNOVATION CENTER
Issue Date: 9/15/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: 22PD-70-PC3-L950
Description: 7000 LUMEN 2X2 PERCEIVE LED TROFFER WITH PYRAMID PATTERN OPTICS AND 90 CRI, 5000 CCT LEDS
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6231.0 lumens
Efficiency: N/A
Efficacy: 97.5 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.37
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')
CIE Type: Direct

Input Watts (W): 63.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P413135
CATALOG NUMBER: 22PD-70-PC3-L950

Luminous Intensity Polar Plot





TEST NUMBER: P413135

CATALOG NUMBER: 22PD-70-PC3-L950

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	105	101	97	107	103	99	96	99	96	93	95	92	90	91	89	87	85																			
2	100	92	86	80	97	90	84	79	87	82	77	83	79	76	80	77	74	72																			
3	91	81	73	67	89	80	72	67	77	70	65	74	69	64	71	67	63	61																			
4	84	72	64	57	82	71	63	57	68	61	56	66	60	55	64	59	54	52																			
5	77	65	56	49	75	63	55	49	61	54	49	59	53	48	58	52	47	45																			
6	71	58	49	43	69	57	49	43	55	48	43	54	47	42	52	46	42	40																			
7	66	53	44	38	64	52	44	38	50	43	38	49	42	37	48	42	37	35																			
8	62	48	40	34	60	48	40	34	46	39	34	45	38	34	44	38	33	31																			
9	58	44	36	31	56	44	36	31	43	35	30	41	35	30	40	34	30	28																			
10	54	41	33	28	53	40	33	28	39	32	28	38	32	28	38	32	27	26																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6241	6241	6241
5°	6249	6245	6253
10°	6265	6263	6265
15°	6272	6281	6271
20°	6241	6292	6237
25°	6168	6269	6164
30°	6077	6196	6068
35°	5972	6090	5972
40°	5859	5963	5859
45°	5705	5817	5713
50°	5510	5618	5532
55°	5254	5358	5254
60°	4900	5022	4868
65°	4397	4552	4341
70°	3761	3895	3651
75°	2984	3068	2830
80°	2139	2218	2035
85°	1411	1457	1321



TEST NUMBER: P413135

CATALOG NUMBER: 22PD-70-PC3-L950

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	220.1	3.5
10°-20°	635.6	10.2
20°-30°	964.4	15.5
30°-40°	1151.7	18.5
40°-50°	1171.3	18.8
50°-60°	1013.1	16.3
60°-70°	697.2	11.2
70°-80°	316.4	5.1
80°-90°	61.2	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1820.1	29.2
0°-40°	2971.8	47.7
0°-60°	5156.2	82.8
0°-90°	6231.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6231.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2319	2319	2319	2319	2319	
5°	2314	2311	2312	2312	2315	220
15°	2252	2253	2254	2251	2251	635
25°	2077	2096	2111	2092	2076	957
35°	1818	1850	1854	1847	1818	1137
45°	1499	1526	1529	1527	1501	1156
55°	1120	1139	1142	1140	1120	1001
65°	690	710	715	709	682	685
75°	287	298	295	292	272	309
85°	46	49	47	46	43	60
90°	0	0	0	0	0	



TEST NUMBER: P413135

CATALOG NUMBER: 22PD-70-PC3-L950

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2319.4	2319.4	2319.4	2319.4	2319.4
2.5°	2319.4	2316.5	2317.2	2317.9	2322.4
5°	2313.5	2311.3	2312.0	2312.0	2315.0
7.5°	2303.9	2303.2	2303.2	2302.5	2304.7
10°	2292.9	2291.4	2292.1	2291.4	2292.9
12.5°	2275.9	2275.9	2276.6	2274.4	2275.9
15°	2251.5	2253.0	2254.5	2250.8	2250.8
17.5°	2220.6	2224.3	2227.9	2221.3	2217.6
20°	2179.2	2188.1	2197.0	2186.6	2177.8
22.5°	2131.3	2146.1	2159.3	2143.1	2131.3
25°	2077.4	2095.9	2111.4	2092.2	2076.0
27.5°	2019.2	2039.8	2054.6	2038.3	2016.2
30°	1955.7	1980.8	1994.1	1978.6	1952.8
32.5°	1887.8	1917.4	1925.5	1915.9	1886.4
35°	1817.8	1850.2	1853.9	1847.3	1817.8
37.5°	1744.7	1775.7	1778.7	1775.0	1744.7
40°	1668.0	1696.8	1697.5	1697.5	1668.0
42.5°	1586.1	1614.1	1614.1	1613.4	1588.3
45°	1499.1	1526.4	1528.6	1527.1	1501.3
47.5°	1412.7	1433.4	1437.1	1434.1	1411.3
50°	1316.1	1337.5	1341.9	1339.0	1321.3
52.5°	1220.2	1240.1	1244.5	1242.3	1222.4
55°	1119.9	1139.1	1142.0	1139.8	1119.9
57.5°	1023.2	1035.8	1038.7	1034.3	1009.2
60°	910.4	928.1	933.2	928.1	904.5
62.5°	801.2	820.4	824.8	817.4	792.3
65°	690.5	709.7	714.9	709.0	681.7
67.5°	585.8	599.8	604.2	597.6	572.5
70°	478.0	495.8	495.0	486.2	464.0
72.5°	371.8	396.2	391.7	386.6	362.2
75°	287.0	298.0	295.1	292.1	272.2
77.5°	205.1	218.4	211.0	211.7	194.8
80°	138.0	150.5	143.1	140.2	131.3
82.5°	87.8	93.0	91.5	90.0	81.9
85°	45.7	48.7	47.2	45.7	42.8
87.5°	17.7	19.2	17.7	17.7	16.2
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)