

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P412565

Luminaire Tested: **24PD-70-PB1-L930**

Issue Date: 9/15/2020



Test Information

Test Method: LM-79-08
Report Number: P412565
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2008-911-45)
Test Lab: INNOVATION CENTER
Issue Date: 9/15/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: 24PD-70-PB1-L930
Description: 7000 LUMEN 2X4 PERCEIVE LED TROFFER WITH BEVEL PATTERN OPTICS AND 90 CRI, 3000 CCT LEDS
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5801.0 lumens
Efficiency: N/A
Efficacy: 112.6 lumens/watt
Spacing Criteria (0/90/45): 1.34 / 1.32 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 51.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P412565
CATALOG NUMBER: 24PD-70-PB1-L930

Luminous Intensity Polar Plot





TEST NUMBER: P412565

CATALOG NUMBER: 24PD-70-PB1-L930

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86																			
2	101	93	87	82	98	91	86	81	88	83	79	85	81	77	82	78	75	73																			
3	92	83	75	69	90	81	74	68	78	72	67	75	70	66	73	69	65	63																			
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	65	60	56	54																			
5	78	66	57	51	76	65	57	51	63	56	50	61	55	50	59	54	49	47																			
6	72	60	51	45	70	59	51	45	57	50	44	55	49	44	54	48	43	41																			
7	67	54	46	40	65	53	45	40	52	45	39	50	44	39	49	43	39	37																			
8	63	49	41	35	61	49	41	35	47	40	35	46	40	35	45	39	35	33																			
9	58	45	37	32	57	45	37	32	44	37	32	43	36	32	42	36	31	30																			
10	55	42	34	29	53	41	34	29	40	33	29	39	33	29	39	33	29	27																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2933	2933	2933
5°	2943	2943	2943
10°	2963	2960	2960
15°	2989	2985	2983
20°	3023	3013	3005
25°	3055	3039	3022
30°	3081	3056	3033
35°	3085	3058	3020
40°	3049	3013	2962
45°	2950	2896	2821
50°	2766	2680	2582
55°	2486	2338	2242
60°	2164	1992	1916
65°	1821	1685	1612
70°	1484	1409	1352
75°	1189	1147	1099
80°	914	841	819
85°	571	553	553



TEST NUMBER: P412565

CATALOG NUMBER: 24PD-70-PB1-L930

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.6	3.6
10°-20°	605.8	10.4
20°-30°	943.8	16.3
30°-40°	1161.1	20.0
40°-50°	1166.2	20.1
50°-60°	898.9	15.5
60°-70°	533.6	9.2
70°-80°	237.6	4.1
80°-90°	46.4	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1757.2	30.3
0°-40°	2918.3	50.3
0°-60°	4983.4	85.9
0°-90°	5801.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5801.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2180	2180	2180	2180	2180	
5°	2179	2180	2179	2177	2179	208
15°	2146	2146	2143	2140	2141	607
25°	2058	2057	2047	2038	2036	949
35°	1878	1875	1862	1846	1839	1173
45°	1550	1546	1522	1496	1483	1190
55°	1060	1040	997	967	956	948
65°	572	547	529	509	506	572
75°	229	224	221	213	212	248
85°	37	35	36	34	36	49
90°	0	0	0	0	0	



TEST NUMBER: P412565

CATALOG NUMBER: 24PD-70-PB1-L930

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2180.1	2180.1	2180.1	2180.1	<i>2180.1</i>
2.5°	<i>2181.2</i>	<i>2180.7</i>	<i>2180.7</i>	<i>2178.4</i>	<i>2183.0</i>
5°	2178.9	2179.5	2178.9	2176.6	<i>2178.9</i>
7.5°	2174.3	2174.9	2173.7	2171.4	<i>2173.7</i>
10°	2168.5	2168.5	2166.2	2165.1	<i>2166.8</i>
12.5°	2158.7	2158.7	2156.4	2154.7	<i>2156.4</i>
15°	2146.0	2146.0	2143.1	2139.6	<i>2141.4</i>
17.5°	2130.4	2130.4	2125.8	2121.2	<i>2122.3</i>
20°	2111.3	2110.8	2104.4	2098.0	<i>2098.6</i>
22.5°	2087.1	2086.5	2078.4	2070.9	<i>2068.6</i>
25°	2057.6	2057.0	2047.2	2037.9	<i>2035.6</i>
27.5°	2023.5	2021.2	2010.2	1999.8	<i>1997.5</i>
30°	1983.1	1981.3	1966.9	1956.5	<i>1951.9</i>
32.5°	1936.3	1931.6	1918.3	1905.6	<i>1899.3</i>
35°	1877.9	1875.0	1861.7	1846.1	<i>1838.6</i>
37.5°	1812.0	1809.1	1794.7	1777.4	<i>1768.7</i>
40°	1735.8	1733.4	1715.5	1697.6	<i>1686.6</i>
42.5°	1647.9	1646.2	1627.1	1602.3	<i>1590.7</i>
45°	1550.3	1546.2	1522.0	1496.5	<i>1482.7</i>
47.5°	1441.6	1434.7	1405.2	1381.0	<i>1366.0</i>
50°	1321.5	1312.2	1280.4	1249.2	<i>1233.6</i>
52.5°	1191.5	1175.3	1142.3	1106.5	<i>1091.5</i>
55°	1059.7	1039.5	996.7	966.7	<i>955.7</i>
57.5°	930.9	901.4	860.9	839.6	<i>828.6</i>
60°	804.3	772.0	740.2	719.4	<i>711.9</i>
62.5°	683.6	656.4	629.2	608.4	<i>603.8</i>
65°	572.0	547.2	529.3	509.1	<i>506.2</i>
67.5°	468.0	456.5	440.3	423.0	<i>420.6</i>
70°	377.3	372.7	358.2	347.8	<i>343.8</i>
72.5°	301.0	296.4	286.0	278.5	<i>277.4</i>
75°	228.8	224.2	220.7	213.2	<i>211.5</i>
77.5°	162.9	163.5	160.6	156.6	<i>157.7</i>
80°	117.9	110.9	108.6	106.3	<i>105.7</i>
82.5°	72.2	68.2	66.4	65.9	<i>67.0</i>
85°	37.0	35.2	35.8	34.1	<i>35.8</i>
87.5°	12.7	12.7	13.3	12.7	<i>13.9</i>
90°	0.0	0.0	0.0	0.0	<i>0.0</i>



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)