

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P413251

Luminaire Tested: **24PD-70-PC3-L940**

Issue Date: 9/15/2020



**Test Information**


Test Method: LM-79-08  
Report Number: P413251  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2008-911-46)  
Test Lab: INNOVATION CENTER  
Issue Date: 9/15/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: 24PD-70-PC3-L940  
Description: 7000 LUMEN 2X4 PERCEIVE LED TROFFER WITH PYRAMID PATTERN OPTICS AND 90 CRI, 4000 CCT LEDS  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5860.0 lumens  
Efficiency: N/A  
Efficacy: 113.8 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.26 / 1.38  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 51.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P413251  
CATALOG NUMBER: 24PD-70-PC3-L940

### Luminous Intensity Polar Plot





TEST NUMBER: P413251

CATALOG NUMBER: 24PD-70-PC3-L940

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	109	105	101	97	107	103	99	96	99	96	93	95	92	90	91	89	87	85								
2	100	92	86	80	97	90	84	79	87	82	77	83	79	75	80	77	74	72								
3	91	81	73	67	89	80	72	66	77	70	65	74	69	64	71	67	63	61								
4	84	72	63	57	81	71	63	57	68	61	56	66	60	55	64	59	54	52								
5	77	64	56	49	75	63	55	49	61	54	48	59	53	48	57	52	47	45								
6	71	58	49	43	69	57	49	43	55	48	42	54	47	42	52	46	42	40								
7	66	53	44	38	64	52	44	38	50	43	38	49	42	37	47	42	37	35								
8	61	48	40	34	60	47	39	34	46	39	34	45	38	33	44	38	33	31								
9	57	44	36	30	56	43	36	30	42	35	30	41	35	30	40	34	30	28								
10	54	41	33	28	52	40	33	28	39	32	27	38	32	27	37	31	27	25								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2885	2885	2885
5°	2888	2887	2889
10°	2894	2890	2893
15°	2904	2898	2899
20°	2913	2909	2896
25°	2905	2916	2875
30°	2876	2906	2840
35°	2834	2870	2791
40°	2784	2817	2734
45°	2721	2751	2665
50°	2637	2667	2572
55°	2529	2551	2453
60°	2361	2387	2279
65°	2127	2180	2044
70°	1806	1886	1734
75°	1398	1500	1334
80°	1040	1086	943
85°	642	687	596



TEST NUMBER: P413251

CATALOG NUMBER: 24PD-70-PC3-L940

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	203.4	3.5
10°-20°	587.9	10.0
20°-30°	900.4	15.4
30°-40°	1083.2	18.5
40°-50°	1104.5	18.8
50°-60°	957.6	16.3
60°-70°	663.9	11.3
70°-80°	303.2	5.2
80°-90°	56.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1691.7	28.9
0°-40°	2774.9	47.4
0°-60°	4836.9	82.5
0°-90°	5860.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5860.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2144	2144	2144	2144	2144	
5°	2138	2138	2137	2136	2139	203
15°	2084	2084	2080	2079	2081	589
25°	1957	1962	1964	1947	1937	901
35°	1725	1744	1747	1725	1699	1079
45°	1430	1448	1446	1426	1400	1102
55°	1078	1084	1087	1061	1046	960
65°	668	682	685	662	642	661
75°	269	284	289	279	257	294
85°	42	43	44	42	39	56
90°	0	0	0	0	0	



TEST NUMBER: P413251

CATALOG NUMBER: 24PD-70-PC3-L940

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2143.9	2143.9	2143.9	2143.9	<i>2143.9</i>
2.5°	<i>2143.9</i>	<i>2143.9</i>	<i>2142.7</i>	<i>2141.5</i>	<i>2145.1</i>
5°	2138.5	2138.5	2137.4	2136.2	<i>2139.1</i>
7.5°	2130.2	2129.6	2128.4	2127.3	<i>2129.0</i>
10°	2118.4	2117.8	2115.4	2114.8	<i>2117.2</i>
12.5°	2103.5	2102.9	2099.3	2099.3	<i>2101.1</i>
15°	2084.5	2083.9	2080.3	2078.6	<i>2080.9</i>
17.5°	2063.1	2062.5	2058.4	2053.6	<i>2054.8</i>
20°	2034.6	2034.6	2031.6	2024.5	<i>2022.7</i>
22.5°	2000.2	2002.0	2002.0	1988.3	<i>1982.9</i>
25°	1956.8	1962.2	1963.9	1946.7	<i>1936.6</i>
27.5°	1907.5	1915.8	1920.6	1898.6	<i>1885.6</i>
30°	1851.1	1864.8	1870.7	1846.9	<i>1827.9</i>
32.5°	1789.3	1806.6	1813.7	1790.5	<i>1766.2</i>
35°	1725.2	1743.6	1747.2	1724.6	<i>1699.1</i>
37.5°	1656.9	1675.9	1680.7	1660.5	<i>1629.0</i>
40°	1585.1	1604.1	1604.1	1587.4	<i>1556.5</i>
42.5°	1509.0	1529.2	1528.6	1508.4	<i>1480.5</i>
45°	1430.0	1447.9	1445.5	1425.9	<i>1400.4</i>
47.5°	1348.7	1360.0	1362.9	1339.8	<i>1315.4</i>
50°	1259.6	1270.9	1273.9	1247.7	<i>1228.7</i>
52.5°	1171.7	1178.8	1183.0	1152.7	<i>1139.1</i>
55°	1077.9	1084.4	1087.4	1060.7	<i>1045.8</i>
57.5°	978.7	987.0	990.6	963.9	<i>947.2</i>
60°	877.2	886.1	887.2	862.3	<i>846.9</i>
62.5°	773.8	785.7	788.1	763.1	<i>744.7</i>
65°	668.1	682.4	684.7	661.6	<i>642.0</i>
67.5°	562.4	581.4	582.0	563.0	<i>539.8</i>
70°	459.1	479.9	479.3	463.2	<i>440.7</i>
72.5°	360.5	379.5	383.6	368.8	<i>346.8</i>
75°	269.0	283.9	288.6	279.1	<i>256.6</i>
77.5°	191.2	204.9	209.0	200.1	<i>183.5</i>
80°	134.2	134.8	140.2	133.0	<i>121.7</i>
82.5°	83.1	82.0	83.7	80.8	<i>74.2</i>
85°	41.6	42.8	44.5	42.2	<i>38.6</i>
87.5°	14.3	14.8	16.0	16.0	<i>14.3</i>
90°	0.0	0.0	0.0	0.0	<i>0.0</i>



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°    - - 45°-225°    - - - - 90°-270°







(END OF REPORT)