

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1471696

Luminaire Tested: 22PTR-25-L835-UNV-STD-W

Issue Date: 6/22/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1471696  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2310-200-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 6/22/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: 22PTR-25-L835-UNV-STD-W  
Description: 2500 LUMEN 2X2 PERCEIVE PT TROFFER WITH 3500K, 80 CRI LEDS AND Frosted Lens White Recessed Frame  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2409.2 lumens  
Efficiency: N/A  
Efficacy: 127.5 lumens/watt  
Spacing Criteria (0/90/45): 1.27 / 1.21 / 1.35  
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')  
CIE Type: Direct

Input Watts (W): 18.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1471696

CATALOG NUMBER: 22PTR-25-L835-UNV-STD-W

### Luminous Intensity Polar Plot



TEST NUMBER: P1471696

CATALOG NUMBER: 22PTR-25-L835-UNV-STD-W

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|--|-----|-----|-----|--|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     |  | 20  |     |     |  |  | 20  |     |     |  |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     |  | 50  |     |     |  |  | 30  |     |     |  |  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  |  | 50  | 30  | 10  |  |  | 0   |
| RCR |     |     |     |     |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  |  | 106 | 106 | 106 |  |  | 102 |
| 1   | 109 | 105 | 101 | 97  | 107 | 103 | 99  | 96  |  | 98  | 95  | 93  |  |  | 95  | 92  | 90  |  |  | 91  |
| 2   | 100 | 92  | 85  | 80  | 97  | 90  | 84  | 79  |  | 87  | 81  | 77  |  |  | 83  | 79  | 75  |  |  | 80  |
| 3   | 91  | 81  | 73  | 67  | 89  | 79  | 72  | 66  |  | 76  | 70  | 65  |  |  | 74  | 68  | 64  |  |  | 71  |
| 4   | 84  | 72  | 63  | 57  | 81  | 71  | 63  | 56  |  | 68  | 61  | 56  |  |  | 66  | 60  | 55  |  |  | 64  |
| 5   | 77  | 64  | 56  | 49  | 75  | 63  | 55  | 49  |  | 61  | 54  | 48  |  |  | 59  | 53  | 48  |  |  | 57  |
| 6   | 71  | 58  | 49  | 43  | 69  | 57  | 49  | 43  |  | 55  | 48  | 42  |  |  | 54  | 47  | 42  |  |  | 52  |
| 7   | 66  | 53  | 44  | 38  | 64  | 52  | 44  | 38  |  | 50  | 43  | 38  |  |  | 49  | 42  | 37  |  |  | 48  |
| 8   | 61  | 48  | 40  | 34  | 60  | 47  | 39  | 34  |  | 46  | 39  | 34  |  |  | 45  | 38  | 33  |  |  | 44  |
| 9   | 57  | 44  | 36  | 31  | 56  | 44  | 36  | 30  |  | 42  | 35  | 30  |  |  | 41  | 35  | 30  |  |  | 40  |
| 10  | 54  | 41  | 33  | 28  | 53  | 40  | 33  | 28  |  | 39  | 32  | 28  |  |  | 38  | 32  | 27  |  |  | 37  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 2434 | 2434 | 2434 |
| 5°  | 2452 | 2432 | 2442 |
| 10° | 2445 | 2426 | 2416 |
| 15° | 2434 | 2415 | 2410 |
| 20° | 2436 | 2397 | 2388 |
| 25° | 2412 | 2377 | 2369 |
| 30° | 2402 | 2375 | 2298 |
| 35° | 2375 | 2332 | 2242 |
| 40° | 2373 | 2271 | 2146 |
| 45° | 2343 | 2212 | 2060 |
| 50° | 2312 | 2113 | 1948 |
| 55° | 2267 | 2014 | 1830 |
| 60° | 2227 | 1885 | 1661 |
| 65° | 2151 | 1729 | 1486 |
| 70° | 2081 | 1504 | 1212 |
| 75° | 1955 | 1187 | 835  |
| 80° | 1695 | 717  | 501  |
| 85° | 1130 | 516  | 482  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2343 cd/sqm

TEST NUMBER: P1471696

CATALOG NUMBER: 22PTR-25-L835-UNV-STD-W

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 85.7   | 3.6       |
| 10°-20°   | 245.3  | 10.2      |
| 20°-30°   | 370.6  | 15.4      |
| 30°-40°   | 440.6  | 18.3      |
| 40°-50°   | 446.9  | 18.5      |
| 50°-60°   | 388.0  | 16.1      |
| 60°-70°   | 275.5  | 11.4      |
| 70°-80°   | 131.6  | 5.5       |
| 80°-90°   | 25.0   | 1.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 701.6  | 29.1      |
| 0°-40°    | 1142.3 | 47.4      |
| 0°-60°    | 1977.2 | 82.1      |
| 0°-90°    | 2409.2 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2409.2 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | 22.5° | 45° | 67.5° | 90° | Flux |
|-----|-----|-------|-----|-------|-----|------|
| 0°  | 904 | 904   | 904 | 904   | 904 |      |
| 5°  | 908 | 904   | 900 | 902   | 904 | 86   |
| 15° | 874 | 876   | 867 | 866   | 865 | 248  |
| 25° | 812 | 811   | 800 | 804   | 798 | 375  |
| 35° | 723 | 722   | 710 | 686   | 682 | 454  |
| 45° | 616 | 610   | 581 | 550   | 541 | 475  |
| 55° | 483 | 469   | 429 | 404   | 390 | 432  |
| 65° | 338 | 312   | 272 | 242   | 233 | 335  |
| 75° | 188 | 154   | 114 | 90    | 80  | 197  |
| 85° | 37  | 19    | 17  | 16    | 16  | 46   |
| 90° | 0   | 0     | 0   | 0     | 0   |      |

TEST NUMBER: P1471696

CATALOG NUMBER: 22PTR-25-L835-UNV-STD-W

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    | 22.5° | 45°   | 67.5° | 90°   |
|-------|-------|-------|-------|-------|-------|
| 0°    | 904.5 | 904.5 | 904.5 | 904.5 | 904.5 |
| 2.5°  | 909.9 | 906.6 | 905.5 | 909.3 | 900.2 |
| 5°    | 907.7 | 904.5 | 900.2 | 902.3 | 903.9 |
| 7.5°  | 901.2 | 898.5 | 892.6 | 897.5 | 892.6 |
| 10°   | 894.8 | 892.1 | 887.8 | 889.4 | 884.0 |
| 12.5° | 888.3 | 881.8 | 880.8 | 881.8 | 878.1 |
| 15°   | 873.8 | 875.9 | 866.8 | 865.7 | 865.1 |
| 17.5° | 866.8 | 861.4 | 851.7 | 852.2 | 851.1 |
| 20°   | 850.6 | 844.1 | 837.1 | 836.1 | 833.9 |
| 22.5° | 833.9 | 826.4 | 819.9 | 823.1 | 818.3 |
| 25°   | 812.4 | 811.3 | 800.5 | 803.7 | 797.8 |
| 27.5° | 793.5 | 789.7 | 784.9 | 777.9 | 769.3 |
| 30°   | 773.0 | 769.3 | 764.4 | 746.1 | 739.6 |
| 32.5° | 751.5 | 747.2 | 737.5 | 715.9 | 708.9 |
| 35°   | 722.9 | 721.8 | 710.0 | 685.8 | 682.5 |
| 37.5° | 701.4 | 689.5 | 679.8 | 655.1 | 645.9 |
| 40°   | 675.5 | 669.1 | 646.4 | 622.7 | 610.9 |
| 42.5° | 647.0 | 639.4 | 613.6 | 588.3 | 575.3 |
| 45°   | 615.7 | 610.3 | 581.3 | 550.5 | 541.4 |
| 47.5° | 583.4 | 578.6 | 544.1 | 514.5 | 502.6 |
| 50°   | 552.2 | 546.2 | 504.8 | 476.2 | 465.4 |
| 52.5° | 518.2 | 508.5 | 467.6 | 439.6 | 429.3 |
| 55°   | 483.2 | 468.7 | 429.3 | 404.0 | 390.0 |
| 57.5° | 446.0 | 432.6 | 388.9 | 362.5 | 351.2 |
| 60°   | 413.7 | 394.9 | 350.2 | 323.2 | 308.7 |
| 62.5° | 372.2 | 356.1 | 313.5 | 281.7 | 274.7 |
| 65°   | 337.8 | 312.4 | 271.5 | 242.4 | 233.3 |
| 67.5° | 302.7 | 273.1 | 231.6 | 202.0 | 197.2 |
| 70°   | 264.5 | 233.8 | 191.2 | 162.1 | 154.1 |
| 72.5° | 225.7 | 195.5 | 154.1 | 123.4 | 118.5 |
| 75°   | 188.0 | 153.5 | 114.2 | 90.5  | 80.3  |
| 77.5° | 147.1 | 115.8 | 80.3  | 55.5  | 49.0  |
| 80°   | 109.4 | 78.1  | 46.3  | 32.9  | 32.3  |
| 82.5° | 71.6  | 45.3  | 24.8  | 25.3  | 24.2  |
| 85°   | 36.6  | 19.4  | 16.7  | 16.2  | 15.6  |
| 87.5° | 7.0   | 7.5   | 8.1   | 8.1   | 8.1   |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |

TEST NUMBER: P1471696

CATALOG NUMBER: 22PTR-25-L835-UNV-STD-W

**CIE UGR TABLE:**

| Reflectances:   |      |                  |      |      |      |      |                |      |      |      |      |
|-----------------|------|------------------|------|------|------|------|----------------|------|------|------|------|
| Ceiling         |      | 0.7              | 0.7  | 0.5  | 0.5  | 0.3  | 0.7            | 0.7  | 0.5  | 0.5  | 0.3  |
| Wall            |      | 0.5              | 0.3  | 0.5  | 0.3  | 0.3  | 0.5            | 0.3  | 0.5  | 0.3  | 0.3  |
| Reference plane |      | 0.2              | 0.2  | 0.2  | 0.2  | 0.2  | 0.2            | 0.2  | 0.2  | 0.2  | 0.2  |
| Room Dimensions |      | Viewed crosswise |      |      |      |      | Viewed endwise |      |      |      |      |
| X=2H            | Y=2H | 15.2             | 16.8 | 15.6 | 17.1 | 17.5 | 13.9           | 15.5 | 14.3 | 15.8 | 16.1 |
|                 | 3H   | 17.1             | 18.5 | 17.4 | 18.8 | 19.2 | 15.2           | 16.6 | 15.6 | 17.0 | 17.3 |
|                 | 4H   | 17.8             | 19.1 | 18.2 | 19.5 | 19.8 | 15.5           | 16.8 | 15.9 | 17.2 | 17.6 |
|                 | 6H   | 18.2             | 19.5 | 18.6 | 19.9 | 20.2 | 15.6           | 16.8 | 16.0 | 17.2 | 17.6 |
|                 | 8H   | 18.4             | 19.6 | 18.8 | 20.0 | 20.4 | 15.6           | 16.8 | 16.0 | 17.1 | 17.5 |
|                 | 12H  | 18.4             | 19.6 | 18.9 | 20.0 | 20.4 | 15.6           | 16.7 | 16.0 | 17.1 | 17.5 |
| 4H              | 2H   | 15.6             | 17.0 | 16.0 | 17.4 | 17.7 | 14.6           | 15.9 | 15.0 | 16.3 | 16.7 |
|                 | 3H   | 17.7             | 18.8 | 18.1 | 19.2 | 19.6 | 16.0           | 17.1 | 16.4 | 17.5 | 17.9 |
|                 | 4H   | 18.5             | 19.5 | 18.9 | 19.9 | 20.3 | 16.4           | 17.4 | 16.8 | 17.8 | 18.2 |
|                 | 6H   | 19.1             | 19.9 | 19.5 | 20.4 | 20.8 | 16.5           | 17.4 | 16.9 | 17.8 | 18.3 |
|                 | 8H   | 19.2             | 20.0 | 19.7 | 20.5 | 21.0 | 16.5           | 17.3 | 17.0 | 17.8 | 18.3 |
|                 | 12H  | 19.3             | 20.1 | 19.8 | 20.5 | 21.0 | 16.5           | 17.3 | 17.0 | 17.8 | 18.2 |
| 8H              | 4H   | 18.6             | 19.4 | 19.0 | 19.8 | 20.3 | 16.6           | 17.5 | 17.1 | 17.9 | 18.4 |
|                 | 6H   | 19.2             | 19.9 | 19.7 | 20.4 | 20.8 | 16.8           | 17.5 | 17.3 | 18.0 | 18.4 |
|                 | 8H   | 19.4             | 20.0 | 19.9 | 20.5 | 21.0 | 16.8           | 17.4 | 17.3 | 18.0 | 18.4 |
|                 | 12H  | 19.5             | 20.1 | 20.0 | 20.6 | 21.1 | 16.9           | 17.4 | 17.4 | 17.9 | 18.5 |
| 12H             | 4H   | 18.5             | 19.3 | 19.0 | 19.8 | 20.2 | 16.7           | 17.4 | 17.1 | 17.9 | 18.4 |
|                 | 6H   | 19.2             | 19.8 | 19.7 | 20.3 | 20.8 | 16.8           | 17.4 | 17.3 | 17.9 | 18.4 |
|                 | 8H   | 19.4             | 19.9 | 19.9 | 20.4 | 21.0 | 16.9           | 17.4 | 17.4 | 17.9 | 18.5 |















(END OF REPORT)