

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1471657

Luminaire Tested: 14PTR-30S-PP3-L835-UNV-STD-B

Issue Date: 6/22/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1471657  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P737727)  
Test Lab: INNOVATION CENTER  
Issue Date: 6/22/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: 14PTR-30S-PP3-L835-UNV-STD-B  
Description: 3000 LUMEN 1X4 PERCEIVE PT TROFFER WITH 3500K, 80 CRI LEDS AND PP3 Lens Black Recess  
Frame  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2111.7 lumens  
Efficiency: N/A  
Efficacy: 88.4 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34  
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 23.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1471657

CATALOG NUMBER: 14PTR-30S-PP3-L835-UNV-STD-B

### Luminous Intensity Polar Plot



TEST NUMBER: P1471657

CATALOG NUMBER: 14PTR-30S-PP3-L835-UNV-STD-B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    | 100 |
| 1   | 109 | 105 | 101 | 97  | 107 | 103 | 99  | 96  | 99  | 96  | 93  | 95  | 92  | 90  | 91  | 89  | 87  | 85  |    | 85  |
| 2   | 100 | 92  | 86  | 80  | 97  | 90  | 84  | 79  | 87  | 82  | 78  | 84  | 79  | 76  | 81  | 77  | 74  | 72  |    | 72  |
| 3   | 92  | 81  | 74  | 67  | 89  | 80  | 73  | 67  | 77  | 71  | 66  | 74  | 69  | 65  | 72  | 67  | 63  | 61  |    | 61  |
| 4   | 84  | 73  | 64  | 58  | 82  | 71  | 63  | 57  | 69  | 62  | 56  | 66  | 60  | 56  | 64  | 59  | 55  | 53  |    | 53  |
| 5   | 77  | 65  | 56  | 50  | 75  | 64  | 56  | 50  | 62  | 55  | 49  | 60  | 54  | 49  | 58  | 52  | 48  | 46  |    | 46  |
| 6   | 72  | 59  | 50  | 44  | 70  | 58  | 50  | 44  | 56  | 49  | 43  | 54  | 48  | 43  | 53  | 47  | 42  | 40  |    | 40  |
| 7   | 66  | 53  | 45  | 39  | 65  | 52  | 44  | 39  | 51  | 44  | 38  | 50  | 43  | 38  | 48  | 42  | 38  | 36  |    | 36  |
| 8   | 62  | 49  | 40  | 35  | 60  | 48  | 40  | 35  | 47  | 39  | 34  | 45  | 39  | 34  | 44  | 38  | 34  | 32  |    | 32  |
| 9   | 58  | 45  | 37  | 31  | 57  | 44  | 36  | 31  | 43  | 36  | 31  | 42  | 35  | 31  | 41  | 35  | 31  | 29  |    | 29  |
| 10  | 54  | 41  | 34  | 28  | 53  | 41  | 33  | 28  | 40  | 33  | 28  | 39  | 33  | 28  | 38  | 32  | 28  | 26  |    | 26  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 2199 | 2199 | 2199 |
| 5°  | 2201 | 2196 | 2208 |
| 10° | 2198 | 2195 | 2206 |
| 15° | 2191 | 2187 | 2197 |
| 20° | 2177 | 2175 | 2184 |
| 25° | 2157 | 2154 | 2156 |
| 30° | 2121 | 2117 | 2121 |
| 35° | 2075 | 2072 | 2074 |
| 40° | 2022 | 2015 | 2021 |
| 45° | 1961 | 1955 | 1958 |
| 50° | 1895 | 1886 | 1873 |
| 55° | 1784 | 1764 | 1758 |
| 60° | 1619 | 1565 | 1568 |
| 65° | 1422 | 1351 | 1349 |
| 70° | 1230 | 1174 | 1161 |
| 75° | 1064 | 1024 | 1002 |
| 80° | 942  | 928  | 886  |
| 85° | 778  | 806  | 760  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 1968 cd/sqm

TEST NUMBER: P1471657

CATALOG NUMBER: 14PTR-30S-PP3-L835-UNV-STD-B

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 77.5   | 3.7       |
| 10°-20°   | 222.0  | 10.5      |
| 20°-30°   | 334.3  | 15.8      |
| 30°-40°   | 394.6  | 18.7      |
| 40°-50°   | 396.8  | 18.8      |
| 50°-60°   | 335.0  | 15.9      |
| 60°-70°   | 215.1  | 10.2      |
| 70°-80°   | 107.0  | 5.1       |
| 80°-90°   | 29.3   | 1.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 633.9  | 30.0      |
| 0°-40°    | 1028.4 | 48.7      |
| 0°-60°    | 1760.2 | 83.4      |
| 0°-90°    | 2111.7 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2111.7 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | 22.5° | 45° | 67.5° | 90° | Flux |
|-----|-----|-------|-----|-------|-----|------|
| 0°  | 817 | 817   | 817 | 817   | 817 |      |
| 5°  | 815 | 815   | 813 | 817   | 818 | 77   |
| 15° | 786 | 787   | 785 | 788   | 788 | 222  |
| 25° | 726 | 727   | 725 | 727   | 726 | 334  |
| 35° | 632 | 632   | 631 | 631   | 631 | 395  |
| 45° | 515 | 517   | 514 | 514   | 514 | 398  |
| 55° | 380 | 380   | 376 | 374   | 375 | 338  |
| 65° | 223 | 220   | 212 | 210   | 212 | 223  |
| 75° | 102 | 102   | 98  | 98    | 96  | 111  |
| 85° | 25  | 26    | 26  | 25    | 25  | 30   |
| 90° | 0   | 0     | 0   | 0     | 0   |      |

TEST NUMBER: P1471657

CATALOG NUMBER: 14PTR-30S-PP3-L835-UNV-STD-B

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    | 22.5° | 45°   | 67.5° | 90°   |
|-------|-------|-------|-------|-------|-------|
| 0°    | 817.3 | 817.3 | 817.3 | 817.3 | 817.3 |
| 2.5°  | 817.0 | 817.3 | 815.1 | 819.0 | 819.7 |
| 5°    | 814.9 | 815.1 | 813.1 | 817.0 | 817.5 |
| 7.5°  | 810.7 | 811.0 | 809.2 | 812.8 | 813.4 |
| 10°   | 804.5 | 805.4 | 803.3 | 806.6 | 807.2 |
| 12.5° | 796.8 | 797.1 | 795.0 | 798.9 | 799.5 |
| 15°   | 786.5 | 786.7 | 785.0 | 788.5 | 788.5 |
| 17.5° | 774.5 | 774.8 | 773.6 | 776.7 | 776.3 |
| 20°   | 760.1 | 760.9 | 759.4 | 761.5 | 762.6 |
| 22.5° | 744.3 | 744.6 | 742.8 | 745.5 | 746.7 |
| 25°   | 726.5 | 726.8 | 725.4 | 726.8 | 726.2 |
| 27.5° | 705.7 | 706.3 | 704.2 | 705.7 | 706.1 |
| 30°   | 682.6 | 684.1 | 681.2 | 682.3 | 682.6 |
| 32.5° | 657.7 | 658.5 | 656.5 | 656.8 | 658.3 |
| 35°   | 631.6 | 631.9 | 630.7 | 631.2 | 631.2 |
| 37.5° | 603.4 | 604.6 | 602.8 | 603.7 | 602.5 |
| 40°   | 575.5 | 574.3 | 573.7 | 574.3 | 575.2 |
| 42.5° | 546.1 | 546.4 | 545.5 | 544.9 | 543.5 |
| 45°   | 515.3 | 517.1 | 513.8 | 514.4 | 514.4 |
| 47.5° | 485.1 | 485.3 | 483.6 | 481.7 | 480.5 |
| 50°   | 452.7 | 452.7 | 450.6 | 449.2 | 447.3 |
| 52.5° | 417.4 | 416.8 | 414.5 | 413.0 | 413.8 |
| 55°   | 380.3 | 380.0 | 375.9 | 374.4 | 374.7 |
| 57.5° | 339.7 | 340.3 | 334.1 | 332.5 | 332.5 |
| 60°   | 300.9 | 297.8 | 290.7 | 288.7 | 291.3 |
| 62.5° | 260.1 | 256.6 | 248.9 | 248.9 | 250.9 |
| 65°   | 223.4 | 220.1 | 212.1 | 210.0 | 211.8 |
| 67.5° | 189.0 | 185.9 | 178.6 | 177.4 | 178.0 |
| 70°   | 156.3 | 153.7 | 149.2 | 146.5 | 147.5 |
| 72.5° | 128.2 | 125.8 | 122.8 | 120.7 | 119.5 |
| 75°   | 102.3 | 101.8 | 98.5  | 97.6  | 96.4  |
| 77.5° | 81.0  | 80.7  | 78.0  | 76.9  | 75.7  |
| 80°   | 60.8  | 60.5  | 59.9  | 58.1  | 57.2  |
| 82.5° | 43.3  | 43.3  | 43.0  | 41.5  | 40.6  |
| 85°   | 25.2  | 26.1  | 26.1  | 24.6  | 24.6  |
| 87.5° | 10.1  | 10.7  | 10.1  | 10.1  | 9.8   |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |

TEST NUMBER: P1471657

CATALOG NUMBER: 14PTR-30S-PP3-L835-UNV-STD-B

**CIE UGR TABLE:**

| Reflectances:   |      |                  |      |      |      |      |                |      |      |      |      |
|-----------------|------|------------------|------|------|------|------|----------------|------|------|------|------|
| Ceiling         |      | 0.7              | 0.7  | 0.5  | 0.5  | 0.3  | 0.7            | 0.7  | 0.5  | 0.5  | 0.3  |
| Wall            |      | 0.5              | 0.3  | 0.5  | 0.3  | 0.3  | 0.5            | 0.3  | 0.5  | 0.3  | 0.3  |
| Reference plane |      | 0.2              | 0.2  | 0.2  | 0.2  | 0.2  | 0.2            | 0.2  | 0.2  | 0.2  | 0.2  |
| Room Dimensions |      | Viewed crosswise |      |      |      |      | Viewed endwise |      |      |      |      |
| X=2H            | Y=2H | 14.0             | 15.6 | 14.3 | 15.9 | 16.2 | 13.8           | 15.4 | 14.2 | 15.7 | 16.0 |
|                 | 3H   | 15.3             | 16.7 | 15.7 | 17.0 | 17.4 | 15.1           | 16.5 | 15.4 | 16.8 | 17.2 |
|                 | 4H   | 15.7             | 17.1 | 16.1 | 17.4 | 17.8 | 15.5           | 16.8 | 15.9 | 17.2 | 17.5 |
|                 | 6H   | 16.1             | 17.3 | 16.5 | 17.7 | 18.1 | 15.8           | 17.0 | 16.2 | 17.4 | 17.8 |
|                 | 8H   | 16.2             | 17.4 | 16.6 | 17.7 | 18.1 | 15.9           | 17.1 | 16.3 | 17.5 | 17.9 |
|                 | 12H  | 16.2             | 17.4 | 16.7 | 17.8 | 18.2 | 16.0           | 17.1 | 16.4 | 17.5 | 17.9 |
| 4H              | 2H   | 14.4             | 15.7 | 14.8 | 16.1 | 16.5 | 14.3           | 15.6 | 14.7 | 16.0 | 16.3 |
|                 | 3H   | 15.9             | 17.0 | 16.3 | 17.4 | 17.8 | 15.7           | 16.8 | 16.1 | 17.2 | 17.6 |
|                 | 4H   | 16.5             | 17.5 | 16.9 | 17.9 | 18.3 | 16.3           | 17.3 | 16.7 | 17.7 | 18.1 |
|                 | 6H   | 16.9             | 17.8 | 17.4 | 18.3 | 18.7 | 16.7           | 17.6 | 17.1 | 18.0 | 18.5 |
|                 | 8H   | 17.1             | 17.9 | 17.6 | 18.3 | 18.8 | 16.8           | 17.7 | 17.3 | 18.1 | 18.6 |
|                 | 12H  | 17.2             | 17.9 | 17.7 | 18.4 | 18.9 | 16.9           | 17.7 | 17.4 | 18.1 | 18.6 |
| 8H              | 4H   | 16.7             | 17.5 | 17.1 | 17.9 | 18.4 | 16.5           | 17.3 | 16.9 | 17.7 | 18.2 |
|                 | 6H   | 17.2             | 17.9 | 17.7 | 18.4 | 18.9 | 17.0           | 17.7 | 17.5 | 18.2 | 18.7 |
|                 | 8H   | 17.5             | 18.1 | 18.0 | 18.6 | 19.1 | 17.2           | 17.8 | 17.7 | 18.3 | 18.8 |
|                 | 12H  | 17.6             | 18.2 | 18.1 | 18.7 | 19.2 | 17.4           | 17.9 | 17.9 | 18.4 | 19.0 |
| 12H             | 4H   | 16.7             | 17.4 | 17.2 | 17.9 | 18.4 | 16.5           | 17.2 | 17.0 | 17.7 | 18.2 |
|                 | 6H   | 17.3             | 17.9 | 17.8 | 18.4 | 18.9 | 17.1           | 17.7 | 17.6 | 18.1 | 18.7 |
|                 | 8H   | 17.5             | 18.1 | 18.0 | 18.6 | 19.1 | 17.3           | 17.8 | 17.8 | 18.3 | 18.9 |













(END OF REPORT)