

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1471746

Luminaire Tested: 24PTR-20S-PB1-L835-UNV-STD-W

Issue Date: 6/22/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1471746  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P737703)  
Test Lab: INNOVATION CENTER  
Issue Date: 6/22/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: 24PTR-20S-PB1-L835-UNV-STD-W  
Description: 2000 LUMEN 2X4 PERCEIVE PT TROFFER WITH 3500K, 80 CRI LEDS AND PB1 Lens White Reces:  
Frame  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2010.1 lumens  
Efficiency: N/A  
Efficacy: 120.4 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.25 / 1.34  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 16.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1471746

CATALOG NUMBER: 24PTR-20S-PB1-L835-UNV-STD-W

### Luminous Intensity Polar Plot



TEST NUMBER: P1471746

CATALOG NUMBER: 24PTR-20S-PB1-L835-UNV-STD-W

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 110 | 105 | 101 | 98  | 107 | 103 | 99  | 96  |  | 99  | 96  | 93  |  | 95  | 93  | 90  |  | 91  | 89  | 88  |
| 2   | 100 | 93  | 86  | 81  | 98  | 91  | 85  | 80  |  | 87  | 83  | 78  |  | 84  | 80  | 77  |  | 81  | 78  | 75  |
| 3   | 92  | 82  | 75  | 69  | 90  | 81  | 74  | 68  |  | 78  | 72  | 67  |  | 75  | 70  | 66  |  | 73  | 68  | 64  |
| 4   | 85  | 73  | 65  | 59  | 83  | 72  | 64  | 58  |  | 70  | 63  | 58  |  | 67  | 62  | 57  |  | 65  | 60  | 56  |
| 5   | 78  | 66  | 57  | 51  | 76  | 65  | 57  | 51  |  | 63  | 56  | 50  |  | 61  | 55  | 50  |  | 59  | 54  | 49  |
| 6   | 72  | 60  | 51  | 45  | 71  | 59  | 51  | 45  |  | 57  | 50  | 44  |  | 55  | 49  | 44  |  | 54  | 48  | 44  |
| 7   | 67  | 54  | 46  | 40  | 66  | 53  | 45  | 40  |  | 52  | 45  | 39  |  | 51  | 44  | 39  |  | 49  | 43  | 39  |
| 8   | 63  | 50  | 41  | 36  | 61  | 49  | 41  | 36  |  | 48  | 41  | 35  |  | 46  | 40  | 35  |  | 45  | 39  | 35  |
| 9   | 59  | 46  | 38  | 32  | 57  | 45  | 37  | 32  |  | 44  | 37  | 32  |  | 43  | 36  | 32  |  | 42  | 36  | 32  |
| 10  | 55  | 42  | 34  | 29  | 54  | 42  | 34  | 29  |  | 41  | 34  | 29  |  | 40  | 33  | 29  |  | 39  | 33  | 29  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 1085 | 1085 | 1085 |
| 5°  | 1085 | 1083 | 1089 |
| 10° | 1085 | 1082 | 1088 |
| 15° | 1083 | 1080 | 1084 |
| 20° | 1079 | 1075 | 1079 |
| 25° | 1073 | 1069 | 1072 |
| 30° | 1065 | 1058 | 1057 |
| 35° | 1049 | 1041 | 1034 |
| 40° | 1028 | 1014 | 996  |
| 45° | 996  | 964  | 924  |
| 50° | 947  | 874  | 799  |
| 55° | 872  | 742  | 688  |
| 60° | 777  | 649  | 590  |
| 65° | 666  | 562  | 502  |
| 70° | 550  | 496  | 460  |
| 75° | 464  | 474  | 449  |
| 80° | 392  | 484  | 461  |
| 85° | 307  | 489  | 429  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 996 cd/sqm

TEST NUMBER: P1471746

CATALOG NUMBER: 24PTR-20S-PB1-L835-UNV-STD-W

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 76.4   | 3.8       |
| 10°-20°   | 219.3  | 10.9      |
| 20°-30°   | 332.2  | 16.5      |
| 30°-40°   | 395.9  | 19.7      |
| 40°-50°   | 387.1  | 19.3      |
| 50°-60°   | 292.8  | 14.6      |
| 60°-70°   | 179.9  | 9.0       |
| 70°-80°   | 95.8   | 4.8       |
| 80°-90°   | 30.6   | 1.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 628.0  | 31.2      |
| 0°-40°    | 1023.9 | 50.9      |
| 0°-60°    | 1703.8 | 84.8      |
| 0°-90°    | 2010.1 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2010.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | 22.5° | 45° | 67.5° | 90° | Flux |
|-----|-----|-------|-----|-------|-----|------|
| 0°  | 806 | 806   | 806 | 806   | 806 |      |
| 5°  | 803 | 804   | 802 | 805   | 806 | 76   |
| 15° | 777 | 778   | 775 | 778   | 778 | 219  |
| 25° | 723 | 722   | 720 | 721   | 722 | 333  |
| 35° | 638 | 638   | 634 | 631   | 630 | 399  |
| 45° | 524 | 521   | 507 | 490   | 486 | 403  |
| 55° | 372 | 353   | 316 | 298   | 294 | 333  |
| 65° | 209 | 192   | 177 | 163   | 158 | 208  |
| 75° | 89  | 90    | 91  | 88    | 86  | 96   |
| 85° | 20  | 26    | 32  | 30    | 28  | 24   |
| 90° | 0   | 0     | 0   | 0     | 0   |      |

TEST NUMBER: P1471746

CATALOG NUMBER: 24PTR-20S-PB1-L835-UNV-STD-W

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    | 22.5° | 45°   | 67.5° | 90°   |
|-------|-------|-------|-------|-------|-------|
| 0°    | 806.1 | 806.1 | 806.1 | 806.1 | 806.1 |
| 2.5°  | 805.2 | 806.1 | 803.1 | 807.2 | 808.1 |
| 5°    | 803.1 | 804.2 | 802.2 | 805.2 | 806.1 |
| 7.5°  | 800.2 | 800.2 | 798.2 | 801.1 | 802.2 |
| 10°   | 794.3 | 794.3 | 792.3 | 795.2 | 796.2 |
| 12.5° | 786.4 | 786.4 | 785.3 | 787.3 | 788.3 |
| 15°   | 777.4 | 778.3 | 775.4 | 778.3 | 778.3 |
| 17.5° | 766.5 | 765.5 | 764.5 | 766.5 | 767.5 |
| 20°   | 753.6 | 753.6 | 750.7 | 752.6 | 753.6 |
| 22.5° | 738.7 | 738.7 | 737.7 | 738.7 | 737.7 |
| 25°   | 722.9 | 721.8 | 719.8 | 720.9 | 721.8 |
| 27.5° | 704.0 | 704.0 | 702.0 | 702.0 | 701.0 |
| 30°   | 685.2 | 684.1 | 681.2 | 679.2 | 680.2 |
| 32.5° | 662.4 | 661.3 | 658.4 | 656.4 | 657.4 |
| 35°   | 638.5 | 637.6 | 633.6 | 630.6 | 629.7 |
| 37.5° | 614.8 | 611.8 | 606.8 | 602.8 | 598.9 |
| 40°   | 585.0 | 582.0 | 577.1 | 568.2 | 567.1 |
| 42.5° | 555.3 | 552.3 | 544.3 | 533.5 | 530.5 |
| 45°   | 523.5 | 520.6 | 506.6 | 489.8 | 485.8 |
| 47.5° | 489.8 | 484.9 | 463.0 | 442.2 | 434.3 |
| 50°   | 452.2 | 443.2 | 417.4 | 390.7 | 381.7 |
| 52.5° | 415.5 | 399.6 | 365.9 | 342.1 | 333.2 |
| 55°   | 371.8 | 353.0 | 316.4 | 298.4 | 293.5 |
| 57.5° | 333.2 | 307.4 | 277.6 | 259.8 | 255.9 |
| 60°   | 288.6 | 264.7 | 241.0 | 225.1 | 219.1 |
| 62.5° | 247.9 | 227.0 | 207.3 | 193.3 | 186.4 |
| 65°   | 209.2 | 192.4 | 176.6 | 162.6 | 157.7 |
| 67.5° | 171.6 | 162.6 | 149.7 | 138.9 | 135.8 |
| 70°   | 139.8 | 134.8 | 126.0 | 121.0 | 117.0 |
| 72.5° | 111.1 | 113.1 | 107.1 | 105.1 | 102.1 |
| 75°   | 89.2  | 90.3  | 91.2  | 88.3  | 86.3  |
| 77.5° | 67.5  | 72.3  | 76.3  | 74.3  | 72.3  |
| 80°   | 50.6  | 55.5  | 62.5  | 59.5  | 59.5  |
| 82.5° | 34.7  | 40.7  | 46.6  | 44.7  | 43.6  |
| 85°   | 19.9  | 25.8  | 31.7  | 29.8  | 27.8  |
| 87.5° | 7.9   | 12.9  | 13.8  | 13.8  | 12.9  |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |

TEST NUMBER: P1471746

CATALOG NUMBER: 24PTR-20S-PB1-L835-UNV-STD-W

**CIE UGR TABLE:**

| Reflectances:   |      |                  |      |      |      |      |                |      |      |      |      |
|-----------------|------|------------------|------|------|------|------|----------------|------|------|------|------|
| Ceiling         |      | 0.7              | 0.7  | 0.5  | 0.5  | 0.3  | 0.7            | 0.7  | 0.5  | 0.5  | 0.3  |
| Wall            |      | 0.5              | 0.3  | 0.5  | 0.3  | 0.3  | 0.5            | 0.3  | 0.5  | 0.3  | 0.3  |
| Reference plane |      | 0.2              | 0.2  | 0.2  | 0.2  | 0.2  | 0.2            | 0.2  | 0.2  | 0.2  | 0.2  |
| Room Dimensions |      | Viewed crosswise |      |      |      |      | Viewed endwise |      |      |      |      |
| X=2H            | Y=2H | 11.2             | 12.7 | 11.5 | 13.0 | 13.4 | 9.9            | 11.4 | 10.2 | 11.8 | 12.1 |
|                 | 3H   | 12.4             | 13.8 | 12.8 | 14.1 | 14.5 | 11.1           | 12.5 | 11.5 | 12.9 | 13.2 |
|                 | 4H   | 12.8             | 14.1 | 13.2 | 14.5 | 14.9 | 11.7           | 13.0 | 12.1 | 13.4 | 13.7 |
|                 | 6H   | 13.1             | 14.3 | 13.5 | 14.7 | 15.1 | 12.2           | 13.4 | 12.6 | 13.8 | 14.2 |
|                 | 8H   | 13.2             | 14.4 | 13.6 | 14.7 | 15.1 | 12.4           | 13.5 | 12.8 | 13.9 | 14.3 |
|                 | 12H  | 13.2             | 14.4 | 13.7 | 14.7 | 15.2 | 12.5           | 13.6 | 13.0 | 14.0 | 14.4 |
| 4H              | 2H   | 11.5             | 12.8 | 11.9 | 13.2 | 13.5 | 10.4           | 11.7 | 10.8 | 12.1 | 12.4 |
|                 | 3H   | 12.9             | 14.0 | 13.4 | 14.4 | 14.8 | 11.9           | 13.0 | 12.3 | 13.4 | 13.8 |
|                 | 4H   | 13.5             | 14.5 | 13.9 | 14.9 | 15.3 | 12.6           | 13.6 | 13.0 | 14.0 | 14.4 |
|                 | 6H   | 13.9             | 14.8 | 14.4 | 15.2 | 15.7 | 13.2           | 14.1 | 13.7 | 14.5 | 15.0 |
|                 | 8H   | 14.1             | 14.9 | 14.5 | 15.3 | 15.8 | 13.5           | 14.3 | 14.0 | 14.7 | 15.2 |
|                 | 12H  | 14.1             | 14.9 | 14.6 | 15.3 | 15.8 | 13.7           | 14.4 | 14.2 | 14.9 | 15.4 |
| 8H              | 4H   | 13.7             | 14.5 | 14.2 | 14.9 | 15.4 | 12.9           | 13.7 | 13.4 | 14.1 | 14.6 |
|                 | 6H   | 14.3             | 14.9 | 14.7 | 15.4 | 15.9 | 13.7           | 14.4 | 14.2 | 14.8 | 15.3 |
|                 | 8H   | 14.5             | 15.1 | 15.0 | 15.6 | 16.1 | 14.0           | 14.6 | 14.5 | 15.1 | 15.6 |
|                 | 12H  | 14.6             | 15.2 | 15.1 | 15.6 | 16.2 | 14.3           | 14.9 | 14.8 | 15.3 | 15.9 |
| 12H             | 4H   | 13.7             | 14.4 | 14.2 | 14.9 | 15.4 | 12.9           | 13.6 | 13.4 | 14.1 | 14.6 |
|                 | 6H   | 14.3             | 14.9 | 14.8 | 15.4 | 15.9 | 13.8           | 14.4 | 14.3 | 14.8 | 15.4 |
|                 | 8H   | 14.6             | 15.1 | 15.1 | 15.6 | 16.2 | 14.2           | 14.7 | 14.7 | 15.2 | 15.8 |













(END OF REPORT)