

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1471784

Luminaire Tested: 24PTR-35S-PLG-L835-UNV-STD-W

Issue Date: 6/22/2026

Test Information

Test Method: LM-79-2019
Report Number: P1471784
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2409-224-3)
Test Lab: INNOVATION CENTER
Issue Date: 6/22/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 24PTR-35S-PLG-L835-UNV-STD-W
Description: 3500 LUMEN 2X4 PERCEIVE PT TROFFER WITH 3500K, 80 CRI LEDS AND PLG Lens White Reces:
Frame
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2870.7 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.22 / 1.26
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 28.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1471784

CATALOG NUMBER: 24PTR-35S-PLG-L835-UNV-STD-W

Luminous Intensity Polar Plot



TEST NUMBER: P1471784

CATALOG NUMBER: 24PTR-35S-PLG-L835-UNV-STD-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	110	106	102	98	107	103	100	97		99	96	94			95	93	91			92
2	101	94	87	82	99	92	86	81		88	84	79			85	81	78			82
3	93	83	76	70	91	82	75	69		79	73	68			76	71	67			74
4	86	75	67	60	84	73	66	60		71	64	59			69	63	58			67
5	79	67	59	53	77	66	58	53		64	57	52			62	56	51			61
6	74	61	53	47	72	60	52	47		58	51	46			57	51	46			55
7	69	56	48	42	67	55	47	42		54	46	41			52	46	41			51
8	64	51	43	38	62	51	43	38		49	42	37			48	42	37			47
9	60	47	39	34	59	47	39	34		46	39	34			44	38	34			43
10	56	44	36	31	55	43	36	31		42	36	31			41	35	31			40

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1714	1714	1714
5°	1711	1714	1712
10°	1710	1711	1708
15°	1703	1705	1701
20°	1689	1692	1687
25°	1666	1667	1662
30°	1629	1629	1625
35°	1570	1565	1558
40°	1455	1439	1434
45°	1271	1251	1256
50°	1098	1084	1090
55°	976	961	963
60°	873	861	861
65°	783	777	780
70°	704	697	704
75°	653	644	653
80°	610	603	581
85°	517	517	460

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1271 cd/sqm

TEST NUMBER: P1471784

CATALOG NUMBER: 24PTR-35S-PLG-L835-UNV-STD-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.6	4.2
10°-20°	345.1	12.0
20°-30°	516.4	18.0
30°-40°	591.7	20.6
40°-50°	511.7	17.8
50°-60°	370.3	12.9
60°-70°	243.9	8.5
70°-80°	132.8	4.6
80°-90°	38.1	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	982.1	34.2
0°-40°	1573.8	54.8
0°-60°	2455.8	85.5
0°-90°	2870.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2870.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1274	1274	1274	1274	1274	
5°	1267	1269	1269	1269	1268	120
15°	1222	1223	1224	1226	1222	345
25°	1122	1122	1123	1124	1119	516
35°	956	955	953	952	948	594
45°	668	666	657	656	660	517
55°	416	414	410	407	410	374
65°	246	248	244	242	245	246
75°	126	126	124	124	126	134
85°	34	34	34	34	30	39
90°	0	0	0	0	0	

TEST NUMBER: P1471784

CATALOG NUMBER: 24PTR-35S-PLG-L835-UNV-STD-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1273.9	1273.9	1273.9	1273.9	1273.9
2.5°	1271.2	1273.9	1273.0	1273.9	1271.2
5°	1266.7	1269.4	1269.4	1269.4	1267.6
7.5°	1260.4	1262.2	1263.1	1264.0	1259.5
10°	1251.3	1253.2	1252.2	1254.1	1250.4
12.5°	1239.6	1239.6	1240.5	1242.3	1238.7
15°	1222.4	1223.3	1224.2	1226.0	1221.5
17.5°	1202.5	1203.4	1204.3	1205.2	1201.6
20°	1179.9	1179.9	1181.7	1182.6	1178.1
22.5°	1151.9	1151.9	1153.7	1156.4	1151.0
25°	1122.1	1122.1	1123.0	1123.9	1119.3
27.5°	1086.8	1086.8	1087.7	1090.4	1085.0
30°	1048.8	1047.9	1048.8	1049.7	1046.1
32.5°	1006.3	1005.4	1004.5	1005.4	1000.9
35°	955.7	954.8	953.0	952.1	948.5
37.5°	896.9	895.1	891.5	891.5	887.9
40°	828.2	823.7	819.2	817.4	816.4
42.5°	748.6	745.0	738.7	737.8	737.8
45°	668.2	666.4	657.3	656.4	660.0
47.5°	595.8	591.3	583.2	581.4	586.8
50°	524.4	525.3	518.1	515.4	520.8
52.5°	468.4	466.5	460.2	458.4	462.9
55°	415.9	414.1	409.6	406.9	410.5
57.5°	368.0	367.1	362.6	361.7	363.5
60°	324.6	323.7	320.1	319.2	320.1
62.5°	283.9	283.9	280.3	278.5	281.2
65°	245.9	247.7	244.1	242.3	245.0
67.5°	211.6	213.4	209.8	208.0	211.6
70°	179.0	180.8	177.2	175.4	179.0
72.5°	151.0	151.9	149.2	148.3	152.8
75°	125.7	125.7	123.9	123.9	125.7
77.5°	102.2	101.3	100.4	100.4	98.6
80°	78.7	77.8	77.8	77.8	75.0
82.5°	56.1	54.2	55.2	56.1	51.5
85°	33.5	33.5	33.5	34.4	29.8
87.5°	13.6	13.6	12.7	13.6	11.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1471784

CATALOG NUMBER: 24PTR-35S-PLG-L835-UNV-STD-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.1	12.6	11.5	13.0	13.3	11.0	12.5	11.4	12.9	13.2
	3H	12.6	13.9	13.0	14.3	14.6	12.5	13.8	12.9	14.2	14.5
	4H	13.1	14.4	13.5	14.7	15.1	13.0	14.3	13.4	14.7	15.0
	6H	13.6	14.7	14.0	15.1	15.5	13.4	14.6	13.9	15.0	15.4
	8H	13.7	14.8	14.1	15.2	15.6	13.6	14.7	14.0	15.1	15.5
	12H	13.8	14.9	14.2	15.2	15.7	13.7	14.7	14.1	15.1	15.5
4H	2H	11.6	12.9	12.0	13.2	13.6	11.5	12.8	11.9	13.2	13.5
	3H	13.3	14.3	13.7	14.7	15.1	13.2	14.2	13.6	14.6	15.0
	4H	14.0	14.9	14.4	15.3	15.8	13.9	14.8	14.3	15.2	15.7
	6H	14.5	15.3	15.0	15.8	16.2	14.4	15.2	14.9	15.7	16.2
	8H	14.7	15.5	15.2	15.9	16.4	14.6	15.4	15.1	15.8	16.3
	12H	14.8	15.5	15.3	16.0	16.5	14.7	15.4	15.2	15.9	16.4
8H	4H	14.2	15.0	14.7	15.4	15.9	14.1	14.9	14.6	15.3	15.8
	6H	14.9	15.5	15.4	16.0	16.5	14.8	15.4	15.3	15.9	16.4
	8H	15.2	15.7	15.7	16.2	16.7	15.1	15.6	15.6	16.1	16.6
	12H	15.4	15.9	15.9	16.4	16.9	15.3	15.8	15.8	16.3	16.8
12H	4H	14.2	14.9	14.7	15.4	15.9	14.2	14.8	14.6	15.3	15.8
	6H	14.9	15.5	15.5	16.0	16.5	14.9	15.4	15.4	15.9	16.4
	8H	15.3	15.8	15.8	16.3	16.8	15.2	15.7	15.7	16.2	16.7

(END OF REPORT)