

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1471762

Luminaire Tested: 24PTR-30S-PB1-L835-UNV-STD-W

Issue Date: 6/22/2026

Test Information

Test Method: LM-79-2019
Report Number: P1471762
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P737703)
Test Lab: INNOVATION CENTER
Issue Date: 6/22/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 24PTR-30S-PB1-L835-UNV-STD-W
Description: 3000 LUMEN 2X4 PERCEIVE PT TROFFER WITH 3500K, 80 CRI LEDS AND PB1 Lens White Reces:
Frame
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2823.4 lumens
Efficiency: N/A
Efficacy: 119.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.25 / 1.34
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 23.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1471762

CATALOG NUMBER: 24PTR-30S-PB1-L835-UNV-STD-W

Luminous Intensity Polar Plot



TEST NUMBER: P1471762

CATALOG NUMBER: 24PTR-30S-PB1-L835-UNV-STD-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	110	105	101	98	107	103	99	96	99	96	93	95	93	90	91	89	88	88	88	86
2	100	93	86	81	98	91	85	80	87	83	78	84	80	77	81	78	75	75	75	73
3	92	82	75	69	90	81	74	68	78	72	67	75	70	66	73	68	64	64	64	62
4	85	73	65	59	83	72	64	58	70	63	58	67	62	57	65	60	56	56	56	54
5	78	66	57	51	76	65	57	51	63	56	50	61	55	50	59	54	49	49	49	47
6	72	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	44	44	42
7	67	54	46	40	66	53	45	40	52	45	39	51	44	39	49	43	39	39	39	37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	35	35	33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	32	32	30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	29	29	27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1523	1523	1523
5°	1524	1522	1529
10°	1524	1520	1528
15°	1521	1517	1523
20°	1515	1510	1515
25°	1507	1501	1505
30°	1495	1487	1484
35°	1473	1462	1453
40°	1443	1424	1399
45°	1399	1354	1298
50°	1329	1227	1122
55°	1225	1042	967
60°	1091	911	828
65°	936	790	705
70°	773	696	646
75°	651	666	630
80°	551	680	648
85°	431	689	602

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1399 cd/sqm

TEST NUMBER: P1471762

CATALOG NUMBER: 24PTR-30S-PB1-L835-UNV-STD-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.4	3.8
10°-20°	308.1	10.9
20°-30°	466.6	16.5
30°-40°	556.0	19.7
40°-50°	543.7	19.3
50°-60°	411.3	14.6
60°-70°	252.7	8.9
70°-80°	134.6	4.8
80°-90°	42.9	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	882.1	31.2
0°-40°	1438.1	50.9
0°-60°	2393.1	84.8
0°-90°	2823.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2823.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1132	1132	1132	1132	1132	
5°	1128	1130	1127	1131	1132	107
15°	1092	1093	1089	1093	1093	308
25°	1015	1014	1011	1012	1014	468
35°	897	896	890	886	884	561
45°	735	731	712	688	682	566
55°	522	496	444	419	412	468
65°	294	270	248	228	222	292
75°	125	127	128	124	121	134
85°	28	36	45	42	39	34
90°	0	0	0	0	0	

TEST NUMBER: P1471762

CATALOG NUMBER: 24PTR-30S-PB1-L835-UNV-STD-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1132.3	1132.3	1132.3	1132.3	1132.3
2.5°	1131.0	1132.3	1128.0	1133.7	1135.1
5°	1128.0	1129.5	1126.7	1131.0	1132.3
7.5°	1123.9	1123.9	1121.2	1125.3	1126.7
10°	1115.6	1115.6	1112.8	1116.9	1118.4
12.5°	1104.5	1104.5	1103.0	1105.8	1107.3
15°	1091.9	1093.2	1089.1	1093.2	1093.2
17.5°	1076.6	1075.3	1073.8	1076.6	1078.0
20°	1058.4	1058.4	1054.3	1057.1	1058.4
22.5°	1037.5	1037.5	1036.2	1037.5	1036.2
25°	1015.3	1013.8	1011.1	1012.5	1013.8
27.5°	988.8	988.8	986.1	986.1	984.6
30°	962.4	960.9	956.8	954.0	955.4
32.5°	930.4	928.9	924.8	922.0	923.3
35°	896.9	895.6	890.0	885.8	884.4
37.5°	863.5	859.3	852.3	846.7	841.2
40°	821.7	817.5	810.6	798.0	796.6
42.5°	779.9	775.8	764.5	749.3	745.1
45°	735.3	731.2	711.6	687.9	682.4
47.5°	687.9	681.1	650.4	621.1	610.0
50°	635.1	622.6	586.3	548.7	536.2
52.5°	583.5	561.3	513.9	480.5	468.0
55°	522.3	495.8	444.3	419.2	412.2
57.5°	468.0	431.8	390.0	364.9	359.4
60°	405.3	371.8	338.5	316.1	307.8
62.5°	348.1	318.9	291.1	271.5	261.9
65°	293.9	270.2	248.0	228.4	221.5
67.5°	241.0	228.4	210.3	195.0	190.8
70°	196.4	189.3	176.9	169.9	164.3
72.5°	156.0	158.8	150.5	147.7	143.4
75°	125.3	126.8	128.1	124.0	121.2
77.5°	94.7	101.6	107.2	104.4	101.6
80°	71.1	77.9	87.7	83.6	83.6
82.5°	48.7	57.2	65.5	62.7	61.3
85°	27.9	36.3	44.6	41.8	39.0
87.5°	11.1	18.1	19.4	19.4	18.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1471762

CATALOG NUMBER: 24PTR-30S-PB1-L835-UNV-STD-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.4	13.9	12.7	14.2	14.5	11.1	12.6	11.4	12.9	13.2
	3H	13.6	15.0	14.0	15.3	15.7	12.3	13.7	12.7	14.0	14.4
	4H	14.0	15.3	14.4	15.7	16.0	12.9	14.2	13.3	14.5	14.9
	6H	14.3	15.5	14.7	15.9	16.3	13.4	14.6	13.8	14.9	15.3
	8H	14.4	15.5	14.8	15.9	16.3	13.6	14.7	14.0	15.1	15.5
	12H	14.4	15.5	14.9	15.9	16.3	13.7	14.8	14.1	15.2	15.6
4H	2H	12.7	14.0	13.1	14.3	14.7	11.6	12.9	12.0	13.2	13.6
	3H	14.1	15.2	14.5	15.6	16.0	13.1	14.2	13.5	14.6	15.0
	4H	14.7	15.7	15.1	16.1	16.5	13.8	14.8	14.2	15.2	15.6
	6H	15.1	16.0	15.6	16.4	16.9	14.4	15.3	14.9	15.7	16.2
	8H	15.2	16.0	15.7	16.5	16.9	14.7	15.5	15.1	15.9	16.4
	12H	15.3	16.0	15.8	16.5	17.0	14.9	15.6	15.4	16.1	16.5
8H	4H	14.9	15.7	15.3	16.1	16.6	14.1	14.9	14.5	15.3	15.8
	6H	15.4	16.1	15.9	16.6	17.1	14.9	15.5	15.4	16.0	16.5
	8H	15.6	16.2	16.2	16.7	17.2	15.2	15.8	15.7	16.3	16.8
	12H	15.8	16.3	16.3	16.8	17.4	15.5	16.0	16.0	16.5	17.1
12H	4H	14.9	15.6	15.4	16.1	16.6	14.1	14.8	14.6	15.3	15.8
	6H	15.5	16.1	16.0	16.6	17.1	15.0	15.6	15.5	16.0	16.6
	8H	15.8	16.3	16.3	16.8	17.3	15.4	15.9	15.9	16.4	16.9

(END OF REPORT)