

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1471778

Luminaire Tested: 24PTR-35S-PB1-L835-UNV-STD-W

Issue Date: 6/22/2026

Test Information

Test Method: LM-79-2019
Report Number: P1471778
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P737703)
Test Lab: INNOVATION CENTER
Issue Date: 6/22/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 24PTR-35S-PB1-L835-UNV-STD-W
Description: 3500 LUMEN 2X4 PERCEIVE PT TROFFER WITH 3500K, 80 CRI LEDS AND PB1 Lens White Reces:
Frame
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3370.0 lumens
Efficiency: N/A
Efficacy: 118.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.25 / 1.34
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 28.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1471778

CATALOG NUMBER: 24PTR-35S-PB1-L835-UNV-STD-W

Luminous Intensity Polar Plot



TEST NUMBER: P1471778

CATALOG NUMBER: 24PTR-35S-PB1-L835-UNV-STD-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	110	105	101	98	107	103	99	96	99	96	93	95	93	90	91	89	88	88	88	86
2	100	93	86	81	98	91	85	80	87	83	78	84	80	77	81	78	75	75	75	73
3	92	82	75	69	90	81	74	68	78	72	67	75	70	66	73	68	64	64	64	62
4	85	73	65	59	83	72	64	58	70	63	58	67	62	57	65	60	56	56	56	54
5	78	66	57	51	76	65	57	51	63	56	50	61	55	50	59	54	49	49	49	47
6	72	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	44	44	42
7	67	54	46	40	66	53	45	40	52	45	39	51	44	39	49	43	39	39	39	37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	35	35	33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	32	32	30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	29	29	27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1818	1818	1818
5°	1818	1816	1825
10°	1819	1815	1824
15°	1815	1811	1818
20°	1809	1802	1809
25°	1799	1792	1796
30°	1785	1774	1772
35°	1758	1745	1734
40°	1723	1700	1670
45°	1670	1616	1550
50°	1587	1465	1340
55°	1462	1244	1154
60°	1302	1087	989
65°	1117	942	842
70°	922	831	772
75°	778	795	752
80°	657	811	773
85°	514	821	719

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1670 cd/sqm

TEST NUMBER: P1471778

CATALOG NUMBER: 24PTR-35S-PB1-L835-UNV-STD-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.1	3.8
10°-20°	367.7	10.9
20°-30°	557.0	16.5
30°-40°	663.7	19.7
40°-50°	649.0	19.3
50°-60°	490.9	14.6
60°-70°	301.6	8.9
70°-80°	160.7	4.8
80°-90°	51.3	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1052.8	31.2
0°-40°	1716.5	50.9
0°-60°	2856.5	84.8
0°-90°	3370.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3370.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1352	1352	1352	1352	1352	
5°	1346	1348	1345	1350	1352	128
15°	1303	1305	1300	1305	1305	368
25°	1212	1210	1207	1209	1210	558
35°	1070	1069	1062	1057	1056	670
45°	878	873	849	821	814	675
55°	623	592	530	500	492	558
65°	351	322	296	273	264	349
75°	150	151	153	148	145	160
85°	33	43	53	50	47	40
90°	0	0	0	0	0	

TEST NUMBER: P1471778

CATALOG NUMBER: 24PTR-35S-PB1-L835-UNV-STD-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1351.5	1351.5	1351.5	1351.5	1351.5
2.5°	1349.9	1351.5	1346.4	1353.3	1354.8
5°	1346.4	1348.2	1344.9	1349.9	1351.5
7.5°	1341.6	1341.6	1338.2	1343.1	1344.9
10°	1331.6	1331.6	1328.3	1333.2	1334.9
12.5°	1318.3	1318.3	1316.6	1319.9	1321.7
15°	1303.3	1304.9	1300.0	1304.9	1304.9
17.5°	1285.0	1283.4	1281.7	1285.0	1286.8
20°	1263.4	1263.4	1258.5	1261.8	1263.4
22.5°	1238.4	1238.4	1236.8	1238.4	1236.8
25°	1211.9	1210.1	1206.8	1208.6	1210.1
27.5°	1180.3	1180.3	1177.0	1177.0	1175.2
30°	1148.7	1147.0	1142.1	1138.8	1140.3
32.5°	1110.5	1108.7	1103.9	1100.5	1102.1
35°	1070.5	1069.0	1062.3	1057.3	1055.7
37.5°	1030.7	1025.7	1017.3	1010.7	1004.0
40°	980.8	975.8	967.6	952.5	950.8
42.5°	930.9	926.0	912.6	894.4	889.4
45°	877.7	872.8	849.4	821.1	814.5
47.5°	821.1	812.9	776.3	741.4	728.1
50°	758.1	743.1	699.8	655.0	640.0
52.5°	696.5	670.0	613.4	573.5	558.6
55°	623.4	591.8	530.4	500.4	492.0
57.5°	558.6	515.4	465.5	435.6	429.0
60°	483.8	443.8	404.0	377.3	367.4
62.5°	415.5	380.6	347.5	324.1	312.6
65°	350.8	322.5	296.0	272.6	264.4
67.5°	287.6	272.6	251.0	232.8	227.8
70°	234.4	226.0	211.2	202.8	196.2
72.5°	186.2	189.5	179.6	176.3	171.2
75°	149.6	151.3	152.9	148.0	144.7
77.5°	113.1	121.3	127.9	124.6	121.3
80°	84.8	93.0	104.7	99.8	99.8
82.5°	58.1	68.2	78.2	74.9	73.1
85°	33.3	43.3	53.2	49.9	46.6
87.5°	13.3	21.6	23.2	23.2	21.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1471778

CATALOG NUMBER: 24PTR-35S-PB1-L835-UNV-STD-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.0	14.5	13.3	14.8	15.2	11.7	13.2	12.0	13.5	13.9
	3H	14.2	15.6	14.6	15.9	16.3	12.9	14.3	13.3	14.7	15.0
	4H	14.6	15.9	15.0	16.3	16.7	13.5	14.8	13.9	15.1	15.5
	6H	14.9	16.1	15.3	16.5	16.9	14.0	15.2	14.4	15.6	16.0
	8H	15.0	16.1	15.4	16.5	16.9	14.2	15.3	14.6	15.7	16.1
	12H	15.0	16.1	15.5	16.5	17.0	14.3	15.4	14.7	15.8	16.2
4H	2H	13.3	14.6	13.7	14.9	15.3	12.2	13.5	12.6	13.9	14.2
	3H	14.7	15.8	15.2	16.2	16.6	13.7	14.8	14.1	15.2	15.6
	4H	15.3	16.3	15.7	16.7	17.1	14.4	15.4	14.8	15.8	16.2
	6H	15.7	16.6	16.2	17.0	17.5	15.0	15.9	15.5	16.3	16.8
	8H	15.8	16.6	16.3	17.1	17.6	15.3	16.1	15.8	16.5	17.0
	12H	15.9	16.7	16.4	17.1	17.6	15.5	16.2	16.0	16.7	17.1
8H	4H	15.5	16.3	16.0	16.7	17.2	14.7	15.5	15.2	15.9	16.4
	6H	16.0	16.7	16.5	17.2	17.7	15.5	16.2	16.0	16.6	17.1
	8H	16.3	16.9	16.8	17.4	17.8	15.8	16.4	16.3	16.9	17.4
	12H	16.4	16.9	16.9	17.4	18.0	16.1	16.7	16.6	17.1	17.7
12H	4H	15.5	16.2	16.0	16.7	17.2	14.7	15.4	15.2	15.9	16.4
	6H	16.1	16.7	16.6	17.2	17.7	15.6	16.2	16.1	16.6	17.2
	8H	16.4	16.9	16.9	17.4	18.0	16.0	16.5	16.5	17.0	17.6

(END OF REPORT)