

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1471825

Luminaire Tested: 24PTR-50S-PB1-L835-UNV-STD-B

Issue Date: 6/22/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1471825  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P737703)  
Test Lab: INNOVATION CENTER  
Issue Date: 6/22/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: 24PTR-50S-PB1-L835-UNV-STD-B  
Description: 5500 LUMEN 2X4 PERCEIVE PT TROFFER WITH 3500K, 80 CRI LEDS AND PB1 Lens Black Recess Frame  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4311.2 lumens  
Efficiency: N/A  
Efficacy: 97.8 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.25 / 1.34  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 44.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1471825

CATALOG NUMBER: 24PTR-50S-PB1-L835-UNV-STD-B

### Luminous Intensity Polar Plot



TEST NUMBER: P1471825

CATALOG NUMBER: 24PTR-50S-PB1-L835-UNV-STD-B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 102 | 102 | 100 |
| 1   | 110 | 105 | 101 | 98  | 107 | 103 | 99  | 96  | 99  | 96  | 93  | 95  | 93  | 90  | 91  | 89  | 88  | 88  | 88  | 86  |
| 2   | 100 | 93  | 86  | 81  | 98  | 91  | 85  | 80  | 87  | 83  | 78  | 84  | 80  | 77  | 81  | 78  | 75  | 75  | 75  | 73  |
| 3   | 92  | 82  | 75  | 69  | 90  | 81  | 74  | 68  | 78  | 72  | 67  | 75  | 70  | 66  | 73  | 68  | 64  | 64  | 64  | 62  |
| 4   | 85  | 73  | 65  | 59  | 83  | 72  | 64  | 58  | 70  | 63  | 58  | 67  | 62  | 57  | 65  | 60  | 56  | 56  | 56  | 54  |
| 5   | 78  | 66  | 57  | 51  | 76  | 65  | 57  | 51  | 63  | 56  | 50  | 61  | 55  | 50  | 59  | 54  | 49  | 49  | 49  | 47  |
| 6   | 72  | 60  | 51  | 45  | 71  | 59  | 51  | 45  | 57  | 50  | 44  | 55  | 49  | 44  | 54  | 48  | 44  | 44  | 44  | 42  |
| 7   | 67  | 54  | 46  | 40  | 66  | 53  | 45  | 40  | 52  | 45  | 39  | 51  | 44  | 39  | 49  | 43  | 39  | 39  | 39  | 37  |
| 8   | 63  | 50  | 41  | 36  | 61  | 49  | 41  | 36  | 48  | 41  | 35  | 46  | 40  | 35  | 45  | 39  | 35  | 35  | 35  | 33  |
| 9   | 59  | 46  | 38  | 32  | 57  | 45  | 37  | 32  | 44  | 37  | 32  | 43  | 36  | 32  | 42  | 36  | 32  | 32  | 32  | 30  |
| 10  | 55  | 42  | 34  | 29  | 54  | 42  | 34  | 29  | 41  | 34  | 29  | 40  | 33  | 29  | 39  | 33  | 29  | 29  | 29  | 27  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 2326 | 2326 | 2326 |
| 5°  | 2326 | 2324 | 2335 |
| 10° | 2327 | 2322 | 2333 |
| 15° | 2322 | 2317 | 2325 |
| 20° | 2314 | 2305 | 2314 |
| 25° | 2302 | 2292 | 2298 |
| 30° | 2283 | 2270 | 2266 |
| 35° | 2249 | 2232 | 2218 |
| 40° | 2204 | 2174 | 2136 |
| 45° | 2136 | 2068 | 1983 |
| 50° | 2030 | 1874 | 1714 |
| 55° | 1871 | 1592 | 1476 |
| 60° | 1665 | 1391 | 1265 |
| 65° | 1429 | 1206 | 1077 |
| 70° | 1179 | 1063 | 987  |
| 75° | 994  | 1017 | 962  |
| 80° | 841  | 1038 | 989  |
| 85° | 658  | 1051 | 920  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2136 cd/sqm

TEST NUMBER: P1471825

CATALOG NUMBER: 24PTR-50S-PB1-L835-UNV-STD-B

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 163.9  | 3.8       |
| 10°-20°   | 470.4  | 10.9      |
| 20°-30°   | 712.6  | 16.5      |
| 30°-40°   | 849.1  | 19.7      |
| 40°-50°   | 830.3  | 19.3      |
| 50°-60°   | 628.0  | 14.6      |
| 60°-70°   | 385.8  | 8.9       |
| 70°-80°   | 205.6  | 4.8       |
| 80°-90°   | 65.6   | 1.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1346.9 | 31.2      |
| 0°-40°    | 2195.9 | 50.9      |
| 0°-60°    | 3654.2 | 84.8      |
| 0°-90°    | 4311.2 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 4311.2 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|-----|------|-------|------|-------|------|------|
| 0°  | 1729 | 1729  | 1729 | 1729  | 1729 |      |
| 5°  | 1722 | 1725  | 1720 | 1727  | 1729 | 164  |
| 15° | 1667 | 1669  | 1663 | 1669  | 1669 | 471  |
| 25° | 1550 | 1548  | 1544 | 1546  | 1548 | 714  |
| 35° | 1370 | 1368  | 1359 | 1352  | 1350 | 857  |
| 45° | 1123 | 1116  | 1087 | 1050  | 1042 | 864  |
| 55° | 798  | 757   | 678  | 640   | 629  | 714  |
| 65° | 449  | 413   | 379  | 349   | 338  | 447  |
| 75° | 191  | 194   | 196  | 189   | 185  | 205  |
| 85° | 43   | 55    | 68   | 64    | 60   | 51   |
| 90° | 0    | 0     | 0    | 0     | 0    |      |

TEST NUMBER: P1471825

CATALOG NUMBER: 24PTR-50S-PB1-L835-UNV-STD-B

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|-------|--------|--------|--------|--------|--------|
| 0°    | 1729.0 | 1729.0 | 1729.0 | 1729.0 | 1729.0 |
| 2.5°  | 1726.9 | 1729.0 | 1722.5 | 1731.2 | 1733.2 |
| 5°    | 1722.5 | 1724.7 | 1720.5 | 1726.9 | 1729.0 |
| 7.5°  | 1716.2 | 1716.2 | 1712.0 | 1718.2 | 1720.5 |
| 10°   | 1703.5 | 1703.5 | 1699.3 | 1705.5 | 1707.7 |
| 12.5° | 1686.5 | 1686.5 | 1684.3 | 1688.5 | 1690.8 |
| 15°   | 1667.3 | 1669.3 | 1663.1 | 1669.3 | 1669.3 |
| 17.5° | 1643.9 | 1641.9 | 1639.7 | 1643.9 | 1646.1 |
| 20°   | 1616.2 | 1616.2 | 1610.0 | 1614.2 | 1616.2 |
| 22.5° | 1584.3 | 1584.3 | 1582.3 | 1584.3 | 1582.3 |
| 25°   | 1550.3 | 1548.1 | 1543.9 | 1546.1 | 1548.1 |
| 27.5° | 1509.9 | 1509.9 | 1505.7 | 1505.7 | 1503.5 |
| 30°   | 1469.5 | 1467.3 | 1461.0 | 1456.8 | 1458.8 |
| 32.5° | 1420.6 | 1418.4 | 1412.1 | 1407.9 | 1409.9 |
| 35°   | 1369.5 | 1367.5 | 1359.0 | 1352.5 | 1350.5 |
| 37.5° | 1318.6 | 1312.1 | 1301.4 | 1292.9 | 1284.4 |
| 40°   | 1254.7 | 1248.3 | 1237.8 | 1218.6 | 1216.3 |
| 42.5° | 1190.9 | 1184.6 | 1167.4 | 1144.2 | 1137.8 |
| 45°   | 1122.8 | 1116.5 | 1086.6 | 1050.5 | 1042.0 |
| 47.5° | 1050.5 | 1040.0 | 993.1  | 948.4  | 931.5  |
| 50°   | 969.9  | 950.7  | 895.3  | 837.9  | 818.7  |
| 52.5° | 891.0  | 857.1  | 784.8  | 733.6  | 714.7  |
| 55°   | 797.5  | 757.1  | 678.5  | 640.1  | 629.4  |
| 57.5° | 714.7  | 659.3  | 595.4  | 557.3  | 548.8  |
| 60°   | 618.9  | 567.8  | 516.9  | 482.7  | 470.0  |
| 62.5° | 531.6  | 486.9  | 444.5  | 414.6  | 399.9  |
| 65°   | 448.8  | 412.6  | 378.7  | 348.7  | 338.2  |
| 67.5° | 367.9  | 348.7  | 321.1  | 297.8  | 291.4  |
| 70°   | 299.8  | 289.1  | 270.1  | 259.4  | 250.9  |
| 72.5° | 238.2  | 242.5  | 229.7  | 225.5  | 219.0  |
| 75°   | 191.3  | 193.6  | 195.6  | 189.3  | 185.1  |
| 77.5° | 144.7  | 155.2  | 163.7  | 159.4  | 155.2  |
| 80°   | 108.5  | 119.0  | 134.0  | 127.7  | 127.7  |
| 82.5° | 74.3   | 87.3   | 100.0  | 95.8   | 93.5   |
| 85°   | 42.6   | 55.4   | 68.1   | 63.9   | 59.6   |
| 87.5° | 17.0   | 27.7   | 29.7   | 29.7   | 27.7   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

TEST NUMBER: P1471825

CATALOG NUMBER: 24PTR-50S-PB1-L835-UNV-STD-B

**CIE UGR TABLE:**

| Reflectances:   |      |                  |      |      |      |      |                |      |      |      |      |
|-----------------|------|------------------|------|------|------|------|----------------|------|------|------|------|
| Ceiling         |      | 0.7              | 0.7  | 0.5  | 0.5  | 0.3  | 0.7            | 0.7  | 0.5  | 0.5  | 0.3  |
| Wall            |      | 0.5              | 0.3  | 0.5  | 0.3  | 0.3  | 0.5            | 0.3  | 0.5  | 0.3  | 0.3  |
| Reference plane |      | 0.2              | 0.2  | 0.2  | 0.2  | 0.2  | 0.2            | 0.2  | 0.2  | 0.2  | 0.2  |
| Room Dimensions |      | Viewed crosswise |      |      |      |      | Viewed endwise |      |      |      |      |
| X=2H            | Y=2H | 13.8             | 15.4 | 14.2 | 15.7 | 16.0 | 12.5           | 14.1 | 12.9 | 14.4 | 14.7 |
|                 | 3H   | 15.1             | 16.5 | 15.4 | 16.8 | 17.1 | 13.8           | 15.2 | 14.2 | 15.5 | 15.9 |
|                 | 4H   | 15.5             | 16.8 | 15.9 | 17.1 | 17.5 | 14.3           | 15.7 | 14.7 | 16.0 | 16.4 |
|                 | 6H   | 15.8             | 17.0 | 16.2 | 17.3 | 17.7 | 14.8           | 16.1 | 15.3 | 16.4 | 16.8 |
|                 | 8H   | 15.8             | 17.0 | 16.3 | 17.4 | 17.8 | 15.0           | 16.2 | 15.5 | 16.6 | 17.0 |
|                 | 12H  | 15.9             | 17.0 | 16.3 | 17.4 | 17.8 | 15.2           | 16.3 | 15.6 | 16.7 | 17.1 |
| 4H              | 2H   | 14.1             | 15.5 | 14.5 | 15.8 | 16.2 | 13.1           | 14.4 | 13.5 | 14.7 | 15.1 |
|                 | 3H   | 15.6             | 16.7 | 16.0 | 17.1 | 17.5 | 14.6           | 15.6 | 15.0 | 16.0 | 16.4 |
|                 | 4H   | 16.1             | 17.1 | 16.6 | 17.5 | 18.0 | 15.2           | 16.2 | 15.7 | 16.6 | 17.1 |
|                 | 6H   | 16.6             | 17.4 | 17.0 | 17.9 | 18.3 | 15.9           | 16.7 | 16.3 | 17.2 | 17.6 |
|                 | 8H   | 16.7             | 17.5 | 17.2 | 17.9 | 18.4 | 16.1           | 16.9 | 16.6 | 17.4 | 17.9 |
|                 | 12H  | 16.8             | 17.5 | 17.3 | 18.0 | 18.5 | 16.3           | 17.1 | 16.8 | 17.5 | 18.0 |
| 8H              | 4H   | 16.4             | 17.2 | 16.8 | 17.6 | 18.1 | 15.5           | 16.3 | 16.0 | 16.8 | 17.3 |
|                 | 6H   | 16.9             | 17.6 | 17.4 | 18.1 | 18.5 | 16.3           | 17.0 | 16.8 | 17.5 | 18.0 |
|                 | 8H   | 17.1             | 17.7 | 17.6 | 18.2 | 18.7 | 16.7           | 17.3 | 17.2 | 17.8 | 18.3 |
|                 | 12H  | 17.3             | 17.8 | 17.8 | 18.3 | 18.9 | 17.0           | 17.5 | 17.5 | 18.0 | 18.6 |
| 12H             | 4H   | 16.4             | 17.1 | 16.9 | 17.6 | 18.0 | 15.6           | 16.3 | 16.1 | 16.8 | 17.2 |
|                 | 6H   | 17.0             | 17.6 | 17.5 | 18.0 | 18.6 | 16.4           | 17.0 | 16.9 | 17.5 | 18.0 |
|                 | 8H   | 17.2             | 17.8 | 17.7 | 18.3 | 18.8 | 16.8           | 17.4 | 17.3 | 17.8 | 18.4 |















(END OF REPORT)