

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1471838

Luminaire Tested: 24PTR-50S-PW1-L835-UNV-STD-W

Issue Date: 6/22/2026

Test Information

Test Method: LM-79-2019
Report Number: P1471838
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P737743)
Test Lab: INNOVATION CENTER
Issue Date: 6/22/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 24PTR-50S-PW1-L835-UNV-STD-W
Description: 5500 LUMEN 2X4 PERCEIVE PT TROFFER WITH 3500K, 80 CRI LEDS AND PW1 Lens White Rece:
Frame
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5094.6 lumens
Efficiency: N/A
Efficacy: 115.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.34
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 44.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1471838

CATALOG NUMBER: 24PTR-50S-PW1-L835-UNV-STD-W

Luminous Intensity Polar Plot



TEST NUMBER: P1471838

CATALOG NUMBER: 24PTR-50S-PW1-L835-UNV-STD-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	109	105	101	97	107	103	99	95	98	95	92		94	92	90		85
2	100	92	85	80	97	90	84	79	86	81	77		83	79	75		71
3	91	81	73	67	89	79	72	66	76	70	65		74	68	64		61
4	84	72	63	57	81	71	63	57	68	61	56		66	60	55		52
5	77	64	56	49	75	63	55	49	61	54	48		59	53	48		45
6	71	58	49	43	69	57	49	43	55	48	42		54	47	42		40
7	66	53	44	38	64	52	44	38	50	43	38		49	42	37		35
8	62	48	40	34	60	48	40	34	46	39	34		45	38	34		31
9	58	44	36	31	56	44	36	31	43	35	30		41	35	30		28
10	54	41	33	28	53	40	33	28	39	32	28		38	32	28		26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2583	2583	2583
5°	2585	2580	2593
10°	2584	2578	2591
15°	2576	2572	2582
20°	2566	2560	2566
25°	2551	2541	2539
30°	2532	2510	2492
35°	2498	2460	2429
40°	2460	2393	2355
45°	2392	2321	2274
50°	2319	2244	2192
55°	2223	2148	2062
60°	2108	1983	1879
65°	1949	1771	1683
70°	1690	1542	1483
75°	1349	1319	1283
80°	1025	1146	1146
85°	758	977	977

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2392 cd/sqm

TEST NUMBER: P1471838

CATALOG NUMBER: 24PTR-50S-PW1-L835-UNV-STD-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.1	3.6
10°-20°	522.2	10.2
20°-30°	789.2	15.5
30°-40°	937.1	18.4
40°-50°	944.1	18.5
50°-60°	816.1	16.0
60°-70°	557.8	10.9
70°-80°	275.0	5.4
80°-90°	71.1	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1493.5	29.3
0°-40°	2430.5	47.7
0°-60°	4190.7	82.3
0°-90°	5094.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5094.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1920	1920	1920	1920	1920	
5°	1914	1915	1910	1918	1920	182
15°	1849	1852	1847	1853	1854	522
25°	1719	1717	1711	1713	1710	792
35°	1521	1516	1498	1484	1479	952
45°	1257	1243	1220	1206	1195	970
55°	948	945	916	888	879	847
65°	612	590	556	532	529	605
75°	260	257	254	254	247	283
85°	49	58	63	65	63	60
90°	0	0	0	0	0	

TEST NUMBER: P1471838

CATALOG NUMBER: 24PTR-50S-PW1-L835-UNV-STD-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1919.7	1919.7	1919.7	1919.7	1919.7
2.5°	1919.2	1919.7	1914.8	1923.4	1925.4
5°	1914.1	1914.8	1909.9	1917.7	1919.7
7.5°	1905.0	1906.3	1900.6	1908.4	1909.9
10°	1891.3	1892.1	1887.2	1894.9	1896.5
12.5°	1873.0	1873.5	1869.3	1876.3	1876.3
15°	1849.4	1851.5	1846.6	1853.1	1853.6
17.5°	1823.1	1823.8	1818.9	1825.9	1827.5
20°	1791.8	1791.8	1787.7	1793.3	1791.8
22.5°	1756.9	1756.9	1752.0	1754.8	1756.1
25°	1718.6	1717.1	1711.4	1713.0	1710.1
27.5°	1674.4	1674.4	1664.4	1664.4	1659.4
30°	1629.7	1626.1	1615.5	1609.0	1604.1
32.5°	1578.3	1573.4	1559.9	1548.6	1544.9
35°	1520.9	1515.7	1497.9	1484.5	1478.8
37.5°	1465.3	1454.0	1430.4	1417.0	1410.5
40°	1400.5	1386.2	1362.2	1343.6	1340.7
42.5°	1330.9	1319.5	1288.3	1274.6	1271.2
45°	1257.0	1243.3	1219.8	1205.6	1195.0
47.5°	1184.4	1174.3	1147.4	1130.3	1126.7
50°	1108.1	1099.6	1071.9	1053.6	1047.1
52.5°	1029.3	1023.6	1000.1	976.5	968.8
55°	947.6	944.7	915.5	888.4	879.1
57.5°	867.2	863.6	827.1	795.9	787.3
60°	783.2	772.6	736.9	707.7	698.4
62.5°	703.6	680.8	642.3	619.6	609.0
65°	612.3	590.4	556.3	532.0	528.6
67.5°	522.9	496.5	470.2	455.2	443.8
70°	429.6	411.8	391.9	379.2	377.1
72.5°	342.7	330.1	320.0	312.2	305.8
75°	259.5	257.4	253.8	253.8	246.8
77.5°	190.8	195.7	198.5	197.7	199.3
80°	132.3	142.2	147.9	148.6	147.9
82.5°	84.0	95.4	104.7	106.0	107.5
85°	49.1	57.6	63.3	64.6	63.3
87.5°	22.0	27.7	29.2	30.5	29.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1471838

CATALOG NUMBER: 24PTR-50S-PW1-L835-UNV-STD-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.0	16.6	15.3	16.9	17.2	14.4	16.0	14.8	16.3	16.6
	3H	16.4	17.9	16.8	18.2	18.6	15.8	17.2	16.2	17.5	17.9
	4H	16.9	18.2	17.3	18.6	19.0	16.3	17.6	16.7	18.0	18.3
	6H	17.1	18.4	17.6	18.8	19.2	16.6	17.9	17.0	18.2	18.6
	8H	17.2	18.4	17.6	18.8	19.2	16.7	17.9	17.2	18.3	18.7
	12H	17.2	18.4	17.7	18.8	19.2	16.8	17.9	17.2	18.3	18.8
4H	2H	15.4	16.8	15.8	17.1	17.5	15.0	16.3	15.4	16.7	17.0
	3H	17.1	18.2	17.5	18.6	19.0	16.5	17.7	16.9	18.1	18.5
	4H	17.6	18.7	18.1	19.1	19.5	17.1	18.1	17.6	18.6	19.0
	6H	18.0	18.9	18.5	19.3	19.8	17.6	18.5	18.1	18.9	19.4
	8H	18.1	18.9	18.6	19.4	19.8	17.8	18.6	18.2	19.0	19.5
	12H	18.2	18.9	18.6	19.4	19.8	17.9	18.6	18.4	19.1	19.6
8H	4H	17.8	18.7	18.3	19.1	19.6	17.4	18.2	17.8	18.6	19.1
	6H	18.3	19.0	18.8	19.5	19.9	17.9	18.6	18.4	19.1	19.6
	8H	18.4	19.0	18.9	19.6	20.0	18.2	18.8	18.7	19.3	19.8
	12H	18.5	19.1	19.0	19.6	20.1	18.3	18.9	18.9	19.4	19.9
12H	4H	17.8	18.6	18.3	19.1	19.5	17.4	18.1	17.9	18.6	19.1
	6H	18.3	18.9	18.8	19.4	19.9	18.0	18.6	18.5	19.1	19.6
	8H	18.5	19.0	19.0	19.5	20.1	18.2	18.8	18.8	19.3	19.8

(END OF REPORT)