

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1056956

Luminaire Tested: CB2-085D-830-1D-UNV-STD-W-8

Issue Date: 7/31/2025

Test Information

Test Method: LM-79-2019
Report Number: P1056956
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 7/31/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-085D-830-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE
2-INCH APERTURE
DOWNLIGHT 850 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6179.9 lumens
Efficiency: N/A
Efficacy: 110.9 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')
CIE Type: Direct


Input Watts (W): 55.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1056956

CATALOG NUMBER: CB2-085D-830-1D-UNV-STD-W-8

Luminous Intensity Polar Plot



TEST NUMBER: P1056956

CATALOG NUMBER: CB2-085D-830-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	109	105	101	97	107	103	99	95	98	95	92	94	92	90	91	89	87
2	100	92	86	80	97	90	84	79	87	82	77	83	79	76	80	77	74
3	91	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63
4	84	73	64	58	82	71	63	57	69	62	56	66	60	56	64	59	55
5	78	65	56	50	76	64	56	50	62	55	49	60	54	49	58	53	48
6	72	59	50	44	70	58	50	44	56	49	43	55	48	43	53	47	43
7	67	54	45	39	65	53	45	39	51	44	39	50	43	38	49	43	38
8	62	49	41	35	61	48	41	35	47	40	35	46	39	35	45	39	34
9	58	45	37	32	57	45	37	32	44	37	32	42	36	31	41	36	31
10	55	42	34	29	54	41	34	29	40	34	29	39	33	29	39	33	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23080	23080	23080
5°	22884	22919	23079
10°	22753	22700	22681
15°	22394	22247	22064
20°	22040	21552	21251
25°	21448	20844	20260
30°	20855	19936	19182
35°	20171	19006	18100
40°	19447	18133	17071
45°	18719	17219	16070
50°	18063	16331	15093
55°	17254	15405	14172
60°	16329	14526	13255
65°	15346	13549	12335
70°	14262	12451	11160
75°	12975	11265	10104
80°	11600	9870	9158
85°	8923	8114	6695

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18719 cd/sqm

TEST NUMBER: P1056956

CATALOG NUMBER: CB2-085D-830-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	249.2	4.0
10°-20°	694.7	11.2
20°-30°	998.9	16.2
30°-40°	1122.7	18.2
40°-50°	1084.5	17.5
50°-60°	916.4	14.8
60°-70°	658.2	10.7
70°-80°	359.7	5.8
80°-90°	95.5	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1942.8	31.4
0°-40°	3065.5	49.6
0°-60°	5066.4	82.0
0°-90°	6179.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6179.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2650	2650	2650	2650	2650	
5°	2618	2653	2622	2622	2640	249
15°	2484	2506	2468	2443	2447	700
25°	2232	2234	2169	2120	2108	1028
35°	1897	1876	1788	1718	1702	1185
45°	1520	1488	1398	1325	1305	1174
55°	1136	1095	1015	951	933	1016
65°	745	717	658	610	599	738
75°	386	362	335	308	300	412
85°	89	83	81	71	67	110
90°	0	0	0	0	0	

TEST NUMBER: P1056956

CATALOG NUMBER: CB2-085D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2650.2	2650.2	2650.2	2650.2	2650.2
2.5°	2632.3	2664.0	2640.4	2643.8	2648.5
5°	2617.7	2653.4	2621.7	2622.2	2640.0
7.5°	2599.0	2632.7	2592.9	2585.6	2602.3
10°	2573.0	2606.8	2567.0	2553.0	2564.9
12.5°	2539.0	2571.1	2532.9	2510.8	2521.1
15°	2483.8	2505.6	2467.5	2443.3	2447.2
17.5°	2423.7	2437.2	2382.3	2361.9	2357.9
20°	2378.2	2390.1	2325.5	2297.0	2293.0
22.5°	2319.8	2330.1	2262.2	2227.1	2221.6
25°	2232.1	2234.1	2169.2	2120.3	2108.4
27.5°	2140.4	2134.1	2062.1	2004.1	1988.6
30°	2073.9	2065.9	1982.5	1921.3	1907.5
32.5°	2002.4	1988.1	1904.6	1838.6	1824.7
35°	1897.3	1875.5	1787.7	1718.4	1702.5
37.5°	1785.3	1760.7	1674.5	1599.0	1581.2
40°	1710.6	1682.8	1595.0	1519.5	1501.6
42.5°	1636.0	1605.0	1515.4	1439.9	1420.4
45°	1519.9	1488.1	1398.1	1324.6	1304.8
47.5°	1409.5	1369.0	1281.7	1208.6	1188.7
50°	1333.2	1289.5	1205.4	1133.9	1114.0
52.5°	1255.3	1210.0	1129.1	1060.8	1041.0
55°	1136.4	1094.7	1014.6	951.3	933.4
57.5°	1018.7	978.6	905.4	845.0	827.5
60°	937.5	903.8	834.0	776.8	761.0
62.5°	859.6	829.0	762.6	710.3	694.4
65°	744.7	716.9	657.5	610.5	598.6
67.5°	633.1	605.3	557.2	515.1	501.6
70°	560.1	532.3	489.0	450.2	438.3
72.5°	490.3	460.9	425.7	390.2	381.5
75°	385.6	361.7	334.8	308.3	300.3
77.5°	293.0	270.0	250.4	231.7	229.7
80°	231.3	211.5	196.8	184.6	182.6
82.5°	172.9	157.8	148.1	139.2	138.8
85°	89.3	83.3	81.2	70.9	67.0
87.5°	26.0	26.0	22.7	19.5	19.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)