

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438874

Luminaire Tested: CB2-B-030U-120D-927-1D-UNV-STD-W-8

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1438874
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2405-119-1, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-B-030U-120D-927-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE, BATWING UPLIGHT
2-INCH APERTURE
DOWNLIGHT 1200 LUMENS PER FOOT
UPLIGHT 300 LUMENS PER FOOT
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12252.3 lumens
Efficiency: N/A
Efficacy: 114.8 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 106.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1438874

CATALOG NUMBER: CB2-B-030U-120D-927-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P1438874

CATALOG NUMBER: CB2-B-030U-120D-927-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	98	98	98	88	88	88	80	80	80	76
1	104	99	95	92	99	95	91	88	86	83	81	78	76	74	71	69	68	64
2	95	87	81	76	90	83	78	73	76	71	68	69	66	62	63	60	58	54
3	87	77	69	63	82	74	67	61	67	62	57	61	57	53	56	52	49	46
4	80	68	60	54	75	66	58	52	60	54	49	55	50	46	50	46	43	40
5	73	61	53	47	70	59	51	45	54	48	43	49	44	40	45	41	38	35
6	68	55	47	41	64	53	45	40	49	42	38	45	40	35	41	37	33	31
7	63	50	42	36	60	48	41	35	45	38	33	41	36	32	38	33	30	27
8	58	46	38	32	56	44	37	31	41	34	30	38	32	28	35	30	27	25
9	55	42	34	29	52	40	33	28	38	31	27	35	29	26	32	28	24	22
10	51	39	31	26	49	37	30	26	35	29	25	32	27	23	30	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	34613	34613	34613
5°	34320	34373	34613
10°	34125	34044	34017
15°	33585	33365	33091
20°	33056	32323	31871
25°	32168	31261	30384
30°	31277	29899	28767
35°	30251	28505	27146
40°	29166	27194	25603
45°	28074	25825	24101
50°	27090	24491	22636
55°	25877	23104	21255
60°	24489	21786	19878
65°	23015	20318	18500
70°	21388	18674	16739
75°	19455	16898	15155
80°	17397	14805	13736
85°	13379	12160	10032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 28074 cd/sqm



TEST NUMBER: P1438874

CATALOG NUMBER: CB2-B-030U-120D-927-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	373.8	3.1
10°-20°	1041.9	8.5
20°-30°	1498.1	12.2
30°-40°	1683.8	13.7
40°-50°	1626.6	13.3
50°-60°	1374.3	11.2
60°-70°	987.1	8.1
70°-80°	539.5	4.4
80°-90°	143.3	1.2
90°-100°	34.0	0.3
100°-110°	210.7	1.7
110°-120°	531.4	4.3
120°-130°	638.8	5.2
130°-140°	579.2	4.7
140°-150°	461.8	3.8
150°-160°	315.0	2.6
160°-170°	166.6	1.4
170°-180°	46.4	0.4
0°-30°	2913.7	23.8
0°-40°	4597.5	37.5
0°-60°	7598.4	62.0
0°-90°	9268.4	75.6
90°-120°	776.1	6.3
90°-150°	2455.9	20.0
90°-180°	2984.0	24.4
0°-180°	12252.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3975	3975	3975	3975	3975	
5°	3926	3980	3932	3933	3959	373
15°	3725	3758	3701	3664	3670	1050
25°	3348	3351	3253	3180	3162	1541
35°	2846	2813	2681	2577	2553	1778
45°	2280	2232	2097	1987	1957	1761
55°	1704	1642	1522	1427	1400	1524
65°	1117	1075	986	916	898	1108
75°	578	542	502	462	450	619
85°	134	125	122	106	100	159
90°	0	0	0	0	0	6
95°	18	44	14	10	10	22
105°	86	241	348	87	59	90
115°	149	329	795	740	564	146
125°	194	399	867	987	992	173
135°	243	442	869	1018	1092	189
145°	311	464	820	988	1077	195
155°	378	474	730	880	926	174
165°	429	469	589	694	726	120
175°	454	460	468	476	485	43
180°	454	454	454	454	454	



TEST NUMBER: P1438874

CATALOG NUMBER: CB2-B-030U-120D-927-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3974.6	3974.6	3974.6	3974.6	3974.6
2.5°	3947.8	3995.4	3960.0	3965.0	3972.2
5°	3925.9	3979.5	3932.0	3932.6	3959.4
7.5°	3897.9	3948.5	3888.8	3877.8	3902.8
10°	3859.0	3909.5	3849.8	3828.9	3846.8
12.5°	3807.8	3856.0	3798.7	3765.6	3781.1
15°	3725.1	3757.8	3700.7	3664.3	3670.3
17.5°	3635.0	3655.2	3572.9	3542.3	3536.4
20°	3566.8	3584.7	3487.7	3444.9	3439.0
22.5°	3479.2	3494.6	3392.7	3340.2	3331.9
25°	3347.7	3350.7	3253.3	3179.9	3162.0
27.5°	3210.1	3200.6	3092.6	3005.7	2982.5
30°	3110.3	3098.4	2973.3	2881.6	2860.7
32.5°	3003.2	2981.7	2856.5	2757.4	2736.6
35°	2845.5	2812.8	2681.2	2577.2	2553.4
37.5°	2677.5	2640.6	2511.4	2398.2	2371.4
40°	2565.5	2523.9	2392.1	2278.9	2252.1
42.5°	2453.5	2407.1	2272.8	2159.5	2130.3
45°	2279.5	2231.9	2096.9	1986.6	1956.9
47.5°	2113.9	2053.2	1922.2	1812.5	1782.8
50°	1999.5	1934.0	1807.7	1700.6	1670.8
52.5°	1882.6	1814.8	1693.3	1591.0	1561.2
55°	1704.3	1641.8	1521.7	1426.7	1399.9
57.5°	1527.8	1467.6	1357.9	1267.3	1241.1
60°	1406.0	1355.4	1250.8	1165.1	1141.3
62.5°	1289.2	1243.3	1143.7	1065.2	1041.4
65°	1116.9	1075.2	986.0	915.6	897.8
67.5°	949.5	907.9	835.7	772.5	752.3
70°	840.0	798.3	733.4	675.2	657.4
72.5°	735.3	691.2	638.5	585.2	572.1
75°	578.2	542.5	502.2	462.3	450.4
77.5°	439.5	404.9	375.5	347.5	344.5
80°	346.9	317.2	295.2	276.9	273.9
82.5°	259.3	236.7	222.2	208.8	208.2
85°	133.9	125.0	121.7	106.4	100.4
87.5°	39.0	39.0	34.1	29.2	29.2
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.7	7.8	3.1	3.1	3.1
95°	17.6	44.4	13.7	9.8	9.8
97.5°	36.8	106.5	74.0	19.9	17.2
100°	50.9	154.2	127.2	29.2	23.5
102.5°	65.0	195.9	200.8	46.4	36.0
105°	86.1	241.2	348.4	87.4	58.7
107.5°	106.9	270.7	534.0	180.4	108.8
110°	119.4	287.8	673.4	281.3	168.3



TEST NUMBER: P1438874

CATALOG NUMBER: CB2-B-030U-120D-927-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	131.9	304.9	750.1	450.9	290.5
115°	148.8	328.7	794.7	739.8	563.7
117.5°	162.9	350.4	833.1	914.9	863.2
120°	172.3	367.5	853.4	940.0	957.2
122.5°	181.6	379.9	864.4	949.7	982.2
125°	193.8	398.6	867.1	986.7	992.4
127.5°	205.9	412.6	880.1	1020.7	1023.3
130°	215.3	422.0	892.6	1032.0	1053.1
132.5°	226.3	429.9	897.3	1038.5	1070.3
135°	242.7	441.8	869.1	1017.6	1092.2
137.5°	263.5	450.3	842.1	1017.0	1065.2
140°	276.0	452.1	828.0	1039.5	1043.3
142.5°	290.1	457.0	824.9	1037.0	1069.9
145°	311.2	464.3	820.2	988.5	1076.6
147.5°	332.4	469.0	802.2	935.0	1012.0
150°	346.5	470.9	784.9	917.2	965.0
152.5°	360.6	472.7	763.0	906.0	946.2
155°	377.8	473.5	730.1	879.9	925.9
157.5°	395.8	471.2	690.6	832.3	882.4
160°	405.2	468.3	665.5	797.7	841.7
162.5°	414.6	467.0	643.6	752.4	804.1
165°	428.7	468.9	589.2	693.7	726.2
167.5°	438.1	467.2	538.3	623.9	669.8
170°	444.3	467.3	507.0	570.5	608.8
172.5°	449.0	459.8	488.2	521.7	547.7
175°	454.1	459.9	467.8	475.9	485.4
177.5°	455.7	458.8	452.6	451.1	454.1
180°	454.1	454.1	454.1	454.1	454.1



TEST NUMBER: P1438874
 CATALOG NUMBER: CB2-B-030U-120D-927-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	21.42	22.55	22.12	23.27	24.12	20.32	21.45	21.02	22.17	23.02
	3H	23.08	24.10	23.80	24.83	25.71	21.87	22.88	22.58	23.61	24.50
	4H	23.72	24.68	24.46	25.42	26.32	22.45	23.41	23.19	24.15	25.05
	6H	24.14	25.02	24.89	25.77	26.68	22.84	23.72	23.58	24.47	25.38
	8H	24.30	25.14	25.05	25.91	26.82	22.98	23.83	23.74	24.60	25.51
	12H	24.38	25.18	25.14	25.94	26.88	23.06	23.86	23.82	24.62	25.56
4H	2H	21.86	22.82	22.60	23.56	24.45	20.98	21.94	21.72	22.68	23.58
	3H	23.75	24.55	24.50	25.33	26.24	22.74	23.54	23.50	24.32	25.23
	4H	24.51	25.23	25.28	26.01	26.96	23.43	24.15	24.19	24.93	25.87
	6H	25.04	25.67	25.83	26.47	27.42	23.92	24.55	24.70	25.35	26.30
	8H	25.25	25.84	26.04	26.64	27.60	24.11	24.70	24.90	25.50	26.46
	12H	25.37	25.90	26.18	26.72	27.69	24.21	24.74	25.02	25.56	26.53
8H	4H	24.69	25.27	25.47	26.07	27.03	23.72	24.31	24.51	25.11	26.07
	6H	25.34	25.82	26.16	26.67	27.63	24.34	24.82	25.16	25.66	26.63
	8H	25.63	26.06	26.46	26.90	27.88	24.61	25.05	25.44	25.89	26.87
	12H	25.82	26.20	26.65	27.03	28.07	24.78	25.16	25.61	25.99	27.02
12H	4H	24.68	25.21	25.49	26.03	26.99	23.74	24.27	24.55	25.09	26.05
	6H	25.37	25.80	26.20	26.64	27.62	24.40	24.83	25.23	25.67	26.65
	8H	25.70	26.08	26.53	26.91	27.95	24.72	25.10	25.55	25.93	26.97