

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438978

Luminaire Tested: CB2-D-030U-030D-927-1D-UNV-STD-W-8

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1438978
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2312-242-13, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-D-030U-030D-927-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE, DIFFUSER DUST COVER UPLIGHT
2-INCH APERTURE
DOWNLIGHT 300 LUMENS PER FOOT
UPLIGHT 300 LUMENS PER FOOT
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4461.6 lumens
Efficiency: N/A
Efficacy: 121.6 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 36.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1438978

CATALOG NUMBER: CB2-D-030U-030D-927-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P1438978

CATALOG NUMBER: CB2-D-030U-030D-927-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50				
1	98	94	90	86	90	87	83	80	73	71	69	61	60	58	50	49	48	43				
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	41	36				
3	82	72	65	59	75	67	61	56	57	52	48	48	44	41	39	37	35	31				
4	75	64	56	50	69	59	53	47	51	46	41	43	39	36	35	32	30	26				
5	69	57	49	43	63	53	46	41	46	40	36	38	34	31	32	29	26	23				
6	63	51	43	38	58	48	41	35	41	36	31	35	31	27	29	26	23	20				
7	59	46	39	33	54	43	36	31	37	32	28	32	27	24	26	23	21	18				
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19	16				
9	51	39	31	26	47	36	29	25	31	26	22	27	23	19	23	19	17	15				
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8339	8339	8339
5°	8268	8280	8338
10°	8220	8202	8195
15°	8091	8038	7972
20°	7964	7787	7678
25°	7750	7531	7320
30°	7535	7203	6931
35°	7288	6867	6539
40°	7027	6552	6167
45°	6763	6221	5806
50°	6526	5900	5453
55°	6234	5566	5121
60°	5899	5248	4788
65°	5545	4894	4457
70°	5154	4499	4033
75°	4687	4071	3651
80°	4193	3566	3310
85°	3227	2928	2418

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6763 cd/sqm



TEST NUMBER: P1438978

CATALOG NUMBER: CB2-D-030U-030D-927-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.0	2.0
10°-20°	251.0	5.6
20°-30°	360.9	8.1
30°-40°	405.6	9.1
40°-50°	391.8	8.8
50°-60°	331.1	7.4
60°-70°	237.8	5.3
70°-80°	130.0	2.9
80°-90°	34.6	0.8
90°-100°	33.8	0.8
100°-110°	139.2	3.1
110°-120°	252.8	5.7
120°-130°	343.9	7.7
130°-140°	397.1	8.9
140°-150°	400.1	9.0
150°-160°	345.3	7.7
160°-170°	234.0	5.2
170°-180°	82.5	1.9
0°-30°	701.9	15.7
0°-40°	1107.6	24.8
0°-60°	1830.5	41.0
0°-90°	2232.8	50.0
90°-120°	425.7	9.5
90°-150°	1566.8	35.1
90°-180°	2229.0	50.0
0°-180°	4461.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	958	958	958	958	958	
5°	946	959	947	947	954	90
15°	897	905	892	883	884	253
25°	806	807	784	766	762	371
35°	686	678	646	621	615	428
45°	549	538	505	479	471	424
55°	411	396	367	344	337	367
65°	269	259	238	221	216	267
75°	139	131	121	111	108	149
85°	32	30	29	26	24	38
90°	0	0	1	0	1	2
95°	33	29	27	21	21	38
105°	138	136	132	125	123	146
115°	262	261	256	249	248	258
125°	389	393	385	377	378	348
135°	519	525	516	507	510	399
145°	643	650	640	633	637	402
155°	752	759	748	744	750	346
165°	831	840	829	824	832	234
175°	870	880	868	863	865	83
180°	874	874	874	874	874	



TEST NUMBER: P1438978

CATALOG NUMBER: CB2-D-030U-030D-927-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	957.5	957.5	957.5	957.5	957.5
2.5°	951.1	962.5	954.0	955.2	956.9
5°	945.8	958.7	947.2	947.4	953.8
7.5°	939.0	951.2	936.8	934.2	940.2
10°	929.6	941.8	927.5	922.4	926.7
12.5°	917.3	928.9	915.1	907.2	910.9
15°	897.4	905.3	891.5	882.8	884.2
17.5°	875.7	880.6	860.7	853.4	851.9
20°	859.3	863.6	840.2	829.9	828.5
22.5°	838.2	841.9	817.3	804.7	802.7
25°	806.5	807.2	783.8	766.1	761.8
27.5°	773.3	771.0	745.0	724.1	718.5
30°	749.3	746.4	716.3	694.2	689.2
32.5°	723.5	718.3	688.1	664.3	659.3
35°	685.5	677.6	645.9	620.9	615.1
37.5°	645.0	636.1	605.0	577.7	571.3
40°	618.1	608.0	576.3	549.0	542.5
42.5°	591.1	579.9	547.5	520.2	513.2
45°	549.1	537.7	505.1	478.6	471.4
47.5°	509.3	494.6	463.1	436.7	429.5
50°	481.7	465.9	435.5	409.7	402.5
52.5°	453.5	437.2	407.9	383.3	376.1
55°	410.6	395.5	366.6	343.7	337.3
57.5°	368.0	353.6	327.1	305.3	299.0
60°	338.7	326.5	301.3	280.7	274.9
62.5°	310.6	299.5	275.5	256.6	250.9
65°	269.1	259.0	237.5	220.6	216.3
67.5°	228.7	218.7	201.3	186.1	181.2
70°	202.4	192.3	176.7	162.7	158.4
72.5°	177.1	166.5	153.8	141.0	137.8
75°	139.3	130.7	121.0	111.4	108.5
77.5°	105.9	97.6	90.5	83.7	83.0
80°	83.6	76.4	71.1	66.7	66.0
82.5°	62.5	57.0	53.5	50.3	50.1
85°	32.3	30.1	29.3	25.6	24.2
87.5°	9.4	9.4	8.3	7.0	7.2
90°	0.0	0.0	0.7	0.0	0.7
92.5°	8.2	7.1	6.7	4.4	5.0
95°	32.7	28.7	27.3	21.1	21.1
97.5°	61.8	57.8	55.6	49.3	48.0
100°	82.5	78.5	76.3	69.5	68.2
102.5°	103.7	101.9	98.2	90.8	89.4
105°	137.7	135.7	132.2	124.7	123.4
107.5°	172.6	173.0	167.8	161.6	159.8
110°	197.7	197.0	192.9	186.7	185.4



TEST NUMBER: P1438978

CATALOG NUMBER: CB2-D-030U-030D-927-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	223.3	222.1	218.0	211.8	210.5
115°	261.8	261.1	256.3	248.8	248.1
117.5°	298.3	300.4	294.8	286.8	286.6
120°	324.5	327.1	320.4	313.5	312.2
122.5°	350.1	353.3	346.6	338.7	338.9
125°	389.2	393.2	385.1	377.0	377.6
127.5°	427.0	431.9	424.4	416.1	416.9
130°	452.6	458.6	450.6	441.8	443.1
132.5°	478.8	484.8	476.8	467.4	469.8
135°	518.7	524.7	516.0	506.6	509.9
137.5°	556.4	562.4	552.8	544.9	548.9
140°	581.5	587.5	577.4	570.0	574.0
142.5°	606.0	613.1	602.5	594.5	599.6
145°	642.8	650.1	640.1	632.7	637.4
147.5°	677.7	685.0	674.8	667.7	672.5
150°	700.1	707.4	696.7	690.6	696.0
152.5°	720.8	729.2	717.9	712.0	718.9
155°	751.9	759.2	748.5	743.8	749.8
157.5°	778.9	787.4	776.7	772.7	777.5
160°	796.9	804.9	794.1	790.2	795.5
162.5°	810.5	819.0	808.9	804.4	810.8
165°	831.0	839.6	828.9	824.3	831.6
167.5°	847.0	856.2	845.4	840.7	848.1
170°	856.9	865.5	854.1	848.9	856.9
172.5°	863.4	872.6	860.7	855.3	860.7
175°	870.5	879.8	868.4	863.0	865.0
177.5°	873.9	881.4	872.3	867.5	873.9
180°	873.9	873.9	873.9	873.9	873.9



TEST NUMBER: P1438978
 CATALOG NUMBER: CB2-D-030U-030D-927-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.37	15.22	15.33	16.20	17.47	13.27	14.12	14.23	15.10	16.37
	3H	16.02	16.78	16.99	17.76	19.06	14.80	15.56	15.77	16.54	17.84
	4H	16.65	17.37	17.63	18.35	19.66	15.37	16.09	16.36	17.08	18.38
	6H	17.05	17.71	18.04	18.70	20.02	15.75	16.41	16.74	17.40	18.71
	8H	17.20	17.83	18.20	18.84	20.15	15.88	16.52	16.89	17.52	18.84
	12H	17.27	17.87	18.28	18.87	20.21	15.95	16.55	16.95	17.55	18.89
4H	2H	14.78	15.50	15.77	16.49	17.79	13.91	14.63	14.90	15.61	16.92
	3H	16.65	17.25	17.65	18.27	19.58	15.64	16.24	16.64	17.26	18.57
	4H	17.40	17.94	18.40	18.95	20.29	16.31	16.86	17.32	17.87	19.21
	6H	17.91	18.39	18.93	19.42	20.76	16.79	17.26	17.81	18.29	19.63
	8H	18.12	18.56	19.14	19.58	20.94	16.98	17.42	18.00	18.44	19.80
	12H	18.23	18.62	19.26	19.66	21.02	17.07	17.46	18.10	18.50	19.86
8H	4H	17.55	17.99	18.57	19.02	20.37	16.59	17.03	17.61	18.05	19.40
	6H	18.19	18.56	19.24	19.62	20.97	17.19	17.56	18.24	18.62	19.97
	8H	18.48	18.80	19.54	19.86	21.22	17.47	17.79	18.52	18.84	20.21
	12H	18.66	18.94	19.71	19.99	21.40	17.62	17.90	18.67	18.94	20.35
12H	4H	17.53	17.93	18.57	18.97	20.33	16.59	16.99	17.63	18.03	19.39
	6H	18.22	18.54	19.27	19.59	20.96	17.25	17.58	18.31	18.63	19.99
	8H	18.54	18.82	19.59	19.87	21.28	17.56	17.84	18.61	18.89	20.30