

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438799

Luminaire Tested: CB2-125U-030D-927-1D-UNV-STD-W-4

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1438799
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2506-466-1, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-125U-030D-927-1D-UNV-STD-W-4
Description: CORELITE BASIC SLOT LED LUMINAIRE, OPEN UPLIGHT
2-INCH APERTURE
DOWNLIGHT 300 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6834.0 lumens
Efficiency: N/A
Efficacy: 140.6 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.23
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 48.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1438799

CATALOG NUMBER: CB2-125U-030D-927-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P1438799

CATALOG NUMBER: CB2-125U-030D-927-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									70									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	99	99	99	99	87	87	87	87	65	65	65	44	44	44	25	25	25	16																			
1	90	86	83	79	79	76	73	70	57	55	53	39	38	37	22	22	21	14																			
2	82	75	70	65	72	66	62	58	50	46	44	34	32	31	20	19	18	12																			
3	75	66	59	54	66	58	53	48	44	40	37	30	28	26	17	16	15	10																			
4	68	58	51	45	60	52	45	41	39	35	31	27	24	22	16	14	13	9																			
5	63	52	44	39	55	46	39	35	34	30	27	24	21	19	14	13	12	8																			
6	58	46	39	33	50	41	35	30	31	26	23	22	19	17	13	11	10	7																			
7	53	42	34	29	47	37	30	26	28	23	20	19	17	15	12	10	9	6																			
8	49	38	30	25	43	33	27	23	25	21	18	18	15	13	11	9	8	5																			
9	46	34	27	22	40	30	24	20	23	19	16	16	13	11	10	8	7	5																			
10	42	31	24	20	37	28	22	18	21	17	14	15	12	10	9	8	7	4																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8339	8339	8339
5°	8268	8280	8338
10°	8220	8201	8196
15°	8091	8039	7972
20°	7963	7787	7677
25°	7749	7531	7320
30°	7534	7202	6931
35°	7289	6868	6540
40°	7026	6550	6168
45°	6764	6222	5806
50°	6525	5899	5455
55°	6234	5566	5120
60°	5901	5250	4790
65°	5543	4896	4455
70°	5154	4497	4033
75°	4690	4071	3654
80°	4193	3571	3310
85°	3217	2938	2418

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6764 cd/sqm



TEST NUMBER: P1438799

CATALOG NUMBER: CB2-125U-030D-927-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.0	0.7
10°-20°	125.5	1.8
20°-30°	180.4	2.6
30°-40°	202.8	3.0
40°-50°	195.9	2.9
50°-60°	165.5	2.4
60°-70°	118.9	1.7
70°-80°	65.0	1.0
80°-90°	17.4	0.3
90°-100°	34.9	0.5
100°-110°	222.4	3.3
110°-120°	706.6	10.3
120°-130°	1025.5	15.0
130°-140°	1102.8	16.1
140°-150°	1038.4	15.2
150°-160°	845.9	12.4
160°-170°	550.6	8.1
170°-180°	190.3	2.8
0°-30°	351.0	5.1
0°-40°	553.8	8.1
0°-60°	915.2	13.4
0°-90°	1116.5	16.3
90°-120°	964.0	14.1
90°-150°	4130.7	60.4
90°-180°	5717.0	83.7
0°-180°	6834.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	479	479	479	479	479	
5°	473	479	474	474	477	45
15°	449	453	446	441	442	126
25°	403	404	392	383	381	186
35°	343	339	323	310	308	214
45°	275	269	253	239	236	212
55°	205	198	183	172	169	184
65°	134	130	119	110	108	133
75°	70	65	60	56	54	75
85°	16	15	15	13	12	19
90°	0	0	0	1	1	4
95°	80	23	25	16	14	101
105°	418	433	44	51	54	440
115°	790	807	815	824	473	777
125°	1122	1142	1142	1162	1177	1003
135°	1412	1429	1427	1436	1454	1089
145°	1653	1666	1654	1656	1678	1033
155°	1836	1847	1827	1823	1849	846
165°	1957	1963	1943	1935	1954	553
175°	2015	2020	1994	1981	1991	192
180°	2005	2005	2005	2005	2005	

TEST NUMBER: P1438799

CATALOG NUMBER: CB2-125U-030D-927-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	478.8	478.8	478.8	478.8	478.8
2.5°	475.5	481.3	477.0	477.6	478.5
5°	472.9	479.3	473.6	473.7	476.9
7.5°	469.5	475.6	468.4	467.1	470.1
10°	464.8	470.9	463.7	461.2	463.4
12.5°	458.7	464.5	457.6	453.6	455.4
15°	448.7	452.6	445.8	441.4	442.1
17.5°	437.8	440.3	430.4	426.7	426.0
20°	429.6	431.8	420.1	415.0	414.2
22.5°	419.1	420.9	408.7	402.3	401.3
25°	403.2	403.6	391.9	383.0	380.9
27.5°	386.7	385.5	372.5	362.0	359.2
30°	374.6	373.2	358.1	347.1	344.6
32.5°	361.7	359.2	344.1	332.1	329.6
35°	342.8	338.8	323.0	310.4	307.6
37.5°	322.5	318.1	302.5	288.9	285.6
40°	309.0	304.0	288.1	274.5	271.3
42.5°	295.5	289.9	273.8	260.1	256.6
45°	274.6	268.8	252.6	239.3	235.7
47.5°	254.6	247.3	231.5	218.3	214.7
50°	240.8	233.0	217.7	204.8	201.3
52.5°	226.8	218.6	204.0	191.6	188.1
55°	205.3	197.8	183.3	171.9	168.6
57.5°	184.0	176.8	163.6	152.6	149.5
60°	169.4	163.3	150.7	140.3	137.5
62.5°	155.3	149.8	137.8	128.3	125.4
65°	134.5	129.5	118.8	110.3	108.1
67.5°	114.4	109.4	100.7	93.1	90.6
70°	101.2	96.2	88.3	81.3	79.2
72.5°	88.6	83.3	76.9	70.5	68.9
75°	69.7	65.3	60.5	55.7	54.3
77.5°	52.9	48.8	45.2	41.9	41.5
80°	41.8	38.2	35.6	33.4	33.0
82.5°	31.2	28.5	26.8	25.1	25.1
85°	16.1	15.1	14.7	12.8	12.1
87.5°	4.7	4.7	4.1	3.8	3.8
90°	0.0	0.0	0.0	1.4	1.4
92.5°	22.0	8.4	5.8	8.4	8.4
95°	79.7	23.0	24.6	15.9	14.5
97.5°	165.6	37.1	35.7	39.2	40.6
100°	230.5	76.0	39.1	45.0	46.4
102.5°	302.4	286.3	40.3	48.5	51.0
105°	417.6	433.2	43.5	50.8	53.6
107.5°	530.7	546.3	202.4	52.6	55.4
110°	606.1	621.6	640.8	53.7	56.5



TEST NUMBER: P1438799

CATALOG NUMBER: CB2-125U-030D-927-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	676.8	695.8	710.4	119.5	58.9
115°	790.2	807.2	814.8	824.2	472.7
117.5°	890.2	911.2	919.8	936.1	952.0
120°	959.8	979.7	985.9	1002.3	1019.3
122.5°	1028.3	1045.8	1049.7	1068.3	1084.2
125°	1122.2	1142.1	1142.5	1161.7	1177.3
127.5°	1216.2	1233.2	1232.4	1246.7	1264.0
130°	1278.8	1290.1	1290.4	1302.4	1320.8
132.5°	1331.0	1346.9	1347.2	1356.9	1375.4
135°	1412.2	1429.2	1426.7	1435.8	1454.2
137.5°	1488.4	1504.9	1500.3	1508.0	1527.0
140°	1538.3	1552.5	1545.6	1553.3	1574.6
142.5°	1584.7	1598.9	1588.5	1595.1	1617.5
145°	1652.9	1665.6	1654.3	1656.2	1677.5
147.5°	1713.5	1725.9	1712.3	1714.2	1734.1
150°	1752.9	1764.2	1747.1	1749.0	1768.9
152.5°	1787.7	1797.9	1779.6	1779.2	1802.5
155°	1835.6	1846.9	1826.9	1823.1	1848.6
157.5°	1879.0	1889.5	1869.5	1866.7	1886.6
160°	1908.0	1915.1	1895.0	1891.1	1910.9
162.5°	1927.8	1936.0	1915.9	1909.7	1929.5
165°	1957.3	1963.0	1942.8	1934.6	1954.4
167.5°	1982.9	1989.4	1963.4	1956.1	1977.3
170°	1997.9	2002.2	1976.2	1966.5	1987.8
172.5°	2007.2	2010.3	1984.3	1973.3	1987.8
175°	2015.3	2019.6	1993.6	1980.8	1990.7
177.5°	2016.8	2019.1	1999.4	1988.2	2005.2
180°	2005.2	2005.2	2005.2	2005.2	2005.2



TEST NUMBER: P1438799

CATALOG NUMBER: CB2-125U-030D-927-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.77	10.39	10.97	11.57	13.25	8.67	9.29	9.87	10.46	12.15
	3H	11.40	11.95	12.60	13.14	14.83	10.18	10.73	11.38	11.92	13.61
	4H	12.01	12.54	13.23	13.73	15.43	10.74	11.27	11.95	12.45	14.15
	6H	12.40	12.89	13.62	14.07	15.79	11.10	11.58	12.32	12.77	14.48
	8H	12.54	13.00	13.77	14.21	15.91	11.23	11.69	12.45	12.89	14.60
	12H	12.61	13.05	13.83	14.24	15.96	11.29	11.72	12.51	12.92	14.64
4H	2H	10.15	10.67	11.37	11.86	13.56	9.27	9.80	10.50	10.98	12.68
	3H	11.99	12.43	13.22	13.65	15.36	10.98	11.42	12.21	12.63	14.35
	4H	12.73	13.14	13.96	14.33	16.06	11.65	12.05	12.88	13.25	14.98
	6H	13.24	13.58	14.47	14.80	16.52	12.11	12.46	13.34	13.68	15.39
	8H	13.44	13.76	14.66	14.97	16.70	12.30	12.62	13.52	13.83	15.56
	12H	13.53	13.82	14.77	15.04	16.78	12.37	12.67	13.61	13.89	15.62
8H	4H	12.87	13.19	14.09	14.40	16.14	11.90	12.23	13.13	13.44	15.17
	6H	13.50	13.77	14.74	15.02	16.75	12.50	12.76	13.74	14.02	15.75
	8H	13.79	14.02	15.04	15.25	17.00	12.77	13.00	14.02	14.23	15.98
	12H	13.95	14.15	15.20	15.38	17.16	12.91	13.11	14.16	14.34	16.12
12H	4H	12.84	13.13	14.08	14.35	16.09	11.89	12.19	13.14	13.41	15.15
	6H	13.53	13.76	14.78	14.99	16.74	12.56	12.79	13.81	14.02	15.77
	8H	13.83	14.03	15.08	15.26	17.04	12.85	13.06	14.11	14.28	16.06