

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438865

Luminaire Tested: CB2-B-030U-085D-927-1D-UNV-STD-W-4

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1438865
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2405-119-1, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-B-030U-085D-927-1D-UNV-STD-W-4
Description: CORELITE BASIC SLOT LED LUMINAIRE, BATWING UPLIGHT
2-INCH APERTURE
DOWNLIGHT 850 LUMENS PER FOOT
UPLIGHT 300 LUMENS PER FOOT
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4747.3 lumens
Efficiency: N/A
Efficacy: 128.0 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 37.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1438865

CATALOG NUMBER: CB2-B-030U-085D-927-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P1438865

CATALOG NUMBER: CB2-B-030U-085D-927-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69																												
1	102	98	94	90	96	93	89	86	83	80	78	73	72	70	65	64	62	58																												
2	93	86	80	74	88	81	76	71	73	68	65	65	62	59	58	55	53	49																												
3	85	76	68	62	80	72	65	60	64	59	55	58	53	50	51	48	45	42																												
4	78	67	59	53	74	64	57	51	57	52	47	52	47	43	46	42	39	36																												
5	72	60	52	46	68	57	50	44	52	45	41	46	41	38	42	38	34	32																												
6	66	54	46	40	63	52	44	39	47	40	36	42	37	33	38	34	30	28																												
7	62	49	41	35	58	47	39	34	43	36	32	38	33	29	35	30	27	25																												
8	57	45	37	31	54	43	36	30	39	33	28	35	30	26	32	28	25	22																												
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	25	22	20																												
10	50	38	30	26	47	36	29	25	33	27	23	30	25	22	27	23	20	18																												

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	24315	24315	24315
5°	24109	24147	24315
10°	23972	23915	23896
15°	23593	23438	23245
20°	23221	22706	22389
25°	22596	21960	21343
30°	21970	21003	20208
35°	21250	20023	19068
40°	20488	19103	17985
45°	19720	18141	16929
50°	19030	17204	15900
55°	18177	16231	14931
60°	17201	15303	13962
65°	16168	14272	12994
70°	15023	13118	11759
75°	13668	11871	10646
80°	12227	10401	9649
85°	9393	8553	7054

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19720 cd/sqm



TEST NUMBER: P1438865

CATALOG NUMBER: CB2-B-030U-085D-927-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.3	2.8
10°-20°	365.9	7.7
20°-30°	526.2	11.1
30°-40°	591.4	12.5
40°-50°	571.3	12.0
50°-60°	482.7	10.2
60°-70°	346.7	7.3
70°-80°	189.5	4.0
80°-90°	50.3	1.1
90°-100°	17.0	0.4
100°-110°	105.4	2.2
110°-120°	265.7	5.6
120°-130°	319.4	6.7
130°-140°	289.6	6.1
140°-150°	230.9	4.9
150°-160°	157.5	3.3
160°-170°	83.3	1.8
170°-180°	23.2	0.5
0°-30°	1023.4	21.6
0°-40°	1614.8	34.0
0°-60°	2668.8	56.2
0°-90°	3255.4	68.6
90°-120°	388.1	8.2
90°-150°	1228.0	25.9
90°-180°	1492.0	31.4
0°-180°	4747.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1396	1396	1396	1396	1396	
5°	1379	1398	1381	1381	1391	131
15°	1308	1320	1300	1287	1289	369
25°	1176	1177	1143	1117	1111	541
35°	999	988	942	905	897	624
45°	801	784	736	698	687	619
55°	599	577	534	501	492	535
65°	392	378	346	322	315	389
75°	203	191	176	162	158	217
85°	47	44	43	37	35	56
90°	0	0	0	0	0	2
95°	9	22	7	5	5	11
105°	43	121	174	44	29	45
115°	74	164	397	370	282	73
125°	97	199	434	493	496	87
135°	121	221	434	509	546	94
145°	156	232	410	494	538	97
155°	189	237	365	440	463	87
165°	214	234	295	347	363	60
175°	227	230	234	238	243	21
180°	227	227	227	227	227	

TEST NUMBER: P1438865

CATALOG NUMBER: CB2-B-030U-085D-927-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1396.0	1396.0	1396.0	1396.0	1396.0
2.5°	1386.6	1403.3	1390.9	1392.7	1395.2
5°	1378.9	1397.7	1381.1	1381.3	1390.7
7.5°	1369.1	1386.8	1365.9	1362.0	1370.8
10°	1355.4	1373.2	1352.2	1344.9	1351.1
12.5°	1337.4	1354.4	1334.2	1322.6	1328.0
15°	1308.4	1319.9	1299.8	1287.0	1289.1
17.5°	1276.7	1283.8	1254.9	1244.2	1242.1
20°	1252.8	1259.1	1225.0	1210.0	1207.9
22.5°	1222.0	1227.4	1191.6	1173.2	1170.3
25°	1175.8	1176.9	1142.7	1116.9	1110.6
27.5°	1127.5	1124.2	1086.2	1055.7	1047.5
30°	1092.4	1088.3	1044.3	1012.1	1004.8
32.5°	1054.8	1047.3	1003.3	968.5	961.2
35°	999.4	987.9	941.7	905.2	896.8
37.5°	940.4	927.5	882.1	842.3	832.9
40°	901.1	886.5	840.2	800.4	791.0
42.5°	861.8	845.5	798.3	758.5	748.2
45°	800.6	783.9	736.5	697.8	687.3
47.5°	742.5	721.2	675.1	636.6	626.2
50°	702.3	679.3	634.9	597.3	586.8
52.5°	661.2	637.4	594.8	558.8	548.4
55°	598.6	576.7	534.5	501.1	491.7
57.5°	536.6	515.5	477.0	445.1	435.9
60°	493.8	476.1	439.3	409.2	400.8
62.5°	452.8	436.7	401.7	374.1	365.8
65°	392.3	377.7	346.3	321.6	315.3
67.5°	333.5	318.9	293.5	271.3	264.2
70°	295.0	280.4	257.6	237.2	230.9
72.5°	258.3	242.8	224.3	205.6	201.0
75°	203.1	190.6	176.4	162.4	158.2
77.5°	154.4	142.2	131.9	122.0	121.0
80°	121.9	111.4	103.7	97.2	96.2
82.5°	91.1	83.1	78.0	73.3	73.1
85°	47.0	43.9	42.8	37.4	35.3
87.5°	13.7	13.7	12.0	10.3	10.3
90°	0.0	0.0	0.0	0.0	0.0
92.5°	2.3	3.9	1.6	1.6	1.6
95°	8.8	22.2	6.9	4.9	4.9
97.5°	18.4	53.2	37.0	10.0	8.6
100°	25.4	77.1	63.6	14.6	11.7
102.5°	32.5	97.9	100.4	23.2	18.0
105°	43.1	120.6	174.2	43.7	29.4
107.5°	53.4	135.4	267.0	90.2	54.4
110°	59.7	143.9	336.7	140.6	84.2



TEST NUMBER: P1438865

CATALOG NUMBER: CB2-B-030U-085D-927-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	66.0	152.5	375.0	225.4	145.2
115°	74.4	164.3	397.4	369.9	281.9
117.5°	81.4	175.2	416.5	457.5	431.6
120°	86.1	183.7	426.7	470.0	478.6
122.5°	90.8	190.0	432.2	474.9	491.1
125°	96.9	199.3	433.6	493.3	496.2
127.5°	103.0	206.3	440.0	510.3	511.7
130°	107.7	211.0	446.3	516.0	526.5
132.5°	113.1	215.0	448.6	519.3	535.2
135°	121.4	220.9	434.5	508.8	546.1
137.5°	131.7	225.1	421.0	508.5	532.6
140°	138.0	226.0	414.0	519.7	521.7
142.5°	145.0	228.5	412.4	518.5	535.0
145°	155.6	232.2	410.1	494.3	538.3
147.5°	166.2	234.5	401.1	467.5	506.0
150°	173.2	235.4	392.5	458.6	482.5
152.5°	180.3	236.4	381.5	453.0	473.1
155°	188.9	236.7	365.1	440.0	462.9
157.5°	197.9	235.6	345.3	416.1	441.2
160°	202.6	234.2	332.8	398.8	420.8
162.5°	207.3	233.5	321.8	376.2	402.1
165°	214.3	234.4	294.6	346.8	363.1
167.5°	219.0	233.6	269.1	311.9	334.9
170°	222.2	233.7	253.5	285.2	304.4
172.5°	224.5	229.9	244.1	260.8	273.8
175°	227.1	229.9	233.9	237.9	242.7
177.5°	227.8	229.4	226.3	225.5	227.1
180°	227.1	227.1	227.1	227.1	227.1



TEST NUMBER: P1438865
 CATALOG NUMBER: CB2-B-030U-085D-927-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.65	20.69	20.44	21.50	22.48	18.55	19.59	19.34	20.40	21.38
	3H	21.31	22.24	22.11	23.06	24.07	20.09	21.03	20.89	21.84	22.85
	4H	21.95	22.83	22.76	23.65	24.67	20.68	21.56	21.49	22.38	23.40
	6H	22.36	23.17	23.19	24.00	25.04	21.06	21.87	21.88	22.70	23.73
	8H	22.51	23.29	23.35	24.13	25.17	21.20	21.98	22.04	22.82	23.86
	12H	22.59	23.33	23.43	24.17	25.23	21.27	22.01	22.11	22.85	23.91
4H	2H	20.08	20.96	20.90	21.79	22.81	19.21	20.09	20.03	20.91	21.93
	3H	21.97	22.70	22.80	23.56	24.59	20.96	21.69	21.79	22.55	23.59
	4H	22.72	23.39	23.56	24.24	25.31	21.64	22.31	22.48	23.16	24.23
	6H	23.25	23.83	24.11	24.71	25.77	22.13	22.70	22.98	23.58	24.65
	8H	23.46	24.00	24.32	24.87	25.95	22.32	22.86	23.18	23.73	24.81
	12H	23.58	24.06	24.46	24.95	26.04	22.42	22.90	23.30	23.79	24.88
8H	4H	22.89	23.43	23.75	24.30	25.38	21.93	22.47	22.79	23.34	24.42
	6H	23.54	23.99	24.43	24.90	25.98	22.54	22.99	23.43	23.90	24.98
	8H	23.83	24.23	24.73	25.14	26.24	22.82	23.21	23.72	24.12	25.22
	12H	24.02	24.36	24.92	25.26	26.42	22.97	23.32	23.88	24.22	25.37
12H	4H	22.88	23.37	23.76	24.26	25.34	21.94	22.43	22.82	23.32	24.40
	6H	23.57	23.97	24.47	24.88	25.97	22.60	23.00	23.50	23.91	25.01
	8H	23.90	24.25	24.80	25.14	26.30	22.92	23.27	23.82	24.17	25.32