

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438881

Luminaire Tested: CB2-B-055U-030D-927-1D-UNV-STD-W-4

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1438881
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2405-119-1, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-B-055U-030D-927-1D-UNV-STD-W-4
Description: CORELITE BASIC SLOT LED LUMINAIRE, BATWING UPLIGHT
2-INCH APERTURE
DOWNLIGHT 300 LUMENS PER FOOT
UPLIGHT 550 LUMENS PER FOOT
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3996.7 lumens
Efficiency: N/A
Efficacy: 155.5 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.23
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 25.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1438881

CATALOG NUMBER: CB2-B-055U-030D-927-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P1438881

CATALOG NUMBER: CB2-B-055U-030D-927-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	76	74	62	60	58	46	45	44	32	31	30	24
2	85	78	72	67	76	70	65	61	55	51	48	41	39	37	28	27	26	20
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	25	23	22	17
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	21	19	15
5	65	54	46	40	58	48	42	37	38	34	30	29	26	23	20	18	17	13
6	60	48	40	35	53	43	37	32	34	30	26	26	23	20	18	16	15	11
7	55	43	36	30	49	39	32	28	31	26	23	24	20	18	17	15	13	10
8	51	39	32	27	45	35	29	24	28	24	20	22	18	16	15	13	12	9
9	47	36	28	24	42	32	26	22	26	21	18	20	17	14	14	12	11	8
10	44	33	26	21	40	30	23	19	24	19	16	18	15	13	13	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8339	8339	8339
5°	8268	8280	8338
10°	8220	8201	8196
15°	8091	8039	7972
20°	7963	7787	7677
25°	7749	7531	7320
30°	7534	7202	6931
35°	7289	6868	6540
40°	7026	6550	6168
45°	6764	6222	5806
50°	6525	5899	5455
55°	6234	5566	5120
60°	5901	5250	4790
65°	5543	4896	4455
70°	5154	4497	4033
75°	4690	4071	3654
80°	4193	3571	3310
85°	3217	2938	2418

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6764 cd/sqm



TEST NUMBER: P1438881

CATALOG NUMBER: CB2-B-055U-030D-927-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.0	1.1
10°-20°	125.5	3.1
20°-30°	180.4	4.5
30°-40°	202.8	5.1
40°-50°	195.9	4.9
50°-60°	165.5	4.1
60°-70°	118.9	3.0
70°-80°	65.0	1.6
80°-90°	17.3	0.4
90°-100°	32.8	0.8
100°-110°	203.4	5.1
110°-120°	512.9	12.8
120°-130°	616.6	15.4
130°-140°	559.0	14.0
140°-150°	445.8	11.2
150°-160°	304.1	7.6
160°-170°	160.8	4.0
170°-180°	44.8	1.1
0°-30°	351.0	8.8
0°-40°	553.8	13.9
0°-60°	915.2	22.9
0°-90°	1116.4	27.9
90°-120°	749.1	18.7
90°-150°	2370.6	59.3
90°-180°	2880.0	72.1
0°-180°	3996.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	479	479	479	479	479	
5°	473	479	474	474	477	45
15°	449	453	446	441	442	126
25°	403	404	392	383	381	186
35°	343	339	323	310	308	214
45°	275	269	253	239	236	212
55°	205	198	183	172	169	184
65°	134	130	119	110	108	133
75°	70	65	60	56	54	75
85°	16	15	15	13	12	19
90°	0	0	0	0	0	1
95°	17	43	13	9	9	22
105°	83	233	336	84	57	87
115°	144	317	767	714	544	141
125°	187	385	837	952	958	167
135°	234	426	839	982	1054	182
145°	300	448	792	954	1039	188
155°	365	457	705	849	894	168
165°	414	453	569	670	701	116
175°	438	444	452	459	469	41
180°	438	438	438	438	438	

TEST NUMBER: P1438881

CATALOG NUMBER: CB2-B-055U-030D-927-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	478.8	478.8	478.8	478.8	478.8
2.5°	475.5	481.3	477.0	477.6	478.5
5°	472.9	479.3	473.6	473.7	476.9
7.5°	469.5	475.6	468.4	467.1	470.1
10°	464.8	470.9	463.7	461.2	463.4
12.5°	458.7	464.5	457.6	453.6	455.4
15°	448.7	452.6	445.8	441.4	442.1
17.5°	437.8	440.3	430.4	426.7	426.0
20°	429.6	431.8	420.1	415.0	414.2
22.5°	419.1	420.9	408.7	402.3	401.3
25°	403.2	403.6	391.9	383.0	380.9
27.5°	386.7	385.5	372.5	362.0	359.2
30°	374.6	373.2	358.1	347.1	344.6
32.5°	361.7	359.2	344.1	332.1	329.6
35°	342.8	338.8	323.0	310.4	307.6
37.5°	322.5	318.1	302.5	288.9	285.6
40°	309.0	304.0	288.1	274.5	271.3
42.5°	295.5	289.9	273.8	260.1	256.6
45°	274.6	268.8	252.6	239.3	235.7
47.5°	254.6	247.3	231.5	218.3	214.7
50°	240.8	233.0	217.7	204.8	201.3
52.5°	226.8	218.6	204.0	191.6	188.1
55°	205.3	197.8	183.3	171.9	168.6
57.5°	184.0	176.8	163.6	152.6	149.5
60°	169.4	163.3	150.7	140.3	137.5
62.5°	155.3	149.8	137.8	128.3	125.4
65°	134.5	129.5	118.8	110.3	108.1
67.5°	114.4	109.4	100.7	93.1	90.6
70°	101.2	96.2	88.3	81.3	79.2
72.5°	88.6	83.3	76.9	70.5	68.9
75°	69.7	65.3	60.5	55.7	54.3
77.5°	52.9	48.8	45.2	41.9	41.5
80°	41.8	38.2	35.6	33.4	33.0
82.5°	31.2	28.5	26.8	25.1	25.1
85°	16.1	15.1	14.7	12.8	12.1
87.5°	4.7	4.7	4.1	3.5	3.5
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.5	7.5	3.0	3.0	3.0
95°	17.0	42.9	13.2	9.4	9.4
97.5°	35.5	102.8	71.4	19.2	16.6
100°	49.1	148.9	122.8	28.2	22.7
102.5°	62.7	189.1	193.9	44.7	34.8
105°	83.1	232.8	336.3	84.4	56.7
107.5°	103.2	261.3	515.4	174.1	105.1
110°	115.3	277.8	650.0	271.5	162.5



TEST NUMBER: P1438881

CATALOG NUMBER: CB2-B-055U-030D-927-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	127.3	294.4	724.0	435.2	280.4
115°	143.6	317.3	767.1	714.1	544.2
117.5°	157.2	338.2	804.1	883.1	833.2
120°	166.3	354.7	823.8	907.3	923.9
122.5°	175.3	366.7	834.4	916.7	948.1
125°	187.1	384.7	837.0	952.4	957.9
127.5°	198.8	398.3	849.5	985.2	987.8
130°	207.8	407.4	861.6	996.2	1016.5
132.5°	218.4	415.0	866.1	1002.5	1033.1
135°	234.3	426.4	838.9	982.2	1054.3
137.5°	254.3	434.6	812.8	981.7	1028.2
140°	266.4	436.4	799.2	1003.4	1007.1
142.5°	280.0	441.1	796.2	1001.0	1032.8
145°	300.4	448.2	791.7	954.2	1039.2
147.5°	320.8	452.7	774.3	902.6	976.8
150°	334.4	454.5	757.7	885.3	931.5
152.5°	348.0	456.3	736.5	874.6	913.3
155°	364.7	457.0	704.8	849.4	893.7
157.5°	382.0	454.8	666.6	803.3	851.8
160°	391.1	452.1	642.4	770.0	812.5
162.5°	400.2	450.8	621.2	726.3	776.2
165°	413.8	452.6	568.7	669.6	701.0
167.5°	422.9	450.9	519.6	602.2	646.6
170°	428.9	451.1	489.4	550.7	587.6
172.5°	433.4	443.8	471.2	503.5	528.7
175°	438.3	443.9	451.6	459.3	468.6
177.5°	439.9	442.8	436.8	435.4	438.3
180°	438.3	438.3	438.3	438.3	438.3



TEST NUMBER: P1438881
 CATALOG NUMBER: CB2-B-055U-030D-927-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.86	12.55	12.99	13.67	15.22	10.76	11.45	11.89	12.57	14.12
	3H	13.49	14.11	14.63	15.24	16.81	12.28	12.89	13.41	14.02	15.59
	4H	14.11	14.70	15.26	15.83	17.40	12.84	13.42	13.99	14.55	16.13
	6H	14.51	15.05	15.66	16.18	17.76	13.20	13.74	14.36	14.87	16.46
	8H	14.65	15.16	15.81	16.31	17.89	13.34	13.85	14.50	15.00	16.58
	12H	14.72	15.20	15.88	16.34	17.95	13.40	13.88	14.56	15.02	16.62
4H	2H	12.25	12.83	13.40	13.96	15.54	11.37	11.96	12.53	13.09	14.66
	3H	14.10	14.59	15.26	15.74	17.33	13.09	13.58	14.25	14.73	16.32
	4H	14.84	15.29	16.00	16.43	18.04	13.76	14.21	14.92	15.35	16.96
	6H	15.35	15.74	16.52	16.90	18.50	14.23	14.61	15.39	15.77	17.37
	8H	15.55	15.91	16.72	17.07	18.68	14.41	14.77	15.58	15.93	17.54
	12H	15.65	15.97	16.83	17.14	18.76	14.49	14.82	15.67	15.98	17.60
8H	4H	14.98	15.34	16.15	16.50	18.11	14.02	14.38	15.18	15.53	17.15
	6H	15.62	15.91	16.80	17.11	18.72	14.62	14.91	15.80	16.11	17.72
	8H	15.91	16.17	17.10	17.34	18.97	14.89	15.15	16.08	16.33	17.96
	12H	16.07	16.30	17.27	17.47	19.14	15.03	15.26	16.23	16.43	18.10
12H	4H	14.96	15.28	16.14	16.45	18.07	14.02	14.34	15.20	15.51	17.13
	6H	15.65	15.90	16.84	17.08	18.71	14.68	14.94	15.87	16.11	17.75
	8H	15.96	16.18	17.15	17.36	19.02	14.98	15.20	16.17	16.38	18.04