

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1056954

Luminaire Tested: CB2-055D-835-1D-UNV-STD-W-8

Issue Date: 7/31/2025

Test Information

Test Method: LM-79-2019
Report Number: P1056954
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 7/31/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-055D-835-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE
2-INCH APERTURE
DOWNLIGHT 550 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4417.3 lumens
Efficiency: N/A
Efficacy: 121.0 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')
CIE Type: Direct


Input Watts (W): 36.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1056954

CATALOG NUMBER: CB2-055D-835-1D-UNV-STD-W-8

Luminous Intensity Polar Plot



TEST NUMBER: P1056954

CATALOG NUMBER: CB2-055D-835-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	109	105	101	97	107	103	99	95	98	95	92	94	92	90	91	89	87
2	100	92	86	80	97	90	84	79	87	82	77	83	79	76	80	77	74
3	91	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63
4	84	73	64	58	82	71	63	57	69	62	56	66	60	56	64	59	55
5	78	65	56	50	76	64	56	50	62	55	49	60	54	49	58	53	48
6	72	59	50	44	70	58	50	44	56	49	43	55	48	43	53	47	43
7	67	54	45	39	65	53	45	39	51	44	39	50	43	38	49	43	38
8	62	49	41	35	61	48	41	35	47	40	35	46	39	35	45	39	34
9	58	45	37	32	57	45	37	32	44	37	32	42	36	31	41	36	31
10	55	42	34	29	54	41	34	29	40	34	29	39	33	29	39	33	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16497	16497	16497
5°	16357	16382	16496
10°	16264	16225	16213
15°	16006	15901	15771
20°	15754	15405	15190
25°	15331	14899	14481
30°	14907	14250	13710
35°	14418	13585	12937
40°	13900	12960	12202
45°	13380	12309	11486
50°	12910	11673	10788
55°	12332	11011	10130
60°	11671	10382	9473
65°	10969	9683	8818
70°	10193	8902	7977
75°	9273	8052	7224
80°	8295	7056	6545
85°	6375	5795	4786

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13380 cd/sqm

TEST NUMBER: P1056954

CATALOG NUMBER: CB2-055D-835-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.1	4.0
10°-20°	496.6	11.2
20°-30°	714.0	16.2
30°-40°	802.5	18.2
40°-50°	775.2	17.5
50°-60°	655.0	14.8
60°-70°	470.5	10.7
70°-80°	257.1	5.8
80°-90°	68.3	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1388.7	31.4
0°-40°	2191.2	49.6
0°-60°	3621.4	82.0
0°-90°	4417.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4417.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1894	1894	1894	1894	1894	
5°	1871	1897	1874	1874	1887	178
15°	1775	1791	1764	1746	1749	500
25°	1596	1597	1550	1516	1507	734
35°	1356	1341	1278	1228	1217	847
45°	1086	1064	999	947	933	839
55°	812	782	725	680	667	726
65°	532	512	470	436	428	528
75°	276	259	239	220	215	295
85°	64	60	58	51	48	79
90°	0	0	0	0	0	

TEST NUMBER: P1056954

CATALOG NUMBER: CB2-055D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1894.3	1894.3	1894.3	1894.3	1894.3
2.5°	1881.5	1904.2	1887.3	1889.7	1893.1
5°	1871.1	1896.6	1874.0	1874.3	1887.0
7.5°	1857.7	1881.8	1853.4	1848.1	1860.0
10°	1839.2	1863.3	1834.8	1824.9	1833.4
12.5°	1814.8	1837.8	1810.4	1794.7	1802.0
15°	1775.3	1790.9	1763.7	1746.4	1749.2
17.5°	1732.4	1742.1	1702.8	1688.3	1685.4
20°	1699.9	1708.4	1662.2	1641.8	1639.0
22.5°	1658.1	1665.5	1617.0	1591.9	1587.9
25°	1595.5	1596.9	1550.5	1515.5	1507.0
27.5°	1529.9	1525.4	1473.9	1432.5	1421.4
30°	1482.4	1476.7	1417.1	1373.3	1363.4
32.5°	1431.3	1421.1	1361.4	1314.2	1304.2
35°	1356.2	1340.6	1277.8	1228.3	1216.9
37.5°	1276.1	1258.5	1196.9	1142.9	1130.2
40°	1222.7	1202.9	1140.0	1086.1	1073.3
42.5°	1169.3	1147.2	1083.2	1029.2	1015.3
45°	1086.4	1063.7	999.4	946.8	932.6
47.5°	1007.5	978.5	916.1	863.9	849.7
50°	952.9	921.7	861.6	810.5	796.3
52.5°	897.2	864.9	807.0	758.3	744.1
55°	812.2	782.5	725.2	680.0	667.2
57.5°	728.1	699.5	647.2	604.0	591.5
60°	670.1	646.0	596.1	555.3	543.9
62.5°	614.4	592.6	545.1	507.7	496.3
65°	532.3	512.5	469.9	436.4	427.9
67.5°	452.5	432.7	398.3	368.2	358.5
70°	400.3	380.5	349.6	321.8	313.3
72.5°	350.4	329.4	304.3	278.9	272.7
75°	275.6	258.6	239.3	220.3	214.7
77.5°	209.4	193.0	179.0	165.6	164.2
80°	165.4	151.2	140.7	132.0	130.5
82.5°	123.6	112.8	105.9	99.5	99.2
85°	63.8	59.6	58.0	50.7	47.9
87.5°	18.6	18.6	16.2	13.9	13.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)