

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1056952

Luminaire Tested: CB2-030D-840-1D-UNV-STD-W-8

Issue Date: 7/31/2025

Test Information

Test Method: LM-79-2019
Report Number: P1056952
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 7/31/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-030D-840-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE
2-INCH APERTURE
DOWNLIGHT 300 LUMENS PER FOOT
DIRECT ONLY
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2281.4 lumens
Efficiency: N/A
Efficacy: 124.7 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')
CIE Type: Direct


Input Watts (W): 18.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1056952

CATALOG NUMBER: CB2-030D-840-1D-UNV-STD-W-8

Luminous Intensity Polar Plot



TEST NUMBER: P1056952

CATALOG NUMBER: CB2-030D-840-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	109	105	101	97	107	103	99	95	98	95	92	94	92	90	91	89	87
2	100	92	86	80	97	90	84	79	87	82	77	83	79	76	80	77	74
3	91	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63
4	84	73	64	58	82	71	63	57	69	62	56	66	60	56	64	59	55
5	78	65	56	50	76	64	56	50	62	55	49	60	54	49	58	53	48
6	72	59	50	44	70	58	50	44	56	49	43	55	48	43	53	47	43
7	67	54	45	39	65	53	45	39	51	44	39	50	43	38	49	43	38
8	62	49	41	35	61	48	41	35	47	40	35	46	39	35	45	39	34
9	58	45	37	32	57	45	37	32	44	37	32	42	36	31	41	36	31
10	55	42	34	29	54	41	34	29	40	34	29	39	33	29	39	33	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8521	8521	8521
5°	8448	8461	8520
10°	8400	8380	8373
15°	8267	8213	8145
20°	8137	7956	7845
25°	7918	7695	7479
30°	7699	7360	7081
35°	7446	7017	6682
40°	7179	6694	6303
45°	6910	6356	5933
50°	6668	6029	5572
55°	6369	5688	5232
60°	6028	5363	4893
65°	5665	5001	4554
70°	5266	4596	4120
75°	4788	4159	3732
80°	4283	3646	3380
85°	3297	2998	2468

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6910 cd/sqm

TEST NUMBER: P1056952

CATALOG NUMBER: CB2-030D-840-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.0	4.0
10°-20°	256.5	11.2
20°-30°	368.8	16.2
30°-40°	414.5	18.2
40°-50°	400.4	17.5
50°-60°	338.3	14.8
60°-70°	243.0	10.7
70°-80°	132.8	5.8
80°-90°	35.3	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	717.2	31.4
0°-40°	1131.7	49.6
0°-60°	1870.4	82.0
0°-90°	2281.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2281.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	978	978	978	978	978	
5°	966	980	968	968	975	92
15°	917	925	911	902	903	258
25°	824	825	801	783	778	379
35°	700	692	660	634	628	438
45°	561	549	516	489	482	433
55°	420	404	375	351	345	375
65°	275	265	243	225	221	273
75°	142	134	124	114	111	152
85°	33	31	30	26	25	41
90°	0	0	0	0	0	

TEST NUMBER: P1056952

CATALOG NUMBER: CB2-030D-840-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	978.4	978.4	978.4	978.4	978.4
2.5°	971.8	983.5	974.8	976.0	977.8
5°	966.4	979.6	967.9	968.0	974.6
7.5°	959.5	971.9	957.2	954.5	960.7
10°	949.9	962.3	947.6	942.5	946.9
12.5°	937.3	949.2	935.1	926.9	930.7
15°	916.9	925.0	910.9	902.0	903.4
17.5°	894.8	899.7	879.5	872.0	870.5
20°	878.0	882.4	858.5	848.0	846.5
22.5°	856.4	860.2	835.1	822.2	820.1
25°	824.0	824.8	800.8	782.7	778.3
27.5°	790.2	787.8	761.3	739.9	734.1
30°	765.6	762.7	731.9	709.3	704.2
32.5°	739.2	734.0	703.1	678.7	673.6
35°	700.4	692.4	660.0	634.4	628.5
37.5°	659.1	650.0	618.2	590.3	583.7
40°	631.5	621.3	588.8	560.9	554.4
42.5°	603.9	592.5	559.4	531.6	524.4
45°	561.1	549.4	516.1	489.0	481.7
47.5°	520.3	505.4	473.1	446.2	438.8
50°	492.2	476.1	445.0	418.6	411.3
52.5°	463.4	446.7	416.8	391.6	384.3
55°	419.5	404.1	374.6	351.2	344.6
57.5°	376.1	361.3	334.3	311.9	305.5
60°	346.1	333.6	307.9	286.8	280.9
62.5°	317.3	306.1	281.5	262.2	256.4
65°	274.9	264.7	242.7	225.4	221.0
67.5°	233.7	223.5	205.7	190.2	185.2
70°	206.8	196.5	180.5	166.2	161.8
72.5°	181.0	170.1	157.2	144.1	140.8
75°	142.3	133.5	123.6	113.8	110.9
77.5°	108.2	99.7	92.4	85.5	84.8
80°	85.4	78.1	72.7	68.2	67.4
82.5°	63.8	58.3	54.7	51.4	51.2
85°	33.0	30.8	30.0	26.2	24.7
87.5°	9.6	9.6	8.4	7.2	7.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)