

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438690

Luminaire Tested: CB2-055U-120D-927-1D-UNV-STD-W-8

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1438690
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2506-466-1, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-055U-120D-927-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE, OPEN UPLIGHT
2-INCH APERTURE
DOWNLIGHT 1200 LUMENS PER FOOT
UPLIGHT 550 LUMENS PER FOOT
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14315.7 lumens
Efficiency: N/A
Efficacy: 113.3 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 126.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1438690

CATALOG NUMBER: CB2-055U-120D-927-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P1438690

CATALOG NUMBER: CB2-055U-120D-927-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	62	61	59	55
2	92	85	79	74	87	80	75	70	71	67	63	63	59	57	55	52	50	46
3	85	75	68	62	79	71	64	59	63	58	53	56	52	48	49	46	43	40
4	78	67	59	52	73	63	56	50	56	50	46	50	45	42	44	40	37	34
5	71	60	51	45	67	56	49	43	50	44	40	45	40	36	40	36	33	30
6	66	54	45	39	62	51	43	38	46	39	35	41	36	32	36	32	29	26
7	61	49	40	35	57	46	39	34	41	35	31	37	32	28	33	29	26	23
8	57	44	36	31	53	42	35	30	38	32	28	34	29	25	30	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	27	23	28	24	21	19
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	34613	34613	34613
5°	34320	34373	34613
10°	34125	34044	34017
15°	33585	33365	33091
20°	33056	32323	31871
25°	32168	31261	30384
30°	31277	29899	28767
35°	30251	28505	27146
40°	29166	27194	25603
45°	28074	25825	24101
50°	27090	24491	22636
55°	25877	23104	21255
60°	24489	21786	19878
65°	23015	20318	18500
70°	21388	18674	16739
75°	19455	16898	15155
80°	17397	14805	13736
85°	13379	12160	10032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 28074 cd/sqm



TEST NUMBER: P1438690

CATALOG NUMBER: CB2-055U-120D-927-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	373.8	2.6
10°-20°	1041.9	7.3
20°-30°	1498.1	10.5
30°-40°	1683.8	11.8
40°-50°	1626.6	11.4
50°-60°	1374.3	9.6
60°-70°	987.1	6.9
70°-80°	539.5	3.8
80°-90°	143.4	1.0
90°-100°	30.9	0.2
100°-110°	196.3	1.4
110°-120°	623.8	4.4
120°-130°	905.2	6.3
130°-140°	973.6	6.8
140°-150°	916.6	6.4
150°-160°	746.7	5.2
160°-170°	486.0	3.4
170°-180°	168.0	1.2
0°-30°	2913.7	20.4
0°-40°	4597.5	32.1
0°-60°	7598.4	53.1
0°-90°	9268.5	64.7
90°-120°	851.0	5.9
90°-150°	3646.4	25.5
90°-180°	5047.0	35.3
0°-180°	14315.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3975	3975	3975	3975	3975	
5°	3926	3980	3932	3933	3959	373
15°	3725	3758	3701	3664	3670	1050
25°	3348	3351	3253	3180	3162	1541
35°	2846	2813	2681	2577	2553	1778
45°	2280	2232	2097	1987	1957	1761
55°	1704	1642	1522	1427	1400	1524
65°	1117	1075	986	916	898	1108
75°	578	542	502	462	450	619
85°	134	125	122	106	100	159
90°	0	0	0	1	1	8
95°	70	20	22	14	13	89
105°	369	382	38	45	47	388
115°	698	713	719	728	417	686
125°	991	1008	1009	1026	1039	886
135°	1247	1262	1259	1268	1284	961
145°	1459	1470	1460	1462	1481	912
155°	1620	1630	1613	1609	1632	747
165°	1728	1733	1715	1708	1725	488
175°	1779	1783	1760	1748	1757	169
180°	1770	1770	1770	1770	1770	



TEST NUMBER: P1438690

CATALOG NUMBER: CB2-055U-120D-927-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3974.6	3974.6	3974.6	3974.6	3974.6
2.5°	3947.8	3995.4	3960.0	3965.0	3972.2
5°	3925.9	3979.5	3932.0	3932.6	3959.4
7.5°	3897.9	3948.5	3888.8	3877.8	3902.8
10°	3859.0	3909.5	3849.8	3828.9	3846.8
12.5°	3807.8	3856.0	3798.7	3765.6	3781.1
15°	3725.1	3757.8	3700.7	3664.3	3670.3
17.5°	3635.0	3655.2	3572.9	3542.3	3536.4
20°	3566.8	3584.7	3487.7	3444.9	3439.0
22.5°	3479.2	3494.6	3392.7	3340.2	3331.9
25°	3347.7	3350.7	3253.3	3179.9	3162.0
27.5°	3210.1	3200.6	3092.6	3005.7	2982.5
30°	3110.3	3098.4	2973.3	2881.6	2860.7
32.5°	3003.2	2981.7	2856.5	2757.4	2736.6
35°	2845.5	2812.8	2681.2	2577.2	2553.4
37.5°	2677.5	2640.6	2511.4	2398.2	2371.4
40°	2565.5	2523.9	2392.1	2278.9	2252.1
42.5°	2453.5	2407.1	2272.8	2159.5	2130.3
45°	2279.5	2231.9	2096.9	1986.6	1956.9
47.5°	2113.9	2053.2	1922.2	1812.5	1782.8
50°	1999.5	1934.0	1807.7	1700.6	1670.8
52.5°	1882.6	1814.8	1693.3	1591.0	1561.2
55°	1704.3	1641.8	1521.7	1426.7	1399.9
57.5°	1527.8	1467.6	1357.9	1267.3	1241.1
60°	1406.0	1355.4	1250.8	1165.1	1141.3
62.5°	1289.2	1243.3	1143.7	1065.2	1041.4
65°	1116.9	1075.2	986.0	915.6	897.8
67.5°	949.5	907.9	835.7	772.5	752.3
70°	840.0	798.3	733.4	675.2	657.4
72.5°	735.3	691.2	638.5	585.2	572.1
75°	578.2	542.5	502.2	462.3	450.4
77.5°	439.5	404.9	375.5	347.5	344.5
80°	346.9	317.2	295.2	276.9	273.9
82.5°	259.3	236.7	222.2	208.8	208.2
85°	133.9	125.0	121.7	106.4	100.4
87.5°	39.0	39.0	34.1	29.5	29.5
90°	0.0	0.0	0.0	1.3	1.3
92.5°	19.5	7.4	5.1	7.4	7.4
95°	70.4	20.3	21.8	14.1	12.8
97.5°	146.2	32.8	31.5	34.6	35.8
100°	203.5	67.1	34.6	39.7	41.0
102.5°	267.0	252.7	35.6	42.8	45.1
105°	368.6	382.4	38.4	44.9	47.4
107.5°	468.4	482.2	178.7	46.4	48.9
110°	535.0	548.8	565.7	47.4	49.9

TEST NUMBER: P1438690

CATALOG NUMBER: CB2-055U-120D-927-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	597.5	614.2	627.2	105.5	52.0
115°	697.5	712.6	719.3	727.6	417.2
117.5°	785.9	804.4	812.0	826.4	840.4
120°	847.3	864.8	870.3	884.8	899.8
122.5°	907.7	923.2	926.6	943.1	957.1
125°	990.6	1008.2	1008.6	1025.5	1039.3
127.5°	1073.6	1088.6	1087.9	1100.5	1115.8
130°	1128.9	1138.9	1139.1	1149.7	1166.0
132.5°	1174.9	1189.0	1189.3	1197.8	1214.1
135°	1246.6	1261.6	1259.4	1267.5	1283.7
137.5°	1313.9	1328.5	1324.4	1331.2	1348.0
140°	1358.0	1370.5	1364.4	1371.2	1390.0
142.5°	1398.9	1411.4	1402.3	1408.1	1427.9
145°	1459.1	1470.3	1460.4	1462.1	1480.8
147.5°	1512.6	1523.6	1511.6	1513.2	1530.8
150°	1547.4	1557.4	1542.3	1544.0	1561.5
152.5°	1578.1	1587.1	1570.9	1570.6	1591.2
155°	1620.4	1630.4	1612.7	1609.3	1631.9
157.5°	1658.7	1668.0	1650.3	1647.9	1665.4
160°	1684.3	1690.6	1672.8	1669.4	1686.9
162.5°	1701.8	1709.0	1691.3	1685.8	1703.3
165°	1727.9	1732.9	1715.1	1707.8	1725.3
167.5°	1750.4	1756.1	1733.2	1726.8	1745.5
170°	1763.7	1767.5	1744.5	1736.0	1754.7
172.5°	1771.9	1774.6	1751.7	1742.0	1754.7
175°	1779.1	1782.8	1759.9	1748.5	1757.3
177.5°	1780.3	1782.3	1765.0	1755.1	1770.1
180°	1770.1	1770.1	1770.1	1770.1	1770.1



TEST NUMBER: P1438690
 CATALOG NUMBER: CB2-055U-120D-927-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.58	21.57	21.40	22.42	23.46	19.48	20.48	20.30	21.32	22.36
	3H	22.23	23.13	23.07	23.98	25.05	21.02	21.91	21.85	22.76	23.84
	4H	22.87	23.71	23.72	24.57	25.65	21.60	22.44	22.45	23.30	24.38
	6H	23.28	24.06	24.14	24.92	26.02	21.97	22.75	22.84	23.62	24.72
	8H	23.43	24.17	24.30	25.06	26.15	22.12	22.86	22.99	23.74	24.84
	12H	23.51	24.21	24.39	25.09	26.21	22.19	22.89	23.06	23.77	24.89
4H	2H	21.00	21.85	21.86	22.71	23.79	20.13	20.97	20.99	21.83	22.92
	3H	22.89	23.59	23.75	24.48	25.58	21.88	22.58	22.74	23.47	24.57
	4H	23.64	24.28	24.52	25.17	26.29	22.56	23.20	23.44	24.08	25.21
	6H	24.16	24.72	25.06	25.63	26.76	23.04	23.59	23.93	24.50	25.63
	8H	24.37	24.89	25.27	25.80	26.94	23.23	23.75	24.13	24.66	25.80
	12H	24.48	24.95	25.40	25.88	27.02	23.33	23.79	24.24	24.72	25.86
8H	4H	23.80	24.32	24.70	25.23	26.37	22.84	23.36	23.74	24.26	25.40
	6H	24.45	24.88	25.38	25.83	26.97	23.45	23.88	24.37	24.83	25.97
	8H	24.74	25.12	25.68	26.06	27.22	23.73	24.10	24.66	25.05	26.20
	12H	24.92	25.26	25.86	26.19	27.40	23.88	24.21	24.82	25.15	26.36
12H	4H	23.79	24.25	24.71	25.18	26.33	22.85	23.31	23.77	24.24	25.39
	6H	24.48	24.86	25.42	25.80	26.96	23.51	23.89	24.45	24.83	25.99
	8H	24.80	25.14	25.74	26.07	27.28	23.83	24.16	24.76	25.09	26.30