

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1056959

Luminaire Tested: CB2-0U-120D-830-1D-UNV-STD-W-8

Issue Date: 7/31/2025

Test Information

Test Method: LM-79-2019
Report Number: P1056959
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 7/31/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-0U-120D-830-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE
2-INCH APERTURE
DOWNLIGHT 1200 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8797.4 lumens
Efficiency: N/A
Efficacy: 99.6 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')
CIE Type: Direct


Input Watts (W): 88.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1056959

CATALOG NUMBER: CB2-0U-120D-830-1D-UNV-STD-W-8

Luminous Intensity Polar Plot



TEST NUMBER: P1056959

CATALOG NUMBER: CB2-OU-120D-830-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	105	101	97	107	103	99	95	98	95	92		94	92	90		91
2	100	92	86	80	97	90	84	79	87	82	77		83	79	76		80
3	91	81	74	67	89	80	73	67	77	71	66		74	69	64		72
4	84	73	64	58	82	71	63	57	69	62	56		66	60	56		64
5	78	65	56	50	76	64	56	50	62	55	49		60	54	49		58
6	72	59	50	44	70	58	50	44	56	49	43		55	48	43		53
7	67	54	45	39	65	53	45	39	51	44	39		50	43	38		49
8	62	49	41	35	61	48	41	35	47	40	35		46	39	35		45
9	58	45	37	32	57	45	37	32	44	37	32		42	36	31		41
10	55	42	34	29	54	41	34	29	40	34	29		39	33	29		39

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	32854	32854	32854
5°	32576	32627	32854
10°	32391	32314	32288
15°	31878	31669	31410
20°	31375	30679	30251
25°	30533	29672	28840
30°	29687	28381	27306
35°	28714	27056	25766
40°	27684	25812	24301
45°	26647	24512	22876
50°	25713	23248	21486
55°	24562	21929	20175
60°	23245	20680	18868
65°	21845	19286	17561
70°	20301	17727	15889
75°	18469	16037	14384
80°	16515	14052	13039
85°	12700	11541	9522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26647 cd/sqm

TEST NUMBER: P1056959

CATALOG NUMBER: CB2-0U-120D-830-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	354.8	4.0
10°-20°	988.9	11.2
20°-30°	1421.9	16.2
30°-40°	1598.2	18.2
40°-50°	1543.9	17.5
50°-60°	1304.5	14.8
60°-70°	937.0	10.7
70°-80°	512.1	5.8
80°-90°	136.0	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2765.7	31.4
0°-40°	4363.9	49.6
0°-60°	7212.3	82.0
0°-90°	8797.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8797.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3773	3773	3773	3773	3773	
5°	3726	3777	3732	3733	3758	354
15°	3536	3567	3513	3478	3484	997
25°	3178	3180	3088	3018	3001	1463
35°	2701	2670	2545	2446	2424	1687
45°	2164	2118	1990	1886	1857	1672
55°	1618	1558	1444	1354	1329	1446
65°	1060	1021	936	869	852	1051
75°	549	515	477	439	428	587
85°	127	119	116	101	95	156
90°	0	0	0	0	0	

TEST NUMBER: P1056959

CATALOG NUMBER: CB2-OU-120D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3772.6	3772.6	3772.6	3772.6	3772.6
2.5°	3747.2	3792.4	3758.8	3763.5	3770.3
5°	3726.4	3777.3	3732.2	3732.8	3758.2
7.5°	3699.8	3747.9	3691.2	3680.7	3704.5
10°	3662.9	3710.9	3654.2	3634.4	3651.3
12.5°	3614.3	3660.1	3605.7	3574.2	3588.9
15°	3535.8	3566.8	3512.6	3478.1	3483.8
17.5°	3450.3	3469.5	3391.3	3362.3	3356.7
20°	3385.5	3402.5	3310.4	3269.9	3264.2
22.5°	3302.4	3317.0	3220.3	3170.4	3162.5
25°	3177.6	3180.4	3088.0	3018.3	3001.4
27.5°	3047.0	3038.0	2935.5	2852.9	2830.9
30°	2952.2	2940.9	2822.3	2735.1	2715.4
32.5°	2850.6	2830.2	2711.3	2617.3	2597.5
35°	2700.9	2669.9	2544.9	2446.2	2423.6
37.5°	2541.5	2506.4	2383.7	2276.3	2250.9
40°	2435.2	2395.6	2270.5	2163.1	2137.6
42.5°	2328.9	2284.8	2157.3	2049.8	2022.1
45°	2163.6	2118.4	1990.3	1885.7	1857.4
47.5°	2006.5	1948.9	1824.5	1720.4	1692.2
50°	1897.9	1835.7	1715.9	1614.1	1585.9
52.5°	1786.9	1722.5	1607.3	1510.1	1481.9
55°	1617.7	1558.4	1444.3	1354.2	1328.8
57.5°	1450.1	1393.1	1288.9	1202.9	1178.0
60°	1334.6	1286.6	1187.3	1105.9	1083.3
62.5°	1223.6	1180.2	1085.6	1011.1	988.5
65°	1060.1	1020.6	935.9	869.1	852.2
67.5°	901.3	861.7	793.2	733.3	714.1
70°	797.3	757.7	696.2	640.9	624.0
72.5°	697.9	656.1	606.0	555.5	543.1
75°	548.9	515.0	476.6	438.8	427.5
77.5°	417.1	384.4	356.5	329.8	327.0
80°	329.3	301.1	280.2	262.8	260.0
82.5°	246.1	224.7	210.9	198.2	197.6
85°	127.1	118.6	115.5	101.0	95.3
87.5°	37.0	37.0	32.4	27.7	27.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)