

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438882

Luminaire Tested: CB2-B-055U-030D-927-1D-UNV-STD-W-8

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1438882
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2405-119-1, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-B-055U-030D-927-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE, BATWING UPLIGHT
2-INCH APERTURE
DOWNLIGHT 300 LUMENS PER FOOT
UPLIGHT 550 LUMENS PER FOOT
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7993.3 lumens
Efficiency: N/A
Efficacy: 142.0 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 56.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1438882

CATALOG NUMBER: CB2-B-055U-030D-927-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P1438882

CATALOG NUMBER: CB2-B-055U-030D-927-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28																				
1	93	89	85	82	83	80	76	74	62	60	58	46	45	44	32	31	30	24																				
2	85	78	72	67	76	70	65	61	55	51	48	41	39	37	28	27	26	20																				
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	25	23	22	17																				
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	21	19	15																				
5	65	54	46	40	58	48	42	37	38	34	30	29	26	23	20	18	17	13																				
6	60	48	40	35	53	43	37	32	34	30	26	26	23	20	18	16	15	11																				
7	55	43	36	30	49	39	32	28	31	26	23	24	20	18	17	15	13	10																				
8	51	39	32	27	45	35	29	24	28	24	20	22	18	16	15	13	12	9																				
9	47	36	28	24	42	32	26	22	26	21	18	20	17	14	14	12	11	8																				
10	44	33	26	21	40	30	23	19	24	19	16	18	15	13	13	11	10	8																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8339	8339	8339
5°	8268	8280	8338
10°	8220	8202	8195
15°	8091	8038	7972
20°	7964	7787	7678
25°	7750	7531	7320
30°	7535	7203	6931
35°	7288	6867	6539
40°	7027	6552	6167
45°	6763	6221	5806
50°	6526	5900	5453
55°	6234	5566	5121
60°	5899	5248	4788
65°	5545	4894	4457
70°	5154	4499	4033
75°	4687	4071	3651
80°	4193	3566	3310
85°	3227	2928	2418

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6763 cd/sqm



TEST NUMBER: P1438882

CATALOG NUMBER: CB2-B-055U-030D-927-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.0	1.1
10°-20°	251.0	3.1
20°-30°	360.9	4.5
30°-40°	405.6	5.1
40°-50°	391.8	4.9
50°-60°	331.1	4.1
60°-70°	237.8	3.0
70°-80°	130.0	1.6
80°-90°	34.5	0.4
90°-100°	65.7	0.8
100°-110°	406.8	5.1
110°-120°	1025.9	12.8
120°-130°	1233.2	15.4
130°-140°	1118.1	14.0
140°-150°	891.6	11.2
150°-160°	608.2	7.6
160°-170°	321.6	4.0
170°-180°	89.5	1.1
0°-30°	701.9	8.8
0°-40°	1107.6	13.9
0°-60°	1830.5	22.9
0°-90°	2232.8	27.9
90°-120°	1498.3	18.7
90°-150°	4741.2	59.3
90°-180°	5761.0	72.1
0°-180°	7993.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	958	958	958	958	958	
5°	946	959	947	947	954	90
15°	897	905	892	883	884	253
25°	806	807	784	766	762	371
35°	686	678	646	621	615	428
45°	549	538	505	479	471	424
55°	411	396	367	344	337	367
65°	269	259	238	221	216	267
75°	139	131	121	111	108	149
85°	32	30	29	26	24	38
90°	0	0	0	0	0	3
95°	34	86	26	19	19	43
105°	166	466	673	169	113	175
115°	287	634	1534	1428	1088	282
125°	374	770	1674	1905	1916	335
135°	469	853	1678	1964	2109	364
145°	601	896	1583	1908	2078	376
155°	729	914	1410	1699	1787	336
165°	828	905	1137	1339	1402	232
175°	877	888	903	919	937	83
180°	877	877	877	877	877	



TEST NUMBER: P1438882

CATALOG NUMBER: CB2-B-055U-030D-927-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	957.5	957.5	957.5	957.5	957.5
2.5°	951.1	962.5	954.0	955.2	956.9
5°	945.8	958.7	947.2	947.4	953.8
7.5°	939.0	951.2	936.8	934.2	940.2
10°	929.6	941.8	927.5	922.4	926.7
12.5°	917.3	928.9	915.1	907.2	910.9
15°	897.4	905.3	891.5	882.8	884.2
17.5°	875.7	880.6	860.7	853.4	851.9
20°	859.3	863.6	840.2	829.9	828.5
22.5°	838.2	841.9	817.3	804.7	802.7
25°	806.5	807.2	783.8	766.1	761.8
27.5°	773.3	771.0	745.0	724.1	718.5
30°	749.3	746.4	716.3	694.2	689.2
32.5°	723.5	718.3	688.1	664.3	659.3
35°	685.5	677.6	645.9	620.9	615.1
37.5°	645.0	636.1	605.0	577.7	571.3
40°	618.1	608.0	576.3	549.0	542.5
42.5°	591.1	579.9	547.5	520.2	513.2
45°	549.1	537.7	505.1	478.6	471.4
47.5°	509.3	494.6	463.1	436.7	429.5
50°	481.7	465.9	435.5	409.7	402.5
52.5°	453.5	437.2	407.9	383.3	376.1
55°	410.6	395.5	366.6	343.7	337.3
57.5°	368.0	353.6	327.1	305.3	299.0
60°	338.7	326.5	301.3	280.7	274.9
62.5°	310.6	299.5	275.5	256.6	250.9
65°	269.1	259.0	237.5	220.6	216.3
67.5°	228.7	218.7	201.3	186.1	181.2
70°	202.4	192.3	176.7	162.7	158.4
72.5°	177.1	166.5	153.8	141.0	137.8
75°	139.3	130.7	121.0	111.4	108.5
77.5°	105.9	97.6	90.5	83.7	83.0
80°	83.6	76.4	71.1	66.7	66.0
82.5°	62.5	57.0	53.5	50.3	50.1
85°	32.3	30.1	29.3	25.6	24.2
87.5°	9.4	9.4	8.2	7.0	7.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	9.1	15.0	6.0	6.0	6.0
95°	34.0	85.7	26.5	18.9	18.9
97.5°	71.0	205.5	142.8	38.4	33.3
100°	98.2	297.8	245.6	56.4	45.3
102.5°	125.5	378.2	387.7	89.5	69.5
105°	166.3	465.6	672.6	168.8	113.4
107.5°	206.3	522.6	1030.9	348.3	210.1
110°	230.5	555.7	1299.9	543.0	325.0



TEST NUMBER: P1438882

CATALOG NUMBER: CB2-B-055U-030D-927-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	254.7	588.7	1448.1	870.4	560.8
115°	287.2	634.5	1534.2	1428.2	1088.3
117.5°	314.4	676.5	1608.3	1766.2	1666.5
120°	332.5	709.4	1647.6	1814.6	1847.9
122.5°	350.7	733.5	1668.7	1833.4	1896.2
125°	374.1	769.5	1674.0	1904.8	1915.9
127.5°	397.5	796.6	1699.0	1970.4	1975.6
130°	415.7	814.7	1723.2	1992.4	2033.0
132.5°	436.8	830.0	1732.2	2004.9	2066.3
135°	468.6	852.8	1677.8	1964.5	2108.6
137.5°	508.6	869.3	1625.7	1963.3	2056.4
140°	532.8	872.7	1598.5	2006.7	2014.1
142.5°	560.0	882.2	1592.4	2002.0	2065.5
145°	600.8	896.4	1583.3	1908.4	2078.4
147.5°	641.6	905.5	1548.6	1805.1	1953.7
150°	668.9	909.0	1515.3	1770.6	1863.0
152.5°	696.1	912.6	1473.0	1749.1	1826.7
155°	729.3	914.1	1409.5	1698.7	1787.4
157.5°	764.1	909.7	1333.2	1606.7	1703.5
160°	782.2	904.2	1284.8	1539.9	1624.9
162.5°	800.4	901.6	1242.5	1452.6	1552.3
165°	827.6	905.2	1137.4	1339.1	1402.0
167.5°	845.7	901.9	1039.2	1204.4	1293.1
170°	857.8	902.1	978.7	1101.3	1175.2
172.5°	866.9	887.6	942.4	1007.1	1057.3
175°	876.7	887.8	903.1	918.7	937.2
177.5°	879.7	885.6	873.7	870.8	876.7
180°	876.7	876.7	876.7	876.7	876.7



TEST NUMBER: P1438882

CATALOG NUMBER: CB2-B-055U-030D-927-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.86	12.55	12.99	13.67	15.22	10.76	11.45	11.89	12.57	14.12
	3H	13.49	14.11	14.63	15.24	16.81	12.28	12.89	13.41	14.02	15.59
	4H	14.11	14.70	15.26	15.83	17.40	12.84	13.43	13.99	14.55	16.13
	6H	14.51	15.04	15.66	16.17	17.76	13.20	13.74	14.36	14.87	16.46
	8H	14.65	15.16	15.81	16.31	17.89	13.34	13.85	14.50	15.00	16.58
	12H	14.72	15.20	15.88	16.34	17.95	13.40	13.88	14.56	15.02	16.62
4H	2H	12.25	12.83	13.40	13.96	15.54	11.37	11.96	12.53	13.09	14.66
	3H	14.10	14.59	15.26	15.74	17.33	13.09	13.58	14.25	14.73	16.32
	4H	14.84	15.29	16.00	16.43	18.04	13.76	14.21	14.92	15.35	16.96
	6H	15.35	15.73	16.52	16.90	18.50	14.23	14.61	15.39	15.77	17.37
	8H	15.55	15.91	16.72	17.07	18.68	14.41	14.77	15.58	15.93	17.54
	12H	15.65	15.97	16.83	17.14	18.76	14.49	14.82	15.67	15.98	17.60
8H	4H	14.98	15.34	16.15	16.50	18.11	14.02	14.38	15.19	15.53	17.15
	6H	15.62	15.91	16.80	17.11	18.72	14.62	14.91	15.80	16.11	17.72
	8H	15.91	16.16	17.10	17.34	18.97	14.89	15.15	16.08	16.32	17.96
	12H	16.07	16.30	17.27	17.47	19.14	15.03	15.26	16.23	16.43	18.10
12H	4H	14.96	15.28	16.14	16.45	18.07	14.02	14.34	15.20	15.51	17.13
	6H	15.65	15.90	16.84	17.08	18.71	14.68	14.94	15.87	16.11	17.75
	8H	15.96	16.18	17.15	17.36	19.02	14.98	15.20	16.17	16.38	18.04