

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438962

Luminaire Tested: CB2-B-125U-085D-927-1D-UNV-STD-W-8

Issue Date: 3/31/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1438962  
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2405-119-1, G2-2312-242-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/31/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: CB2-B-125U-085D-927-1D-UNV-STD-W-8  
Description: CORELITE BASIC SLOT LED LUMINAIRE, BATWING UPLIGHT  
2-INCH APERTURE  
DOWNLIGHT 850 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 19561.9 lumens  
Efficiency: N/A  
Efficacy: 129.0 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 151.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1438962

CATALOG NUMBER: CB2-B-125U-085D-927-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P1438962

CATALOG NUMBER: CB2-B-125U-085D-927-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33																												
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	35	35	28																												
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	29	24																												
3	78	69	62	57	70	63	57	52	50	46	43	39	36	34	28	27	25	20																												
4	72	61	54	48	64	56	49	44	45	40	36	35	32	29	25	23	22	18																												
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19	15																												
6	60	49	41	35	54	44	38	33	36	31	27	28	25	22	21	19	17	14																												
7	56	44	36	31	50	40	33	29	33	28	24	26	22	19	19	17	15	12																												
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	18	15	13	11																												
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10																												
10	45	33	26	22	41	30	24	20	25	20	17	20	16	14	15	13	11	9																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	24315	24315	24315
5°	24109	24146	24314
10°	23972	23915	23896
15°	23592	23438	23246
20°	23221	22706	22389
25°	22596	21960	21343
30°	21971	21004	20208
35°	21251	20023	19069
40°	20488	19103	17985
45°	19721	18141	16929
50°	19030	17205	15902
55°	18177	16229	14931
60°	17203	15305	13963
65°	16168	14274	12996
70°	15023	13118	11759
75°	13668	11868	10646
80°	12222	10401	9649
85°	9403	8543	7044

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 19721 cd/sqm



TEST NUMBER: P1438962

CATALOG NUMBER: CB2-B-125U-085D-927-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	262.6	1.3
10°-20°	731.9	3.7
20°-30°	1052.4	5.4
30°-40°	1182.8	6.0
40°-50°	1142.6	5.8
50°-60°	965.4	4.9
60°-70°	693.4	3.5
70°-80°	379.0	1.9
80°-90°	100.7	0.5
90°-100°	148.8	0.8
100°-110°	921.6	4.7
110°-120°	2324.2	11.9
120°-130°	2793.9	14.3
130°-140°	2533.2	12.9
140°-150°	2020.0	10.3
150°-160°	1377.9	7.0
160°-170°	728.7	3.7
170°-180°	202.8	1.0
0°-30°	2046.8	10.5
0°-40°	3229.6	16.5
0°-60°	5337.6	27.3
0°-90°	6510.7	33.3
90°-120°	3394.6	17.4
90°-150°	10741.7	54.9
90°-180°	13051.0	66.7
0°-180°	19561.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2792	2792	2792	2792	2792	
5°	2758	2796	2762	2762	2781	262
15°	2617	2640	2600	2574	2578	738
25°	2352	2354	2285	2234	2221	1083
35°	1999	1976	1883	1810	1794	1249
45°	1601	1568	1473	1396	1375	1237
55°	1197	1153	1069	1002	983	1070
65°	785	755	693	643	631	778
75°	406	381	353	325	316	434
85°	94	88	86	75	70	112
90°	0	0	0	0	0	7
95°	77	194	60	43	43	98
105°	377	1055	1524	382	257	396
115°	651	1438	3476	3236	2466	638
125°	848	1743	3793	4316	4341	759
135°	1062	1932	3801	4451	4777	825
145°	1361	2031	3587	4324	4709	851
155°	1652	2071	3193	3849	4050	760
165°	1875	2051	2577	3034	3176	526
175°	1986	2011	2046	2081	2123	188
180°	1986	1986	1986	1986	1986	

TEST NUMBER: P1438962

CATALOG NUMBER: CB2-B-125U-085D-927-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2792.0	2792.0	2792.0	2792.0	2792.0
2.5°	2773.2	2806.7	2781.8	2785.3	2790.3
5°	2757.8	2795.5	2762.1	2762.5	2781.3
7.5°	2738.2	2773.7	2731.7	2724.0	2741.6
10°	2710.8	2746.3	2704.4	2689.7	2702.2
12.5°	2674.9	2708.7	2668.5	2645.2	2656.1
15°	2616.7	2639.7	2599.6	2574.1	2578.3
17.5°	2553.5	2567.7	2509.8	2488.4	2484.2
20°	2505.6	2518.1	2450.0	2420.0	2415.8
22.5°	2444.0	2454.9	2383.3	2346.4	2340.5
25°	2351.6	2353.7	2285.4	2233.8	2221.2
27.5°	2255.0	2248.3	2172.5	2111.4	2095.1
30°	2184.9	2176.5	2088.7	2024.2	2009.6
32.5°	2109.6	2094.6	2006.6	1937.0	1922.4
35°	1998.9	1975.9	1883.4	1810.4	1793.7
37.5°	1880.9	1855.0	1764.2	1684.6	1665.8
40°	1802.2	1772.9	1680.4	1600.8	1582.0
42.5°	1723.5	1690.9	1596.5	1517.0	1496.5
45°	1601.3	1567.8	1473.0	1395.5	1374.6
47.5°	1485.0	1442.3	1350.3	1273.3	1252.4
50°	1404.6	1358.6	1269.9	1194.6	1173.7
52.5°	1322.5	1274.8	1189.5	1117.6	1096.7
55°	1197.2	1153.3	1068.9	1002.2	983.4
57.5°	1073.2	1031.0	953.9	890.2	871.8
60°	987.7	952.2	878.7	818.4	801.7
62.5°	905.6	873.4	803.4	748.3	731.6
65°	784.6	755.3	692.7	643.2	630.7
67.5°	667.0	637.7	587.1	542.7	528.5
70°	590.0	560.8	515.2	474.3	461.8
72.5°	516.5	485.6	448.5	411.1	401.9
75°	406.2	381.1	352.7	324.8	316.4
77.5°	308.7	284.5	263.8	244.1	242.0
80°	243.7	222.8	207.4	194.5	192.4
82.5°	182.1	166.3	156.1	146.6	146.2
85°	94.1	87.8	85.5	74.7	70.5
87.5°	27.4	27.4	23.9	20.5	20.5
90°	0.0	0.0	0.0	0.0	0.0
92.5°	20.5	33.9	13.7	13.7	13.7
95°	77.1	194.2	59.9	42.8	42.8
97.5°	161.0	465.7	323.6	87.1	75.3
100°	222.6	674.6	556.5	127.9	102.7
102.5°	284.2	856.8	878.4	202.7	157.5
105°	376.7	1054.8	1523.9	382.4	256.8
107.5°	467.5	1184.0	2335.6	789.1	476.0
110°	522.2	1258.9	2945.1	1230.2	736.3



TEST NUMBER: P1438962

CATALOG NUMBER: CB2-B-125U-085D-927-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	577.0	1333.8	3280.7	1972.0	1270.5
115°	650.7	1437.6	3475.9	3235.8	2465.7
117.5°	712.3	1532.7	3643.7	4001.6	3775.6
120°	753.4	1607.3	3732.8	4111.2	4186.5
122.5°	794.5	1661.8	3780.7	4153.8	4296.1
125°	847.6	1743.3	3792.7	4315.5	4340.6
127.5°	900.7	1804.7	3849.2	4464.2	4475.9
130°	941.8	1845.8	3904.0	4514.0	4606.0
132.5°	989.7	1880.4	3924.6	4542.4	4681.4
135°	1061.6	1932.2	3801.3	4450.8	4777.3
137.5°	1152.4	1969.4	3683.1	4448.2	4659.1
140°	1207.2	1977.3	3621.5	4546.5	4563.2
142.5°	1268.8	1998.8	3607.8	4535.7	4679.7
145°	1361.3	2031.0	3587.2	4323.7	4708.8
147.5°	1453.7	2051.4	3508.5	4089.7	4426.3
150°	1515.4	2059.5	3433.1	4011.5	4220.8
152.5°	1577.0	2067.6	3337.2	3962.8	4138.6
155°	1652.4	2070.9	3193.4	3848.6	4049.6
157.5°	1731.1	2060.9	3020.5	3640.2	3859.5
160°	1772.2	2048.5	2910.9	3488.9	3681.4
162.5°	1813.3	2042.7	2815.0	3291.0	3517.0
165°	1875.0	2050.7	2577.0	3034.0	3176.3
167.5°	1916.0	2043.3	2354.4	2728.8	2929.7
170°	1943.4	2043.9	2217.4	2495.2	2662.6
172.5°	1964.0	2010.9	2135.2	2281.6	2395.5
175°	1986.2	2011.4	2046.2	2081.4	2123.2
177.5°	1993.1	2006.5	1979.4	1972.9	1986.2
180°	1986.2	1986.2	1986.2	1986.2	1986.2



TEST NUMBER: P1438962  
 CATALOG NUMBER: CB2-B-125U-085D-927-1D-UNV-STD-W-8

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.30	17.02	17.39	18.11	19.60	15.20	15.92	16.29	17.01	18.50
	3H	17.93	18.58	19.03	19.68	21.19	16.72	17.36	17.82	18.46	19.97
	4H	18.56	19.17	19.67	20.27	21.78	17.28	17.90	18.39	18.99	20.51
	6H	18.95	19.52	20.07	20.62	22.14	17.65	18.21	18.77	19.31	20.84
	8H	19.10	19.63	20.22	20.75	22.27	17.78	18.32	18.91	19.44	20.96
	12H	19.17	19.67	20.29	20.78	22.33	17.84	18.35	18.97	19.46	21.01
4H	2H	16.69	17.31	17.81	18.40	19.92	15.82	16.43	16.93	17.53	19.04
	3H	18.55	19.06	19.67	20.18	21.71	17.54	18.05	18.66	19.18	20.70
	4H	19.29	19.76	20.42	20.87	22.42	18.21	18.68	19.33	19.79	21.34
	6H	19.80	20.20	20.93	21.34	22.88	18.68	19.08	19.81	20.21	21.75
	8H	20.00	20.38	21.14	21.51	23.06	18.86	19.24	20.00	20.37	21.92
	12H	20.10	20.44	21.25	21.58	23.14	18.94	19.28	20.09	20.42	21.98
8H	4H	19.43	19.81	20.57	20.94	22.49	18.47	18.85	19.60	19.97	21.53
	6H	20.07	20.38	21.22	21.55	23.10	19.07	19.38	20.22	20.55	22.10
	8H	20.36	20.63	21.52	21.78	23.35	19.34	19.61	20.50	20.76	22.34
	12H	20.53	20.77	21.69	21.91	23.52	19.49	19.72	20.65	20.87	22.48
12H	4H	19.41	19.75	20.56	20.89	22.45	18.47	18.81	19.62	19.95	21.51
	6H	20.10	20.37	21.26	21.52	23.09	19.13	19.40	20.29	20.55	22.13
	8H	20.41	20.65	21.57	21.79	23.40	19.43	19.67	20.59	20.82	22.42