

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438986

Luminaire Tested: CB2-D-030U-055D-927-1D-UNV-STD-W-8

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1438986
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2312-242-13, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-D-030U-055D-927-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE, DIFFUSER DUST COVER UPLIGHT
2-INCH APERTURE
DOWNLIGHT 550 LUMENS PER FOOT
UPLIGHT 300 LUMENS PER FOOT
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6494.2 lumens
Efficiency: N/A
Efficacy: 118.3 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 54.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1438986

CATALOG NUMBER: CB2-D-030U-055D-927-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P1438986

CATALOG NUMBER: CB2-D-030U-055D-927-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	102	97	93	90	95	92	88	85	81	79	76	72	70	68	63	61	60	56
2	93	85	79	74	87	80	75	70	71	67	64	63	60	57	55	53	51	47
3	85	75	68	62	79	71	64	59	63	58	54	56	52	49	49	46	44	40
4	78	67	59	53	73	63	56	50	56	51	46	50	46	42	44	41	38	35
5	71	60	51	45	67	57	49	44	51	45	40	45	40	37	40	36	33	30
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	27
7	61	49	41	35	57	46	39	34	42	36	31	37	32	29	33	29	26	24
8	57	44	37	31	54	42	35	30	38	32	28	34	29	26	31	27	24	21
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	28	24	21	19
10	50	37	30	25	47	36	29	24	32	27	23	29	25	21	26	22	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15930	15930	15930
5°	15795	15819	15930
10°	15705	15668	15656
15°	15456	15355	15229
20°	15213	14875	14668
25°	14805	14387	13983
30°	14394	13761	13240
35°	13923	13118	12493
40°	13423	12515	11782
45°	12921	11885	11092
50°	12467	11272	10417
55°	11908	10633	9782
60°	11271	10025	9148
65°	10592	9351	8515
70°	9844	8594	7702
75°	8954	7776	6975
80°	8009	6816	6324
85°	6155	5596	4616

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12921 cd/sqm



TEST NUMBER: P1438986

CATALOG NUMBER: CB2-D-030U-055D-927-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.0	2.6
10°-20°	479.5	7.4
20°-30°	689.4	10.6
30°-40°	774.9	11.9
40°-50°	748.6	11.5
50°-60°	632.5	9.7
60°-70°	454.3	7.0
70°-80°	248.3	3.8
80°-90°	66.0	1.0
90°-100°	33.8	0.5
100°-110°	139.2	2.1
110°-120°	252.8	3.9
120°-130°	343.9	5.3
130°-140°	397.1	6.1
140°-150°	400.1	6.2
150°-160°	345.3	5.3
160°-170°	234.0	3.6
170°-180°	82.5	1.3
0°-30°	1341.0	20.6
0°-40°	2115.9	32.6
0°-60°	3496.9	53.8
0°-90°	4265.5	65.7
90°-120°	425.7	6.6
90°-150°	1566.8	24.1
90°-180°	2229.0	34.3
0°-180°	6494.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1829	1829	1829	1829	1829	
5°	1807	1831	1810	1810	1822	172
15°	1714	1729	1703	1686	1689	483
25°	1541	1542	1497	1463	1455	709
35°	1310	1294	1234	1186	1175	818
45°	1049	1027	965	914	901	811
55°	784	756	700	657	644	701
65°	514	495	454	421	413	510
75°	266	250	231	213	207	285
85°	62	58	56	49	46	73
90°	0	0	1	0	1	4
95°	33	29	27	21	21	38
105°	138	136	132	125	123	146
115°	262	261	256	249	248	258
125°	389	393	385	377	378	348
135°	519	525	516	507	510	399
145°	643	650	640	633	637	402
155°	752	759	748	744	750	346
165°	831	840	829	824	832	234
175°	870	880	868	863	865	83
180°	874	874	874	874	874	



TEST NUMBER: P1438986

CATALOG NUMBER: CB2-D-030U-055D-927-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1829.2	1829.2	1829.2	1829.2	1829.2
2.5°	1816.9	1838.8	1822.5	1824.8	1828.1
5°	1806.8	1831.4	1809.6	1809.9	1822.2
7.5°	1793.9	1817.2	1789.7	1784.6	1796.1
10°	1776.0	1799.3	1771.8	1762.2	1770.4
12.5°	1752.4	1774.6	1748.2	1733.0	1740.1
15°	1714.3	1729.4	1703.1	1686.4	1689.1
17.5°	1672.9	1682.2	1644.3	1630.2	1627.5
20°	1641.5	1649.7	1605.1	1585.4	1582.7
22.5°	1601.2	1608.3	1561.4	1537.2	1533.4
25°	1540.7	1542.0	1497.2	1463.4	1455.2
27.5°	1477.4	1473.0	1423.3	1383.3	1372.6
30°	1431.4	1425.9	1368.4	1326.2	1316.6
32.5°	1382.1	1372.3	1314.6	1269.0	1259.4
35°	1309.6	1294.5	1233.9	1186.1	1175.1
37.5°	1232.3	1215.3	1155.8	1103.7	1091.4
40°	1180.7	1161.5	1100.9	1048.8	1036.4
42.5°	1129.2	1107.8	1046.0	993.8	980.4
45°	1049.1	1027.1	965.0	914.3	900.6
47.5°	972.9	944.9	884.6	834.2	820.5
50°	920.2	890.1	832.0	782.6	768.9
52.5°	866.4	835.2	779.3	732.2	718.5
55°	784.3	755.6	700.3	656.6	644.3
57.5°	703.1	675.4	625.0	583.2	571.2
60°	647.1	623.8	575.6	536.2	525.2
62.5°	593.3	572.2	526.3	490.2	479.3
65°	514.0	494.8	453.8	421.4	413.2
67.5°	437.0	417.8	384.6	355.5	346.2
70°	386.6	367.4	337.5	310.7	302.5
72.5°	338.4	318.1	293.8	269.3	263.3
75°	266.1	249.7	231.1	212.8	207.3
77.5°	202.2	186.4	172.8	159.9	158.5
80°	159.7	146.0	135.9	127.4	126.1
82.5°	119.3	108.9	102.2	96.1	95.8
85°	61.6	57.5	56.0	49.0	46.2
87.5°	17.9	17.9	15.8	13.4	13.6
90°	0.0	0.0	0.7	0.0	0.7
92.5°	8.2	7.1	6.7	4.4	5.0
95°	32.7	28.7	27.3	21.1	21.1
97.5°	61.8	57.8	55.6	49.3	48.0
100°	82.5	78.5	76.3	69.5	68.2
102.5°	103.7	101.9	98.2	90.8	89.4
105°	137.7	135.7	132.2	124.7	123.4
107.5°	172.6	173.0	167.8	161.6	159.8
110°	197.7	197.0	192.9	186.7	185.4



TEST NUMBER: P1438986

CATALOG NUMBER: CB2-D-030U-055D-927-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	223.3	222.1	218.0	211.8	210.5
115°	261.8	261.1	256.3	248.8	248.1
117.5°	298.3	300.4	294.8	286.8	286.6
120°	324.5	327.1	320.4	313.5	312.2
122.5°	350.1	353.3	346.6	338.7	338.9
125°	389.2	393.2	385.1	377.0	377.6
127.5°	427.0	431.9	424.4	416.1	416.9
130°	452.6	458.6	450.6	441.8	443.1
132.5°	478.8	484.8	476.8	467.4	469.8
135°	518.7	524.7	516.0	506.6	509.9
137.5°	556.4	562.4	552.8	544.9	548.9
140°	581.5	587.5	577.4	570.0	574.0
142.5°	606.0	613.1	602.5	594.5	599.6
145°	642.8	650.1	640.1	632.7	637.4
147.5°	677.7	685.0	674.8	667.7	672.5
150°	700.1	707.4	696.7	690.6	696.0
152.5°	720.8	729.2	717.9	712.0	718.9
155°	751.9	759.2	748.5	743.8	749.8
157.5°	778.9	787.4	776.7	772.7	777.5
160°	796.9	804.9	794.1	790.2	795.5
162.5°	810.5	819.0	808.9	804.4	810.8
165°	831.0	839.6	828.9	824.3	831.6
167.5°	847.0	856.2	845.4	840.7	848.1
170°	856.9	865.5	854.1	848.9	856.9
172.5°	863.4	872.6	860.7	855.3	860.7
175°	870.5	879.8	868.4	863.0	865.0
177.5°	873.9	881.4	872.3	867.5	873.9
180°	873.9	873.9	873.9	873.9	873.9



TEST NUMBER: P1438986
 CATALOG NUMBER: CB2-D-030U-055D-927-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.96	18.96	18.77	19.80	20.83	16.86	17.86	17.67	18.70	19.73
	3H	19.61	20.52	20.44	21.36	22.42	18.40	19.30	19.22	20.14	21.20
	4H	20.25	21.10	21.09	21.95	23.02	18.98	19.83	19.82	20.68	21.75
	6H	20.66	21.44	21.51	22.30	23.38	19.35	20.14	20.21	21.00	22.08
	8H	20.81	21.56	21.67	22.43	23.52	19.50	20.25	20.36	21.12	22.20
	12H	20.89	21.60	21.76	22.47	23.58	19.57	20.28	20.44	21.15	22.26
4H	2H	18.38	19.24	19.23	20.09	21.15	17.51	18.36	18.36	19.21	20.28
	3H	20.27	20.98	21.12	21.86	22.94	19.26	19.97	20.12	20.85	21.93
	4H	21.02	21.66	21.89	22.54	23.66	19.94	20.58	20.81	21.46	22.57
	6H	21.55	22.10	22.43	23.01	24.12	20.42	20.98	21.31	21.88	23.00
	8H	21.75	22.28	22.64	23.17	24.30	20.61	21.13	21.50	22.03	23.16
	12H	21.87	22.34	22.78	23.25	24.39	20.71	21.18	21.62	22.10	23.23
8H	4H	21.19	21.71	22.07	22.61	23.73	20.22	20.74	21.11	21.64	22.77
	6H	21.83	22.26	22.75	23.21	24.33	20.83	21.26	21.75	22.20	23.33
	8H	22.12	22.51	23.05	23.44	24.58	21.11	21.49	22.03	22.42	23.57
	12H	22.31	22.64	23.23	23.57	24.76	21.26	21.60	22.19	22.53	23.72
12H	4H	21.17	21.64	22.08	22.56	23.69	20.23	20.70	21.14	21.62	22.75
	6H	21.86	22.25	22.79	23.18	24.32	20.90	21.28	21.82	22.21	23.36
	8H	22.19	22.52	23.12	23.45	24.64	21.21	21.55	22.14	22.47	23.67