

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438985

Luminaire Tested: CB2-D-030U-055D-927-1D-UNV-STD-W-4

Issue Date: 3/31/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1438985  
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2312-242-13, G2-2312-242-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/31/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: CB2-D-030U-055D-927-1D-UNV-STD-W-4  
Description: CORELITE BASIC SLOT LED LUMINAIRE, DIFFUSER DUST COVER UPLIGHT  
2-INCH APERTURE  
DOWNLIGHT 550 LUMENS PER FOOT  
UPLIGHT 300 LUMENS PER FOOT  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3247.1 lumens  
Efficiency: N/A  
Efficacy: 121.2 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 26.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1438985

CATALOG NUMBER: CB2-D-030U-055D-927-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1438985

CATALOG NUMBER: CB2-D-030U-055D-927-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	102	97	93	90	95	92	88	85	81	79	76	72	70	68	63	61	60	56
2	93	85	79	74	87	80	75	70	71	67	64	63	60	57	55	53	51	47
3	85	75	68	62	79	71	64	59	63	58	54	56	52	49	49	46	44	40
4	78	67	59	53	73	63	56	50	56	51	46	50	46	42	44	41	38	35
5	71	60	51	45	67	57	49	44	51	45	40	45	40	37	40	36	33	30
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	27
7	61	49	41	35	57	46	39	34	42	36	31	37	32	29	33	29	26	24
8	57	44	37	31	54	42	35	30	38	32	28	34	29	26	31	27	24	21
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	28	24	21	19
10	50	37	30	25	47	36	29	24	32	27	23	29	25	21	26	22	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15930	15930	15930
5°	15795	15819	15930
10°	15705	15668	15656
15°	15457	15356	15230
20°	15214	14874	14667
25°	14804	14387	13983
30°	14394	13761	13240
35°	13923	13119	12494
40°	13424	12514	11782
45°	12919	11885	11092
50°	12467	11272	10419
55°	11910	10634	9781
60°	11269	10025	9148
65°	10592	9351	8515
70°	9844	8596	7705
75°	8957	7779	6972
80°	8004	6811	6319
85°	6155	5596	4616

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12919 cd/sqm



TEST NUMBER: P1438985

CATALOG NUMBER: CB2-D-030U-055D-927-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	86.0	2.6
10°-20°	239.8	7.4
20°-30°	344.7	10.6
30°-40°	387.5	11.9
40°-50°	374.3	11.5
50°-60°	316.2	9.7
60°-70°	227.1	7.0
70°-80°	124.2	3.8
80°-90°	33.0	1.0
90°-100°	16.9	0.5
100°-110°	69.6	2.1
110°-120°	126.4	3.9
120°-130°	172.0	5.3
130°-140°	198.5	6.1
140°-150°	200.1	6.2
150°-160°	172.6	5.3
160°-170°	117.0	3.6
170°-180°	41.3	1.3
0°-30°	670.5	20.6
0°-40°	1057.9	32.6
0°-60°	1748.5	53.8
0°-90°	2132.8	65.7
90°-120°	212.9	6.6
90°-150°	783.4	24.1
90°-180°	1114.0	34.3
0°-180°	3247.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	915	915	915	915	915	
5°	903	916	905	905	911	86
15°	857	865	852	843	845	242
25°	770	771	749	732	728	355
35°	655	647	617	593	588	409
45°	524	514	482	457	450	405
55°	392	378	350	328	322	351
65°	257	247	227	211	207	255
75°	133	125	116	106	104	142
85°	31	29	28	24	23	37
90°	0	0	0	0	0	2
95°	16	14	14	11	11	19
105°	69	68	66	62	62	73
115°	131	130	128	124	124	129
125°	195	197	193	188	189	174
135°	259	262	258	253	255	200
145°	321	325	320	316	319	201
155°	376	380	374	372	375	173
165°	416	420	414	412	416	117
175°	435	440	434	432	432	41
180°	437	437	437	437	437	

TEST NUMBER: P1438985

CATALOG NUMBER: CB2-D-030U-055D-927-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	914.6	914.6	914.6	914.6	914.6
2.5°	908.4	919.4	911.2	912.4	914.0
5°	903.4	915.7	904.8	904.9	911.1
7.5°	896.9	908.6	894.8	892.3	898.1
10°	888.0	899.6	885.9	881.1	885.2
12.5°	876.2	887.3	874.1	866.5	870.1
15°	857.2	864.7	851.6	843.2	844.6
17.5°	836.4	841.1	822.2	815.1	813.8
20°	820.8	824.9	802.5	792.7	791.3
22.5°	800.6	804.1	780.7	768.6	766.7
25°	770.3	771.0	748.6	731.7	727.6
27.5°	738.7	736.5	711.6	691.6	686.3
30°	715.7	713.0	684.2	663.1	658.3
32.5°	691.1	686.1	657.3	634.5	629.7
35°	654.8	647.3	617.0	593.0	587.6
37.5°	616.1	607.6	577.9	551.8	545.7
40°	590.4	580.8	550.4	524.4	518.2
42.5°	564.6	553.9	523.0	496.9	490.2
45°	524.5	513.6	482.5	457.1	450.3
47.5°	486.4	472.5	442.3	417.1	410.2
50°	460.1	445.0	416.0	391.3	384.5
52.5°	433.2	417.6	389.6	366.1	359.3
55°	392.2	377.8	350.2	328.3	322.1
57.5°	351.6	337.7	312.5	291.6	285.6
60°	323.5	311.9	287.8	268.1	262.6
62.5°	296.6	286.1	263.2	245.1	239.6
65°	257.0	247.4	226.9	210.7	206.6
67.5°	218.5	208.9	192.3	177.8	173.1
70°	193.3	183.7	168.8	155.4	151.3
72.5°	169.2	159.1	146.9	134.7	131.7
75°	133.1	124.8	115.6	106.4	103.6
77.5°	101.1	93.2	86.4	80.0	79.3
80°	79.8	73.0	67.9	63.7	63.0
82.5°	59.7	54.5	51.1	48.0	47.9
85°	30.8	28.8	28.0	24.5	23.1
87.5°	9.0	9.0	7.9	6.7	6.8
90°	0.0	0.0	0.3	0.0	0.3
92.5°	4.1	3.6	3.3	2.2	2.5
95°	16.4	14.4	13.6	10.6	10.6
97.5°	30.9	28.9	27.8	24.7	24.0
100°	41.2	39.2	38.2	34.7	34.1
102.5°	51.9	50.9	49.1	45.4	44.7
105°	68.8	67.8	66.1	62.4	61.7
107.5°	86.3	86.5	83.9	80.8	79.9
110°	98.8	98.5	96.5	93.4	92.7



TEST NUMBER: P1438985

CATALOG NUMBER: CB2-D-030U-055D-927-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	111.7	111.1	109.0	105.9	105.2
115°	130.9	130.5	128.2	124.4	124.1
117.5°	149.1	150.2	147.4	143.4	143.3
120°	162.2	163.6	160.2	156.8	156.1
122.5°	175.1	176.7	173.3	169.3	169.5
125°	194.6	196.6	192.6	188.5	188.8
127.5°	213.5	216.0	212.2	208.1	208.5
130°	226.3	229.3	225.3	220.9	221.5
132.5°	239.4	242.4	238.4	233.7	234.9
135°	259.4	262.4	258.0	253.3	254.9
137.5°	278.2	281.2	276.4	272.4	274.4
140°	290.7	293.7	288.7	285.0	287.0
142.5°	303.0	306.5	301.2	297.3	299.8
145°	321.4	325.1	320.0	316.3	318.7
147.5°	338.9	342.5	337.4	333.9	336.3
150°	350.0	353.7	348.3	345.3	348.0
152.5°	360.4	364.6	359.0	356.0	359.4
155°	375.9	379.6	374.2	371.9	374.9
157.5°	389.4	393.7	388.3	386.4	388.8
160°	398.4	402.4	397.1	395.1	397.8
162.5°	405.3	409.5	404.4	402.2	405.4
165°	415.5	419.8	414.5	412.2	415.8
167.5°	423.5	428.1	422.7	420.3	424.1
170°	428.4	432.8	427.1	424.4	428.4
172.5°	431.7	436.3	430.3	427.7	430.3
175°	435.2	439.9	434.2	431.5	432.5
177.5°	436.9	440.7	436.1	433.7	436.9
180°	436.9	436.9	436.9	436.9	436.9



TEST NUMBER: P1438985  
 CATALOG NUMBER: CB2-D-030U-055D-927-1D-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.96	18.96	18.77	19.80	20.83	16.86	17.86	17.67	18.70	19.73
	3H	19.61	20.52	20.44	21.36	22.42	18.40	19.30	19.22	20.14	21.20
	4H	20.25	21.10	21.09	21.95	23.02	18.98	19.83	19.82	20.68	21.75
	6H	20.66	21.44	21.51	22.30	23.38	19.36	20.14	20.21	21.00	22.08
	8H	20.81	21.56	21.67	22.43	23.52	19.50	20.25	20.36	21.12	22.21
	12H	20.89	21.60	21.76	22.47	23.58	19.57	20.28	20.44	21.15	22.26
4H	2H	18.38	19.24	19.23	20.09	21.15	17.51	18.36	18.36	19.21	20.28
	3H	20.27	20.98	21.12	21.86	22.94	19.26	19.97	20.12	20.85	21.93
	4H	21.02	21.66	21.89	22.54	23.66	19.94	20.58	20.81	21.46	22.57
	6H	21.55	22.10	22.43	23.01	24.12	20.42	20.98	21.31	21.88	23.00
	8H	21.75	22.28	22.64	23.17	24.30	20.61	21.14	21.50	22.03	23.16
	12H	21.87	22.34	22.78	23.25	24.39	20.71	21.18	21.62	22.10	23.23
8H	4H	21.19	21.71	22.07	22.61	23.73	20.22	20.74	21.11	21.64	22.77
	6H	21.83	22.26	22.75	23.21	24.33	20.83	21.26	21.75	22.20	23.33
	8H	22.13	22.51	23.05	23.44	24.58	21.11	21.49	22.03	22.42	23.57
	12H	22.31	22.64	23.24	23.57	24.76	21.26	21.60	22.19	22.53	23.72
12H	4H	21.17	21.64	22.08	22.56	23.69	20.23	20.70	21.14	21.62	22.75
	6H	21.86	22.25	22.79	23.18	24.32	20.90	21.28	21.82	22.21	23.36
	8H	22.19	22.52	23.12	23.45	24.64	21.21	21.55	22.14	22.47	23.67