

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438585

Luminaire Tested: CB2-030U-030D-830-1D-UNV-STD-W-4

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1438585
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2506-466-1, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-030U-030D-830-1D-UNV-STD-W-4
Description: CORELITE BASIC SLOT LED LUMINAIRE, OPEN UPLIGHT
2-INCH APERTURE
DOWNLIGHT 300 LUMENS PER FOOT
UPLIGHT 300 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2300.5 lumens
Efficiency: N/A
Efficacy: 128.5 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 17.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1438585

CATALOG NUMBER: CB2-030U-030D-830-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P1438585

CATALOG NUMBER: CB2-030U-030D-830-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	53	53	53	46				
1	97	93	89	86	89	85	82	79	71	69	67	59	57	55	47	46	45	39				
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	41	39	38	33				
3	81	72	64	59	74	66	60	55	55	51	47	46	42	40	37	34	32	28				
4	74	63	56	50	68	59	52	46	49	44	40	41	37	34	33	30	28	24				
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	25	21				
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22	19				
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19	17				
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17	15				
9	50	38	31	26	46	35	29	24	30	25	21	26	21	19	21	18	16	14				
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7914	7914	7914
5°	7849	7861	7915
10°	7803	7785	7778
15°	7680	7629	7566
20°	7559	7392	7288
25°	7355	7149	6947
30°	7152	6836	6579
35°	6917	6517	6207
40°	6669	6218	5855
45°	6419	5904	5510
50°	6194	5601	5175
55°	5918	5284	4862
60°	5601	4981	4546
65°	5263	4645	4228
70°	4889	4273	3830
75°	4448	3863	3466
80°	3982	3390	3139
85°	3058	2778	2298

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6419 cd/sqm



TEST NUMBER: P1438585

CATALOG NUMBER: CB2-030U-030D-830-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.7	1.9
10°-20°	119.1	5.2
20°-30°	171.3	7.4
30°-40°	192.5	8.4
40°-50°	186.0	8.1
50°-60°	157.1	6.8
60°-70°	112.9	4.9
70°-80°	61.7	2.7
80°-90°	16.4	0.7
90°-100°	7.6	0.3
100°-110°	48.3	2.1
110°-120°	153.4	6.7
120°-130°	222.5	9.7
130°-140°	239.3	10.4
140°-150°	225.3	9.8
150°-160°	183.6	8.0
160°-170°	119.5	5.2
170°-180°	41.3	1.8
0°-30°	333.1	14.5
0°-40°	525.6	22.8
0°-60°	868.7	37.8
0°-90°	1059.7	46.1
90°-120°	209.2	9.1
90°-150°	896.4	39.0
90°-180°	1241.0	53.9
0°-180°	2300.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	454	454	454	454	454	
5°	449	455	450	450	453	43
15°	426	430	423	419	420	120
25°	383	383	372	364	362	176
35°	325	322	306	295	292	203
45°	261	255	240	227	224	201
55°	195	188	174	163	160	174
65°	128	123	113	105	103	127
75°	66	62	57	53	52	71
85°	15	14	14	12	12	18
90°	0	0	0	0	0	1
95°	17	5	5	4	3	22
105°	91	94	9	11	12	95
115°	172	175	177	179	103	169
125°	244	248	248	252	256	218
135°	306	310	310	312	316	236
145°	359	362	359	359	364	224
155°	398	401	396	396	401	184
165°	425	426	422	420	424	120
175°	437	438	433	430	432	42
180°	435	435	435	435	435	

TEST NUMBER: P1438585

CATALOG NUMBER: CB2-030U-030D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	454.4	454.4	454.4	454.4	454.4
2.5°	451.4	456.8	452.8	453.3	454.1
5°	448.9	455.0	449.6	449.6	452.7
7.5°	445.7	451.4	444.6	443.4	446.2
10°	441.2	447.0	440.2	437.8	439.8
12.5°	435.4	440.9	434.3	430.5	432.3
15°	425.9	429.6	423.1	419.0	419.6
17.5°	415.6	417.9	408.5	405.0	404.3
20°	407.8	409.8	398.8	393.9	393.2
22.5°	397.8	399.5	387.9	381.9	380.9
25°	382.7	383.1	372.0	363.6	361.5
27.5°	367.0	365.9	353.6	343.6	341.0
30°	355.6	354.2	339.9	329.5	327.1
32.5°	343.4	340.9	326.6	315.3	312.9
35°	325.3	321.6	306.5	294.7	291.9
37.5°	306.1	301.9	287.1	274.2	271.1
40°	293.3	288.6	273.5	260.5	257.5
42.5°	280.5	275.2	259.9	246.9	243.6
45°	260.6	255.2	239.7	227.1	223.7
47.5°	241.7	234.7	219.8	207.2	203.8
50°	228.6	221.1	206.7	194.4	191.0
52.5°	215.2	207.5	193.6	181.9	178.5
55°	194.9	187.7	174.0	163.1	160.1
57.5°	174.7	167.8	155.3	144.9	141.9
60°	160.8	155.0	143.0	133.2	130.5
62.5°	147.4	142.2	130.8	121.8	119.1
65°	127.7	122.9	112.7	104.7	102.6
67.5°	108.6	103.8	95.5	88.3	86.0
70°	96.0	91.3	83.9	77.2	75.2
72.5°	84.1	79.0	73.0	66.9	65.4
75°	66.1	62.0	57.4	52.9	51.5
77.5°	50.2	46.3	42.9	39.7	39.4
80°	39.7	36.3	33.8	31.7	31.3
82.5°	29.6	27.1	25.4	23.9	23.8
85°	15.3	14.3	13.9	12.2	11.5
87.5°	4.5	4.5	3.9	3.4	3.4
90°	0.0	0.0	0.0	0.3	0.3
92.5°	4.8	1.8	1.3	1.8	1.8
95°	17.3	5.0	5.3	3.5	3.1
97.5°	35.9	8.1	7.7	8.5	8.8
100°	50.0	16.5	8.5	9.8	10.1
102.5°	65.6	62.1	8.7	10.5	11.1
105°	90.6	94.0	9.4	11.0	11.6
107.5°	115.2	118.5	43.9	11.4	12.0
110°	131.5	134.9	139.1	11.7	12.3



TEST NUMBER: P1438585

CATALOG NUMBER: CB2-030U-030D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	146.9	151.0	154.2	25.9	12.8
115°	171.5	175.2	176.8	178.9	102.6
117.5°	193.2	197.7	199.6	203.2	206.6
120°	208.3	212.6	214.0	217.5	221.2
122.5°	223.1	227.0	227.8	231.8	235.3
125°	243.5	247.8	247.9	252.1	255.5
127.5°	263.9	267.6	267.4	270.6	274.3
130°	277.5	280.0	280.0	282.6	286.6
132.5°	288.8	292.3	292.4	294.5	298.5
135°	306.5	310.2	309.6	311.6	315.6
137.5°	323.0	326.6	325.6	327.3	331.4
140°	333.8	336.9	335.4	337.1	341.7
142.5°	343.9	347.0	344.7	346.2	351.0
145°	358.7	361.5	359.0	359.4	364.0
147.5°	371.8	374.6	371.6	372.0	376.3
150°	380.4	382.9	379.1	379.6	383.9
152.5°	388.0	390.2	386.2	386.1	391.2
155°	398.3	400.8	396.5	395.6	401.2
157.5°	407.8	410.1	405.7	405.1	409.4
160°	414.1	415.6	411.2	410.4	414.7
162.5°	418.4	420.1	415.8	414.4	418.7
165°	424.8	426.0	421.6	419.8	424.1
167.5°	430.3	431.7	426.1	424.5	429.1
170°	433.6	434.5	428.9	426.8	431.4
172.5°	435.6	436.3	430.6	428.2	431.4
175°	437.4	438.3	432.6	429.9	432.0
177.5°	437.7	438.2	433.9	431.5	435.2
180°	435.2	435.2	435.2	435.2	435.2

TEST NUMBER: P1438585
 CATALOG NUMBER: CB2-030U-030D-830-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.81	14.63	14.80	15.63	16.96	12.71	13.53	13.71	14.53	15.86
	3H	15.45	16.19	16.46	17.20	18.55	14.24	14.97	15.24	15.98	17.33
	4H	16.08	16.77	17.10	17.79	19.14	14.81	15.50	15.82	16.52	17.87
	6H	16.48	17.12	17.51	18.14	19.51	15.18	15.82	16.20	16.83	18.20
	8H	16.63	17.23	17.66	18.27	19.63	15.32	15.92	16.35	16.96	18.32
	12H	16.70	17.28	17.74	18.31	19.69	15.38	15.95	16.41	16.98	18.37
4H	2H	14.22	14.91	15.24	15.92	17.28	13.34	14.03	14.36	15.05	16.40
	3H	16.08	16.66	17.11	17.70	19.07	15.07	15.65	16.10	16.69	18.06
	4H	16.82	17.35	17.86	18.39	19.78	15.74	16.27	16.78	17.31	18.70
	6H	17.34	17.80	18.39	18.86	20.24	16.22	16.67	17.27	17.73	19.12
	8H	17.55	17.97	18.59	19.02	20.42	16.41	16.83	17.46	17.88	19.28
	12H	17.65	18.03	18.72	19.10	20.51	16.49	16.88	17.56	17.94	19.35
8H	4H	16.98	17.40	18.03	18.45	19.86	16.01	16.44	17.06	17.49	18.89
	6H	17.62	17.97	18.69	19.06	20.46	16.62	16.97	17.69	18.06	19.46
	8H	17.91	18.22	18.99	19.29	20.71	16.89	17.20	17.97	18.28	19.70
	12H	18.08	18.35	19.16	19.42	20.88	17.04	17.31	18.12	18.38	19.84
12H	4H	16.96	17.34	18.02	18.40	19.81	16.02	16.40	17.08	17.46	18.87
	6H	17.65	17.95	18.73	19.03	20.45	16.68	16.99	17.76	18.07	19.48
	8H	17.96	18.23	19.05	19.30	20.77	16.98	17.26	18.07	18.33	19.79