

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1438655

Luminaire Tested: CB2-055U-055D-830-1D-UNV-STD-W-4

Issue Date: 3/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1438655
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2506-466-1, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-055U-055D-830-1D-UNV-STD-W-4
Description: CORELITE BASIC SLOT LED LUMINAIRE, OPEN UPLIGHT
2-INCH APERTURE
DOWNLIGHT 550 LUMENS PER FOOT
UPLIGHT 550 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4419.8 lumens
Efficiency: N/A
Efficacy: 127.7 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 34.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1438655

CATALOG NUMBER: CB2-055U-055D-830-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P1438655

CATALOG NUMBER: CB2-055U-055D-830-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46					46			
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44					39				
2	88	81	75	70	81	75	70	65	63	59	56	51	49	46	41	39	38					33				
3	81	72	64	59	74	66	60	55	55	51	47	46	42	39	37	34	32					28				
4	74	63	56	50	68	58	52	46	49	44	40	41	37	34	33	30	28					24				
5	68	57	49	43	62	52	45	40	44	39	35	37	33	29	30	27	24					21				
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22					19				
7	58	46	38	33	53	42	36	31	36	31	27	30	26	23	25	22	19					17				
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17					15				
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	16					14				
10	47	35	28	23	43	32	26	22	28	23	19	24	20	17	19	16	14					12				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15120	15120	15120
5°	14992	15015	15120
10°	14908	14872	14860
15°	14671	14575	14454
20°	14439	14120	13922
25°	14052	13656	13272
30°	13662	13061	12566
35°	13215	12451	11858
40°	12742	11880	11184
45°	12264	11281	10528
50°	11833	10698	9888
55°	11302	10094	9286
60°	10698	9517	8684
65°	10056	8877	8082
70°	9345	8158	7313
75°	8499	7382	6622
80°	7603	6470	5998
85°	5835	5316	4377

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12264 cd/sqm



TEST NUMBER: P1438655

CATALOG NUMBER: CB2-055U-055D-830-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.6	1.8
10°-20°	227.6	5.1
20°-30°	327.2	7.4
30°-40°	367.8	8.3
40°-50°	355.3	8.0
50°-60°	300.2	6.8
60°-70°	215.6	4.9
70°-80°	117.8	2.7
80°-90°	31.3	0.7
90°-100°	14.6	0.3
100°-110°	93.2	2.1
110°-120°	296.1	6.7
120°-130°	429.6	9.7
130°-140°	462.0	10.5
140°-150°	435.0	9.8
150°-160°	354.4	8.0
160°-170°	230.7	5.2
170°-180°	79.7	1.8
0°-30°	636.4	14.4
0°-40°	1004.2	22.7
0°-60°	1659.6	37.5
0°-90°	2024.4	45.8
90°-120°	403.9	9.1
90°-150°	1730.6	39.2
90°-180°	2395.0	54.2
0°-180°	4419.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	868	868	868	868	868	
5°	858	869	859	859	865	81
15°	814	821	808	800	802	229
25°	731	732	711	694	691	337
35°	622	614	586	563	558	388
45°	498	488	458	434	427	385
55°	372	359	332	312	306	333
65°	244	235	215	200	196	242
75°	126	118	110	101	98	135
85°	29	27	27	23	22	35
90°	0	0	0	1	1	2
95°	33	10	10	7	6	42
105°	175	182	18	21	22	184
115°	331	338	341	345	198	325
125°	470	478	479	487	493	420
135°	592	599	598	602	609	456
145°	692	698	693	694	703	433
155°	769	774	765	764	774	355
165°	820	822	814	810	819	232
175°	844	846	835	830	834	80
180°	840	840	840	840	840	



TEST NUMBER: P1438655

CATALOG NUMBER: CB2-055U-055D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	868.1	868.1	868.1	868.1	868.1
2.5°	862.3	872.7	864.9	866.0	867.6
5°	857.5	869.2	858.8	858.9	864.8
7.5°	851.4	862.4	849.4	847.0	852.4
10°	842.9	853.9	840.9	836.3	840.2
12.5°	831.7	842.2	829.7	822.5	825.8
15°	813.6	820.8	808.3	800.3	801.6
17.5°	793.9	798.4	780.4	773.7	772.4
20°	779.0	782.9	761.8	752.4	751.1
22.5°	759.9	763.3	741.0	729.6	727.7
25°	731.2	731.8	710.6	694.5	690.6
27.5°	701.1	699.1	675.5	656.5	651.4
30°	679.3	676.7	649.4	629.4	624.8
32.5°	655.9	651.3	623.9	602.3	597.7
35°	621.5	614.4	585.6	562.9	557.7
37.5°	584.8	576.8	548.5	523.8	517.9
40°	560.4	551.3	522.5	497.7	491.9
42.5°	535.9	525.8	496.4	471.7	465.3
45°	497.9	487.5	458.0	433.9	427.4
47.5°	461.7	448.5	419.8	395.9	389.4
50°	436.7	422.4	394.8	371.4	364.9
52.5°	411.2	396.4	369.8	347.5	341.0
55°	372.2	358.6	332.4	311.6	305.8
57.5°	333.7	320.6	296.6	276.8	271.1
60°	307.1	296.0	273.2	254.5	249.3
62.5°	281.6	271.6	249.8	232.7	227.5
65°	244.0	234.9	215.4	200.0	196.1
67.5°	207.4	198.3	182.5	168.7	164.3
70°	183.5	174.4	160.2	147.5	143.6
72.5°	160.6	151.0	139.5	127.8	125.0
75°	126.3	118.5	109.7	101.0	98.4
77.5°	96.0	88.4	82.0	75.9	75.2
80°	75.8	69.3	64.5	60.5	59.8
82.5°	56.6	51.7	48.5	45.6	45.5
85°	29.2	27.3	26.6	23.2	21.9
87.5°	8.5	8.5	7.4	6.5	6.5
90°	0.0	0.0	0.0	0.6	0.6
92.5°	9.2	3.5	2.4	3.5	3.5
95°	33.4	9.7	10.3	6.7	6.1
97.5°	69.4	15.6	14.9	16.4	17.0
100°	96.6	31.8	16.4	18.8	19.4
102.5°	126.7	119.9	16.9	20.3	21.4
105°	174.9	181.5	18.2	21.3	22.5
107.5°	222.3	228.9	84.8	22.0	23.2
110°	253.9	260.4	268.5	22.5	23.7



TEST NUMBER: P1438655

CATALOG NUMBER: CB2-055U-055D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	283.5	291.5	297.6	50.1	24.7
115°	331.0	338.2	341.4	345.3	198.0
117.5°	373.0	381.8	385.4	392.2	398.8
120°	402.1	410.4	413.1	419.9	427.0
122.5°	430.8	438.2	439.8	447.6	454.2
125°	470.2	478.5	478.7	486.7	493.2
127.5°	509.5	516.6	516.3	522.3	529.6
130°	535.8	540.5	540.6	545.6	553.4
132.5°	557.6	564.3	564.4	568.5	576.2
135°	591.6	598.8	597.7	601.5	609.3
137.5°	623.6	630.5	628.6	631.8	639.7
140°	644.5	650.4	647.5	650.8	659.7
142.5°	663.9	669.9	665.5	668.3	677.6
145°	692.5	697.8	693.1	693.9	702.8
147.5°	717.9	723.1	717.4	718.2	726.5
150°	734.4	739.1	732.0	732.7	741.1
152.5°	749.0	753.2	745.6	745.4	755.2
155°	769.0	773.8	765.4	763.8	774.5
157.5°	787.2	791.6	783.2	782.1	790.4
160°	799.4	802.3	793.9	792.3	800.6
162.5°	807.6	811.1	802.7	800.1	808.4
165°	820.0	822.4	814.0	810.5	818.8
167.5°	830.7	833.5	822.6	819.5	828.4
170°	837.0	838.8	827.9	823.9	832.8
172.5°	840.9	842.2	831.3	826.7	832.8
175°	844.3	846.1	835.2	829.8	834.0
177.5°	844.9	845.9	837.6	832.9	840.1
180°	840.1	840.1	840.1	840.1	840.1

TEST NUMBER: P1438655

CATALOG NUMBER: CB2-055U-055D-830-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.04	16.85	17.03	17.85	19.19	14.94	15.75	15.93	16.76	18.09
	3H	17.68	18.41	18.68	19.42	20.77	16.46	17.19	17.46	18.20	19.55
	4H	18.30	18.99	19.32	20.01	21.37	17.03	17.72	18.05	18.74	20.10
	6H	18.70	19.34	19.73	20.36	21.73	17.40	18.04	18.43	19.06	20.43
	8H	18.85	19.46	19.88	20.49	21.86	17.54	18.14	18.57	19.18	20.55
	12H	18.92	19.50	19.96	20.53	21.92	17.60	18.18	18.64	19.21	20.60
4H	2H	16.44	17.13	17.46	18.15	19.51	15.56	16.26	16.59	17.27	18.63
	3H	18.30	18.88	19.34	19.93	21.30	17.30	17.87	18.33	18.92	20.29
	4H	19.05	19.58	20.09	20.61	22.01	17.97	18.49	19.01	19.53	20.93
	6H	19.57	20.02	20.62	21.08	22.47	18.44	18.89	19.49	19.95	21.34
	8H	19.77	20.19	20.82	21.24	22.65	18.63	19.05	19.68	20.10	21.51
	12H	19.87	20.25	20.94	21.32	22.73	18.71	19.10	19.78	20.16	21.58
8H	4H	19.20	19.62	20.25	20.68	22.08	18.24	18.66	19.29	19.71	21.12
	6H	19.84	20.19	20.92	21.29	22.69	18.84	19.19	19.91	20.28	21.69
	8H	20.13	20.44	21.21	21.52	22.94	19.11	19.42	20.20	20.50	21.92
	12H	20.30	20.57	21.39	21.65	23.11	19.26	19.53	20.35	20.61	22.07
12H	4H	19.18	19.56	20.25	20.63	22.04	18.24	18.62	19.31	19.69	21.10
	6H	19.87	20.18	20.95	21.26	22.68	18.90	19.21	19.98	20.29	21.71
	8H	20.18	20.45	21.27	21.53	22.99	19.21	19.48	20.29	20.55	22.01