

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1056950

Luminaire Tested: CB2-0U-030D-830-1D-UNV-STD-W-8

Issue Date: 7/31/2025

Test Information

Test Method: LM-79-2019
Report Number: P1056950
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 7/31/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-0U-030D-830-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE
2-INCH APERTURE
DOWNLIGHT 300 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2119.3 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')
CIE Type: Direct


Input Watts (W): 18.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1056950

CATALOG NUMBER: CB2-0U-030D-830-1D-UNV-STD-W-8

Luminous Intensity Polar Plot



TEST NUMBER: P1056950

CATALOG NUMBER: CB2-OU-030D-830-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	109	105	101	97	107	103	99	95	98	95	92	94	92	90	91	89	87
2	100	92	86	80	97	90	84	79	87	82	77	83	79	76	80	77	74
3	91	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63
4	84	73	64	58	82	71	63	57	69	62	56	66	60	56	64	59	55
5	78	65	56	50	76	64	56	50	62	55	49	60	54	49	58	53	48
6	72	59	50	44	70	58	50	44	56	49	43	55	48	43	53	47	43
7	67	54	45	39	65	53	45	39	51	44	39	50	43	38	49	43	38
8	62	49	41	35	61	48	41	35	47	40	35	46	39	35	45	39	34
9	58	45	37	32	57	45	37	32	44	37	32	42	36	31	41	36	31
10	55	42	34	29	54	41	34	29	40	34	29	39	33	29	39	33	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7915	7915	7915
5°	7848	7860	7915
10°	7803	7785	7778
15°	7680	7629	7567
20°	7559	7391	7288
25°	7356	7148	6947
30°	7152	6837	6579
35°	6918	6518	6208
40°	6669	6218	5855
45°	6419	5905	5511
50°	6194	5601	5177
55°	5917	5284	4860
60°	5600	4981	4546
65°	5263	4647	4231
70°	4891	4270	3827
75°	4448	3863	3466
80°	3977	3385	3139
85°	3058	2778	2298

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6419 cd/sqm

TEST NUMBER: P1056950

CATALOG NUMBER: CB2-OU-030D-830-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.5	4.0
10°-20°	238.2	11.2
20°-30°	342.6	16.2
30°-40°	385.0	18.2
40°-50°	371.9	17.5
50°-60°	314.3	14.8
60°-70°	225.7	10.7
70°-80°	123.4	5.8
80°-90°	32.8	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	666.3	31.4
0°-40°	1051.3	49.6
0°-60°	1737.5	82.0
0°-90°	2119.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2119.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	909	909	909	909	909	
5°	898	910	899	899	905	85
15°	852	859	846	838	839	240
25°	766	766	744	727	723	352
35°	651	643	613	589	584	406
45°	521	510	480	454	448	403
55°	390	375	348	326	320	348
65°	255	246	226	209	205	253
75°	132	124	115	106	103	141
85°	31	29	28	24	23	38
90°	0	0	0	0	0	

TEST NUMBER: P1056950

CATALOG NUMBER: CB2-0U-030D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	908.9	908.9	908.9	908.9	908.9
2.5°	902.7	913.6	905.5	906.7	908.3
5°	897.7	910.0	899.1	899.2	905.4
7.5°	891.3	902.9	889.2	886.7	892.4
10°	882.4	894.0	880.3	875.5	879.6
12.5°	870.7	881.7	868.6	861.1	864.6
15°	851.8	859.3	846.2	837.9	839.3
17.5°	831.2	835.8	817.0	810.0	808.6
20°	815.6	819.7	797.5	787.7	786.4
22.5°	795.6	799.1	775.8	763.8	761.9
25°	765.5	766.2	743.9	727.1	723.0
27.5°	734.0	731.9	707.2	687.3	682.0
30°	711.2	708.5	679.9	658.9	654.2
32.5°	686.7	681.8	653.2	630.5	625.8
35°	650.7	643.2	613.1	589.3	583.9
37.5°	612.3	603.8	574.3	548.4	542.2
40°	586.6	577.1	547.0	521.1	515.0
42.5°	561.0	550.4	519.7	493.8	487.1
45°	521.2	510.3	479.5	454.3	447.5
47.5°	483.4	469.5	439.5	414.5	407.7
50°	457.2	442.2	413.4	388.9	382.1
52.5°	430.5	415.0	387.2	363.8	357.0
55°	389.7	375.4	348.0	326.2	320.1
57.5°	349.3	335.6	310.5	289.8	283.8
60°	321.5	309.9	286.0	266.4	261.0
62.5°	294.8	284.3	261.5	243.6	238.1
65°	255.4	245.9	225.5	209.4	205.3
67.5°	217.1	207.6	191.1	176.7	172.0
70°	192.1	182.5	167.7	154.4	150.3
72.5°	168.1	158.1	146.0	133.8	130.8
75°	132.2	124.1	114.8	105.7	103.0
77.5°	100.5	92.6	85.9	79.5	78.8
80°	79.3	72.5	67.5	63.3	62.6
82.5°	59.3	54.1	50.8	47.7	47.6
85°	30.6	28.6	27.8	24.3	23.0
87.5°	8.9	8.9	7.8	6.7	6.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)