

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1056953

Luminaire Tested: CB2-0U-055D-830-1D-UNV-STD-W-8

Issue Date: 7/31/2025

Test Information

Test Method: LM-79-2019
Report Number: P1056953
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 7/31/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-0U-055D-830-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE
2-INCH APERTURE
DOWNLIGHT 550 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4048.7 lumens
Efficiency: N/A
Efficacy: 110.9 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')
CIE Type: Direct


Input Watts (W): 36.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1056953

CATALOG NUMBER: CB2-0U-055D-830-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P1056953

CATALOG NUMBER: CB2-OU-055D-830-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	109	105	101	97	107	103	99	95	98	95	92	94	92	90	91	89	87	85				
2	100	92	86	80	97	90	84	79	87	82	77	83	79	76	80	77	74	72				
3	91	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61				
4	84	73	64	58	82	71	63	57	69	62	56	66	60	56	64	59	55	53				
5	78	65	56	50	76	64	56	50	62	55	49	60	54	49	58	53	48	46				
6	72	59	50	44	70	58	50	44	56	49	43	55	48	43	53	47	43	41				
7	67	54	45	39	65	53	45	39	51	44	39	50	43	38	49	43	38	36				
8	62	49	41	35	61	48	41	35	47	40	35	46	39	35	45	39	34	33				
9	58	45	37	32	57	45	37	32	44	37	32	42	36	31	41	36	31	29				
10	55	42	34	29	54	41	34	29	40	34	29	39	33	29	39	33	29	27				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15120	15120	15120
5°	14992	15015	15120
10°	14907	14871	14860
15°	14671	14575	14455
20°	14440	14119	13923
25°	14052	13656	13273
30°	13663	13062	12567
35°	13215	12451	11858
40°	12741	11879	11184
45°	12263	11281	10528
50°	11833	10699	9889
55°	11304	10092	9284
60°	10698	9517	8683
65°	10054	8875	8082
70°	9342	8158	7313
75°	8499	7382	6622
80°	7603	6470	5998
85°	5845	5316	4387

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12263 cd/sqm

TEST NUMBER: P1056953

CATALOG NUMBER: CB2-OU-055D-830-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.3	4.0
10°-20°	455.1	11.2
20°-30°	654.4	16.2
30°-40°	735.5	18.2
40°-50°	710.5	17.5
50°-60°	600.3	14.8
60°-70°	431.2	10.7
70°-80°	235.7	5.8
80°-90°	62.6	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1272.8	31.4
0°-40°	2008.4	49.6
0°-60°	3319.2	82.0
0°-90°	4048.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4048.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1736	1736	1736	1736	1736	
5°	1715	1738	1718	1718	1730	163
15°	1627	1642	1617	1601	1603	459
25°	1462	1464	1421	1389	1381	673
35°	1243	1229	1171	1126	1115	776
45°	996	975	916	868	855	769
55°	744	717	665	623	612	666
65°	488	470	431	400	392	484
75°	253	237	219	202	197	270
85°	58	55	53	46	44	72
90°	0	0	0	0	0	



TEST NUMBER: P1056953

CATALOG NUMBER: CB2-OU-055D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1736.2	1736.2	1736.2	1736.2	1736.2
2.5°	1724.5	1745.3	1729.9	1732.1	1735.2
5°	1715.0	1738.4	1717.6	1717.9	1729.6
7.5°	1702.7	1724.8	1698.7	1693.9	1704.9
10°	1685.7	1707.8	1681.7	1672.6	1680.4
12.5°	1663.4	1684.4	1659.4	1644.9	1651.7
15°	1627.2	1641.5	1616.6	1600.7	1603.3
17.5°	1587.9	1596.7	1560.8	1547.4	1544.8
20°	1558.1	1565.9	1523.5	1504.9	1502.3
22.5°	1519.8	1526.6	1482.1	1459.1	1455.5
25°	1462.4	1463.7	1421.2	1389.1	1381.3
27.5°	1402.3	1398.1	1351.0	1313.0	1302.8
30°	1358.7	1353.5	1298.9	1258.8	1249.7
32.5°	1311.9	1302.5	1247.8	1204.5	1195.4
35°	1243.0	1228.7	1171.2	1125.8	1115.4
37.5°	1169.6	1153.5	1097.0	1047.6	1035.9
40°	1120.7	1102.5	1044.9	995.5	983.8
42.5°	1071.8	1051.5	992.8	943.3	930.6
45°	995.7	974.9	916.0	867.8	854.8
47.5°	923.4	896.9	839.7	791.8	778.8
50°	873.4	844.8	789.7	742.9	729.9
52.5°	822.4	792.7	739.7	695.0	682.0
55°	744.5	717.2	664.7	623.2	611.5
57.5°	667.4	641.1	593.2	553.6	542.1
60°	614.2	592.1	546.4	508.9	498.5
62.5°	563.1	543.1	499.6	465.3	454.9
65°	487.9	469.7	430.7	400.0	392.2
67.5°	414.8	396.6	365.1	337.5	328.6
70°	366.9	348.7	320.4	295.0	287.2
72.5°	321.2	302.0	278.9	255.7	249.9
75°	252.6	237.0	219.4	202.0	196.8
77.5°	192.0	176.9	164.1	151.8	150.5
80°	151.6	138.6	129.0	120.9	119.6
82.5°	113.3	103.4	97.0	91.2	90.9
85°	58.5	54.6	53.2	46.5	43.9
87.5°	17.0	17.0	14.9	12.8	12.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)