

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1439100

Luminaire Tested: CB2-D-125U-120D-930-1D-UNV-STD-W-8

Issue Date: 3/31/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1439100  
REPORT IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2312-242-13, G2-2312-242-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/31/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: CB2-D-125U-120D-930-1D-UNV-STD-W-8  
Description: CORELITE BASIC SLOT LED LUMINAIRE, DIFFUSER DUST COVER UPLIGHT  
2-INCH APERTURE  
DOWNLIGHT 1200 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 20210.4 lumens  
Efficiency: N/A  
Efficacy: 109.7 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 184.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1439100

CATALOG NUMBER: CB2-D-125U-120D-930-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P1439100

CATALOG NUMBER: CB2-D-125U-120D-930-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49					49			
1	98	93	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47	41					41			
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	40	35					35			
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	38	36	34	30					30			
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	34	32	29	26					26			
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	31	28	26	22					22			
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20					20			
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18					18			
8	54	42	34	29	50	39	32	28	34	28	24	29	24	21	24	21	18	16					16			
9	51	38	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17	14					14			
10	47	35	28	23	44	33	26	22	29	23	20	24	20	17	20	17	15	13					13			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	36786	36786	36786
5°	36475	36532	36786
10°	36267	36181	36153
15°	35693	35459	35168
20°	35131	34351	33872
25°	34187	33224	32291
30°	33241	31777	30573
35°	32151	30294	28850
40°	30997	28901	27210
45°	29837	27446	25613
50°	28790	26029	24058
55°	27501	24554	22589
60°	26027	23153	21125
65°	24460	21594	19661
70°	22730	19848	17788
75°	20677	17958	16107
80°	18491	15732	14599
85°	14219	12930	10662

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 29837 cd/sqm



TEST NUMBER: P1439100

CATALOG NUMBER: CB2-D-125U-120D-930-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	397.2	2.0
10°-20°	1107.3	5.5
20°-30°	1592.1	7.9
30°-40°	1789.5	8.9
40°-50°	1728.7	8.6
50°-60°	1460.6	7.2
60°-70°	1049.1	5.2
70°-80°	573.4	2.8
80°-90°	152.5	0.8
90°-100°	156.9	0.8
100°-110°	647.2	3.2
110°-120°	1174.9	5.8
120°-130°	1598.8	7.9
130°-140°	1845.6	9.1
140°-150°	1859.9	9.2
150°-160°	1605.0	7.9
160°-170°	1087.8	5.4
170°-180°	383.7	1.9
0°-30°	3096.7	15.3
0°-40°	4886.2	24.2
0°-60°	8075.4	40.0
0°-90°	9850.5	48.7
90°-120°	1979.1	9.8
90°-150°	7283.4	36.0
90°-180°	10360.0	51.3
0°-180°	20210.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	4224	4224	4224	4224	4224	
5°	4172	4229	4179	4180	4208	396
15°	3959	3994	3933	3894	3901	1116
25°	3558	3561	3458	3380	3360	1638
35°	3024	2989	2850	2739	2714	1889
45°	2423	2372	2228	2111	2080	1872
55°	1811	1745	1617	1516	1488	1619
65°	1187	1143	1048	973	954	1177
75°	614	577	534	491	479	657
85°	142	133	129	113	107	169
90°	0	0	3	0	3	11
95°	152	134	127	98	98	177
105°	640	631	615	580	574	679
115°	1217	1214	1191	1156	1153	1201
125°	1809	1828	1790	1752	1755	1616
135°	2411	2439	2399	2355	2370	1857
145°	2988	3022	2975	2941	2963	1867
155°	3495	3529	3479	3458	3486	1607
165°	3863	3903	3853	3832	3866	1088
175°	4046	4090	4037	4012	4021	384
180°	4062	4062	4062	4062	4062	

TEST NUMBER: P1439100

CATALOG NUMBER: CB2-D-125U-120D-930-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	4224.1	4224.1	4224.1	4224.1	4224.1
2.5°	4195.7	4246.3	4208.6	4214.0	4221.5
5°	4172.4	4229.3	4178.9	4179.5	4208.0
7.5°	4142.6	4196.4	4132.9	4121.2	4147.8
10°	4101.2	4155.0	4091.5	4069.3	4088.3
12.5°	4046.9	4098.1	4037.2	4002.0	4018.4
15°	3958.9	3993.7	3933.0	3894.4	3900.7
17.5°	3863.2	3884.7	3797.2	3764.7	3758.4
20°	3790.7	3809.7	3706.6	3661.2	3654.9
22.5°	3697.6	3714.0	3605.7	3549.9	3541.0
25°	3557.8	3561.0	3457.6	3379.5	3360.5
27.5°	3411.7	3401.5	3286.8	3194.4	3169.7
30°	3305.6	3292.9	3160.0	3062.5	3040.3
32.5°	3191.7	3168.9	3035.8	2930.5	2908.4
35°	3024.2	2989.4	2849.5	2739.0	2713.7
37.5°	2845.6	2806.4	2669.0	2548.7	2520.2
40°	2726.6	2682.3	2542.2	2421.9	2393.5
42.5°	2607.6	2558.2	2415.5	2295.1	2264.1
45°	2422.6	2372.0	2228.5	2111.3	2079.7
47.5°	2246.6	2182.1	2042.9	1926.3	1894.7
50°	2125.0	2055.4	1921.2	1807.3	1775.7
52.5°	2000.8	1928.7	1799.6	1690.9	1659.2
55°	1811.3	1744.9	1617.2	1516.3	1487.8
57.5°	1623.7	1559.8	1443.2	1346.8	1319.0
60°	1494.3	1440.5	1329.3	1238.2	1212.9
62.5°	1370.1	1321.4	1215.5	1132.1	1106.8
65°	1187.0	1142.8	1047.9	973.1	954.1
67.5°	1009.1	964.9	888.2	821.1	799.5
70°	892.7	848.4	779.5	717.6	698.6
72.5°	781.4	734.6	678.6	622.0	608.1
75°	614.5	576.6	533.7	491.3	478.7
77.5°	467.0	430.4	399.1	369.3	366.1
80°	368.7	337.1	313.7	294.3	291.1
82.5°	275.6	251.5	236.1	221.9	221.2
85°	142.3	132.8	129.4	113.1	106.7
87.5°	41.4	41.4	36.9	31.1	31.7
90°	0.0	0.0	3.2	0.1	3.2
92.5°	38.0	33.1	31.1	20.3	23.4
95°	152.1	133.5	126.7	98.2	98.2
97.5°	287.1	268.5	258.6	229.3	223.1
100°	383.4	364.8	354.9	323.1	316.9
102.5°	482.3	473.6	456.3	421.9	415.7
105°	640.1	630.8	614.7	579.7	573.5
107.5°	802.3	804.2	780.1	751.4	742.7
110°	918.9	915.8	896.7	868.1	861.9



TEST NUMBER: P1439100

CATALOG NUMBER: CB2-D-125U-120D-930-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	1038.1	1032.5	1013.3	984.7	978.5
115°	1216.8	1213.7	1191.4	1156.5	1153.4
117.5°	1386.6	1396.5	1370.1	1333.3	1332.1
120°	1508.3	1520.7	1489.3	1457.4	1451.2
122.5°	1627.4	1642.3	1610.9	1574.2	1575.5
125°	1809.3	1827.9	1790.3	1752.3	1755.4
127.5°	1984.8	2007.8	1972.8	1934.2	1938.0
130°	2104.0	2131.9	2094.5	2053.4	2059.6
132.5°	2225.7	2253.5	2216.2	2172.7	2183.8
135°	2411.3	2439.2	2398.7	2354.7	2370.2
137.5°	2586.3	2614.1	2569.8	2532.8	2551.4
140°	2702.9	2730.7	2683.9	2649.4	2668.0
142.5°	2816.9	2849.8	2800.5	2763.6	2787.2
145°	2988.0	3022.1	2975.4	2941.0	2962.7
147.5°	3150.3	3184.4	3137.0	3103.9	3126.2
150°	3254.2	3288.3	3238.4	3210.4	3235.2
152.5°	3350.5	3389.6	3337.2	3309.4	3341.7
155°	3495.0	3529.1	3479.2	3457.6	3485.5
157.5°	3620.5	3660.2	3610.4	3591.9	3614.2
160°	3704.2	3741.3	3691.5	3673.0	3697.8
162.5°	3767.5	3807.2	3759.9	3739.1	3768.8
165°	3862.6	3902.9	3853.1	3831.7	3865.8
167.5°	3937.4	3980.1	3929.8	3907.7	3942.4
170°	3983.0	4023.3	3970.3	3945.8	3983.0
172.5°	4013.4	4056.2	4000.7	3976.0	4000.7
175°	4046.4	4089.7	4036.9	4011.7	4021.0
177.5°	4062.2	4096.9	4054.6	4032.5	4062.2
180°	4062.2	4062.2	4062.2	4062.2	4062.2



TEST NUMBER: P1439100  
 CATALOG NUMBER: CB2-D-125U-120D-930-1D-UNV-STD-W-8

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.41	20.25	20.38	21.23	22.52	18.31	19.15	19.28	20.13	21.42
	3H	21.05	21.80	22.03	22.79	24.11	19.83	20.59	20.82	21.58	22.89
	4H	21.68	22.39	22.67	23.39	24.71	20.41	21.12	21.40	22.11	23.43
	6H	22.08	22.74	23.09	23.74	25.07	20.78	21.43	21.78	22.43	23.77
	8H	22.23	22.85	23.24	23.87	25.20	20.92	21.54	21.93	22.56	23.89
	12H	22.30	22.89	23.32	23.90	25.26	20.98	21.57	21.99	22.58	23.94
4H	2H	19.81	20.53	20.82	21.52	22.84	18.94	19.65	19.94	20.65	21.97
	3H	21.68	22.27	22.69	23.30	24.63	20.67	21.27	21.68	22.29	23.62
	4H	22.43	22.97	23.44	23.99	25.34	21.35	21.89	22.36	22.90	24.26
	6H	22.95	23.41	23.97	24.45	25.81	21.82	22.29	22.85	23.33	24.68
	8H	23.15	23.59	24.18	24.62	25.99	22.01	22.44	23.04	23.48	24.85
	12H	23.25	23.65	24.30	24.70	26.07	22.10	22.49	23.14	23.54	24.91
8H	4H	22.58	23.02	23.61	24.05	25.42	21.62	22.05	22.65	23.09	24.45
	6H	23.22	23.58	24.28	24.66	26.02	22.22	22.58	23.27	23.66	25.02
	8H	23.51	23.83	24.57	24.89	26.27	22.50	22.81	23.56	23.87	25.26
	12H	23.69	23.96	24.75	25.02	26.45	22.64	22.92	23.71	23.98	25.41
12H	4H	22.56	22.95	23.61	24.00	25.38	21.62	22.01	22.67	23.06	24.44
	6H	23.25	23.57	24.31	24.63	26.01	22.28	22.60	23.34	23.66	25.05
	8H	23.57	23.85	24.63	24.90	26.33	22.59	22.87	23.65	23.92	25.35